

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702455

Luminaire Tested: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-12)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CF
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL FROSTED GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1130.2 lumens
Efficiency: N/A
Efficacy: 71.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.55
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702455

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CF

Luminous Intensity Polar Plot



TEST NUMBER: P702455

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	98	107	103	99	96	98	95	93		94	92	90		90	88	87	84
2	101	94	88	83	99	92	87	82	88	84	80		85	81	78		82	79	76	74
3	94	85	78	72	92	83	77	72	80	75	70		77	73	69		75	71	67	65
4	88	77	70	64	85	76	69	64	73	67	63		71	66	62		69	64	61	59
5	82	71	63	58	80	70	63	57	68	61	56		66	60	56		64	59	55	53
6	77	66	58	52	75	65	57	52	63	56	52		61	55	51		59	54	50	49
7	73	61	53	48	71	60	53	48	58	52	47		57	51	47		55	50	47	45
8	69	57	50	44	67	56	49	44	55	48	44		53	48	44		52	47	43	42
9	65	53	46	41	64	53	46	41	52	45	41		50	45	41		49	44	40	39
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109715
5°	80953
10°	51477
15°	40914
20°	28212
25°	14184
30°	11166
35°	9734
40°	8969
45°	7952
50°	6614
55°	5242
60°	4157
65°	3287
70°	2573
75°	2054
80°	1686
85°	1357

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7952 cd/sqm

TEST NUMBER: P702455

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	10.4
10°-20°	226.1	20.0
20°-30°	164.2	14.5
30°-40°	150.6	13.3
40°-50°	155.4	13.7
50°-60°	122.1	10.8
60°-70°	83.0	7.3
70°-80°	53.2	4.7
80°-90°	32.9	2.9
90°-100°	19.1	1.7
100°-110°	5.7	0.5
110°-120°	0.2	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.1	45.0
0°-40°	658.7	58.3
0°-60°	936.2	82.8
0°-90°	1105.3	97.8
90°-120°	24.9	2.2
90°-150°	24.9	2.2
90°-180°	25.0	2.2
0°-180°	1130.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1682	
5°	1383	118
15°	826	226
25°	322	164
35°	239	151
45°	203	155
55°	136	122
65°	83	83
75°	50	53
85°	30	26
90°	22	13
95°	18	13
105°	5	6
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702455

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1681.7
2.5°	1623.0
5°	1383.2
7.5°	1123.7
10°	963.4
12.5°	878.7
15°	826.5
17.5°	762.6
20°	607.5
22.5°	406.7
25°	322.0
27.5°	289.4
30°	264.6
32.5°	247.7
35°	238.6
37.5°	230.7
40°	225.5
42.5°	216.4
45°	203.4
47.5°	187.7
50°	170.8
52.5°	152.5
55°	135.6
57.5°	119.9
60°	106.9
62.5°	93.9
65°	83.4
67.5°	73.0
70°	63.9
72.5°	56.1
75°	49.5
77.5°	44.3
80°	39.1
82.5°	33.9
85°	30.0
87.5°	26.1
90°	22.2
92.5°	20.9
95°	18.3
97.5°	14.3
100°	10.4
102.5°	7.8
105°	5.2
107.5°	2.6
110°	1.3

TEST NUMBER: P702455

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)