

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702457

Luminaire Tested: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702457
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-10)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF
Description: FARALLON 6" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1040.4 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.81
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702457

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

Luminous Intensity Polar Plot



TEST NUMBER: P702457

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		99	99	99	97
1	110	106	102	99	107	103	100	97	99	96	93		94	92	90		90	89	87	85
2	102	96	90	86	100	94	89	84	90	86	82		86	83	80		83	80	78	76
3	96	87	81	76	93	86	80	75	83	77	73		80	75	72		77	73	70	68
4	90	80	73	68	88	79	72	67	76	71	66		74	69	65		71	67	64	62
5	85	74	67	62	83	73	66	61	71	65	61		69	64	60		67	62	59	57
6	80	69	62	57	78	68	61	56	66	60	56		64	59	55		63	58	54	53
7	75	64	57	52	74	64	57	52	62	56	52		60	55	51		59	54	51	49
8	71	60	53	49	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	68	57	50	45	66	56	50	45	55	49	45		54	48	45		53	48	44	43
10	64	54	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58938
5°	52492
10°	46043
15°	40914
20°	35963
25°	30033
30°	13478
35°	7180
40°	5704
45°	4586
50°	3687
55°	2922
60°	2434
65°	2053
70°	1889
75°	1730
80°	1574
85°	1416

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4586 cd/sqm

TEST NUMBER: P702457

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.4	8.1
10°-20°	232.2	22.3
20°-30°	283.2	27.2
30°-40°	119.9	11.5
40°-50°	91.0	8.7
50°-60°	68.9	6.6
60°-70°	52.6	5.1
70°-80°	44.1	4.2
80°-90°	34.1	3.3
90°-100°	22.8	2.2
100°-110°	6.7	0.6
110°-120°	0.5	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.8	57.6
0°-40°	719.7	69.2
0°-60°	879.6	84.5
0°-90°	1010.4	97.1
90°-120°	30.0	2.9
90°-150°	30.0	2.9
90°-180°	30.0	2.9
0°-180°	1040.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	903	
5°	897	84
15°	826	232
25°	682	283
35°	176	120
45°	117	91
55°	76	69
65°	52	53
75°	42	44
85°	31	27
90°	26	14
95°	22	16
105°	5	7
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702457

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

CANDELA DISTRIBUTION (FULL):

0°	
0°	903.4
2.5°	902.1
5°	896.9
7.5°	881.3
10°	861.7
12.5°	844.8
15°	826.5
17.5°	804.4
20°	774.4
22.5°	737.9
25°	681.8
27.5°	531.9
30°	319.4
32.5°	209.9
35°	176.0
37.5°	157.7
40°	143.4
42.5°	130.4
45°	117.3
47.5°	105.6
50°	95.2
52.5°	84.7
55°	75.6
57.5°	69.1
60°	62.6
62.5°	56.1
65°	52.1
67.5°	49.5
70°	46.9
72.5°	44.3
75°	41.7
77.5°	39.1
80°	36.5
82.5°	33.9
85°	31.3
87.5°	28.7
90°	26.1
92.5°	24.8
95°	22.2
97.5°	16.9
100°	13.0
102.5°	9.1
105°	5.2
107.5°	3.9
110°	1.3

TEST NUMBER: P702457

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	1.3
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)