

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155819

Luminaire Tested: **AVS-E02-LED-E-U-T3-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P155819
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E02-LED-E-U-T3-7030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA
Light Source: (42) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5633.4 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2


Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P155819
 CATALOG NUMBER: AVS-E02-LED-E-U-T3-7030

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 6.1 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155819
CATALOG NUMBER: AVS-E02-LED-E-U-T3-7030

Luminous Intensity Polar Plot



— Vertical Plane Through 67.5-Deg Lateral - - - Horizontal Cone Through 66-Deg Vertical

REPORT NUMBER: P155819

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1945.4	0.0	1945.4
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	3688.0	0.0	3688.0
	% Fixture	65.5	0.0	65.5
Total	Lumens	5633.4	0.0	5633.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	1.0
10°-20°	171.6	3.0
20°-30°	294.9	5.2
30°-40°	478.9	8.5
40°-50°	799.5	14.2
50°-60°	1258.9	22.3
60°-70°	1716.6	30.5
70°-80°	743.1	13.2
80°-90°	111.7	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5633.4	100.0
0°-180°	5633.4	100.0



REPORT NUMBER: P155819


CATALOG NUMBER: AVS-E02-LED-E-U-T3-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	263.5	4.7			
FM	(30°-60°)	1573.2	27.9			
FH	(60°-80°)	1759.5	31.2			G1/1800
FVH	(80°-90°)	91.7	1.6			G1/100
BL	(0°-30°)	261.1	4.6	B1/500		
BM	(30°-60°)	964.0	17.1	B1/1000		
BH	(60°-80°)	700.2	12.4	B2/1000		G2/1000
BVH	(80°-90°)	20.0	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type III Short





REPORT NUMBER: P155819

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0
2.5°	609.5	611.9	609.5	610.2	610.8	610.2	609.5	609.5	607.7	608.9	610.2
5°	607.0	608.9	608.3	608.9	609.5	608.9	608.3	608.9	607.7	608.3	610.2
7.5°	604.0	603.4	604.0	605.3	606.4	606.4	606.4	607.0	606.4	606.4	608.3
10°	594.9	595.5	596.7	598.5	599.2	601.0	601.0	602.8	603.4	604.7	607.0
12.5°	583.3	583.9	585.2	586.3	589.4	592.4	592.4	596.7	598.5	601.6	605.9
15°	574.8	575.4	576.6	577.8	580.3	583.3	585.2	590.1	593.1	598.5	604.7
17.5°	579.7	579.1	580.3	580.9	580.9	583.3	583.3	586.9	590.7	595.5	603.4
20°	593.7	593.7	594.9	594.9	594.3	595.5	593.1	593.1	593.7	596.1	601.6
22.5°	607.7	607.0	609.5	610.8	611.3	613.2	610.8	610.2	607.0	605.3	607.0
25°	621.0	620.5	623.5	625.4	628.4	630.3	630.3	630.3	627.8	624.8	622.9
27.5°	641.8	641.8	644.9	646.6	649.1	652.7	654.6	654.6	655.1	650.9	647.9
30°	676.5	677.1	677.7	680.1	682.6	683.8	686.2	688.1	689.8	687.5	682.6
32.5°	717.9	714.2	714.2	717.9	720.9	724.6	725.8	728.3	731.9	730.1	729.4
35°	767.3	766.0	764.8	766.0	769.6	773.9	778.8	783.0	780.6	784.2	782.5
37.5°	840.3	841.5	842.1	842.1	841.5	842.7	845.2	849.4	848.2	849.4	851.8
40°	960.8	956.6	952.3	953.0	946.8	948.1	938.3	942.6	943.2	939.0	940.7
42.5°	1081.5	1083.8	1085.7	1090.6	1086.3	1083.8	1074.7	1074.7	1069.8	1065.6	1064.4
45°	1211.7	1216.6	1217.2	1226.9	1223.3	1231.2	1237.9	1236.1	1228.2	1227.6	1219.1
47.5°	1315.9	1323.7	1332.2	1343.8	1353.0	1370.7	1391.3	1401.7	1407.8	1412.6	1402.9
50°	1393.8	1397.4	1419.4	1437.6	1457.7	1486.9	1515.5	1552.7	1582.5	1596.6	1609.9
52.5°	1435.8	1444.9	1468.7	1497.3	1532.6	1576.5	1622.7	1681.8	1733.0	1767.0	1797.5
55°	1444.9	1454.1	1480.8	1517.4	1565.5	1624.6	1690.9	1771.3	1848.0	1913.8	1977.7
57.5°	1419.4	1429.7	1458.3	1500.3	1557.0	1628.8	1712.2	1817.6	1923.5	2030.1	2124.5
60°	1372.4	1385.3	1411.4	1452.8	1515.5	1596.6	1696.4	1828.5	1977.1	2140.3	2321.1
62.5°	1295.1	1308.5	1332.8	1378.5	1443.1	1532.6	1648.3	1812.7	2022.8	2279.7	2600.6
65°	1170.9	1177.0	1206.8	1253.2	1310.4	1409.0	1536.3	1734.7	2008.2	2365.6	2807.7
66°	1114.9	1125.3	1143.5	1180.6	1235.4	1328.0	1455.9	1657.4	1952.7	2335.8	2802.2
67.5°	1027.3	1035.1	1047.4	1072.2	1105.8	1174.0	1295.1	1485.7	1783.4	2184.8	2685.9
70°	830.6	834.2	850.7	859.2	870.8	893.3	937.1	1046.7	1278.7	1655.6	2167.7
72.5°	566.3	576.6	594.3	618.7	650.3	680.7	701.5	715.4	765.4	987.7	1444.4
75°	415.2	426.2	448.8	481.0	536.5	599.8	665.5	696.0	675.2	646.6	804.4
77.5°	241.1	255.8	274.6	305.7	356.8	440.8	553.5	653.4	720.9	725.2	688.7
80°	101.7	103.5	115.1	130.9	162.6	221.7	309.3	453.1	602.8	703.9	727.7
82.5°	23.1	28.6	36.6	43.2	53.0	73.1	108.4	180.2	325.8	510.9	666.1
85°	8.5	8.5	11.6	17.1	19.5	22.0	28.6	45.7	77.9	143.7	299.6
87.5°	0.0	0.6	1.2	1.2	2.5	3.0	4.9	6.7	6.1	5.5	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155819

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0
2.5°	608.9	608.3	607.0	607.0	607.0	607.0	605.9	606.4	605.3	605.9	605.9
5°	608.3	608.3	607.7	606.4	607.0	607.0	607.7	606.4	606.4	607.0	606.4
7.5°	608.3	607.7	607.7	607.7	608.3	607.7	608.3	608.3	608.3	608.9	608.9
10°	608.3	608.3	609.5	610.2	610.2	610.8	612.5	612.5	613.2	613.8	615.0
12.5°	608.9	611.3	613.2	615.0	615.6	616.8	619.9	619.9	621.0	622.9	623.5
15°	609.5	613.2	616.8	618.0	619.3	621.7	624.8	625.9	627.8	629.6	630.8
17.5°	608.9	613.8	618.0	619.9	621.7	624.8	628.4	629.6	632.0	634.5	636.9
20°	608.3	615.0	621.7	624.1	626.5	630.8	635.6	638.8	641.1	644.9	647.3
22.5°	611.9	619.9	629.0	632.6	636.9	642.4	649.1	652.7	655.8	659.5	661.2
25°	623.5	629.6	640.5	646.6	652.1	661.2	670.4	674.6	678.3	681.3	682.0
27.5°	643.0	644.9	658.2	666.1	674.1	688.7	699.6	702.7	709.3	711.8	711.2
30°	674.6	671.6	682.6	694.7	706.3	726.4	739.8	747.8	753.8	753.8	748.9
32.5°	720.3	715.4	718.5	732.5	745.9	775.1	791.0	801.3	805.6	804.4	794.0
35°	780.0	777.0	775.1	786.1	807.4	841.5	862.2	867.7	874.4	873.2	859.8
37.5°	850.7	848.2	848.2	861.0	881.7	932.2	954.7	958.4	957.8	948.1	923.1
40°	934.1	932.8	927.4	934.6	952.3	1018.0	1048.5	1053.4	1046.7	1030.9	1001.7
42.5°	1054.0	1046.7	1029.6	1033.9	1047.4	1111.2	1150.8	1164.2	1157.5	1141.7	1094.2
45°	1210.5	1202.6	1174.0	1170.3	1177.6	1233.7	1284.8	1287.9	1286.6	1266.5	1210.5
47.5°	1394.4	1382.2	1351.7	1342.0	1339.6	1391.3	1440.6	1445.5	1442.5	1412.6	1337.7
50°	1593.5	1575.9	1555.8	1549.0	1539.3	1576.5	1626.3	1626.9	1614.8	1573.4	1503.4
52.5°	1806.0	1799.9	1796.3	1789.5	1785.3	1817.6	1848.0	1829.7	1811.5	1768.3	1707.4
55°	2020.3	2045.3	2070.9	2073.3	2080.6	2115.3	2114.7	2064.8	2051.4	2027.7	1967.4
57.5°	2248.1	2340.6	2421.0	2445.9	2470.3	2534.8	2528.8	2479.5	2462.4	2433.2	2383.2
60°	2558.0	2807.7	3039.6	3095.0	3133.4	3210.8	3203.4	3127.4	3162.6	3160.2	3095.6
62.5°	2992.1	3407.4	3755.1	3840.3	3867.2	3875.6	3829.3	3747.2	3781.9	3820.8	3622.4
65°	3286.2	3774.6	4131.4	4197.1	4200.8	4099.1	3996.2	3899.4	3890.9	3857.4	3573.7
66°	3293.0	3792.8	4150.9	4214.8	4192.2	4053.5	3923.1	3825.7	3783.7	3710.1	3416.0
67.5°	3174.8	3679.0	4064.5	4132.0	4082.7	3886.0	3706.4	3580.9	3498.8	3379.4	3120.0
70°	2666.4	3166.3	3641.2	3767.3	3783.1	3489.6	3240.5	3093.3	2982.4	2818.5	2595.1
72.5°	1982.6	2434.4	2853.3	2973.9	3035.3	2800.9	2590.9	2478.9	2327.3	2154.9	1996.0
75°	1242.8	1561.9	1842.5	1927.2	1869.3	1687.9	1561.9	1514.9	1365.8	1262.9	1190.4
77.5°	710.6	810.5	833.0	800.7	732.5	560.8	398.9	295.3	256.4	283.7	313.0
80°	693.6	635.6	506.6	445.7	403.7	277.6	163.2	112.0	93.2	95.6	103.5
82.5°	751.4	806.2	663.7	541.3	454.2	306.8	169.2	90.2	60.9	71.8	80.9
85°	488.3	679.5	611.9	515.8	417.7	262.5	139.5	46.8	31.1	40.8	56.1
87.5°	49.3	54.2	46.3	62.7	46.8	22.0	11.0	6.7	6.1	7.4	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155819

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0	607.0
2.5°	606.4	606.4	607.0	607.7	608.3	608.9	608.9	608.9	608.9	610.2	609.5
5°	607.7	608.9	610.2	610.8	611.9	611.9	613.8	613.2	613.2	615.0	615.6
7.5°	610.2	611.9	614.4	613.8	616.2	615.6	616.8	616.8	615.0	615.6	614.4
10°	615.6	618.0	619.3	617.4	618.0	615.6	615.0	611.9	608.3	606.4	604.0
12.5°	624.8	627.2	627.2	624.1	620.5	615.0	610.8	604.0	598.5	595.5	592.4
15°	632.6	635.1	634.5	629.6	624.1	615.6	609.5	601.6	593.7	588.8	585.8
17.5°	638.8	640.0	638.1	631.4	625.4	617.4	611.3	602.8	593.7	587.6	582.1
20°	647.9	646.6	642.4	633.9	627.2	619.9	615.0	607.7	597.3	589.4	581.5
22.5°	661.2	656.4	648.5	639.4	632.6	625.9	621.0	613.2	602.8	593.1	583.9
25°	679.0	669.2	658.2	648.5	642.4	635.1	629.6	621.0	610.2	599.2	588.2
27.5°	704.5	687.5	673.5	664.9	658.2	649.1	642.4	631.4	619.9	607.0	594.9
30°	733.2	709.9	696.6	689.8	682.6	672.8	662.5	648.5	635.1	621.0	606.4
32.5°	770.3	742.3	729.4	722.8	713.1	700.8	688.7	672.8	654.0	635.6	618.0
35°	819.0	790.4	777.0	766.6	753.2	737.4	719.7	698.4	672.8	648.5	625.9
37.5°	871.3	840.3	827.5	816.6	796.5	775.8	750.8	719.7	685.0	652.7	624.8
40°	937.7	909.1	892.6	873.8	850.1	814.1	775.1	730.1	685.6	646.0	613.2
42.5°	1021.8	993.2	968.8	939.0	897.5	842.1	786.7	728.3	674.6	629.6	594.3
45°	1133.2	1098.4	1056.5	1004.0	937.1	859.8	787.4	716.7	654.0	604.0	566.3
47.5°	1269.5	1216.6	1147.8	1059.5	963.3	864.7	777.6	693.6	621.7	567.5	525.5
50°	1431.5	1348.1	1234.8	1105.2	976.7	857.3	753.2	658.9	576.1	518.1	468.3
52.5°	1616.6	1480.2	1313.4	1138.0	976.1	833.0	711.8	606.4	516.4	451.8	404.4
55°	1834.0	1631.3	1394.4	1162.4	959.1	787.9	648.5	532.7	442.7	383.0	339.2
57.5°	2152.4	1876.1	1535.6	1200.1	924.9	718.5	562.6	444.5	365.4	308.7	271.6
60°	2734.6	2284.6	1790.2	1276.3	872.5	616.8	462.2	350.2	283.7	238.0	213.2
62.5°	3173.0	2600.6	1927.8	1259.2	767.3	491.4	342.8	255.1	208.8	177.8	162.0
65°	3110.3	2502.6	1781.0	1084.5	601.6	346.4	227.8	173.6	143.7	129.1	120.0
66°	2968.4	2374.7	1653.8	976.1	520.0	288.0	187.6	145.5	123.6	113.3	107.2
67.5°	2699.3	2137.2	1426.0	800.1	399.5	208.8	141.2	115.1	100.5	96.2	91.9
70°	2243.8	1704.4	1001.0	465.8	203.9	116.3	89.5	80.4	76.7	76.1	74.9
72.5°	1719.6	1206.2	589.4	220.4	105.9	77.3	69.4	66.3	65.2	65.2	65.8
75°	1054.0	677.7	260.6	107.8	74.3	65.2	61.5	60.3	59.7	60.3	59.7
77.5°	351.9	215.5	111.4	81.6	67.6	60.3	57.8	56.6	56.6	56.6	56.6
80°	107.8	93.8	85.3	75.5	63.9	57.2	53.6	53.0	53.6	54.2	52.3
82.5°	80.9	76.7	71.8	66.9	57.8	51.2	49.9	49.9	49.9	48.1	45.7
85°	59.7	59.1	48.7	45.7	42.6	42.6	42.6	42.6	40.8	37.7	35.3
87.5°	11.0	10.4	11.0	11.6	17.1	18.2	18.2	19.5	21.3	20.1	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155819

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	607.0	607.0	607.0	607.0	607.0
2.5°	609.5	608.9	610.8	609.5	610.2
5°	615.0	614.4	615.6	614.4	616.2
7.5°	613.2	611.9	611.3	611.9	612.5
10°	600.4	599.2	598.5	597.9	598.5
12.5°	589.4	586.9	586.9	585.8	586.3
15°	581.5	579.7	579.1	577.8	578.4
17.5°	577.8	574.8	573.6	572.3	572.3
20°	575.4	571.7	569.9	568.7	568.1
22.5°	575.4	569.9	567.5	566.3	565.7
25°	577.8	571.2	567.5	565.7	565.1
27.5°	582.7	574.2	569.9	567.5	567.5
30°	591.2	580.3	574.2	571.2	570.6
32.5°	599.8	585.2	576.6	573.0	571.7
35°	604.0	585.2	574.8	568.7	567.5
37.5°	599.2	577.2	564.5	555.3	553.5
40°	583.9	560.8	546.8	538.2	537.1
42.5°	563.8	541.3	524.9	518.8	517.0
45°	536.5	509.6	493.2	484.7	485.3
47.5°	489.5	462.2	447.6	439.6	440.8
50°	434.2	407.4	394.6	386.0	387.9
52.5°	373.3	348.9	336.7	332.4	331.2
55°	309.3	290.5	282.0	277.1	275.2
57.5°	250.9	237.5	231.4	225.3	225.9
60°	197.9	191.2	189.3	182.7	182.1
62.5°	155.9	151.6	149.7	144.9	145.5
65°	118.1	116.9	118.1	115.1	116.3
66°	106.5	107.2	107.2	105.4	106.5
67.5°	91.9	93.2	95.0	93.2	94.4
70°	76.1	77.3	78.5	78.5	78.5
72.5°	66.3	67.6	68.2	68.2	68.2
75°	60.9	61.5	62.1	60.9	60.9
77.5°	57.2	57.2	56.1	55.4	54.8
80°	51.7	51.2	49.3	48.1	48.1
82.5°	43.2	42.0	40.8	39.0	39.0
85°	32.8	31.7	30.5	28.0	26.8
87.5°	17.1	17.6	17.1	14.0	12.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)