

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152604

Luminaire Tested: **AVS-F02-LED-E-U-SL4-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152604
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-SL4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (14) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4454.8 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B1 - U0 - G1


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P152604
 CATALOG NUMBER: AVS-F02-LED-E-U-SL4-7030

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 9.6 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152604
CATALOG NUMBER: AVS-F02-LED-E-U-SL4-7030

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P152604

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	924.8	0.0	924.8
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	3530.0	0.0	3530.0
	% Fixture	79.2	0.0	79.2
Total	Lumens	4454.8	0.0	4454.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	2.0
10°-20°	243.1	5.5
20°-30°	359.9	8.1
30°-40°	454.8	10.2
40°-50°	514.3	11.5
50°-60°	731.9	16.4
60°-70°	1363.1	30.6
70°-80°	624.7	14.0
80°-90°	74.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4454.8	100.0
0°-180°	4454.8	100.0



REPORT NUMBER: P152604


CATALOG NUMBER: AVS-F02-LED-E-U-SL4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	405.6	9.1			
FM	(30°-60°)	1305.1	29.3			
FH	(60°-80°)	1764.3	39.6			G1/1800
FVH	(80°-90°)	55.0	1.2			G1/100
BL	(0°-30°)	286.1	6.4	B1/500		
BM	(30°-60°)	395.9	8.9	B1/1000		
BH	(60°-80°)	223.6	5.0	B1/500		G1/500
BVH	(80°-90°)	19.1	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P152604

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6
2.5°	965.1	967.7	964.6	964.1	964.1	963.6	960.6	960.1	956.1	956.6	957.6
5°	972.1	973.2	971.2	970.7	969.6	967.7	965.1	962.1	959.1	956.1	953.6
7.5°	979.2	978.1	976.7	976.7	975.1	972.1	967.2	963.1	956.6	953.1	948.5
10°	989.2	987.8	985.7	984.8	982.2	977.7	970.7	965.1	957.1	950.1	942.5
12.5°	998.8	998.2	995.2	993.8	989.7	985.2	976.7	968.1	957.6	946.5	936.5
15°	1015.9	1013.9	1010.9	1007.9	1001.3	995.2	982.2	972.1	957.1	942.5	926.9
17.5°	1045.5	1042.0	1039.0	1032.4	1024.5	1013.9	994.8	977.7	957.1	936.0	918.3
20°	1099.8	1092.3	1088.3	1079.7	1065.6	1046.5	1016.9	989.2	958.5	931.4	907.8
22.5°	1161.1	1156.2	1150.6	1145.1	1122.9	1095.3	1055.1	1013.9	967.7	929.4	899.3
25°	1230.1	1223.5	1220.4	1210.9	1190.3	1158.7	1103.8	1046.5	988.2	937.5	899.3
27.5°	1291.3	1289.3	1288.8	1277.7	1258.1	1220.9	1156.2	1087.3	1016.4	954.1	906.8
30°	1347.2	1345.1	1344.1	1338.1	1315.4	1271.2	1200.8	1123.4	1047.0	977.2	920.8
32.5°	1406.4	1399.9	1396.9	1385.4	1359.7	1307.9	1227.5	1147.0	1071.2	999.8	936.5
35°	1454.7	1449.2	1443.1	1426.5	1390.4	1329.0	1239.1	1155.1	1080.7	1012.3	944.5
37.5°	1489.8	1484.4	1475.9	1454.7	1409.9	1336.1	1238.5	1152.6	1077.2	1010.4	946.0
40°	1505.5	1499.9	1490.9	1464.2	1413.5	1332.0	1229.0	1141.0	1066.6	999.8	940.0
42.5°	1499.5	1495.4	1483.8	1458.2	1402.4	1314.0	1209.9	1119.4	1046.5	982.7	926.4
45°	1476.3	1473.3	1462.3	1435.1	1377.3	1284.8	1181.8	1092.3	1022.4	961.6	908.3
47.5°	1441.7	1440.6	1429.5	1402.9	1345.6	1255.6	1152.6	1065.6	998.2	940.9	893.3
50°	1403.4	1398.4	1392.8	1368.3	1316.0	1230.5	1131.5	1049.0	984.8	933.5	886.7
52.5°	1379.3	1377.8	1372.7	1350.7	1300.4	1216.0	1122.0	1043.0	983.7	931.9	883.2
55°	1593.5	1597.0	1550.7	1454.7	1370.3	1256.2	1150.6	1073.7	1008.3	956.1	920.4
57.5°	2357.0	2341.5	2262.0	2071.5	1856.4	1572.3	1367.8	1243.6	1162.7	1171.7	1189.8
60°	2746.0	2743.0	2728.5	2654.6	2511.3	2295.1	2055.3	1780.4	1693.0	1702.5	1709.5
62.5°	2920.0	2924.5	2935.5	2907.9	2870.2	2807.4	2687.8	2577.1	2460.0	2416.3	2299.2
65°	3000.4	3008.4	3033.6	3049.1	3063.7	3074.8	3122.1	3251.7	3337.2	3177.3	2805.4
67.5°	2834.0	2872.7	2955.6	3036.6	3109.0	3212.0	3371.8	3673.0	3882.6	3686.0	3146.6
70°	2065.9	2118.8	2213.7	2464.0	2731.5	2965.2	3274.8	3733.3	4049.4	3897.6	3231.1
72.5°	1295.3	1309.9	1352.1	1444.1	1642.7	1942.8	2484.1	3171.8	3536.7	3415.5	2731.0
75°	821.9	826.8	825.4	846.5	880.2	945.5	1159.7	1873.5	2422.8	2233.8	1522.1
77.5°	489.6	497.1	500.1	506.6	522.8	545.9	563.5	637.4	1015.9	986.2	552.4
80°	410.2	416.2	411.2	409.6	399.6	392.5	401.1	392.5	364.5	350.9	323.2
82.5°	217.1	216.7	215.1	229.7	259.4	282.5	300.1	296.1	267.9	228.2	193.6
85°	119.2	123.1	123.1	128.2	123.6	124.1	128.2	135.2	125.2	104.6	85.5
87.5°	10.1	15.5	12.5	15.5	21.1	15.1	14.6	14.6	12.5	9.0	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152604

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6
2.5°	955.0	954.1	952.0	950.6	950.6	948.0	946.5	945.5	945.0	943.0	943.0
5°	952.0	948.5	945.0	942.5	940.9	938.4	934.4	932.4	929.9	927.9	926.9
7.5°	945.5	939.0	933.5	929.4	924.4	920.4	915.3	910.8	906.3	904.2	903.3
10°	935.4	926.9	918.3	910.8	903.8	896.8	890.3	883.7	878.1	874.1	870.2
12.5°	925.9	912.8	901.8	890.7	879.7	871.1	862.1	852.5	844.5	836.9	834.9
15°	912.8	897.7	883.7	870.2	856.6	842.5	831.4	820.8	807.8	799.3	792.7
17.5°	900.7	882.7	865.6	849.5	833.0	818.3	801.8	787.7	774.6	761.6	752.0
20°	887.7	868.1	850.1	831.9	813.8	795.2	776.1	758.0	742.0	726.3	710.8
22.5°	876.2	856.1	838.4	818.9	798.8	777.6	755.5	732.8	714.3	694.2	676.1
25°	869.1	846.9	828.9	809.7	787.7	764.6	739.4	712.7	690.2	667.0	645.4
27.5°	869.1	840.4	821.9	802.8	780.1	755.5	727.9	698.7	673.1	647.5	620.8
30°	876.7	841.5	816.4	796.2	773.1	746.4	715.8	685.1	657.0	626.8	601.1
32.5°	883.7	843.4	812.3	786.6	760.0	733.9	702.7	670.1	638.9	610.3	583.1
35°	888.2	843.4	804.8	772.1	742.0	716.3	685.6	653.0	621.2	593.2	568.0
37.5°	888.7	839.5	792.7	755.5	723.8	697.2	668.1	637.4	607.3	581.0	560.0
40°	883.7	831.4	780.6	737.9	704.8	677.6	651.0	623.3	596.2	574.5	556.5
42.5°	874.6	822.9	769.1	723.8	689.1	661.0	636.4	612.7	589.1	570.6	555.4
45°	861.0	811.3	758.5	715.3	681.1	651.4	627.4	607.7	587.6	572.0	557.0
47.5°	849.0	807.3	762.1	720.8	685.1	654.5	629.8	613.3	597.6	587.2	566.5
50°	846.5	805.3	763.5	725.4	689.1	658.0	636.4	627.9	623.3	616.8	585.1
52.5°	839.5	804.8	774.6	753.5	730.4	715.8	693.2	701.2	696.2	673.1	615.8
55°	913.4	923.4	951.5	991.7	1028.9	1037.5	1035.0	1025.4	974.6	838.4	689.6
57.5°	1255.6	1312.4	1365.7	1389.3	1386.3	1359.7	1340.6	1301.9	1228.5	1062.6	835.4
60°	1731.2	1740.2	1712.0	1670.4	1600.0	1541.1	1478.3	1405.9	1299.4	1137.0	924.9
62.5°	2169.0	2047.4	1922.2	1804.6	1697.5	1604.0	1516.6	1415.5	1276.8	1107.4	913.4
65°	2478.1	2220.7	2023.2	1854.3	1703.0	1572.3	1463.2	1332.0	1175.8	1022.9	846.5
67.5°	2637.5	2242.9	1939.8	1704.6	1489.8	1308.9	1163.6	1036.0	919.9	853.1	740.9
70°	2459.5	1903.6	1481.3	1215.4	958.5	768.6	607.3	509.7	476.1	539.4	560.9
72.5°	1832.7	1239.1	881.1	681.7	522.3	416.2	319.2	250.8	204.0	214.1	277.9
75°	866.6	534.8	378.0	287.6	228.7	189.5	154.8	141.8	118.7	98.5	92.5
77.5°	337.3	245.8	203.1	148.8	105.6	85.0	72.3	69.8	71.4	69.3	68.4
80°	256.9	173.9	109.1	79.9	68.9	60.8	53.8	51.8	52.7	55.3	57.8
82.5°	143.2	89.4	66.3	57.8	51.8	44.2	40.2	37.2	37.7	40.7	46.2
85°	55.3	43.2	39.7	38.2	35.6	28.6	24.7	25.2	28.6	34.2	34.2
87.5°	6.0	6.0	8.1	6.0	6.0	6.0	5.5	6.5	7.0	9.0	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152604

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6	950.6
2.5°	942.0	942.0	942.0	940.9	941.5	939.5	939.5	937.9	940.5	939.0	938.4
5°	927.5	926.9	924.9	924.9	924.9	924.9	926.4	922.4	925.4	925.4	923.9
7.5°	902.8	902.8	897.2	900.3	899.3	900.7	902.8	900.7	903.8	905.8	904.2
10°	868.6	868.6	864.0	867.6	866.1	869.6	873.2	871.1	873.2	876.2	877.1
12.5°	830.9	828.9	824.9	826.4	826.4	828.4	829.8	832.4	834.9	839.0	840.9
15°	787.2	784.1	779.2	779.2	776.1	777.1	780.1	781.1	786.1	791.7	798.2
17.5°	742.4	734.9	729.3	722.8	717.8	721.9	725.4	727.9	731.9	740.4	745.0
20°	700.2	685.1	674.6	666.0	660.5	663.0	667.6	670.6	674.1	676.1	677.6
22.5°	658.4	641.3	626.8	616.3	607.3	609.7	607.7	606.2	608.7	602.2	601.7
25°	622.3	602.2	582.6	570.1	559.0	555.4	544.9	542.4	535.3	529.8	525.8
27.5°	596.2	570.1	548.4	533.8	516.3	503.2	489.6	476.1	468.5	459.5	454.9
30°	575.5	547.9	522.3	497.6	474.5	454.4	436.3	418.8	406.6	393.6	385.1
32.5°	556.5	530.8	499.7	466.0	434.8	412.2	388.6	368.5	349.3	332.2	319.7
35°	543.4	514.7	475.0	433.8	398.7	372.0	346.8	318.1	295.0	273.0	259.4
37.5°	536.4	501.1	452.4	406.6	367.5	337.3	306.1	273.0	244.8	224.1	203.6
40°	530.8	487.6	432.3	382.5	341.3	305.1	268.9	229.7	198.5	176.9	160.8
42.5°	524.8	472.5	414.7	363.4	317.7	275.4	231.7	190.1	160.3	145.3	138.2
45°	518.2	459.5	398.1	345.3	294.6	243.3	193.1	154.3	136.7	131.7	131.7
47.5°	516.8	450.9	386.0	327.8	268.4	206.1	157.3	133.2	128.2	129.2	131.2
50°	522.8	448.4	375.4	307.2	233.8	166.8	133.2	125.2	126.2	129.2	132.2
52.5°	537.3	450.4	364.5	278.4	192.5	137.7	123.1	122.7	125.7	130.2	133.2
55°	562.0	450.4	343.3	235.8	153.8	123.6	119.6	121.7	125.7	129.6	132.2
57.5°	614.7	445.9	306.1	188.5	128.7	118.7	118.7	121.1	124.7	128.7	130.7
60°	677.6	439.8	253.9	145.8	116.2	114.6	118.1	121.1	124.1	127.7	129.6
62.5°	681.7	424.2	201.0	120.6	109.5	112.1	117.6	121.7	122.7	125.2	127.7
65°	626.3	369.9	159.9	108.1	106.5	110.6	116.2	119.2	119.6	120.6	123.1
67.5°	548.4	301.6	129.2	102.1	103.5	108.1	111.1	113.6	115.1	117.6	118.1
70°	450.4	242.3	110.6	96.0	97.5	102.6	105.1	107.6	110.6	113.6	112.1
72.5°	319.2	188.5	97.0	89.4	91.5	96.0	99.1	101.0	103.5	106.5	104.6
75°	135.8	131.7	83.9	80.9	83.9	86.9	89.9	93.0	95.5	97.0	97.0
77.5°	69.3	77.4	72.3	72.3	74.4	77.4	79.9	82.9	84.5	85.9	88.0
80°	58.9	59.8	60.8	62.8	64.9	67.9	70.4	72.8	73.4	73.9	74.9
82.5°	48.8	50.8	51.8	54.8	56.3	57.3	58.9	58.9	59.8	59.8	58.3
85°	35.2	37.7	39.2	39.7	39.2	39.7	40.2	41.2	43.7	43.7	41.8
87.5°	10.1	9.5	12.0	12.5	13.6	15.5	17.6	21.1	22.1	23.1	23.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152604

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	950.6	950.6	950.6	950.6
2.5°	937.9	939.0	937.0	937.5
5°	923.9	925.9	923.4	926.4
7.5°	905.8	908.8	908.3	907.8
10°	879.7	883.7	883.7	885.2
12.5°	846.5	849.0	851.0	852.0
15°	801.8	806.3	808.8	808.8
17.5°	748.0	751.0	752.4	750.5
20°	679.6	678.5	679.1	674.1
22.5°	600.7	602.2	597.6	598.7
25°	523.3	520.7	522.8	519.8
27.5°	448.4	448.9	443.3	445.9
30°	377.0	374.5	367.5	371.0
32.5°	308.1	301.6	294.1	289.5
35°	243.3	233.3	229.7	228.2
37.5°	191.0	180.0	176.5	172.4
40°	151.8	147.8	146.3	147.3
42.5°	136.3	136.3	137.2	137.7
45°	132.2	133.7	135.2	135.8
47.5°	132.7	134.2	136.3	136.7
50°	133.7	135.2	136.7	137.2
52.5°	134.2	134.2	135.2	135.8
55°	133.2	132.7	133.2	133.7
57.5°	131.2	130.2	130.7	132.2
60°	130.2	128.7	129.6	130.7
62.5°	127.7	127.2	128.2	128.7
65°	122.2	122.7	124.1	124.1
67.5°	117.1	117.6	118.1	118.7
70°	<i>111.1</i>	<i>111.6</i>	<i>112.6</i>	<i>113.1</i>
72.5°	104.0	106.0	107.6	109.5
75°	98.5	100.5	103.5	105.6
77.5°	89.0	90.5	94.0	96.5
80°	75.4	74.9	75.4	76.9
82.5°	57.8	57.8	57.3	56.8
85°	40.7	40.2	38.8	38.8
87.5°	22.1	21.7	21.1	20.1
90°	0.0	0.0	0.0	0.0

(END OF REPORT)