

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702518

Luminaire Tested: 340-6C-20-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702518
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-12)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-20-D010 / 340-EU4C-1020-9727-4LBW1LI-CF
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL FROSTED GLASS KIT.
Light Source: 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1353.2 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.55
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702518

CATALOG NUMBER: 340-6C-20-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

Luminous Intensity Polar Plot



TEST NUMBER: P702518

CATALOG NUMBER: 340-6C-20-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	98	107	103	99	96	98	95	93		94	92	90		90	88	87	84
2	101	94	88	83	99	92	87	82	88	84	80		85	81	78		82	79	76	74
3	94	85	78	72	92	83	77	72	80	75	70		77	73	69		75	71	67	65
4	88	77	70	64	85	76	69	64	73	67	63		71	66	62		69	64	61	59
5	82	71	63	58	80	70	63	57	68	61	56		66	60	56		64	59	55	53
6	77	66	58	52	75	65	57	52	63	56	52		61	55	51		59	54	50	49
7	73	61	53	48	71	60	53	48	58	52	47		57	51	47		55	50	47	45
8	69	57	50	44	67	56	49	44	55	48	44		53	48	44		52	47	43	42
9	65	53	46	41	64	53	46	41	52	45	41		50	45	41		49	44	40	39
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131355
5°	96919
10°	61630
15°	48982
20°	33775
25°	16981
30°	13368
35°	11651
40°	10739
45°	9519
50°	7920
55°	6274
60°	4977
65°	3938
70°	3081
75°	2460
80°	2018
85°	1624

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9519 cd/sqm

TEST NUMBER: P702518

CATALOG NUMBER: 340-6C-20-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.0	10.4
10°-20°	270.7	20.0
20°-30°	196.6	14.5
30°-40°	180.3	13.3
40°-50°	186.0	13.7
50°-60°	146.2	10.8
60°-70°	99.4	7.3
70°-80°	63.7	4.7
80°-90°	39.3	2.9
90°-100°	22.8	1.7
100°-110°	6.9	0.5
110°-120°	0.2	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.3	45.0
0°-40°	788.6	58.3
0°-60°	1120.9	82.8
0°-90°	1323.3	97.8
90°-120°	29.9	2.2
90°-150°	29.9	2.2
90°-180°	30.0	2.2
0°-180°	1353.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2013	
5°	1656	141
15°	990	271
25°	386	197
35°	286	180
45°	244	186
55°	162	146
65°	100	99
75°	59	64
85°	36	31
90°	26	15
95°	22	16
105°	6	7
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702518

CATALOG NUMBER: 340-6C-20-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

CANDELA DISTRIBUTION (FULL):

0°	
0°	2013.4
2.5°	1943.1
5°	1656.0
7.5°	1345.4
10°	1153.4
12.5°	1051.9
15°	989.5
17.5°	913.0
20°	727.3
22.5°	487.0
25°	385.5
27.5°	346.5
30°	316.8
32.5°	296.5
35°	285.6
37.5°	276.3
40°	270.0
42.5°	259.1
45°	243.5
47.5°	224.7
50°	204.5
52.5°	182.6
55°	162.3
57.5°	143.6
60°	128.0
62.5°	112.4
65°	99.9
67.5°	87.4
70°	76.5
72.5°	67.1
75°	59.3
77.5°	53.1
80°	46.8
82.5°	40.6
85°	35.9
87.5°	31.2
90°	26.5
92.5°	25.0
95°	21.9
97.5°	17.2
100°	12.5
102.5°	9.4
105°	6.2
107.5°	3.1
110°	1.6

TEST NUMBER: P702518

CATALOG NUMBER: 340-6C-20-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)