

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702495

Luminaire Tested: 340-6C-20-D010 / 340-EU4C-1020-9030-4LBW1LI-GFF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-14)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-20-D010 / 340-EU4C-1020-9030-4LBW1LI-GFF
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, FROSTED OUTSIDE KIT.
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1329.9 lumens
Efficiency: N/A
Efficacy: 61.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.63
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702495

CATALOG NUMBER: 340-6C-20-D010 / 340-EU4C-1020-9030-4LBW1LI-GFF

Luminous Intensity Polar Plot



TEST NUMBER: P702495

CATALOG NUMBER: 340-6C-20-D010 / 340-EU4C-1020-9030-4LBW1LI-GFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109		104	104	104		99	99	99	96
1	107	102	97	93	104	99	95	91	94	91	88		90	87	84		85	83	81	79
2	98	89	82	77	95	87	81	75	83	78	73		79	75	71		76	72	69	66
3	90	79	71	65	87	77	70	64	74	68	62		71	65	61		68	63	59	57
4	83	71	63	56	80	70	62	56	67	60	54		64	58	53		61	56	52	50
5	77	65	56	49	75	63	55	49	61	54	48		58	52	47		56	51	47	44
6	72	59	50	44	70	58	50	44	56	49	43		54	47	43		52	46	42	40
7	67	54	46	40	65	53	45	40	51	44	39		50	43	39		48	43	38	36
8	63	50	42	37	61	49	42	36	48	41	36		46	40	36		45	39	35	33
9	60	47	39	34	58	46	39	34	45	38	33		43	37	33		42	37	33	31
10	56	44	36	31	55	43	36	31	42	35	31		41	35	31		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74955
5°	66485
10°	55410
15°	31008
20°	20726
25°	16012
30°	12942
35°	10790
40°	9617
45°	8820
50°	8044
55°	7213
60°	6435
65°	5565
70°	4772
75°	4041
80°	3428
85°	2864

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8820 cd/sqm

TEST NUMBER: P702495

CATALOG NUMBER: 340-6C-20-D010 / 340-EU4C-1020-9030-4LBW1LI-GFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.6	7.9
10°-20°	183.9	13.8
20°-30°	168.7	12.7
30°-40°	167.7	12.6
40°-50°	174.2	13.1
50°-60°	167.4	12.6
60°-70°	140.0	10.5
70°-80°	103.3	7.8
80°-90°	69.9	5.3
90°-100°	40.5	3.0
100°-110°	8.4	0.6
110°-120°	0.2	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	458.2	34.5
0°-40°	625.9	47.1
0°-60°	967.5	72.8
0°-90°	1280.7	96.3
90°-120°	49.2	3.7
90°-150°	49.2	3.7
90°-180°	49.0	3.7
0°-180°	1329.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1149	
5°	1136	106
15°	626	184
25°	364	169
35°	264	168
45°	226	174
55°	187	167
65°	141	140
75°	97	103
85°	63	55
90°	50	28
95°	39	27
105°	6	8
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702495

CATALOG NUMBER: 340-6C-20-D010 / 340-EU4C-1020-9030-4LBW1LI-GFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1148.9
2.5°	1147.3
5°	1136.0
7.5°	1110.0
10°	1037.0
12.5°	837.4
15°	626.4
17.5°	514.4
20°	446.3
22.5°	399.2
25°	363.5
27.5°	334.3
30°	306.7
32.5°	282.4
35°	264.5
37.5°	251.5
40°	241.8
42.5°	233.7
45°	225.6
47.5°	217.5
50°	207.7
52.5°	198.0
55°	186.6
57.5°	176.9
60°	165.5
62.5°	152.5
65°	141.2
67.5°	129.8
70°	118.5
72.5°	107.1
75°	97.4
77.5°	87.6
80°	79.5
82.5°	71.4
85°	63.3
87.5°	56.8
90°	50.3
92.5°	45.4
95°	38.9
97.5°	29.2
100°	19.5
102.5°	11.4
105°	6.5
107.5°	3.2
110°	1.6

TEST NUMBER: P702495

CATALOG NUMBER: 340-6C-20-D010 / 340-EU4C-1020-9030-4LBW1LI-GFF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)