

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155844

Luminaire Tested: **AVS-F04-LED-E-U-T3-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P155844
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-T3-7030
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA
Light Source: (28) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9301 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P155844

CATALOG NUMBER: AVS-F04-LED-E-U-T3-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 10 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155844

CATALOG NUMBER: AVS-F04-LED-E-U-T3-7030

Luminous Intensity Polar Plot



— Vertical Plane Through 67.5-Deg Lateral - - - Horizontal Cone Through 66-Deg Vertical

REPORT NUMBER: P155844

CATALOG NUMBER: AVS-F04-LED-E-U-T3-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3211.9	0.0	3211.9
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	6089.1	0.0	6089.1
	% Fixture	65.5	0.0	65.5
Total	Lumens	9301.0	0.0	9301.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	1.0
10°-20°	283.3	3.0
20°-30°	486.9	5.2
30°-40°	790.6	8.5
40°-50°	1320.0	14.2
50°-60°	2078.5	22.3
60°-70°	2834.3	30.5
70°-80°	1226.9	13.2
80°-90°	184.5	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9301.0	100.0
0°-180°	9301.0	100.0

Coefficient of Utilization



REPORT NUMBER: P155844


CATALOG NUMBER: AVS-F04-LED-E-U-T3-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	435.1	4.7			
FM (30°-60°)	2597.5	27.9			
FH (60°-80°)	2905.0	31.2			G2/5000
FVH (80°-90°)	151.5	1.6			G2/225
BL (0°-30°)	431.1	4.6	B1/500		
BM (30°-60°)	1591.6	17.1	B2/2500		
BH (60°-80°)	1156.2	12.4	B3/2500		G3/2500
BVH (80°-90°)	33.0	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type III Short





REPORT NUMBER: P155844

CATALOG NUMBER: AVS-F04-LED-E-U-T3-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3
2.5°	1006.3	1010.4	1006.3	1007.4	1008.3	1007.4	1006.3	1006.3	1003.3	1005.3	1007.4
5°	1002.3	1005.3	1004.4	1005.3	1006.3	1005.3	1004.4	1005.3	1003.3	1004.4	1007.4
7.5°	997.3	996.3	997.3	999.3	1001.3	1001.3	1001.3	1002.3	1001.3	1001.3	1004.4
10°	982.2	983.2	985.2	988.2	989.2	992.2	992.2	995.2	996.3	998.2	1002.3
12.5°	963.1	964.1	966.1	968.1	973.2	978.1	978.1	985.2	988.2	993.3	1000.3
15°	949.0	950.1	952.0	954.1	958.0	963.1	966.1	974.2	979.2	988.2	998.2
17.5°	957.1	956.1	958.0	959.1	959.1	963.1	963.1	969.1	975.1	983.2	996.3
20°	980.2	980.2	982.2	982.2	981.2	983.2	979.2	979.2	980.2	984.2	993.3
22.5°	1003.3	1002.3	1006.3	1008.3	1009.3	1012.3	1008.3	1007.4	1002.3	999.3	1002.3
25°	1025.4	1024.5	1029.4	1032.4	1037.5	1040.5	1040.5	1040.5	1036.5	1031.5	1028.5
27.5°	1059.6	1059.6	1064.7	1067.7	1071.7	1077.7	1080.7	1080.7	1081.8	1074.7	1069.6
30°	1116.9	1117.9	1119.0	1122.9	1126.9	1129.0	1133.0	1136.1	1139.1	1135.0	1126.9
32.5°	1185.3	1179.3	1179.3	1185.3	1190.3	1196.4	1198.3	1202.4	1208.4	1205.4	1204.4
35°	1266.7	1264.7	1262.7	1264.7	1270.8	1277.7	1285.8	1292.8	1288.8	1294.8	1291.8
37.5°	1387.4	1389.3	1390.4	1390.4	1389.3	1391.4	1395.4	1402.4	1400.4	1402.4	1406.4
40°	1586.4	1579.4	1572.3	1573.4	1563.3	1565.3	1549.2	1556.3	1557.2	1550.3	1553.3
42.5°	1785.5	1789.4	1792.5	1800.5	1793.5	1789.4	1774.4	1774.4	1766.3	1759.3	1757.3
45°	2000.6	2008.6	2009.6	2025.7	2019.7	2032.7	2043.8	2040.8	2027.8	2026.7	2012.6
47.5°	2172.5	2185.6	2199.7	2218.8	2233.8	2263.0	2297.2	2314.3	2324.4	2332.3	2316.3
50°	2301.1	2307.3	2343.4	2373.6	2406.7	2455.0	2502.3	2563.6	2612.8	2636.0	2658.0
52.5°	2370.6	2385.6	2424.9	2472.1	2530.4	2602.8	2679.2	2776.7	2861.1	2917.4	2967.7
55°	2385.6	2400.7	2445.0	2505.3	2584.7	2682.2	2791.8	2924.5	3051.2	3159.7	3265.3
57.5°	2343.4	2360.5	2407.8	2477.1	2570.6	2689.2	2826.9	3000.9	3175.9	3351.7	3507.6
60°	2266.0	2287.2	2330.4	2398.7	2502.3	2636.0	2800.8	3019.0	3264.2	3533.7	3832.3
62.5°	2138.3	2160.4	2200.6	2276.1	2382.6	2530.4	2721.5	2992.8	3339.7	3763.9	4293.8
65°	1933.3	1943.3	1992.5	2068.9	2163.4	2326.3	2536.5	2864.1	3315.5	3905.7	4635.5
66°	1840.7	1857.8	1888.0	1949.3	2039.8	2192.6	2403.7	2736.5	3224.0	3856.5	4626.5
67.5°	1696.0	1709.0	1729.1	1770.4	1825.7	1938.2	2138.3	2453.0	2944.6	3607.2	4434.5
70°	1371.3	1377.3	1404.5	1418.5	1437.6	1474.8	1547.2	1728.2	2111.2	2733.5	3579.0
72.5°	934.9	952.0	981.2	1021.5	1073.7	1123.9	1158.1	1181.2	1263.7	1630.7	2384.7
75°	685.6	703.7	740.9	794.2	885.7	990.3	1098.9	1149.1	1114.9	1067.7	1328.1
77.5°	398.1	422.3	453.4	504.7	589.1	727.9	913.9	1078.8	1190.3	1197.3	1137.0
80°	167.9	170.9	190.1	216.2	268.4	365.9	510.7	748.0	995.2	1162.2	1201.3
82.5°	38.2	47.3	60.3	71.4	87.5	120.6	179.0	297.6	537.8	843.4	1099.8
85°	14.1	14.1	19.1	28.2	32.1	36.2	47.3	75.4	128.7	237.3	494.6
87.5°	0.0	1.0	2.0	2.0	4.0	5.1	8.1	11.1	10.1	9.0	30.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155844

CATALOG NUMBER: AVS-F04-LED-E-U-T3-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3
2.5°	1005.3	1004.4	1002.3	1002.3	1002.3	1002.3	1000.3	1001.3	999.3	1000.3	1000.3
5°	1004.4	1004.4	1003.3	1001.3	1002.3	1002.3	1003.3	1001.3	1001.3	1002.3	1001.3
7.5°	1004.4	1003.3	1003.3	1003.3	1004.4	1003.3	1004.4	1004.4	1004.4	1005.3	1005.3
10°	1004.4	1004.4	1006.3	1007.4	1007.4	1008.3	1011.4	1011.4	1012.3	1013.4	1015.3
12.5°	1005.3	1009.3	1012.3	1015.3	1016.4	1018.4	1023.4	1023.4	1025.4	1028.5	1029.4
15°	1006.3	1012.3	1018.4	1020.4	1022.4	1026.4	1031.5	1033.5	1036.5	1039.5	1041.6
17.5°	1005.3	1013.4	1020.4	1023.4	1026.4	1031.5	1037.5	1039.5	1043.5	1047.6	1051.6
20°	1004.4	1015.3	1026.4	1030.5	1034.5	1041.6	1049.5	1054.6	1058.7	1064.7	1068.7
22.5°	1010.4	1023.4	1038.5	1044.6	1051.6	1060.6	1071.7	1077.7	1082.7	1088.8	1091.8
25°	1029.4	1039.5	1057.6	1067.7	1076.7	1091.8	1106.8	1113.9	1119.9	1125.0	1126.0
27.5°	1061.7	1064.7	1086.7	1099.8	1112.8	1137.0	1155.1	1160.1	1171.2	1175.2	1174.2
30°	1113.9	1108.9	1126.9	1147.0	1166.2	1199.4	1221.5	1234.5	1244.6	1244.6	1236.6
32.5°	1189.3	1181.2	1186.3	1209.4	1231.5	1279.8	1305.9	1323.0	1330.1	1328.1	1311.0
35°	1287.8	1282.8	1279.8	1297.8	1333.1	1389.3	1423.5	1432.5	1443.6	1441.7	1419.5
37.5°	1404.5	1400.4	1400.4	1421.6	1455.8	1539.2	1576.4	1582.4	1581.3	1565.3	1524.0
40°	1542.2	1540.2	1531.1	1543.2	1572.3	1680.9	1731.2	1739.2	1728.2	1702.0	1653.8
42.5°	1740.2	1728.2	1700.0	1707.0	1729.1	1834.7	1900.1	1922.2	1911.1	1885.0	1806.5
45°	1998.5	1985.5	1938.2	1932.2	1944.2	2036.8	2121.2	2126.2	2124.2	2091.1	1998.5
47.5°	2302.2	2282.1	2231.8	2215.8	2211.7	2297.2	2378.5	2386.6	2381.7	2332.3	2208.7
50°	2631.0	2601.8	2568.6	2557.5	2541.5	2602.8	2685.2	2686.2	2666.1	2597.7	2482.2
52.5°	2981.8	2971.7	2965.7	2954.6	2947.6	3000.9	3051.2	3021.0	2990.9	2919.5	2819.0
55°	3335.6	3376.9	3419.1	3423.1	3435.2	3492.5	3491.5	3409.0	3386.9	3347.8	3248.2
57.5°	3711.7	3864.5	3997.2	4038.3	4078.7	4185.2	4175.1	4093.7	4065.5	4017.3	3934.8
60°	4223.4	4635.5	5018.5	5110.1	5173.4	5301.0	5289.0	5163.3	5221.7	5217.6	5111.1
62.5°	4940.2	5625.8	6199.8	6340.6	6384.8	6398.9	6322.5	6186.7	6244.0	6308.4	5980.7
65°	5425.7	6232.0	6821.1	6929.7	6935.8	6767.9	6597.9	6438.1	6424.0	6368.7	5900.2
66°	5436.8	6262.2	6853.3	6958.9	6921.7	6692.4	6477.3	6316.5	6247.0	6125.5	5639.9
67.5°	5241.8	6074.2	6710.6	6822.2	6740.7	6416.0	6119.4	5912.3	5776.6	5579.6	5151.3
70°	4402.3	5227.7	6011.8	6219.9	6246.1	5761.6	5350.4	5107.0	4924.0	4653.7	4284.7
72.5°	3273.4	4019.3	4711.0	4910.1	5011.5	4624.5	4277.6	4092.6	3842.4	3557.8	3295.4
75°	2051.9	2578.7	3042.1	3181.9	3086.3	2786.7	2578.7	2501.2	2254.9	2085.1	1965.4
77.5°	1173.3	1338.1	1375.2	1322.0	1209.4	925.9	658.4	487.6	423.2	468.5	516.8
80°	1145.1	1049.5	836.5	735.9	666.5	458.4	269.4	185.0	153.8	157.8	170.9
82.5°	1240.6	1331.1	1095.9	893.8	749.9	506.6	279.5	148.8	100.5	118.7	133.7
85°	806.3	1122.0	1010.4	851.5	689.6	433.3	230.3	77.4	51.3	67.4	92.5
87.5°	81.5	89.4	76.4	103.5	77.4	36.2	18.1	11.1	10.1	12.0	18.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155844

CATALOG NUMBER: AVS-F04-LED-E-U-T3-7030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3
2.5°	1001.3	1001.3	1002.3	1003.3	1004.4	1005.3	1005.3	1005.3	1005.3	1007.4	1006.3
5°	1003.3	1005.3	1007.4	1008.3	1010.4	1010.4	1013.4	1012.3	1012.3	1015.3	1016.4
7.5°	1007.4	1010.4	1014.4	1013.4	1017.4	1016.4	1018.4	1018.4	1015.3	1016.4	1014.4
10°	1016.4	1020.4	1022.4	1019.4	1020.4	1016.4	1015.3	1010.4	1004.4	1001.3	997.3
12.5°	1031.5	1035.4	1035.4	1030.5	1024.5	1015.3	1008.3	997.3	988.2	983.2	978.1
15°	1044.6	1048.6	1047.6	1039.5	1030.5	1016.4	1006.3	993.3	980.2	972.1	967.2
17.5°	1054.6	1056.6	1053.6	1042.5	1032.4	1019.4	1009.3	995.2	980.2	970.2	961.1
20°	1069.6	1067.7	1060.6	1046.5	1035.4	1023.4	1015.3	1003.3	986.2	973.2	960.1
22.5°	1091.8	1083.7	1070.7	1055.5	1044.6	1033.5	1025.4	1012.3	995.2	979.2	964.1
25°	1120.9	1104.9	1086.7	1070.7	1060.6	1048.6	1039.5	1025.4	1007.4	989.2	971.2
27.5°	1163.1	1135.0	1111.9	1097.8	1086.7	1071.7	1060.6	1042.5	1023.4	1002.3	982.2
30°	1210.4	1172.2	1150.1	1139.1	1126.9	1110.9	1093.8	1070.7	1048.6	1025.4	1001.3
32.5°	1271.7	1225.5	1204.4	1193.4	1177.2	1157.1	1137.0	1110.9	1079.7	1049.5	1020.4
35°	1352.1	1304.9	1282.8	1265.7	1243.6	1217.4	1188.3	1153.1	1110.9	1070.7	1033.5
37.5°	1438.7	1387.4	1366.2	1348.2	1314.9	1280.8	1239.6	1188.3	1131.0	1077.7	1031.5
40°	1548.2	1500.9	1473.8	1442.6	1403.4	1344.1	1279.8	1205.4	1132.0	1066.6	1012.3
42.5°	1686.9	1639.7	1599.5	1550.3	1481.9	1390.4	1298.9	1202.4	1113.9	1039.5	981.2
45°	1870.9	1813.6	1744.2	1657.8	1547.2	1419.5	1299.9	1183.3	1079.7	997.3	934.9
47.5°	2096.1	2008.6	1895.0	1749.2	1590.5	1427.6	1283.8	1145.1	1026.4	937.0	867.6
50°	2363.5	2225.8	2038.8	1824.7	1612.5	1415.5	1243.6	1087.8	951.1	855.5	773.1
52.5°	2669.1	2443.9	2168.5	1879.0	1611.5	1375.2	1175.2	1001.3	852.5	745.9	667.6
55°	3028.1	2693.3	2302.2	1919.2	1583.4	1300.9	1070.7	879.7	730.9	632.3	560.0
57.5°	3553.8	3097.4	2535.4	1981.5	1527.0	1186.3	928.9	733.9	603.2	509.7	448.4
60°	4514.9	3772.0	2955.6	2107.2	1440.6	1018.4	763.0	578.0	468.5	393.1	351.8
62.5°	5238.8	4293.8	3182.9	2079.0	1266.7	811.3	566.0	421.2	344.9	293.6	267.5
65°	5135.2	4131.9	2940.6	1790.5	993.3	572.0	376.0	286.5	237.3	213.2	198.0
66°	4900.9	3920.7	2730.5	1611.5	858.5	475.5	309.6	240.3	204.0	186.9	176.9
67.5°	4456.6	3528.7	2354.5	1321.0	659.5	344.9	233.3	190.1	165.9	158.9	151.8
70°	3704.7	2813.9	1652.7	769.1	336.8	192.0	147.8	132.7	126.6	125.7	123.6
72.5°	2839.1	1991.5	973.2	363.9	174.9	127.7	114.6	109.5	107.6	107.6	108.6
75°	1740.2	1119.0	430.3	177.9	122.7	107.6	101.6	99.5	98.5	99.5	98.5
77.5°	581.0	355.9	183.9	134.7	111.6	99.5	95.5	93.5	93.5	93.5	93.5
80°	177.9	154.8	140.7	124.7	105.6	94.5	88.5	87.5	88.5	89.4	86.4
82.5°	133.7	126.6	118.7	110.6	95.5	84.5	82.5	82.5	82.5	79.4	75.4
85°	98.5	97.5	80.4	75.4	70.4	70.4	70.4	70.4	67.4	62.3	58.3
87.5°	18.1	17.1	18.1	19.1	28.2	30.2	30.2	32.1	35.2	33.2	33.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155844

CATALOG NUMBER: AVS-F04-LED-E-U-T3-7030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	1002.3	1002.3	1002.3	1002.3	1002.3
2.5°	1006.3	1005.3	1008.3	1006.3	1007.4
5°	1015.3	1014.4	1016.4	1014.4	1017.4
7.5°	1012.3	1010.4	1009.3	1010.4	1011.4
10°	991.3	989.2	988.2	987.3	988.2
12.5°	973.2	969.1	969.1	967.2	968.1
15°	960.1	957.1	956.1	954.1	955.0
17.5°	954.1	949.0	947.0	945.0	945.0
20°	950.1	944.0	940.9	939.0	937.9
22.5°	950.1	940.9	937.0	934.9	934.0
25°	954.1	943.0	937.0	934.0	933.0
27.5°	962.1	948.0	940.9	937.0	937.0
30°	976.2	958.0	948.0	943.0	942.0
32.5°	990.3	966.1	952.0	946.0	944.0
35°	997.3	966.1	949.0	939.0	937.0
37.5°	989.2	953.1	931.9	916.9	913.9
40°	964.1	925.9	902.8	888.7	886.7
42.5°	930.9	893.8	866.6	856.6	853.5
45°	885.7	841.5	814.3	800.2	801.2
47.5°	808.3	763.0	739.0	725.8	727.9
50°	716.8	672.5	651.4	637.4	640.4
52.5°	616.3	576.1	556.0	548.9	546.9
55°	510.7	479.6	465.5	457.4	454.4
57.5°	414.2	392.1	382.1	372.0	373.0
60°	326.7	315.6	312.6	301.6	300.6
62.5°	257.4	250.4	247.4	239.3	240.3
65°	195.0	193.1	195.0	190.1	192.0
66°	176.0	176.9	176.9	173.9	176.0
67.5°	151.8	153.8	156.8	153.8	155.9
70°	125.7	127.7	129.6	129.6	129.6
72.5°	109.5	111.6	112.6	112.6	112.6
75°	100.5	101.6	102.6	100.5	100.5
77.5°	94.5	94.5	92.5	91.5	90.5
80°	85.5	84.5	81.5	79.4	79.4
82.5°	71.4	69.3	67.4	64.4	64.4
85°	54.3	52.2	50.3	46.2	44.2
87.5°	28.2	29.1	28.2	23.1	20.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)