

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148621

Luminaire Tested: **AVS-E03-LED-E-U-5XQ-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148621
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E03-LED-E-U-5XQ-7050
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (63) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9790.2 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B4 - U0 - G3


Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P148621
 CATALOG NUMBER: AVS-E03-LED-E-U-5XQ-7050

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 9.3 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148621
CATALOG NUMBER: AVS-E03-LED-E-U-5XQ-7050

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical



REPORT NUMBER: P148621

CATALOG NUMBER: AVS-E03-LED-E-U-5XQ-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4895.1	0.0	4895.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4895.1	0.0	4895.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	9790.2	0.0	9790.2
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	0.9
10°-20°	261.5	2.7
20°-30°	437.9	4.5
30°-40°	667.6	6.8
40°-50°	1066.0	10.9
50°-60°	1639.0	16.7
60°-70°	2386.5	24.4
70°-80°	2688.3	27.5
80°-90°	555.0	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9790.2	100.0
0°-180°	9790.2	100.0



REPORT NUMBER: P148621


CATALOG NUMBER: AVS-E03-LED-E-U-5XQ-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	393.9	4.0			
FM	(30°-60°)	1686.3	17.2			
FH	(60°-80°)	2537.4	25.9			G2/5000
FVH	(80°-90°)	277.5	2.8			G3/500
BL	(0°-30°)	393.9	4.0	B1/500		
BM	(30°-60°)	1686.3	17.2	B2/2500		
BH	(60°-80°)	2537.4	25.9	B4/5000		G2/5000
BVH	(80°-90°)	277.5	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G3

Type V Short





REPORT NUMBER: P148621

CATALOG NUMBER: AVS-E03-LED-E-U-5XQ-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	927.6	927.6	927.6	927.6	927.6	927.6	927.6	927.6	927.6	927.6	927.6
2.5°	929.1	929.6	929.4	928.9	929.1	928.9	928.4	928.1	926.3	927.4	928.9
5°	929.1	928.7	928.4	928.1	928.1	928.9	928.1	927.4	927.0	927.7	926.8
7.5°	928.7	927.7	927.0	926.8	927.0	927.4	926.5	925.6	926.3	925.6	924.6
10°	927.0	926.3	926.6	925.6	925.8	925.6	924.6	923.7	924.2	923.5	922.3
12.5°	927.7	926.3	926.0	925.6	925.3	925.1	923.7	922.5	922.7	922.3	920.9
15°	927.7	926.8	926.6	925.6	925.3	924.8	923.2	922.7	922.7	922.0	920.4
17.5°	928.1	927.7	927.6	926.3	925.8	925.6	923.7	923.0	923.7	922.3	921.2
20°	929.6	929.1	929.4	928.6	927.6	927.6	926.3	925.8	926.0	925.8	923.0
22.5°	932.7	932.7	933.3	933.1	932.7	933.0	931.9	932.0	932.2	932.2	929.9
25°	941.5	941.1	941.8	941.8	942.0	943.8	943.0	942.8	944.0	944.0	941.8
27.5°	957.9	957.3	957.9	958.3	959.7	962.0	961.5	962.3	964.2	963.7	961.7
30°	976.9	976.4	977.6	979.2	980.2	983.8	982.2	986.1	987.9	989.4	987.9
32.5°	1004.6	1004.6	1006.8	1007.9	1010.2	1013.8	1014.3	1017.4	1019.7	1022.3	1020.5
35°	1041.5	1041.0	1042.7	1044.6	1047.4	1050.8	1052.0	1056.2	1059.7	1061.6	1058.1
37.5°	1097.9	1095.1	1098.4	1099.5	1101.8	1102.6	1106.1	1111.3	1115.1	1114.6	1112.3
40°	1174.3	1173.9	1172.6	1171.1	1174.6	1176.0	1176.0	1182.8	1189.0	1188.0	1187.8
42.5°	1263.6	1261.3	1259.8	1259.8	1261.9	1262.4	1270.4	1275.4	1279.8	1280.8	1279.8
45°	1359.6	1357.3	1357.8	1356.8	1357.5	1360.8	1365.5	1374.9	1383.2	1383.4	1379.1
47.5°	1462.7	1455.5	1461.1	1453.3	1458.1	1460.6	1472.2	1486.0	1500.4	1503.0	1499.2
50°	1567.5	1566.6	1566.1	1564.6	1566.8	1572.4	1586.6	1608.4	1622.3	1631.5	1625.4
52.5°	1681.8	1677.9	1676.2	1673.6	1675.9	1686.8	1706.7	1725.6	1750.5	1761.0	1752.5
55°	1793.2	1791.8	1785.2	1784.9	1789.8	1807.0	1828.5	1851.9	1878.9	1890.6	1887.6
57.5°	1907.6	1900.1	1898.0	1894.9	1904.7	1920.8	1947.3	1989.3	2017.3	2030.7	2023.0
60°	2019.4	2013.7	2009.3	2008.3	2015.0	2037.5	2075.5	2126.1	2160.7	2178.1	2165.8
62.5°	2139.5	2135.9	2130.8	2124.9	2138.9	2167.9	2215.1	2271.0	2322.1	2343.6	2324.9
65°	2288.7	2281.2	2275.6	2268.2	2279.8	2316.2	2375.4	2454.2	2522.7	2547.8	2534.5
67.5°	2446.2	2439.3	2439.8	2435.2	2455.8	2506.3	2582.7	2689.7	2781.6	2824.4	2799.2
70°	2583.7	2587.6	2588.6	2607.4	2642.7	2719.7	2846.9	3014.4	3153.8	3219.2	3192.2
71°	2543.2	2551.7	2564.8	2584.2	2645.3	2736.4	2910.1	3113.0	3279.2	3390.1	3352.8
72.5°	2428.3	2433.4	2440.1	2469.8	2538.9	2659.4	2838.1	3070.1	3283.8	3427.2	3384.1
75°	2262.0	2266.9	2269.2	2290.1	2352.8	2458.0	2621.8	2827.5	3016.0	3138.0	3126.0
77.5°	2011.2	2011.9	2029.8	2062.0	2132.5	2252.8	2425.2	2638.7	2815.9	2910.8	2850.6
80°	1444.2	1434.5	1453.0	1494.3	1581.5	1719.5	1896.0	2139.7	2336.5	2425.2	2331.8
82.5°	549.4	579.2	626.1	694.4	723.9	877.3	1042.1	1185.2	1350.9	1536.1	1489.6
85°	59.1	66.4	83.4	103.4	130.6	180.6	249.6	340.7	419.9	493.6	438.1
87.5°	22.0	22.6	25.1	29.0	29.5	30.8	32.8	38.2	35.6	30.8	24.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148621

CATALOG NUMBER: AVS-E03-LED-E-U-5XQ-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	927.6	927.6	927.6	927.6	927.6	927.6	927.6	927.6
2.5°	927.6	927.9	927.6	927.9	927.9	926.8	927.0	926.6
5°	927.4	926.6	926.8	927.0	926.8	927.4	926.6	927.0
7.5°	926.0	924.6	925.0	925.0	924.6	925.3	924.8	924.6
10°	923.5	921.5	922.5	922.0	921.7	922.0	922.0	921.9
12.5°	921.2	919.9	920.2	919.9	919.7	920.4	920.2	920.4
15°	920.6	918.7	918.3	917.9	918.1	918.7	918.7	919.4
17.5°	920.2	917.6	917.3	916.9	917.1	918.1	918.3	917.9
20°	921.7	919.6	919.2	918.7	918.3	919.7	919.4	919.4
22.5°	928.9	926.3	926.0	924.0	923.2	923.9	923.5	923.5
25°	940.4	937.4	936.4	933.5	931.5	931.4	930.7	930.2
27.5°	961.2	956.6	955.5	953.3	950.5	950.9	949.4	949.2
30°	985.3	981.2	977.6	974.3	971.0	969.6	967.9	967.7
32.5°	1016.9	1012.2	1007.9	1003.7	999.2	997.4	994.3	992.7
35°	1055.6	1049.4	1044.4	1041.5	1036.9	1034.6	1032.5	1034.8
37.5°	1109.7	1102.3	1099.7	1096.4	1093.3	1089.7	1090.5	1089.7
40°	1184.7	1178.0	1175.3	1169.5	1168.7	1164.7	1167.3	1164.6
42.5°	1277.2	1264.9	1263.1	1258.4	1257.0	1254.7	1255.6	1253.9
45°	1378.0	1367.0	1365.0	1357.5	1357.8	1352.3	1354.5	1354.5
47.5°	1491.4	1479.9	1470.4	1465.0	1463.0	1459.7	1461.5	1461.1
50°	1608.4	1592.7	1582.3	1571.7	1567.2	1568.4	1564.8	1571.0
52.5°	1734.1	1710.8	1695.9	1685.9	1677.2	1679.0	1679.5	1681.2
55°	1864.1	1834.4	1812.8	1799.8	1791.9	1792.3	1794.6	1796.7
57.5°	1995.0	1957.8	1928.5	1909.0	1903.9	1906.2	1906.2	1905.9
60°	2130.7	2086.1	2048.3	2026.3	2021.7	2020.4	2030.4	2027.0
62.5°	2276.5	2222.8	2183.8	2155.6	2148.9	2153.6	2162.5	2160.4
65°	2469.6	2395.4	2345.2	2317.2	2305.9	2310.6	2322.6	2322.1
67.5°	2718.7	2615.0	2548.6	2512.7	2504.5	2510.2	2516.8	2523.1
70°	3091.2	2943.1	2848.2	2770.5	2737.2	2730.8	2737.4	2737.6
71°	3222.2	3052.1	2901.0	2806.2	2751.5	2728.4	2730.2	2718.7
72.5°	3216.9	3007.3	2830.6	2731.2	2655.3	2636.9	2627.9	2614.0
75°	3000.1	2811.3	2657.9	2549.6	2476.6	2454.7	2438.8	2437.9
77.5°	2720.7	2581.5	2412.4	2297.7	2208.7	2172.5	2156.4	2155.9
80°	2187.2	1978.5	1854.9	1785.9	1678.4	1647.5	1614.5	1602.3
82.5°	1322.7	1033.6	840.3	746.7	694.9	572.3	513.6	485.8
85°	308.1	218.9	150.9	99.0	71.3	56.7	43.6	38.5
87.5°	20.8	16.4	14.6	11.8	9.0	8.7	5.4	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)