

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702552

Luminaire Tested: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-CC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-11)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-CC
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1896.3 lumens
Efficiency: N/A
Efficacy: 60.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.71
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702552

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-CC

Luminous Intensity Polar Plot



TEST NUMBER: P702552

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-CC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	61		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	54	50	69	60	54	50	59	54	50		58	53	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	215372
5°	175853
10°	128864
15°	111276
20°	95296
25°	88088
30°	71009
35°	46098
40°	34858
45°	19449
50°	11327
55°	7518
60°	5128
65°	3196
70°	2766
75°	2092
80°	1540
85°	1572

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19449 cd/sqm

TEST NUMBER: P702552

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-CC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.2	12.2
10°-20°	461.0	24.3
20°-30°	545.0	28.7
30°-40°	381.4	20.1
40°-50°	177.9	9.4
50°-60°	61.8	3.3
60°-70°	23.5	1.2
70°-80°	9.5	0.5
80°-90°	2.3	0.1
90°-100°	1.4	0.1
100°-110°	0.8	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1238.2	65.3
0°-40°	1619.6	85.4
0°-60°	1859.3	98.1
0°-90°	1894.6	99.9
90°-120°	2.3	0.1
90°-150°	2.3	0.1
90°-180°	2.0	0.1
0°-180°	1896.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3301	
5°	2685	232
15°	1648	461
25°	1224	545
35°	579	381
45°	211	178
55°	66	62
65°	21	23
75°	8	10
85°	2	2
90°	0	0
95°	0	1
105°	0	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702552

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-CC

CANDELA DISTRIBUTION (FULL):

0°	
0°	3301.2
2.5°	3137.9
5°	2685.2
7.5°	2238.7
10°	1945.2
12.5°	1771.5
15°	1647.5
17.5°	1535.9
20°	1372.6
22.5°	1250.6
25°	1223.7
27.5°	1120.4
30°	942.6
32.5°	742.1
35°	578.8
37.5°	473.4
40°	409.3
42.5°	318.3
45°	210.8
47.5°	146.8
50°	111.6
52.5°	84.8
55°	66.1
57.5°	51.7
60°	39.3
62.5°	28.9
65°	20.7
67.5°	18.6
70°	14.5
72.5°	12.4
75°	8.3
77.5°	6.2
80°	4.1
82.5°	2.1
85°	2.1
87.5°	2.1
90°	0.0
92.5°	0.0
95°	0.0
97.5°	2.1
100°	2.1
102.5°	2.1
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P702552

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-CC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)