

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152046

Luminaire Tested: **AVS-F03-LED-E-U-SL4-HSS-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152046
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F03-LED-E-U-SL4-HSS-7050
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (21) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5170.9 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B0 - U0 - G2


Input Watts (W): 78.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P152046
 CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7050

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 11.6 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P152046
CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7050

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P152046

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	154.0	0.0	154.0
	% Fixture	3.0	0.0	3.0
Street Side	Lumens	5016.9	0.0	5016.9
	% Fixture	97.0	0.0	97.0
Total	Lumens	5170.9	0.0	5170.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.1	0.8
10°-20°	138.4	2.7
20°-30°	264.9	5.1
30°-40°	440.5	8.5
40°-50°	596.0	11.5
50°-60°	932.1	18.0
60°-70°	1916.4	37.1
70°-80°	771.1	14.9
80°-90°	71.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5170.9	100.0
0°-180°	5170.9	100.0



REPORT NUMBER: P152046


CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	384.8	7.4			
FM	(30°-60°)	1898.3	36.7			
FH	(60°-80°)	2665.1	51.5			G2/5000
FVH	(80°-90°)	68.7	1.3			G1/100
BL	(0°-30°)	58.6	1.1	B0/110		
BM	(30°-60°)	70.3	1.4	B0/220		
BH	(60°-80°)	22.5	0.4	B0/110		G0/110
BVH	(80°-90°)	2.6	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type IV Short





REPORT NUMBER: P152046

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5
2.5°	520.9	515.0	508.3	508.3	499.8	499.8	494.7	481.1	479.5	471.8	464.2
5°	665.0	659.9	651.4	643.7	637.0	625.2	616.7	600.6	582.8	565.8	550.6
7.5°	805.6	803.0	787.8	785.3	774.2	754.7	737.8	714.1	683.6	659.9	631.9
10°	936.1	930.1	926.7	912.3	896.2	875.0	848.8	820.0	784.4	747.2	707.4
12.5°	1039.4	1036.0	1020.7	1014.8	997.8	976.7	943.6	906.3	870.8	822.5	776.0
15°	1116.5	1110.5	1100.3	1091.0	1070.7	1052.0	1021.6	980.9	937.7	885.2	829.3
17.5°	1180.8	1169.8	1167.3	1152.8	1131.7	1109.6	1075.8	1038.5	987.7	935.1	874.2
20°	1267.3	1252.0	1246.9	1225.7	1201.1	1170.7	1131.7	1085.1	1031.7	974.1	911.5
22.5°	1368.9	1357.8	1346.8	1328.2	1296.9	1253.7	1196.9	1146.1	1078.3	1014.8	947.0
25°	1512.8	1503.5	1485.8	1460.3	1421.3	1369.7	1301.1	1226.5	1146.9	1065.6	986.0
27.5°	1652.6	1644.1	1631.5	1612.0	1568.0	1511.2	1426.4	1331.6	1230.8	1132.5	1044.5
30°	1783.9	1776.3	1763.6	1744.1	1705.2	1649.2	1553.6	1451.9	1326.5	1212.1	1106.3
32.5°	1925.4	1922.9	1908.5	1880.5	1846.6	1771.2	1667.0	1557.8	1430.7	1298.5	1174.9
35°	2085.5	2066.0	2052.4	2024.6	1966.9	1886.4	1764.5	1645.0	1511.2	1375.6	1237.6
37.5°	2221.0	2202.4	2185.5	2149.8	2079.6	1977.1	1839.0	1707.7	1569.6	1431.6	1291.0
40°	2320.1	2310.8	2290.5	2243.9	2165.1	2043.1	1894.1	1750.9	1612.0	1473.1	1334.1
42.5°	2393.9	2379.5	2356.6	2308.3	2215.1	2076.2	1916.1	1768.7	1631.5	1498.4	1362.1
45°	2420.9	2409.1	2387.9	2335.3	2234.6	2085.5	1915.2	1763.6	1632.3	1506.1	1380.7
47.5°	2404.9	2393.0	2374.4	2325.2	2226.1	2074.5	1900.0	1749.2	1623.8	1508.6	1397.7
50°	2351.5	2344.7	2330.3	2288.8	2199.9	2053.3	1886.4	1741.6	1622.2	1521.3	1421.3
52.5°	2346.4	2342.2	2324.4	2282.9	2192.2	2046.5	1884.8	1745.8	1636.6	1537.4	1438.3
55°	2867.4	2807.3	2672.5	2558.1	2370.2	2146.5	1970.3	1814.4	1697.5	1600.9	1531.5
57.5°	4075.2	3985.5	3808.5	3590.8	3158.8	2734.4	2394.7	2149.0	2027.9	1983.8	2010.2
60°	4641.1	4625.1	4597.1	4493.8	4272.6	3907.6	3500.9	3061.3	2885.2	2869.8	2923.2
62.5°	4909.6	4899.5	4908.0	4895.2	4826.6	4719.9	4603.0	4413.3	4238.8	4126.1	3887.3
65°	5033.4	5040.1	5088.4	5126.5	5134.9	5162.9	5248.5	5484.8	5657.6	5367.0	4703.8
67.5°	4719.1	4758.9	4869.8	5008.8	5171.4	5328.9	5583.1	6081.1	6436.1	6094.7	5152.7
69°	3906.7	3926.2	4197.3	4459.0	4856.3	5134.1	5502.6	6155.6	6554.7	6169.2	5117.2
70°	3075.8	3093.5	3384.0	3739.8	4411.6	4769.0	5251.0	6029.5	6443.7	6070.2	4934.2
72.5°	1387.5	1362.1	1464.6	1655.2	2385.4	2953.0	3795.8	4885.1	5316.3	4863.1	3691.6
75°	969.0	958.0	969.0	969.9	1083.4	1397.7	1763.6	2648.0	3274.8	2825.8	1763.6
77.5°	750.5	742.9	735.2	726.8	740.3	829.3	864.9	939.4	1219.8	1153.7	672.5
80°	593.8	587.0	605.7	599.7	599.7	609.8	603.1	575.1	522.7	484.6	433.7
82.5°	276.2	277.8	277.8	301.6	363.4	424.4	443.8	416.0	369.3	314.3	253.3
85°	26.2	29.6	49.9	77.1	153.4	172.8	173.7	144.0	144.0	113.5	91.5
87.5°	0.0	0.8	0.8	0.8	7.7	21.1	17.8	5.1	2.6	2.6	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152046
 CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5
2.5°	450.7	448.1	437.9	427.8	418.4	408.3	399.0	389.6	379.5	371.9	362.6
5°	526.8	508.3	487.0	466.7	446.4	425.2	403.2	383.7	363.4	344.8	326.9
7.5°	603.9	567.6	538.8	502.3	469.3	436.3	405.7	374.4	345.6	318.5	293.1
10°	669.2	625.2	580.2	533.7	486.2	442.2	399.8	362.6	324.5	291.4	260.1
12.5°	722.6	666.6	611.6	553.2	499.8	443.8	391.4	346.4	301.6	264.2	232.1
15°	770.9	706.4	640.4	572.6	504.9	441.3	382.9	326.9	281.2	238.9	202.5
17.5°	809.8	736.1	661.6	585.3	512.4	437.9	371.9	313.4	260.1	216.0	180.4
20°	843.7	766.6	686.1	600.6	517.5	437.1	362.6	296.5	241.5	194.8	160.1
22.5°	875.0	797.9	711.5	620.1	525.2	436.3	354.1	283.7	225.3	178.8	144.0
25°	910.6	829.3	738.7	640.4	538.8	439.6	349.0	273.6	210.9	163.5	131.3
27.5°	950.5	864.9	770.9	665.8	556.6	446.4	347.3	262.6	198.2	149.1	121.1
30°	1006.3	907.3	803.0	691.2	572.6	454.0	345.6	255.9	185.5	138.0	111.0
32.5°	1055.4	948.7	838.7	717.5	590.4	461.7	344.8	246.5	173.7	127.0	103.3
35°	1107.2	986.8	869.1	742.9	605.7	470.2	343.9	239.7	162.6	116.1	95.8
37.5°	1152.0	1019.1	892.8	764.9	622.6	477.7	344.8	233.8	152.4	106.7	88.9
40°	1190.2	1052.0	919.1	785.3	640.4	489.6	345.6	227.9	142.3	98.2	83.0
42.5°	1224.0	1083.4	947.0	808.1	660.7	503.2	350.7	222.8	133.9	90.7	77.1
45°	1250.3	1112.2	977.5	840.3	693.8	525.2	360.0	219.4	125.4	83.8	72.0
47.5°	1277.4	1154.6	1029.2	891.1	742.1	559.9	376.1	218.5	118.5	78.8	67.8
50°	1314.6	1196.9	1074.9	942.8	786.1	595.5	395.5	219.4	110.2	73.7	63.5
52.5°	1341.8	1240.1	1134.2	1032.5	891.1	703.9	471.0	234.6	105.9	69.4	58.4
55°	1501.9	1484.0	1486.6	1503.5	1394.3	1197.7	787.8	338.9	124.6	78.8	57.6
57.5°	2117.7	2180.4	2216.8	2216.0	2035.5	1688.2	1058.0	435.4	139.0	91.5	68.6
60°	2927.5	2880.1	2813.2	2648.0	2408.2	1927.0	1183.3	468.4	120.3	72.8	62.7
62.5°	3643.3	3365.4	3119.0	2851.3	2537.0	2010.2	1208.8	465.9	105.1	55.0	44.0
65°	4089.6	3589.9	3191.8	2856.4	2486.2	1940.6	1143.5	427.8	88.9	44.9	36.4
67.5°	4196.4	3468.8	2905.5	2477.7	2077.0	1510.4	839.5	321.9	69.4	37.3	32.2
69°	3963.4	3083.3	2407.4	1922.0	1511.2	1002.1	519.3	203.3	53.4	33.9	29.6
70°	3645.8	2681.9	1960.9	1542.5	1119.0	703.9	363.4	143.1	43.2	31.3	27.2
72.5°	2345.6	1408.7	963.9	670.9	461.7	280.4	142.3	64.4	33.1	26.2	22.1
75°	909.7	520.9	377.8	287.2	224.5	155.9	86.4	41.6	28.0	22.1	16.9
77.5°	448.1	343.1	280.4	192.3	111.8	69.4	46.6	32.2	22.9	16.1	11.0
80°	354.1	235.4	140.6	87.3	66.1	49.9	35.5	26.2	16.9	10.2	7.7
82.5°	181.2	99.1	72.8	59.3	49.1	39.0	28.8	18.7	11.0	6.7	5.9
85°	56.8	41.6	37.3	36.4	33.9	28.0	20.3	11.8	6.7	4.2	4.2
87.5°	4.2	5.9	7.7	5.9	6.7	5.9	7.7	5.1	3.4	3.4	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152046

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.5
2.5°	355.8	345.6	336.3	330.4	319.4	315.1	310.9	309.2	301.6	303.2	296.5
5°	310.9	293.1	279.6	266.0	253.3	243.9	236.4	227.0	219.4	216.0	209.2
7.5°	270.3	247.4	229.5	215.1	199.9	188.1	177.9	171.1	164.4	157.5	154.2
10°	234.6	210.1	189.7	175.3	160.9	150.8	143.1	138.0	133.9	131.3	130.5
12.5°	201.6	177.9	159.3	146.5	135.5	130.5	127.0	124.6	123.6	122.8	122.8
15°	176.2	152.4	138.0	128.7	123.6	121.1	120.3	118.5	116.9	116.1	116.1
17.5°	152.4	134.7	124.6	119.5	116.9	115.2	113.5	111.8	110.2	109.2	109.2
20°	136.4	122.0	116.9	113.5	111.0	109.2	106.7	105.1	104.1	103.3	102.5
22.5°	123.6	114.4	111.0	108.4	105.1	102.5	100.8	99.1	97.4	96.6	95.8
25°	114.4	108.4	105.9	102.5	99.1	96.6	94.0	91.5	89.7	88.9	87.3
27.5°	107.6	103.3	100.0	95.8	92.3	89.7	87.3	84.7	83.0	81.3	80.5
30°	101.7	97.4	93.2	89.7	85.6	83.0	79.6	77.1	76.3	74.5	72.8
32.5°	95.8	91.5	87.3	83.0	78.8	75.4	73.7	70.3	68.6	67.8	66.1
35°	88.9	84.7	79.6	76.3	72.0	68.6	66.1	63.5	61.9	60.1	59.3
37.5°	83.0	77.9	72.8	68.6	65.2	61.9	59.3	56.8	55.0	53.4	52.5
40°	76.3	71.2	66.1	61.9	58.4	56.0	53.4	50.8	49.1	48.3	48.3
42.5°	70.3	64.4	59.3	56.0	53.4	49.9	47.5	44.9	44.0	43.2	44.0
45°	64.4	58.4	54.2	50.8	48.3	44.9	42.4	40.6	39.8	40.6	41.6
47.5°	59.3	53.4	49.1	46.6	44.0	41.6	39.0	37.3	37.3	39.0	40.6
50°	54.2	48.3	44.9	43.2	40.6	38.1	34.7	33.9	34.7	36.4	38.1
52.5°	49.1	42.4	39.8	39.0	36.4	33.9	31.3	30.5	31.3	33.1	32.2
55°	44.0	37.3	36.4	35.5	33.1	29.6	27.2	27.2	27.2	26.2	24.6
57.5°	42.4	33.1	32.2	31.3	28.8	25.4	23.7	22.1	21.1	18.7	17.8
60°	44.0	29.6	29.6	28.0	25.4	22.1	19.5	16.9	15.2	13.6	13.6
62.5°	35.5	27.2	26.2	24.6	21.1	17.8	15.2	12.7	11.8	11.0	11.0
65°	28.8	24.6	22.9	20.3	17.8	14.4	11.8	10.2	9.3	9.3	10.2
67.5°	26.2	22.1	19.5	16.9	14.4	11.0	9.3	8.5	8.5	9.3	9.3
69°	24.6	20.3	17.8	15.2	12.7	10.2	8.5	8.5	8.5	8.5	9.3
70°	22.9	19.5	16.9	14.4	11.0	8.5	7.7	7.7	8.5	8.5	9.3
72.5°	17.8	15.2	14.4	11.8	8.5	7.7	6.7	7.7	7.7	8.5	8.5
75°	13.6	11.0	11.0	9.3	6.7	5.9	5.9	6.7	6.7	7.7	7.7
77.5°	9.3	7.7	7.7	6.7	5.9	5.1	5.1	5.9	6.7	6.7	7.7
80°	6.7	5.9	5.1	5.9	5.1	4.2	5.1	5.9	5.9	6.7	6.7
82.5°	5.1	5.1	5.1	5.1	4.2	4.2	5.1	5.1	5.9	6.7	6.7
85°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.1	5.1	5.9	5.9
87.5°	2.6	2.6	2.6	3.4	3.4	4.2	4.2	4.2	4.2	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152046

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	390.5	390.5	390.5	390.5
2.5°	294.8	293.9	290.6	291.4
5°	206.7	201.6	205.0	204.1
7.5°	151.6	150.8	149.9	151.6
10°	129.6	129.6	128.7	129.6
12.5°	122.0	122.0	122.0	122.0
15°	116.1	116.1	115.2	115.2
17.5°	109.2	109.2	109.2	108.4
20°	102.5	101.7	101.7	101.7
22.5°	94.9	94.0	94.0	94.0
25°	87.3	86.4	86.4	86.4
27.5°	79.6	78.8	77.9	77.9
30°	72.0	71.2	70.3	70.3
32.5°	64.4	63.5	62.7	62.7
35°	57.6	57.6	56.8	56.0
37.5°	51.7	51.7	51.7	51.7
40°	47.5	48.3	48.3	48.3
42.5°	44.9	45.7	46.6	47.5
45°	43.2	44.9	45.7	45.7
47.5°	42.4	43.2	44.0	44.0
50°	39.0	38.1	38.1	38.1
52.5°	31.3	29.6	28.8	28.0
55°	22.9	22.1	20.3	20.3
57.5°	16.1	16.1	15.2	15.2
60°	12.7	12.7	11.8	12.7
62.5°	11.0	11.0	11.0	11.0
65°	10.2	10.2	10.2	10.2
67.5°	10.2	10.2	10.2	10.2
69°	9.3	9.3	9.3	9.3
70°	9.3	9.3	9.3	9.3
72.5°	8.5	8.5	8.5	8.5
75°	7.7	8.5	8.5	8.5
77.5°	7.7	7.7	7.7	7.7
80°	6.7	6.7	7.7	7.7
82.5°	6.7	6.7	6.7	6.7
85°	5.9	5.9	6.7	6.7
87.5°	5.1	5.1	5.9	5.9
90°	0.0	0.0	0.0	0.0

(END OF REPORT)