

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702592

Luminaire Tested: 340-6C-30-D010 / 340-EU4C-3040-9024-4LBW1LI-GFC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702592  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-30-D010 / 340-EU4C-3040-9024-4LBW1LI-GFC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C  
KIT.  
Light Source: 2400K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1780.0 lumens  
Efficiency: N/A  
Efficacy: 56.3 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74  
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')  
CIE Type: Direct

Input Watts (W): 31.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702592

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9024-4LBW1LI-GFC

### Luminous Intensity Polar Plot



TEST NUMBER: P702592

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9024-4LBW1LI-GFC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	100497
5°	90276
10°	77879
15°	49101
20°	35062
25°	26927
30°	21698
35°	18252
40°	16101
45°	13769
50°	11053
55°	8609
60°	6770
65°	5345
70°	4321
75°	3443
80°	2794
85°	2199

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13769 cd/sqm

TEST NUMBER: P702592

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9024-4LBW1LI-GFC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	145.0	8.1
10°-20°	286.3	16.1
20°-30°	283.6	15.9
30°-40°	282.6	15.9
40°-50°	269.7	15.2
50°-60°	201.3	11.3
60°-70°	136.5	7.7
70°-80°	89.0	5.0
80°-90°	54.1	3.0
90°-100°	28.2	1.6
100°-110°	3.8	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	714.9	40.2
0°-40°	997.5	56.0
0°-60°	1468.6	82.5
0°-90°	1748.1	98.2
90°-120°	32.0	1.8
90°-150°	32.0	1.8
90°-180°	32.0	1.8
0°-180°	1780.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1540	
5°	1542	145
15°	992	286
25°	611	284
35°	447	283
45°	352	270
55°	223	201
65°	136	136
75°	83	89
85°	49	43
90°	36	20
95°	26	19
105°	2	4
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702592

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9024-4LBW1LI-GFC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1540.4
2.5°	1542.5
5°	1542.5
7.5°	1530.3
10°	1457.5
12.5°	1232.8
15°	991.9
17.5°	856.3
20°	755.0
22.5°	674.1
25°	611.3
27.5°	558.7
30°	514.2
32.5°	475.7
35°	447.4
37.5°	425.1
40°	404.8
42.5°	382.6
45°	352.2
47.5°	319.8
50°	285.4
52.5°	253.0
55°	222.7
57.5°	196.4
60°	174.1
62.5°	153.8
65°	135.6
67.5°	121.5
70°	107.3
72.5°	95.1
75°	83.0
77.5°	72.9
80°	64.8
82.5°	56.7
85°	48.6
87.5°	42.5
90°	36.4
92.5°	32.4
95°	26.3
97.5°	20.2
100°	12.1
102.5°	6.1
105°	2.0
107.5°	0.0
110°	0.0

TEST NUMBER: P702592

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9024-4LBW1LI-GFC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)