

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148612

Luminaire Tested: **AVS-E02-LED-E-U-5XQ-7060**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148612
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E02-LED-E-U-5XQ-7060
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (42) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6526.8 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B3 - U0 - G2


Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P148612
 CATALOG NUMBER: AVS-E02-LED-E-U-5XQ-7060

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 6.2 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148612
CATALOG NUMBER: AVS-E02-LED-E-U-5XQ-7060

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical



REPORT NUMBER: P148612

CATALOG NUMBER: AVS-E02-LED-E-U-5XQ-7060

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3263.4	0.0	3263.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3263.4	0.0	3263.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	6526.8	0.0	6526.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.9	0.9
10°-20°	174.3	2.7
20°-30°	291.9	4.5
30°-40°	445.1	6.8
40°-50°	710.7	10.9
50°-60°	1092.7	16.7
60°-70°	1591.0	24.4
70°-80°	1792.2	27.5
80°-90°	370.0	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6526.8	100.0
0°-180°	6526.8	100.0



REPORT NUMBER: P148612


CATALOG NUMBER: AVS-E02-LED-E-U-5XQ-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	262.6	4.0			
FM	(30°-60°)	1124.2	17.2			
FH	(60°-80°)	1691.6	25.9			G1/1800
FVH	(80°-90°)	185.0	2.8			G2/225
BL	(0°-30°)	262.6	4.0	B1/500		
BM	(30°-60°)	1124.2	17.2	B2/2500		
BH	(60°-80°)	1691.6	25.9	B3/2500		G1/1800
BVH	(80°-90°)	185.0	2.8			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P148612

CATALOG NUMBER: AVS-E02-LED-E-U-5XQ-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	618.4	618.4	618.4	618.4	618.4	618.4	618.4	618.4	618.4	618.4	618.4
2.5°	619.5	619.8	619.6	619.3	619.4	619.3	618.9	618.8	617.5	618.2	619.3
5°	619.5	619.1	618.9	618.8	618.8	619.3	618.8	618.2	618.0	618.4	617.9
7.5°	619.1	618.4	618.0	617.9	618.0	618.2	617.7	617.0	617.5	617.0	616.4
10°	618.0	617.5	617.7	617.0	617.2	617.0	616.4	615.9	616.2	615.6	614.8
12.5°	618.4	617.5	617.4	617.0	616.9	616.7	615.9	614.9	615.1	614.8	614.0
15°	618.4	617.8	617.7	617.0	616.9	616.5	615.5	615.1	615.1	614.6	613.6
17.5°	618.7	618.4	618.4	617.5	617.2	617.0	615.9	615.3	615.9	614.8	614.1
20°	619.8	619.5	619.6	619.1	618.4	618.4	617.5	617.2	617.4	617.2	615.3
22.5°	621.8	621.8	622.2	622.0	621.9	622.0	621.3	621.3	621.5	621.5	619.9
25°	627.7	627.5	627.8	627.8	628.0	629.2	628.6	628.5	629.3	629.3	627.8
27.5°	638.5	638.2	638.5	639.0	639.8	641.2	640.9	641.5	642.9	642.5	641.1
30°	651.2	650.9	651.7	652.8	653.5	655.9	654.8	657.4	658.5	659.6	658.5
32.5°	669.6	669.6	671.3	671.9	673.5	675.9	676.2	678.2	679.8	681.6	680.3
35°	694.3	694.0	695.1	696.4	698.2	700.5	701.3	704.0	706.5	707.7	705.5
37.5°	731.9	730.1	732.3	733.0	734.5	735.0	737.4	740.9	743.4	743.1	741.6
40°	783.0	782.6	781.7	780.7	783.1	783.9	783.9	788.6	792.6	792.0	791.8
42.5°	842.4	840.8	839.8	839.9	841.2	841.6	846.8	850.4	853.3	853.9	853.3
45°	906.4	904.9	905.2	904.6	905.0	907.3	910.4	916.7	922.1	922.3	919.4
47.5°	975.1	970.4	974.1	968.8	972.0	973.8	981.5	990.7	1000.2	1002.0	999.5
50°	1045.0	1044.5	1044.0	1043.0	1044.6	1048.3	1057.7	1072.2	1081.5	1087.7	1083.5
52.5°	1121.2	1118.7	1117.4	1115.6	1117.3	1124.6	1137.8	1150.5	1167.0	1174.1	1168.4
55°	1195.4	1194.6	1190.1	1189.9	1193.2	1204.7	1219.0	1234.6	1252.5	1260.4	1258.3
57.5°	1271.7	1266.7	1265.4	1263.3	1269.8	1280.6	1298.2	1326.2	1344.9	1353.8	1348.6
60°	1346.3	1342.5	1339.6	1338.9	1343.3	1358.3	1383.7	1417.4	1440.5	1452.1	1443.9
62.5°	1426.3	1423.9	1420.5	1416.6	1425.9	1445.2	1476.7	1514.0	1548.1	1562.4	1549.9
65°	1525.8	1520.8	1517.1	1512.1	1519.8	1544.1	1583.6	1636.2	1681.8	1698.5	1689.6
67.5°	1630.9	1626.2	1626.5	1623.4	1637.2	1670.8	1721.9	1793.2	1854.3	1882.9	1866.1
70°	1722.5	1725.1	1725.8	1738.2	1761.9	1813.2	1897.9	2009.6	2102.5	2146.1	2128.1
71°	1695.5	1701.1	1709.8	1722.8	1763.5	1824.2	1940.0	2075.2	2186.1	2260.0	2235.2
72.5°	1618.9	1622.3	1626.7	1646.6	1692.5	1773.0	1892.1	2046.7	2189.2	2284.8	2256.1
75°	1508.0	1511.3	1512.8	1526.6	1568.6	1638.8	1747.8	1885.0	2010.7	2092.0	2084.0
77.5°	1340.7	1341.3	1353.3	1374.6	1421.7	1501.9	1616.8	1759.1	1877.3	1940.5	1900.3
80°	962.8	956.4	968.6	996.2	1054.3	1146.3	1264.0	1426.4	1557.6	1616.8	1554.5
82.5°	366.3	386.1	417.4	463.0	482.7	584.9	694.7	790.1	900.5	1024.0	993.1
85°	39.4	44.4	55.5	68.9	87.0	120.4	166.4	227.2	279.9	329.0	292.1
87.5°	14.7	15.0	16.8	19.4	19.7	20.5	21.9	25.5	23.8	20.5	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148612

CATALOG NUMBER: AVS-E02-LED-E-U-5XQ-7060

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	618.4	618.4	618.4	618.4	618.4	618.4	618.4	618.4
2.5°	618.4	618.5	618.4	618.5	618.5	617.8	618.0	617.7
5°	618.2	617.7	617.9	618.0	617.9	618.2	617.7	618.0
7.5°	617.4	616.4	616.7	616.7	616.4	616.9	616.5	616.4
10°	615.6	614.3	615.0	614.6	614.5	614.6	614.6	614.7
12.5°	614.1	613.3	613.5	613.3	613.1	613.7	613.5	613.6
15°	613.8	612.4	612.2	611.9	612.0	612.4	612.4	613.0
17.5°	613.5	611.7	611.6	611.2	611.4	612.1	612.2	611.9
20°	614.5	613.1	612.7	612.4	612.2	613.2	613.0	613.0
22.5°	619.3	617.5	617.4	616.0	615.5	616.0	615.6	615.8
25°	626.9	624.9	624.2	622.4	620.9	620.9	620.5	620.1
27.5°	640.8	637.7	637.1	635.4	633.6	634.0	633.0	632.7
30°	656.9	654.1	651.8	649.5	647.3	646.4	645.3	645.1
32.5°	677.9	674.8	671.9	669.2	666.1	665.0	662.9	661.9
35°	703.7	699.7	696.2	694.3	691.3	689.7	688.3	689.9
37.5°	739.8	734.9	733.2	730.9	728.9	726.5	727.0	726.4
40°	789.7	785.3	783.6	779.7	779.2	776.4	778.1	776.4
42.5°	851.5	843.3	842.1	839.0	837.9	836.5	837.1	836.0
45°	918.8	911.4	910.1	905.1	905.2	901.7	903.0	903.0
47.5°	994.3	986.5	980.3	976.7	975.2	973.1	974.3	974.1
50°	1072.3	1061.9	1054.8	1047.8	1044.8	1045.6	1043.2	1047.3
52.5°	1156.1	1140.5	1130.6	1123.9	1118.1	1119.3	1119.6	1120.8
55°	1242.8	1223.0	1208.6	1199.8	1194.6	1194.9	1196.5	1197.8
57.5°	1329.9	1305.2	1285.7	1272.7	1269.3	1270.9	1270.9	1270.7
60°	1420.5	1390.7	1365.6	1350.9	1347.8	1346.9	1353.6	1351.4
62.5°	1517.6	1481.9	1455.9	1437.1	1432.6	1435.6	1441.7	1440.3
65°	1646.4	1597.0	1563.4	1544.8	1537.3	1540.3	1548.4	1548.1
67.5°	1812.4	1743.3	1699.1	1675.1	1669.6	1673.4	1677.9	1682.1
70°	2060.7	1962.1	1898.9	1846.9	1824.8	1820.5	1824.9	1825.1
71°	2148.2	2034.7	1934.1	1870.8	1834.4	1819.0	1820.1	1812.4
72.5°	2144.6	2004.9	1887.0	1820.8	1770.2	1757.9	1751.9	1742.6
75°	2000.0	1874.2	1771.9	1699.7	1651.0	1636.5	1625.9	1625.3
77.5°	1813.9	1720.9	1608.3	1531.8	1472.4	1448.3	1437.5	1437.3
80°	1458.1	1319.1	1236.7	1190.7	1119.0	1098.2	1076.4	1068.2
82.5°	881.8	689.0	560.2	497.8	463.2	381.6	342.4	323.9
85°	205.4	145.9	100.5	66.0	47.6	37.8	29.0	25.7
87.5°	13.9	11.0	9.7	7.9	6.0	5.8	3.6	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)