

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702645

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9024-4LBW1LI-CQ

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702645  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9024-4LBW1LI-CQ  
Description: FARALLON 6" LED GLASS DOWNLIGHT CYLINDRICAL FROSTED, QUADRATE ETCHED GLASS KIT.  
Light Source: 2400K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2048.2 lumens  
Efficiency: N/A  
Efficacy: 50.7 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.54  
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702645

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9024-4LBW1LI-CQ

### Luminous Intensity Polar Plot



TEST NUMBER: P702645

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9024-4LBW1LI-CQ

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	110	105	102	98	107	103	100	97	98	96	93		94	92	90		90	89	87	85
2	102	95	89	84	99	93	87	83	89	84	81		85	82	78		82	79	76	74
3	95	86	79	73	92	84	78	72	81	75	71		78	73	70		75	71	68	66
4	88	78	71	65	86	77	70	64	74	68	63		72	67	62		69	65	61	59
5	83	72	64	58	81	71	63	58	68	62	57		66	61	57		64	60	56	54
6	78	66	59	53	76	65	58	53	63	57	52		62	56	52		60	55	51	49
7	73	62	54	49	71	61	54	49	59	53	48		58	52	48		56	51	47	46
8	69	58	50	45	68	57	50	45	55	49	45		54	48	44		53	48	44	42
9	66	54	47	42	64	53	47	42	52	46	42		51	45	41		50	45	41	40
10	62	51	44	40	61	50	44	39	49	43	39		48	43	39		47	42	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	204366
5°	146806
10°	93145
15°	74570
20°	51302
25°	28438
30°	22302
35°	18729
40°	16455
45°	13648
50°	11204
55°	8876
60°	7065
65°	5561
70°	4430
75°	3572
80°	2889
85°	2380

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13648 cd/sqm

TEST NUMBER: P702645

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9024-4LBW1LI-CQ

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	214.4	10.5
10°-20°	411.4	20.1
20°-30°	319.3	15.6
30°-40°	290.5	14.2
40°-50°	269.5	13.2
50°-60°	207.4	10.1
60°-70°	142.0	6.9
70°-80°	92.2	4.5
80°-90°	57.4	2.8
90°-100°	33.3	1.6
100°-110°	10.5	0.5
110°-120°	0.3	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	945.1	46.1
0°-40°	1235.7	60.3
0°-60°	1712.6	83.6
0°-90°	2004.1	97.8
90°-120°	44.1	2.2
90°-150°	44.1	2.2
90°-180°	44.0	2.1
0°-180°	2048.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3132	
5°	2508	214
15°	1506	411
25°	646	319
35°	459	291
45°	349	270
55°	230	207
65°	141	142
75°	86	92
85°	53	46
90°	38	22
95°	31	23
105°	10	11
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702645

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9024-4LBW1LI-CQ

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3132.5
2.5°	2993.8
5°	2508.4
7.5°	2039.7
10°	1743.2
12.5°	1597.3
15°	1506.4
17.5°	1389.3
20°	1104.7
22.5°	772.4
25°	645.6
27.5°	583.4
30°	528.5
32.5°	485.4
35°	459.1
37.5°	442.4
40°	413.7
42.5°	380.2
45°	349.1
47.5°	318.0
50°	289.3
52.5°	258.2
55°	229.6
57.5°	205.6
60°	181.7
62.5°	160.2
65°	141.1
67.5°	126.7
70°	110.0
72.5°	98.0
75°	86.1
77.5°	76.5
80°	67.0
82.5°	59.8
85°	52.6
87.5°	45.4
90°	38.3
92.5°	35.9
95°	31.1
97.5°	26.3
100°	19.1
102.5°	14.3
105°	9.6
107.5°	4.8
110°	2.4

TEST NUMBER: P702645

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9024-4LBW1LI-CQ

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)