

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152028

Luminaire Tested: **AVS-E02-LED-E-U-SL4-HSS-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P152028  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: AVS-E02-LED-E-U-SL4-HSS-8030  
Description: VISION SITE SMALL LED LUMINAIRE  
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD  
Light Source: (42) 3000K CCT, 80 CRI LEDs  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3434.7 lumens  
Efficiency: N/A  
Efficacy: 65.9 lumens/watt  
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')  
IES Classification: Type IV - Short - Semi-Cutoff  
BUG Rating: B0 - U0 - G1  
  
Input Watts (W): 52.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P152028  
 CATALOG NUMBER: AVS-E02-LED-E-U-SL4-HSS-8030

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 7.7 fc  
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P152028  
CATALOG NUMBER: AVS-E02-LED-E-U-SL4-HSS-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral    - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P152028

CATALOG NUMBER: AVS-E02-LED-E-U-SL4-HSS-8030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	102.3	0.0	102.3
	% Fixture	3.0	0.0	3.0
<b>Street Side</b>	Lumens	3332.4	0.0	3332.4
	% Fixture	97.0	0.0	97.0
<b>Total</b>	Lumens	3434.7	0.0	3434.7
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.7	0.8
10°-20°	91.9	2.7
20°-30°	175.9	5.1
30°-40°	292.6	8.5
40°-50°	395.9	11.5
50°-60°	619.2	18.0
60°-70°	1273.0	37.1
70°-80°	512.2	14.9
80°-90°	47.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3434.7	100.0
0°-180°	3434.7	100.0



REPORT NUMBER: P152028


CATALOG NUMBER: AVS-E02-LED-E-U-SL4-HSS-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	255.6	7.4			
FM	(30°-60°)	1260.9	36.7			
FH	(60°-80°)	1770.3	51.5			G1/1800
FVH	(80°-90°)	45.6	1.3			G1/100
BL	(0°-30°)	38.9	1.1	B0/110		
BM	(30°-60°)	46.7	1.4	B0/220		
BH	(60°-80°)	14.9	0.4	B0/110		G0/110
BVH	(80°-90°)	1.8	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G1**

Type IV Short





REPORT NUMBER: P152028  
 CATALOG NUMBER: AVS-E02-LED-E-U-SL4-HSS-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4
2.5°	346.0	342.1	337.6	337.6	332.0	332.0	328.6	319.6	318.4	313.4	308.3
5°	441.7	438.3	432.6	427.7	423.1	415.2	409.6	399.0	387.2	375.9	365.7
7.5°	535.1	533.4	523.3	521.6	514.3	501.3	490.1	474.3	454.1	438.3	419.8
10°	621.8	617.8	615.5	606.0	595.3	581.2	563.8	544.7	521.0	496.3	469.8
12.5°	690.4	688.1	678.0	674.1	662.8	648.7	626.8	602.1	578.4	546.3	515.4
15°	741.6	737.6	730.9	724.7	711.2	698.9	678.5	651.6	622.9	588.0	550.9
17.5°	784.4	777.0	775.3	765.8	751.7	737.1	714.6	689.8	656.1	621.1	580.6
20°	841.8	831.6	828.2	814.2	797.8	777.6	751.7	720.7	685.3	647.0	605.4
22.5°	909.2	902.0	894.6	882.3	861.5	832.7	795.0	761.2	716.3	674.1	629.0
25°	1004.9	998.8	986.9	970.1	944.1	909.8	864.2	814.7	761.9	707.9	654.9
27.5°	1097.7	1092.1	1083.7	1070.8	1041.5	1003.8	947.6	884.5	817.5	752.2	693.8
30°	1185.0	1179.9	1171.5	1158.5	1132.6	1095.5	1031.9	964.4	881.1	805.2	734.8
32.5°	1279.0	1277.2	1267.7	1249.1	1226.6	1176.5	1107.4	1034.7	950.4	862.6	780.4
35°	1385.3	1372.3	1363.3	1344.8	1306.5	1253.1	1172.0	1092.6	1003.8	913.8	822.1
37.5°	1475.3	1462.9	1451.7	1428.1	1381.3	1313.3	1221.6	1134.3	1042.6	950.9	857.5
40°	1541.1	1534.9	1521.5	1490.5	1438.1	1357.1	1258.1	1163.0	1070.8	978.4	886.2
42.5°	1590.1	1580.5	1565.3	1533.3	1471.4	1379.1	1272.7	1174.8	1083.7	995.3	904.8
45°	1608.1	1600.2	1586.1	1551.3	1484.2	1385.3	1272.1	1171.5	1084.2	1000.4	917.1
47.5°	1597.4	1589.5	1577.1	1544.5	1478.7	1377.9	1262.1	1161.9	1078.7	1002.1	928.4
50°	1562.0	1557.4	1547.9	1520.3	1461.2	1363.9	1253.1	1156.8	1077.5	1010.6	944.1
52.5°	1558.5	1555.8	1543.9	1516.4	1456.2	1359.4	1251.9	1159.7	1087.0	1021.2	955.4
55°	1904.6	1864.7	1775.2	1699.3	1574.3	1425.8	1308.7	1205.2	1127.6	1063.4	1017.3
57.5°	2706.9	2647.4	2529.7	2385.1	2098.1	1816.3	1590.7	1427.5	1347.0	1317.7	1335.2
60°	3082.8	3072.1	3053.6	2984.9	2838.0	2595.5	2325.5	2033.5	1916.4	1906.3	1941.8
62.5°	3261.1	3254.4	3260.1	3251.6	3206.0	3135.1	3057.5	2931.5	2815.5	2740.7	2582.1
65°	3343.3	3347.9	3379.9	3405.2	3410.9	3429.4	3486.2	3643.2	3758.0	3565.0	3124.5
67.5°	3134.6	3161.0	3234.7	3327.0	3435.0	3539.7	3708.5	4039.4	4275.1	4048.4	3422.7
69°	2595.0	2608.0	2788.0	2961.9	3225.7	3410.3	3655.0	4088.8	4353.9	4097.8	3399.1
70°	2043.0	2054.8	2247.9	2484.1	2930.4	3167.8	3488.0	4005.0	4280.2	4032.0	3277.5
72.5°	921.7	904.8	972.8	1099.5	1584.5	1961.5	2521.2	3244.9	3531.3	3230.3	2452.1
75°	643.7	636.4	643.7	644.2	719.7	928.4	1171.5	1758.9	2175.2	1877.0	1171.5
77.5°	498.5	493.5	488.4	482.8	491.8	550.9	574.5	624.0	810.3	766.3	446.7
80°	394.4	389.9	402.3	398.3	398.3	405.1	400.6	382.1	347.2	321.9	288.1
82.5°	183.4	184.6	184.6	200.3	241.3	281.9	294.8	276.3	245.3	208.7	168.2
85°	17.4	19.7	33.2	51.2	101.9	114.8	115.3	95.6	95.6	75.4	60.7
87.5°	0.0	0.5	0.5	0.5	5.1	14.1	11.8	3.4	1.7	1.7	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152028  
 CATALOG NUMBER: AVS-E02-LED-E-U-SL4-HSS-8030

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4
2.5°	299.4	297.6	290.9	284.1	277.9	271.2	265.0	258.9	252.0	247.0	240.8
5°	349.9	337.6	323.5	310.1	296.5	282.5	267.9	254.9	241.3	229.0	217.2
7.5°	401.1	377.0	357.8	333.7	311.7	289.7	269.5	248.7	229.5	211.6	194.7
10°	444.5	415.2	385.4	354.5	323.0	293.7	265.6	240.8	215.5	193.6	172.7
12.5°	480.0	442.8	406.2	367.5	332.0	294.8	260.0	230.2	200.3	175.5	154.2
15°	512.0	469.2	425.4	380.3	335.3	293.2	254.3	217.2	186.8	158.7	134.5
17.5°	537.9	488.9	439.5	388.8	340.4	290.9	247.0	208.2	172.7	143.5	119.9
20°	560.4	509.2	455.8	399.0	343.8	290.4	240.8	196.9	160.3	129.4	106.3
22.5°	581.2	530.1	472.6	411.9	348.8	289.7	235.2	188.5	149.6	118.8	95.6
25°	604.9	550.9	490.7	425.4	357.8	292.0	231.8	181.8	140.1	108.6	87.3
27.5°	631.3	574.5	512.0	442.3	369.6	296.5	230.7	174.4	131.7	99.1	80.4
30°	668.4	602.6	533.4	459.2	380.3	301.6	229.5	169.9	123.2	91.7	73.7
32.5°	701.0	630.2	557.0	476.6	392.1	306.6	229.0	163.7	115.3	84.4	68.6
35°	735.4	655.5	577.3	493.5	402.3	312.2	228.4	159.3	108.0	77.1	63.6
37.5°	765.2	676.9	593.1	508.1	413.6	317.3	229.0	155.3	101.2	70.9	59.1
40°	790.6	698.9	610.5	521.6	425.4	325.2	229.5	151.4	94.5	65.3	55.1
42.5°	813.1	719.7	629.0	536.8	438.9	334.2	233.0	148.0	88.9	60.2	51.2
45°	830.5	738.8	649.3	558.1	460.8	348.8	239.2	145.7	83.3	55.8	47.9
47.5°	848.5	766.9	683.6	591.9	492.8	371.9	249.8	145.2	78.8	52.3	45.0
50°	873.3	795.0	714.0	626.2	522.2	395.5	262.8	145.7	73.2	48.9	42.2
52.5°	891.3	823.7	753.4	685.9	591.9	467.6	312.8	155.9	70.4	46.1	38.9
55°	997.6	985.8	987.5	998.8	926.1	795.6	523.3	225.1	82.7	52.3	38.2
57.5°	1406.6	1448.3	1472.4	1471.9	1352.1	1121.3	702.8	289.2	92.2	60.7	45.6
60°	1944.6	1913.1	1868.6	1758.9	1599.7	1280.1	786.0	311.2	79.9	48.4	41.7
62.5°	2420.0	2235.4	2071.7	1893.9	1685.2	1335.2	802.9	309.4	69.7	36.6	29.2
65°	2716.5	2384.6	2120.1	1897.3	1651.4	1289.0	759.6	284.1	59.1	29.8	24.1
67.5°	2787.5	2304.1	1929.9	1645.8	1379.7	1003.2	557.6	213.8	46.1	24.8	21.3
69°	2632.6	2048.1	1599.1	1276.7	1003.8	665.6	344.9	135.0	35.4	22.5	19.7
70°	2421.7	1781.3	1302.6	1024.6	743.3	467.6	241.3	95.1	28.7	20.8	18.0
72.5°	1558.0	935.8	640.3	445.6	306.6	186.2	94.5	42.8	22.0	17.4	14.6
75°	604.2	346.0	251.0	190.8	149.1	103.5	57.4	27.6	18.5	14.6	11.3
77.5°	297.6	227.9	186.2	127.8	74.3	46.1	31.0	21.3	15.2	10.7	7.4
80°	235.2	156.4	93.4	57.9	43.9	33.2	23.6	17.4	11.3	6.7	5.1
82.5°	120.4	65.8	48.4	39.4	32.6	25.9	19.2	12.3	7.4	4.5	3.9
85°	37.7	27.6	24.8	24.1	22.5	18.5	13.5	7.9	4.5	2.8	2.8
87.5°	2.8	3.9	5.1	3.9	4.5	3.9	5.1	3.4	2.3	2.3	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P152028

CATALOG NUMBER: AVS-E02-LED-E-U-SL4-HSS-8030

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4
2.5°	236.3	229.5	223.4	219.5	212.1	209.3	206.5	205.4	200.3	201.5	196.9
5°	206.5	194.7	185.7	176.7	168.2	162.1	157.0	150.8	145.7	143.5	139.0
7.5°	179.5	164.2	152.4	142.9	132.7	124.9	118.1	113.7	109.1	104.7	102.4
10°	155.9	139.6	126.0	116.5	106.9	100.1	95.1	91.7	88.9	87.3	86.6
12.5°	133.9	118.1	105.8	97.3	90.1	86.6	84.4	82.7	82.2	81.6	81.6
15°	117.0	101.2	91.7	85.5	82.2	80.4	79.9	78.8	77.6	77.1	77.1
17.5°	101.2	89.4	82.7	79.4	77.6	76.5	75.4	74.3	73.2	72.5	72.5
20°	90.6	81.0	77.6	75.4	73.7	72.5	70.9	69.7	69.2	68.6	68.1
22.5°	82.2	76.0	73.7	72.0	69.7	68.1	66.9	65.8	64.7	64.1	63.6
25°	76.0	72.0	70.4	68.1	65.8	64.1	62.5	60.7	59.7	59.1	57.9
27.5°	71.5	68.6	66.4	63.6	61.3	59.7	57.9	56.3	55.1	54.0	53.5
30°	67.6	64.7	61.9	59.7	56.8	55.1	52.8	51.2	50.7	49.5	48.4
32.5°	63.6	60.7	57.9	55.1	52.3	50.1	48.9	46.7	45.6	45.0	43.9
35°	59.1	56.3	52.8	50.7	47.9	45.6	43.9	42.2	41.0	40.0	39.4
37.5°	55.1	51.8	48.4	45.6	43.3	41.0	39.4	37.7	36.6	35.4	34.9
40°	50.7	47.3	43.9	41.0	38.9	37.1	35.4	33.8	32.6	32.0	32.0
42.5°	46.7	42.8	39.4	37.1	35.4	33.2	31.5	29.8	29.2	28.7	29.2
45°	42.8	38.9	36.0	33.8	32.0	29.8	28.1	27.0	26.4	27.0	27.6
47.5°	39.4	35.4	32.6	31.0	29.2	27.6	25.9	24.8	24.8	25.9	27.0
50°	36.0	32.0	29.8	28.7	27.0	25.3	23.1	22.5	23.1	24.1	25.3
52.5°	32.6	28.1	26.4	25.9	24.1	22.5	20.8	20.2	20.8	22.0	21.3
55°	29.2	24.8	24.1	23.6	22.0	19.7	18.0	18.0	18.0	17.4	16.3
57.5°	28.1	22.0	21.3	20.8	19.2	16.9	15.8	14.6	14.1	12.3	11.8
60°	29.2	19.7	19.7	18.5	16.9	14.6	13.0	11.3	10.2	9.0	9.0
62.5°	23.6	18.0	17.4	16.3	14.1	11.8	10.2	8.4	7.9	7.4	7.4
65°	19.2	16.3	15.2	13.5	11.8	9.5	7.9	6.7	6.2	6.2	6.7
67.5°	17.4	14.6	13.0	11.3	9.5	7.4	6.2	5.6	5.6	6.2	6.2
69°	16.3	13.5	11.8	10.2	8.4	6.7	5.6	5.6	5.6	5.6	6.2
70°	15.2	13.0	11.3	9.5	7.4	5.6	5.1	5.1	5.6	5.6	6.2
72.5°	11.8	10.2	9.5	7.9	5.6	5.1	4.5	5.1	5.1	5.6	5.6
75°	9.0	7.4	7.4	6.2	4.5	3.9	3.9	4.5	4.5	5.1	5.1
77.5°	6.2	5.1	5.1	4.5	3.9	3.4	3.4	3.9	4.5	4.5	5.1
80°	4.5	3.9	3.4	3.9	3.4	2.8	3.4	3.9	3.9	4.5	4.5
82.5°	3.4	3.4	3.4	3.4	2.8	2.8	3.4	3.4	3.9	4.5	4.5
85°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.4	3.4	3.9	3.9
87.5°	1.7	1.7	1.7	2.3	2.3	2.8	2.8	2.8	2.8	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152028

CATALOG NUMBER: AVS-E02-LED-E-U-SL4-HSS-8030

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	259.4	259.4	259.4	259.4
2.5°	195.9	195.2	193.0	193.6
5°	137.3	133.9	136.2	135.6
7.5°	100.7	100.1	99.6	100.7
10°	86.1	86.1	85.5	86.1
12.5°	81.0	81.0	81.0	81.0
15°	77.1	77.1	76.5	76.5
17.5°	72.5	72.5	72.5	72.0
20°	68.1	67.6	67.6	67.6
22.5°	63.0	62.5	62.5	62.5
25°	57.9	57.4	57.4	57.4
27.5°	52.8	52.3	51.8	51.8
30°	47.9	47.3	46.7	46.7
32.5°	42.8	42.2	41.7	41.7
35°	38.2	38.2	37.7	37.1
37.5°	34.3	34.3	34.3	34.3
40°	31.5	32.0	32.0	32.0
42.5°	29.8	30.4	31.0	31.5
45°	28.7	29.8	30.4	30.4
47.5°	28.1	28.7	29.2	29.2
50°	25.9	25.3	25.3	25.3
52.5°	20.8	19.7	19.2	18.5
55°	15.2	14.6	13.5	13.5
57.5°	10.7	10.7	10.2	10.2
60°	8.4	8.4	7.9	8.4
62.5°	7.4	7.4	7.4	7.4
65°	6.7	6.7	6.7	6.7
67.5°	6.7	6.7	6.7	6.7
69°	6.2	6.2	6.2	6.2
70°	6.2	6.2	6.2	6.2
72.5°	5.6	5.6	5.6	5.6
75°	5.1	5.6	5.6	5.6
77.5°	5.1	5.1	5.1	5.1
80°	4.5	4.5	5.1	5.1
82.5°	4.5	4.5	4.5	4.5
85°	3.9	3.9	4.5	4.5
87.5°	3.4	3.4	3.9	3.9
90°	0.0	0.0	0.0	0.0

(END OF REPORT)