

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702650

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-CC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702650  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-CC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2493.3 lumens  
Efficiency: N/A  
Efficacy: 61.7 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.71  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702650

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-CC

### Luminous Intensity Polar Plot



TEST NUMBER: P702650

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-CC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	61		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	54	50	69	60	54	50	59	54	50		58	53	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	283190
5°	231225
10°	169440
15°	146316
20°	125303
25°	115831
30°	93368
35°	60617
40°	45836
45°	25576
50°	14900
55°	9896
60°	6733
65°	4199
70°	3624
75°	2748
80°	2029
85°	2021

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25576 cd/sqm

TEST NUMBER: P702650

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-CC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	305.3	12.2
10°-20°	606.2	24.3
20°-30°	716.6	28.7
30°-40°	501.5	20.1
40°-50°	234.0	9.4
50°-60°	81.2	3.3
60°-70°	30.8	1.2
70°-80°	12.5	0.5
80°-90°	2.9	0.1
90°-100°	1.8	0.1
100°-110°	1.1	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1628.1	65.3
0°-40°	2129.6	85.4
0°-60°	2444.8	98.1
0°-90°	2491.1	99.9
90°-120°	2.9	0.1
90°-150°	2.9	0.1
90°-180°	3.0	0.1
0°-180°	2493.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4341	
5°	3531	305
15°	2166	606
25°	1609	717
35°	761	501
45°	277	234
55°	87	81
65°	27	31
75°	11	13
85°	3	3
90°	0	0
95°	0	1
105°	0	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702650

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-CC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4340.7
2.5°	4126.0
5°	3530.7
7.5°	2943.6
10°	2557.7
12.5°	2329.4
15°	2166.3
17.5°	2019.5
20°	1804.8
22.5°	1644.4
25°	1609.1
27.5°	1473.2
30°	1239.4
32.5°	975.8
35°	761.1
37.5°	622.4
40°	538.2
42.5°	418.6
45°	277.2
47.5°	193.0
50°	146.8
52.5°	111.4
55°	87.0
57.5°	68.0
60°	51.6
62.5°	38.1
65°	27.2
67.5°	24.5
70°	19.0
72.5°	16.3
75°	10.9
77.5°	8.2
80°	5.4
82.5°	2.7
85°	2.7
87.5°	2.7
90°	0.0
92.5°	0.0
95°	0.0
97.5°	2.7
100°	2.7
102.5°	2.7
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P702650

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-CC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)