

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152048

Luminaire Tested: **AVS-E04-LED-E-U-SL4-HSS-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152048
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E04-LED-E-U-SL4-HSS-8030
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (84) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6869.4 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B0 - U0 - G2


Input Watts (W): 97.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P152048
 CATALOG NUMBER: AVS-E04-LED-E-U-SL4-HSS-8030

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 15.4 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P152048
CATALOG NUMBER: AVS-E04-LED-E-U-SL4-HSS-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical



REPORT NUMBER: P152048

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-HSS-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	204.6	0.0	204.6
	% Fixture	3.0	0.0	3.0
Street Side	Lumens	6664.9	0.0	6664.9
	% Fixture	97.0	0.0	97.0
Total	Lumens	6869.4	0.0	6869.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.3	0.8
10°-20°	183.8	2.7
20°-30°	351.9	5.1
30°-40°	585.2	8.5
40°-50°	791.8	11.5
50°-60°	1238.3	18.0
60°-70°	2545.9	37.1
70°-80°	1024.4	14.9
80°-90°	94.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6869.4	100.0
0°-180°	6869.4	100.0

Coefficient of Utilization



REPORT NUMBER: P152048


CATALOG NUMBER: AVS-E04-LED-E-U-SL4-HSS-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	511.2	7.4			
FM	(30°-60°)	2521.9	36.7			
FH	(60°-80°)	3540.5	51.5			G2/5000
FVH	(80°-90°)	91.2	1.3			G1/100
BL	(0°-30°)	77.8	1.1	B0/110		
BM	(30°-60°)	93.4	1.4	B0/220		
BH	(60°-80°)	29.8	0.4	B0/110		G0/110
BVH	(80°-90°)	3.5	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type IV Short





REPORT NUMBER: P152048

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-HSS-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8
2.5°	692.1	684.1	675.2	675.2	663.9	663.9	657.2	639.2	636.9	626.8	616.7
5°	883.4	876.6	865.4	855.2	846.2	830.5	819.3	797.8	774.2	751.7	731.5
7.5°	1070.2	1066.8	1046.5	1043.2	1028.5	1002.7	980.1	948.6	908.1	876.6	839.5
10°	1243.5	1235.6	1231.1	1212.0	1190.6	1162.5	1127.6	1089.3	1042.1	992.5	939.7
12.5°	1380.7	1376.3	1356.1	1348.2	1325.6	1297.5	1253.6	1204.1	1156.8	1092.6	1030.8
15°	1483.2	1475.3	1461.8	1449.4	1422.4	1397.6	1357.1	1303.1	1245.7	1176.0	1101.7
17.5°	1568.7	1554.1	1550.7	1531.6	1503.4	1474.2	1429.1	1379.7	1312.1	1242.4	1161.3
20°	1683.5	1663.2	1656.5	1628.3	1595.8	1555.2	1503.4	1441.6	1370.7	1294.1	1210.9
22.5°	1818.5	1803.9	1789.2	1764.5	1722.9	1665.5	1590.1	1522.6	1432.5	1348.2	1258.1
25°	2009.8	1997.4	1973.8	1940.1	1888.3	1819.7	1728.5	1629.4	1523.7	1415.6	1309.8
27.5°	2195.5	2184.2	2167.4	2141.5	2083.0	2007.6	1895.0	1769.0	1635.1	1504.6	1387.6
30°	2369.9	2359.8	2342.9	2317.0	2265.3	2191.0	2063.8	1928.8	1762.3	1610.4	1469.6
32.5°	2557.8	2554.5	2535.3	2498.2	2453.2	2353.1	2214.6	2069.4	1900.6	1725.1	1560.8
35°	2770.6	2744.7	2726.6	2689.5	2613.0	2506.1	2344.0	2185.4	2007.6	1827.6	1644.1
37.5°	2950.6	2925.8	2903.3	2856.1	2762.7	2626.5	2443.1	2268.6	2085.2	1901.8	1715.0
40°	3082.3	3069.8	3042.9	2980.9	2876.3	2714.3	2516.3	2326.0	2141.5	1956.9	1772.3
42.5°	3180.2	3161.0	3130.7	3066.5	2942.7	2758.1	2545.5	2349.6	2167.4	1990.7	1809.5
45°	3216.2	3200.4	3172.3	3102.5	2968.6	2770.6	2544.4	2342.9	2168.5	2000.8	1834.3
47.5°	3194.8	3179.1	3154.3	3089.0	2957.3	2756.0	2524.1	2323.8	2157.2	2004.2	1856.8
50°	3123.9	3114.9	3095.8	3040.6	2922.5	2727.8	2506.1	2313.7	2155.0	2021.0	1888.3
52.5°	3117.1	3111.5	3087.9	3032.7	2912.3	2718.8	2503.8	2319.3	2174.1	2042.5	1910.8
55°	3809.2	3729.3	3550.4	3398.4	3148.6	2851.6	2617.5	2410.5	2255.1	2126.8	2034.6
57.5°	5413.9	5294.6	5059.5	4770.3	4196.4	3632.5	3181.2	2854.9	2694.0	2635.5	2670.4
60°	6165.6	6144.2	6107.2	5969.8	5676.2	5191.1	4651.0	4066.9	3832.8	3812.5	3883.5
62.5°	6522.4	6508.8	6520.1	6503.2	6412.1	6270.3	6115.0	5862.9	5631.1	5481.5	5164.1
65°	6686.6	6695.6	6759.8	6810.5	6821.7	6858.9	6972.5	7286.4	7516.1	7130.1	6248.9
67.5°	6269.1	6322.1	6469.4	6654.0	6870.1	7079.4	7417.0	8078.7	8550.2	8096.7	6845.3
69°	5189.9	5215.9	5576.0	5923.7	6451.5	6820.6	7310.1	8177.7	8707.8	8195.8	6798.0
70°	4086.0	4109.6	4495.6	4968.3	5860.6	6335.5	6975.9	8010.1	8560.3	8064.0	6555.0
72.5°	1843.3	1809.5	1945.7	2198.9	3168.9	3922.9	5042.6	6489.7	7062.5	6460.5	4904.1
75°	1287.4	1272.7	1287.4	1288.5	1439.3	1856.8	2342.9	3517.7	4350.5	3754.1	2342.9
77.5°	997.0	986.9	976.8	965.5	983.5	1101.7	1148.9	1248.0	1620.4	1532.6	893.5
80°	788.8	779.9	804.6	796.7	796.7	810.3	801.2	764.0	694.3	643.7	576.2
82.5°	366.8	369.1	369.1	400.6	482.8	563.8	589.6	552.5	490.7	417.5	336.5
85°	34.9	39.4	66.4	102.4	203.7	229.5	230.7	191.3	191.3	150.8	121.6
87.5°	0.0	1.1	1.1	1.1	10.2	28.1	23.6	6.7	3.4	3.4	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152048
 CATALOG NUMBER: AVS-E04-LED-E-U-SL4-HSS-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8
2.5°	598.7	595.3	581.8	568.3	556.0	542.4	530.1	517.6	504.1	494.0	481.7
5°	700.0	675.2	647.0	620.1	593.1	564.9	535.6	509.7	482.8	458.0	434.4
7.5°	802.4	754.0	715.8	667.4	623.4	579.6	539.1	497.4	459.2	423.1	389.3
10°	889.0	830.5	770.9	708.9	645.9	587.5	531.2	481.7	431.0	387.2	345.5
12.5°	959.9	885.6	812.4	734.8	663.9	589.6	519.9	460.2	400.6	351.1	308.3
15°	1024.0	938.5	850.8	760.7	670.7	586.3	508.6	434.4	373.6	317.3	268.9
17.5°	1075.9	977.9	878.9	777.6	680.8	581.8	494.0	416.4	345.5	286.9	239.7
20°	1120.8	1018.4	911.5	797.8	687.6	580.6	481.7	393.9	320.7	258.9	212.6
22.5°	1162.5	1060.1	945.3	823.7	697.7	579.6	470.4	377.0	299.4	237.4	191.3
25°	1209.7	1101.7	981.2	850.8	715.8	584.0	463.6	363.5	280.2	217.2	174.4
27.5°	1262.6	1148.9	1024.0	884.5	739.4	593.1	461.3	348.8	263.3	198.0	160.9
30°	1336.9	1205.2	1066.8	918.2	760.7	603.2	459.2	339.9	246.4	183.4	147.5
32.5°	1402.2	1260.3	1114.1	953.2	784.4	613.3	458.0	327.5	230.7	168.8	137.3
35°	1470.8	1311.0	1154.6	986.9	804.6	624.6	456.9	318.4	216.1	154.2	127.2
37.5°	1530.5	1353.8	1186.1	1016.2	827.2	634.7	458.0	310.6	202.6	141.8	118.1
40°	1581.0	1397.6	1220.9	1043.2	850.8	650.5	459.2	302.7	189.0	130.6	110.3
42.5°	1626.1	1439.3	1258.1	1073.6	877.7	668.4	465.9	296.0	177.8	120.4	102.4
45°	1660.9	1477.5	1298.7	1116.3	921.7	697.7	478.2	291.5	166.5	111.4	95.6
47.5°	1697.0	1533.8	1367.3	1183.8	985.8	743.8	499.7	290.4	157.5	104.7	90.1
50°	1746.5	1590.1	1428.1	1252.4	1044.2	791.1	525.5	291.5	146.3	97.9	84.4
52.5°	1782.5	1647.5	1506.8	1371.8	1183.8	935.1	625.7	311.7	140.6	92.2	77.6
55°	1995.2	1971.6	1974.9	1997.4	1852.2	1591.2	1046.5	450.2	165.4	104.7	76.5
57.5°	2813.3	2896.6	2945.0	2943.8	2704.1	2242.8	1405.5	578.4	184.6	121.6	91.2
60°	3889.1	3826.1	3737.2	3517.7	3199.3	2560.1	1572.1	622.3	159.8	96.8	83.3
62.5°	4840.0	4470.9	4143.4	3787.9	3370.4	2670.4	1605.8	619.0	139.6	73.2	58.5
65°	5433.1	4769.1	4240.2	3794.6	3302.8	2578.1	1519.2	568.3	118.1	59.7	48.4
67.5°	5574.8	4608.2	3859.9	3291.6	2759.3	2006.4	1115.2	427.7	92.2	49.5	42.8
69°	5265.4	4096.2	3198.1	2553.4	2007.6	1331.3	689.8	270.1	70.9	45.0	39.4
70°	4843.4	3562.8	2605.1	2049.2	1486.5	935.1	482.8	190.2	57.4	41.7	36.0
72.5°	3116.1	1871.4	1280.6	891.3	613.3	372.4	189.0	85.5	43.9	34.9	29.2
75°	1208.6	692.1	501.9	381.5	298.2	207.0	114.8	55.1	37.1	29.2	22.5
77.5°	595.3	455.8	372.4	255.4	148.5	92.2	61.9	42.8	30.4	21.3	14.6
80°	470.4	312.8	186.8	116.0	87.8	66.4	47.3	34.9	22.5	13.5	10.2
82.5°	240.8	131.7	96.8	78.8	65.3	51.8	38.2	24.8	14.6	9.0	7.9
85°	75.4	55.1	49.5	48.4	45.0	37.1	27.0	15.8	9.0	5.6	5.6
87.5°	5.6	7.9	10.2	7.9	9.0	7.9	10.2	6.7	4.5	4.5	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152048

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-HSS-8030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8
2.5°	472.6	459.2	446.7	438.9	424.2	418.7	413.0	410.8	400.6	402.9	393.9
5°	413.0	389.3	371.4	353.4	336.5	324.0	314.0	301.6	291.5	286.9	277.9
7.5°	359.0	328.6	305.0	285.8	265.6	249.8	236.3	227.4	218.3	209.3	204.8
10°	311.7	279.1	252.0	233.0	213.8	200.3	190.2	183.4	177.8	174.4	173.3
12.5°	267.9	236.3	211.6	194.7	180.0	173.3	168.8	165.4	164.2	163.2	163.2
15°	234.1	202.6	183.4	171.1	164.2	160.9	159.8	157.5	155.3	154.2	154.2
17.5°	202.6	179.0	165.4	158.7	155.3	153.1	150.8	148.5	146.3	145.2	145.2
20°	181.1	162.1	155.3	150.8	147.5	145.2	141.8	139.6	138.4	137.3	136.2
22.5°	164.2	151.9	147.5	144.0	139.6	136.2	133.9	131.7	129.4	128.3	127.2
25°	151.9	144.0	140.6	136.2	131.7	128.3	124.9	121.6	119.3	118.1	116.0
27.5°	142.9	137.3	132.7	127.2	122.7	119.3	116.0	112.5	110.3	108.0	106.9
30°	135.0	129.4	123.8	119.3	113.7	110.3	105.8	102.4	101.2	99.1	96.8
32.5°	127.2	121.6	116.0	110.3	104.7	100.1	97.9	93.4	91.2	90.1	87.8
35°	118.1	112.5	105.8	101.2	95.6	91.2	87.8	84.4	82.2	79.9	78.8
37.5°	110.3	103.5	96.8	91.2	86.6	82.2	78.8	75.4	73.2	70.9	69.7
40°	101.2	94.5	87.8	82.2	77.6	74.3	70.9	67.6	65.3	64.1	64.1
42.5°	93.4	85.5	78.8	74.3	70.9	66.4	63.0	59.7	58.5	57.4	58.5
45°	85.5	77.6	72.0	67.6	64.1	59.7	56.3	54.0	52.8	54.0	55.1
47.5°	78.8	70.9	65.3	61.9	58.5	55.1	51.8	49.5	49.5	51.8	54.0
50°	72.0	64.1	59.7	57.4	54.0	50.7	46.1	45.0	46.1	48.4	50.7
52.5°	65.3	56.3	52.8	51.8	48.4	45.0	41.7	40.5	41.7	43.9	42.8
55°	58.5	49.5	48.4	47.3	43.9	39.4	36.0	36.0	36.0	34.9	32.6
57.5°	56.3	43.9	42.8	41.7	38.2	33.8	31.5	29.2	28.1	24.8	23.6
60°	58.5	39.4	39.4	37.1	33.8	29.2	25.9	22.5	20.2	18.0	18.0
62.5°	47.3	36.0	34.9	32.6	28.1	23.6	20.2	16.9	15.8	14.6	14.6
65°	38.2	32.6	30.4	27.0	23.6	19.2	15.8	13.5	12.3	12.3	13.5
67.5°	34.9	29.2	25.9	22.5	19.2	14.6	12.3	11.3	11.3	12.3	12.3
69°	32.6	27.0	23.6	20.2	16.9	13.5	11.3	11.3	11.3	11.3	12.3
70°	30.4	25.9	22.5	19.2	14.6	11.3	10.2	10.2	11.3	11.3	12.3
72.5°	23.6	20.2	19.2	15.8	11.3	10.2	9.0	10.2	10.2	11.3	11.3
75°	18.0	14.6	14.6	12.3	9.0	7.9	7.9	9.0	9.0	10.2	10.2
77.5°	12.3	10.2	10.2	9.0	7.9	6.7	6.7	7.9	9.0	9.0	10.2
80°	9.0	7.9	6.7	7.9	6.7	5.6	6.7	7.9	7.9	9.0	9.0
82.5°	6.7	6.7	6.7	6.7	5.6	5.6	6.7	6.7	7.9	9.0	9.0
85°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	6.7	6.7	7.9	7.9
87.5°	3.4	3.4	3.4	4.5	4.5	5.6	5.6	5.6	5.6	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152048

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-HSS-8030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	518.8	518.8	518.8	518.8
2.5°	391.6	390.5	386.0	387.2
5°	274.6	267.9	272.3	271.2
7.5°	201.5	200.3	199.2	201.5
10°	172.1	172.1	171.1	172.1
12.5°	162.1	162.1	162.1	162.1
15°	154.2	154.2	153.1	153.1
17.5°	145.2	145.2	145.2	144.0
20°	136.2	135.0	135.0	135.0
22.5°	126.0	124.9	124.9	124.9
25°	116.0	114.8	114.8	114.8
27.5°	105.8	104.7	103.5	103.5
30°	95.6	94.5	93.4	93.4
32.5°	85.5	84.4	83.3	83.3
35°	76.5	76.5	75.4	74.3
37.5°	68.6	68.6	68.6	68.6
40°	63.0	64.1	64.1	64.1
42.5°	59.7	60.7	61.9	63.0
45°	57.4	59.7	60.7	60.7
47.5°	56.3	57.4	58.5	58.5
50°	51.8	50.7	50.7	50.7
52.5°	41.7	39.4	38.2	37.1
55°	30.4	29.2	27.0	27.0
57.5°	21.3	21.3	20.2	20.2
60°	16.9	16.9	15.8	16.9
62.5°	14.6	14.6	14.6	14.6
65°	13.5	13.5	13.5	13.5
67.5°	13.5	13.5	13.5	13.5
69°	12.3	12.3	12.3	12.3
70°	12.3	12.3	12.3	12.3
72.5°	11.3	11.3	11.3	11.3
75°	10.2	11.3	11.3	11.3
77.5°	10.2	10.2	10.2	10.2
80°	9.0	9.0	10.2	10.2
82.5°	9.0	9.0	9.0	9.0
85°	7.9	7.9	9.0	9.0
87.5°	6.7	6.7	7.9	7.9
90°	0.0	0.0	0.0	0.0

(END OF REPORT)