

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702691

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GFF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-14)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GFF
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, FROSTED OUTSIDE KIT.
Light Source: 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2227.4 lumens
Efficiency: N/A
Efficacy: 55.1 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.63
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702691

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GFF

Luminous Intensity Polar Plot



TEST NUMBER: P702691

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109		104	104	104		99	99	99	96
1	107	102	97	93	104	99	95	91	94	91	88		90	87	84		85	83	81	79
2	98	89	82	77	95	87	81	75	83	78	73		79	75	71		76	72	69	66
3	90	79	71	65	87	77	70	64	74	68	62		71	65	61		68	63	59	57
4	83	71	63	56	80	70	62	56	67	60	54		64	58	53		61	56	52	50
5	77	65	56	49	75	63	55	49	61	54	48		58	52	47		56	51	47	44
6	72	59	50	44	70	58	50	44	56	49	43		54	47	43		52	46	42	40
7	67	54	46	40	65	53	45	40	51	44	39		50	43	39		48	43	38	36
8	63	50	42	37	61	49	42	36	48	41	36		46	40	36		45	39	35	33
9	60	47	39	34	58	46	39	34	45	38	33		43	37	33		42	37	33	31
10	56	44	36	31	55	43	36	31	42	35	31		41	35	31		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125549
5°	111351
10°	92803
15°	51938
20°	34713
25°	26817
30°	21677
35°	18072
40°	16109
45°	14770
50°	13473
55°	12084
60°	10779
65°	9322
70°	7990
75°	6767
80°	5743
85°	4796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14770 cd/sqm

TEST NUMBER: P702691

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.9	7.9
10°-20°	308.0	13.8
20°-30°	282.5	12.7
30°-40°	280.8	12.6
40°-50°	291.7	13.1
50°-60°	280.4	12.6
60°-70°	234.6	10.5
70°-80°	173.0	7.8
80°-90°	117.1	5.3
90°-100°	67.9	3.0
100°-110°	14.1	0.6
110°-120°	0.3	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	767.4	34.5
0°-40°	1048.2	47.1
0°-60°	1620.4	72.7
0°-90°	2145.1	96.3
90°-120°	82.4	3.7
90°-150°	82.4	3.7
90°-180°	82.0	3.7
0°-180°	2227.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1924	
5°	1903	177
15°	1049	308
25°	609	282
35°	443	281
45°	378	292
55°	313	280
65°	236	235
75°	163	173
85°	106	92
90°	84	47
95°	65	46
105°	11	14
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702691

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1924.4
2.5°	1921.7
5°	1902.6
7.5°	1859.2
10°	1736.8
12.5°	1402.5
15°	1049.2
17.5°	861.6
20°	747.5
22.5°	668.6
25°	608.8
27.5°	559.9
30°	513.7
32.5°	472.9
35°	443.0
37.5°	421.3
40°	405.0
42.5°	391.4
45°	377.8
47.5°	364.2
50°	347.9
52.5°	331.6
55°	312.6
57.5°	296.3
60°	277.2
62.5°	255.5
65°	236.5
67.5°	217.4
70°	198.4
72.5°	179.4
75°	163.1
77.5°	146.8
80°	133.2
82.5°	119.6
85°	106.0
87.5°	95.1
90°	84.3
92.5°	76.1
95°	65.2
97.5°	48.9
100°	32.6
102.5°	19.0
105°	10.9
107.5°	5.4
110°	2.7

TEST NUMBER: P702691

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GFF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)