

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702660

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702660  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-FF  
Description: FARALLON 6" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2255.5 lumens  
Efficiency: N/A  
Efficacy: 55.8 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.81  
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')  
CIE Type: Direct

Input Watts (W): 40.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702660

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

### Luminous Intensity Polar Plot



TEST NUMBER: P702660

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		99	99	99	97
1	110	106	102	99	107	103	100	97	99	96	93		94	92	90		90	89	87	85
2	102	96	90	86	100	94	89	84	90	86	82		86	83	80		83	80	78	76
3	96	87	81	76	93	86	80	75	83	77	73		80	75	72		77	73	70	68
4	90	80	73	68	88	79	72	67	76	71	66		74	69	65		71	67	64	62
5	85	74	67	62	83	73	66	61	71	65	61		69	64	60		67	62	59	57
6	80	69	62	57	78	68	61	56	66	60	56		64	59	55		63	58	54	53
7	75	64	57	52	74	64	57	52	62	56	52		60	55	51		59	54	51	49
8	71	60	53	49	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	68	57	50	45	66	56	50	45	55	49	45		54	48	45		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	127774
5°	113798
10°	99818
15°	88698
20°	77958
25°	65109
30°	29218
35°	15563
40°	12366
45°	9946
50°	7989
55°	6336
60°	5277
65°	4454
70°	4096
75°	3750
80°	3411
85°	3067

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9946 cd/sqm

TEST NUMBER: P702660

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.0	8.1
10°-20°	503.4	22.3
20°-30°	613.9	27.2
30°-40°	259.9	11.5
40°-50°	197.2	8.7
50°-60°	149.3	6.6
60°-70°	114.1	5.1
70°-80°	95.6	4.2
80°-90°	74.0	3.3
90°-100°	49.4	2.2
100°-110°	14.7	0.7
110°-120°	1.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1300.3	57.6
0°-40°	1560.2	69.2
0°-60°	1906.8	84.5
0°-90°	2190.4	97.1
90°-120°	65.1	2.9
90°-150°	65.1	2.9
90°-180°	65.0	2.9
0°-180°	2255.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1958	
5°	1944	183
15°	1792	503
25°	1478	614
35°	382	260
45°	254	197
55°	164	149
65°	113	114
75°	90	96
85°	68	58
90°	56	31
95°	48	34
105°	11	15
115°	0	1
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702660

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1958.5
2.5°	1955.7
5°	1944.4
7.5°	1910.5
10°	1868.1
12.5°	1831.3
15°	1791.8
17.5°	1743.7
20°	1678.7
22.5°	1599.6
25°	1478.1
27.5°	1153.1
30°	692.4
32.5°	455.0
35°	381.5
37.5°	342.0
40°	310.9
42.5°	282.6
45°	254.4
47.5°	228.9
50°	206.3
52.5°	183.7
55°	163.9
57.5°	149.8
60°	135.7
62.5°	121.5
65°	113.0
67.5°	107.4
70°	101.7
72.5°	96.1
75°	90.4
77.5°	84.8
80°	79.1
82.5°	73.5
85°	67.8
87.5°	62.2
90°	56.5
92.5°	53.7
95°	48.0
97.5°	36.7
100°	28.3
102.5°	19.8
105°	11.3
107.5°	8.5
110°	2.8

TEST NUMBER: P702660

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	2.8
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)