

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702696

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-GCC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702696  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-GCC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA  
Light Source: 3000K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2806.0 lumens  
Efficiency: N/A  
Efficacy: 69.5 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.89  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702696

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-GCC

### Luminous Intensity Polar Plot



TEST NUMBER: P702696

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-GCC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90	87	85	83
3	100	93	87	83	98	91	86	82	88	84	81		86	82	79		84	81	78	76
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	74	71	70
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	58	78	68	62	57	67	61	57		66	60	57		64	60	56	55
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61	56	52	51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49	48
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54	49	46	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	187286
5°	180045
10°	171269
15°	154388
20°	139473
25°	118984
30°	101534
35°	73137
40°	55826
45°	37542
50°	23233
55°	16709
60°	12161
65°	8290
70°	7001
75°	5697
80°	5297
85°	4267

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 37542 cd/sqm

TEST NUMBER: P702696

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-GCC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	257.5	9.2
10°-20°	644.7	23.0
20°-30°	760.0	27.1
30°-40°	590.9	21.1
40°-50°	324.1	11.6
50°-60°	135.1	4.8
60°-70°	57.2	2.0
70°-80°	24.6	0.9
80°-90°	6.9	0.2
90°-100°	3.1	0.1
100°-110°	1.9	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1662.3	59.2
0°-40°	2253.1	80.3
0°-60°	2712.4	96.7
0°-90°	2801.0	99.8
90°-120°	4.9	0.2
90°-150°	4.9	0.2
90°-180°	5.0	0.2
0°-180°	2806.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2871	
5°	2749	258
15°	2286	645
25°	1653	760
35°	918	591
45°	407	324
55°	147	135
65°	54	57
75°	23	25
85°	6	6
90°	3	2
95°	3	2
105°	3	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702696

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-GCC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2870.7
2.5°	2839.6
5°	2749.2
7.5°	2667.3
10°	2585.3
12.5°	2435.6
15°	2285.8
17.5°	2189.8
20°	2008.9
22.5°	1791.4
25°	1652.9
27.5°	1517.3
30°	1347.8
32.5°	1141.5
35°	918.3
37.5°	757.2
40°	655.5
42.5°	556.6
45°	406.9
47.5°	293.9
50°	228.9
52.5°	180.8
55°	146.9
57.5°	118.7
60°	93.2
62.5°	67.8
65°	53.7
67.5°	45.2
70°	36.7
72.5°	28.3
75°	22.6
77.5°	17.0
80°	14.1
82.5°	8.5
85°	5.7
87.5°	2.8
90°	2.8
92.5°	2.8
95°	2.8
97.5°	2.8
100°	2.8
102.5°	2.8
105°	2.8
107.5°	0.0
110°	0.0

TEST NUMBER: P702696

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-GCC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)