

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702674

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-FF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-10)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-FF
Description: FARALLON 6" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2290.5 lumens
Efficiency: N/A
Efficacy: 56.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.81
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702674

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-FF

Luminous Intensity Polar Plot



TEST NUMBER: P702674

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-FF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		99	99	99	97
1	110	106	102	99	107	103	100	97	99	96	93		94	92	90		90	89	87	85
2	102	96	90	86	100	94	89	84	90	86	82		86	83	80		83	80	78	76
3	96	87	81	76	93	86	80	75	82	77	73		80	75	72		77	73	70	68
4	90	80	73	68	88	79	72	67	76	71	66		74	69	65		71	67	64	62
5	85	74	67	62	83	73	66	61	71	65	61		69	64	60		67	62	59	57
6	80	69	62	57	78	68	61	56	66	60	56		64	59	55		63	58	54	53
7	75	64	57	52	74	64	57	52	62	56	52		60	55	51		59	54	51	49
8	71	60	53	49	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	68	57	50	45	66	56	50	45	55	49	45		54	48	45		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129757
5°	115559
10°	101363
15°	90074
20°	79170
25°	66118
30°	29670
35°	15804
40°	12557
45°	10098
50°	8113
55°	6436
60°	5358
65°	4525
70°	4160
75°	3809
80°	3467
85°	3117

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10098 cd/sqm

TEST NUMBER: P702674

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-FF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.8	8.1
10°-20°	511.2	22.3
20°-30°	623.4	27.2
30°-40°	264.0	11.5
40°-50°	200.3	8.7
50°-60°	151.6	6.6
60°-70°	115.9	5.1
70°-80°	97.1	4.2
80°-90°	75.1	3.3
90°-100°	50.1	2.2
100°-110°	14.9	0.7
110°-120°	1.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1320.4	57.6
0°-40°	1584.4	69.2
0°-60°	1936.3	84.5
0°-90°	2224.4	97.1
90°-120°	66.1	2.9
90°-150°	66.1	2.9
90°-180°	66.0	2.9
0°-180°	2290.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1989	
5°	1974	186
15°	1820	511
25°	1501	623
35°	387	264
45°	258	200
55°	166	152
65°	115	116
75°	92	97
85°	69	59
90°	57	32
95°	49	35
105°	12	15
115°	0	1
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P702674

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-FF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1988.9
2.5°	1986.0
5°	1974.5
7.5°	1940.1
10°	1897.0
12.5°	1859.7
15°	1819.6
17.5°	1770.8
20°	1704.8
22.5°	1624.4
25°	1501.0
27.5°	1170.9
30°	703.1
32.5°	462.1
35°	387.4
37.5°	347.3
40°	315.7
42.5°	287.0
45°	258.3
47.5°	232.5
50°	209.5
52.5°	186.5
55°	166.5
57.5°	152.1
60°	137.8
62.5°	123.4
65°	114.8
67.5°	109.1
70°	103.3
72.5°	97.6
75°	91.8
77.5°	86.1
80°	80.4
82.5°	74.6
85°	68.9
87.5°	63.1
90°	57.4
92.5°	54.5
95°	48.8
97.5°	37.3
100°	28.7
102.5°	20.1
105°	11.5
107.5°	8.6
110°	2.9

TEST NUMBER: P702674

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-FF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	2.9
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)