

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152613

Luminaire Tested: **AVS-F03-LED-E-U-SL4-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P152613  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: AVS-F03-LED-E-U-SL4-8030  
Description: VISION SITE SMALL LED LUMINAIRE  
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL  
Light Source: (21) 3000K CCT, 80 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6174.7 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short - Full Cutoff  
BUG Rating: B1 - U0 - G2


Input Watts (W): 78.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P152613  
 CATALOG NUMBER: AVS-F03-LED-E-U-SL4-8030

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 13.2 fc  
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152613  
CATALOG NUMBER: AVS-F03-LED-E-U-SL4-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral    - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P152613

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-8030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1281.8	0.0	1281.8
	% Fixture	20.8	0.0	20.8
<b>Street Side</b>	Lumens	4892.9	0.0	4892.9
	% Fixture	79.2	0.0	79.2
<b>Total</b>	Lumens	6174.7	0.0	6174.7
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.1	2.0
10°-20°	337.0	5.5
20°-30°	498.8	8.1
30°-40°	630.4	10.2
40°-50°	712.9	11.5
50°-60°	1014.5	16.4
60°-70°	1889.4	30.6
70°-80°	865.9	14.0
80°-90°	102.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6174.7	100.0
0°-180°	6174.7	100.0

**Coefficient of Utilization**



REPORT NUMBER: P152613


CATALOG NUMBER: AVS-F03-LED-E-U-SL4-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	562.3	9.1			
FM	(30°-60°)	1809.0	29.3			
FH	(60°-80°)	2445.4	39.6			G2/5000
FVH	(80°-90°)	76.3	1.2			G1/100
BL	(0°-30°)	396.6	6.4	B1/500		
BM	(30°-60°)	548.8	8.9	B1/1000		
BH	(60°-80°)	309.9	5.0	B1/500		G1/500
BVH	(80°-90°)	26.5	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**

Type IV Short





REPORT NUMBER: P152613

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5
2.5°	1337.7	1341.2	1337.0	1336.4	1336.4	1335.6	1331.5	1330.8	1325.2	1325.9	1327.3
5°	1347.5	1348.9	1346.1	1345.4	1344.0	1341.2	1337.7	1333.6	1329.3	1325.2	1321.7
7.5°	1357.2	1355.9	1353.8	1353.8	1351.7	1347.5	1340.5	1334.9	1325.9	1321.0	1314.7
10°	1371.2	1369.1	1366.3	1364.9	1361.5	1355.1	1345.4	1337.7	1326.6	1316.8	1306.4
12.5°	1384.5	1383.7	1379.6	1377.4	1371.9	1365.6	1353.8	1341.9	1327.3	1311.9	1298.0
15°	1408.1	1405.3	1401.1	1397.0	1387.9	1379.6	1361.5	1347.5	1326.6	1306.4	1284.8
17.5°	1449.2	1444.4	1440.1	1431.1	1419.9	1405.3	1378.9	1355.1	1326.6	1297.3	1273.0
20°	1524.5	1514.0	1508.4	1496.6	1477.1	1450.6	1409.5	1371.2	1328.7	1291.1	1258.3
22.5°	1609.4	1602.5	1594.8	1587.2	1556.5	1518.2	1462.5	1405.3	1341.2	1288.3	1246.4
25°	1704.9	1695.9	1691.7	1678.4	1649.8	1606.0	1530.1	1450.6	1369.7	1299.4	1246.4
27.5°	1789.9	1787.2	1786.4	1771.1	1743.9	1692.3	1602.5	1507.0	1408.8	1322.4	1256.9
30°	1867.3	1864.5	1863.1	1854.7	1823.3	1762.1	1664.5	1557.2	1451.3	1354.4	1276.4
32.5°	1949.4	1940.4	1936.3	1920.2	1884.7	1813.0	1701.5	1589.9	1484.8	1385.8	1298.0
35°	2016.4	2008.7	2000.3	1977.3	1927.2	1842.2	1717.4	1601.1	1498.0	1403.2	1309.1
37.5°	2065.1	2057.4	2045.6	2016.4	1954.3	1851.9	1716.8	1597.6	1493.1	1400.4	1311.3
40°	2086.7	2079.1	2066.5	2029.6	1959.2	1846.3	1703.5	1581.6	1478.4	1385.8	1302.9
42.5°	2078.3	2072.7	2056.8	2021.2	1943.9	1821.2	1677.0	1551.6	1450.6	1362.1	1284.0
45°	2046.3	2042.2	2026.8	1989.2	1909.0	1780.8	1638.0	1514.0	1417.2	1332.8	1259.0
47.5°	1998.2	1996.9	1981.6	1944.6	1865.2	1740.4	1597.6	1477.1	1383.7	1304.2	1238.1
50°	1945.3	1938.3	1930.7	1896.5	1824.0	1705.6	1568.4	1454.1	1364.9	1293.9	1229.0
52.5°	1911.8	1909.7	1902.8	1872.1	1802.5	1685.4	1555.1	1445.7	1363.5	1291.7	1224.1
55°	2208.6	2213.6	2149.4	2016.4	1899.3	1741.1	1594.8	1488.2	1397.6	1325.2	1275.8
57.5°	3266.9	3245.4	3135.3	2871.3	2573.1	2179.4	1895.9	1723.7	1611.5	1624.0	1649.2
60°	3806.2	3802.1	3781.9	3679.5	3480.9	3181.2	2848.9	2467.9	2346.6	2359.8	2369.6
62.5°	4047.4	4053.6	4068.9	4030.6	3978.3	3891.3	3725.5	3572.1	3409.8	3349.2	3186.8
65°	4158.9	4169.9	4204.8	4226.4	4246.6	4262.0	4327.5	4507.2	4625.6	4404.0	3888.5
67.5°	3928.2	3981.9	4096.8	4209.0	4309.3	4452.1	4673.7	5091.1	5381.6	5109.1	4361.6
70°	2863.6	2936.8	3068.4	3415.4	3786.0	4110.1	4539.3	5174.6	5613.0	5402.5	4478.7
72.5°	1795.4	1815.6	1874.2	2001.8	2276.9	2692.8	3443.3	4396.4	4902.3	4734.3	3785.4
75°	1139.2	1146.1	1144.0	1173.3	1220.0	1310.6	1607.4	2596.7	3358.2	3096.3	2109.7
77.5°	678.7	689.1	693.3	702.3	724.6	756.7	781.0	883.4	1408.1	1367.0	765.7
80°	568.5	576.9	569.9	567.9	553.9	544.1	556.0	544.1	505.2	486.3	448.0
82.5°	301.0	300.3	298.2	318.4	359.5	391.6	416.0	410.4	371.4	316.3	268.3
85°	165.1	170.7	170.7	177.6	171.4	172.1	177.6	187.5	173.5	144.9	118.4
87.5°	13.9	21.6	17.4	21.6	29.2	20.9	20.2	20.2	17.4	12.5	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152613

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-8030

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5
2.5°	1323.8	1322.4	1319.6	1317.5	1317.5	1314.1	1311.9	1310.6	1309.8	1307.0	1307.0
5°	1319.6	1314.7	1309.8	1306.4	1304.2	1300.8	1295.2	1292.4	1288.9	1286.2	1284.8
7.5°	1310.6	1301.5	1293.9	1288.3	1281.3	1275.8	1268.7	1262.5	1256.2	1253.5	1252.0
10°	1296.6	1284.8	1273.0	1262.5	1252.7	1243.0	1233.9	1224.9	1217.2	1211.6	1206.0
12.5°	1283.4	1265.3	1249.9	1234.6	1219.3	1207.5	1194.9	1181.7	1170.5	1160.1	1157.3
15°	1265.3	1244.4	1224.9	1206.0	1187.3	1167.8	1152.4	1137.7	1119.7	1107.8	1098.8
17.5°	1248.6	1223.4	1199.8	1177.5	1154.5	1134.3	1111.3	1091.8	1073.7	1055.5	1042.3
20°	1230.5	1203.2	1178.1	1153.1	1128.0	1102.3	1075.8	1050.7	1028.4	1006.7	985.2
22.5°	1214.4	1186.5	1162.2	1135.0	1107.2	1077.8	1047.2	1015.9	990.1	962.2	937.1
25°	1204.7	1174.0	1148.9	1122.5	1091.8	1059.7	1024.9	988.0	956.6	924.6	894.6
27.5°	1204.7	1165.0	1139.2	1112.6	1081.3	1047.2	1008.9	968.5	933.0	897.4	860.5
30°	1215.1	1166.3	1131.5	1103.6	1071.6	1034.6	992.1	949.6	910.7	868.8	833.3
32.5°	1224.9	1169.1	1125.9	1090.4	1053.5	1017.2	974.0	928.7	885.6	845.8	808.2
35°	1231.1	1169.1	1115.4	1070.2	1028.4	992.8	950.4	905.1	861.1	822.2	787.4
37.5°	1231.8	1163.5	1098.8	1047.2	1003.3	966.3	926.0	883.4	841.7	805.4	776.2
40°	1224.9	1152.4	1082.1	1022.8	976.8	939.2	902.3	863.9	826.3	796.4	771.3
42.5°	1212.3	1140.5	1066.0	1003.3	955.2	916.2	882.1	849.3	816.6	790.8	769.8
45°	1193.5	1124.6	1051.4	991.5	944.0	903.0	869.5	842.4	814.5	792.8	772.0
47.5°	1176.8	1119.0	1056.3	999.1	949.6	907.2	873.1	850.1	828.4	813.8	785.2
50°	1173.3	1116.2	1058.3	1005.4	955.2	912.0	882.1	870.3	863.9	854.9	811.0
52.5°	1163.5	1115.4	1073.7	1044.5	1012.3	992.1	960.8	971.9	965.0	933.0	853.5
55°	1266.0	1279.9	1319.0	1374.6	1426.2	1438.0	1434.6	1421.3	1351.0	1162.2	956.0
57.5°	1740.4	1819.2	1893.1	1925.8	1921.6	1884.7	1858.2	1804.6	1702.8	1472.8	1157.9
60°	2399.6	2412.1	2373.1	2315.2	2217.7	2136.2	2049.1	1948.8	1801.0	1576.1	1282.0
62.5°	3006.4	2837.8	2664.4	2501.2	2352.8	2223.3	2102.1	1962.0	1769.7	1534.9	1266.0
65°	3434.9	3078.1	2804.4	2570.3	2360.5	2179.4	2028.2	1846.3	1629.6	1417.8	1173.3
67.5°	3655.8	3108.8	2688.7	2362.6	2065.1	1814.3	1613.0	1436.0	1275.0	1182.4	1026.9
70°	3409.1	2638.5	2053.3	1684.7	1328.7	1065.3	841.7	706.5	659.8	747.6	777.5
72.5°	2540.3	1717.4	1221.3	944.8	723.9	576.9	442.4	347.7	282.9	296.8	385.3
75°	1201.1	741.3	523.9	398.5	317.0	262.7	214.6	196.5	164.5	136.6	128.2
77.5°	467.5	340.7	281.5	206.2	146.3	117.7	100.3	96.9	99.0	96.2	94.7
80°	356.1	241.0	151.2	110.8	95.4	84.4	74.5	71.8	73.2	76.7	80.1
82.5°	198.5	124.0	92.0	80.1	71.8	61.3	55.8	51.6	52.2	56.5	64.1
85°	76.7	59.9	55.0	53.0	49.4	39.7	34.1	34.8	39.7	47.4	47.4
87.5°	8.4	8.4	11.2	8.4	8.4	8.4	7.7	9.0	9.7	12.5	14.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P152613

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-8030

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5
2.5°	1305.7	1305.7	1305.7	1304.2	1305.0	1302.2	1302.2	1300.1	1303.6	1301.5	1300.8
5°	1285.5	1284.8	1282.0	1282.0	1282.0	1282.0	1284.0	1278.5	1282.7	1282.7	1280.6
7.5°	1251.3	1251.3	1243.6	1247.9	1246.4	1248.6	1251.3	1248.6	1252.7	1255.5	1253.5
10°	1203.9	1203.9	1197.7	1202.6	1200.5	1205.4	1210.3	1207.5	1210.3	1214.4	1215.9
12.5°	1151.7	1148.9	1143.3	1145.4	1145.4	1148.2	1150.3	1153.8	1157.3	1162.9	1165.6
15°	1091.1	1086.9	1079.9	1079.9	1075.8	1077.2	1081.3	1082.7	1089.7	1097.4	1106.4
17.5°	1029.1	1018.7	1011.0	1001.9	994.9	1000.5	1005.4	1008.9	1014.4	1026.3	1032.5
20°	970.6	949.6	935.0	923.2	915.5	919.0	925.3	929.4	934.3	937.1	939.2
22.5°	912.7	889.0	868.8	854.2	841.7	845.2	842.4	840.3	843.7	834.7	834.0
25°	862.6	834.7	807.6	790.1	774.8	769.8	755.2	751.8	742.1	734.4	728.8
27.5°	826.3	790.1	760.1	739.9	715.5	697.4	678.7	659.8	649.3	636.8	630.6
30°	797.7	759.5	723.9	689.7	657.7	629.8	604.8	580.4	563.6	545.5	533.7
32.5°	771.3	735.8	692.5	645.9	602.7	571.3	538.5	510.7	484.2	460.5	443.1
35°	753.2	713.5	658.4	601.2	552.5	515.5	480.7	441.0	409.0	378.3	359.5
37.5°	743.4	694.6	627.0	563.6	509.3	467.5	424.4	378.3	339.3	310.8	282.2
40°	735.8	675.9	599.2	530.3	473.1	422.9	372.7	318.4	275.2	245.3	223.0
42.5°	727.4	654.9	574.8	503.7	440.3	381.8	321.2	263.3	222.3	201.3	191.6
45°	718.3	636.8	551.8	478.7	408.3	337.2	267.6	213.9	189.5	182.6	182.6
47.5°	716.3	625.0	535.1	454.3	372.0	285.7	218.0	184.7	177.6	179.1	181.9
50°	724.6	621.5	520.4	425.7	323.9	231.3	184.7	173.5	174.9	179.1	183.2
52.5°	744.8	624.2	505.2	386.0	266.8	190.9	170.7	170.1	174.2	180.4	184.7
55°	779.0	624.2	475.9	326.7	213.2	171.4	165.8	168.6	174.2	179.8	183.2
57.5°	852.1	618.0	424.4	261.2	178.3	164.5	164.5	167.9	172.7	178.3	181.1
60°	939.2	609.6	351.8	202.1	160.9	158.9	163.7	167.9	172.1	177.0	179.8
62.5°	944.8	588.1	278.7	167.3	151.9	155.3	163.0	168.6	170.1	173.5	177.0
65°	868.1	512.7	221.6	149.8	147.7	153.3	160.9	165.1	165.8	167.3	170.7
67.5°	760.1	418.0	179.1	141.5	143.5	149.8	154.0	157.5	159.6	163.0	163.7
70°	624.2	335.9	153.3	133.1	135.1	142.2	145.6	149.1	153.3	157.5	155.3
72.5°	442.4	261.2	134.5	124.0	126.8	133.1	137.3	140.0	143.5	147.7	144.9
75°	188.1	182.6	116.4	112.1	116.4	120.5	124.8	128.9	132.3	134.5	134.5
77.5°	96.2	107.3	100.3	100.3	103.1	107.3	110.8	114.9	117.1	119.2	122.0
80°	81.6	82.9	84.4	87.0	89.8	94.1	97.5	101.0	101.8	102.4	103.8
82.5°	67.6	70.4	71.8	76.0	78.0	79.4	81.6	81.6	82.9	82.9	80.8
85°	48.8	52.2	54.3	55.0	54.3	55.0	55.8	57.1	60.6	60.6	57.8
87.5°	13.9	13.3	16.7	17.4	18.9	21.6	24.4	29.2	30.7	32.0	32.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152613

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-8030

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1317.5	1317.5	1317.5	1317.5
2.5°	1300.1	1301.5	1298.8	1299.4
5°	1280.6	1283.4	1279.9	1284.0
7.5°	1255.5	1259.7	1259.0	1258.3
10°	1219.3	1224.9	1224.9	1226.9
12.5°	1173.3	1176.8	1179.6	1180.9
15°	1111.3	1117.5	1121.0	1121.0
17.5°	1036.8	1040.9	1043.0	1040.2
20°	942.0	940.6	941.2	934.3
22.5°	832.6	834.7	828.4	829.8
25°	725.3	721.9	724.6	720.4
27.5°	621.5	622.2	614.5	618.0
30°	522.6	519.1	509.3	514.2
32.5°	427.2	418.0	407.6	401.3
35°	337.2	323.3	318.4	316.3
37.5°	264.8	249.4	244.6	239.0
40°	210.4	204.9	202.8	204.1
42.5°	188.8	188.8	190.3	190.9
45°	183.2	185.3	187.5	188.1
47.5°	183.9	186.0	188.8	189.5
50°	185.3	187.5	189.5	190.3
52.5°	186.0	186.0	187.5	188.1
55°	184.7	183.9	184.7	185.3
57.5°	181.9	180.4	181.1	183.2
60°	180.4	178.3	179.8	181.1
62.5°	177.0	176.3	177.6	178.3
65°	169.3	170.1	172.1	172.1
67.5°	162.4	163.0	163.7	164.5
70°	154.0	154.7	156.1	156.8
72.5°	144.2	147.0	149.1	151.9
75°	136.6	139.4	143.5	146.3
77.5°	123.3	125.4	130.3	133.8
80°	104.6	103.8	104.6	106.6
82.5°	80.1	80.1	79.4	78.8
85°	56.5	55.8	53.7	53.7
87.5°	30.7	29.9	29.2	27.9
90°	0.0	0.0	0.0	0.0

(END OF REPORT)