

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702679

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-CF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-12)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-CF
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL FROSTED GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2539.7 lumens
Efficiency: N/A
Efficacy: 62.9 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.55
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702679

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-CF

Luminous Intensity Polar Plot



TEST NUMBER: P702679

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-CF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	98	107	103	99	96	98	95	93		94	92	90		90	88	87	84
2	101	94	88	83	99	92	87	82	88	84	80		85	81	78		82	79	76	74
3	94	85	78	72	92	83	77	72	80	75	70		77	73	69		75	71	67	65
4	88	77	70	64	85	76	69	64	73	67	63		71	66	62		69	64	61	59
5	82	71	63	58	80	70	63	57	68	61	56		66	60	56		64	59	55	53
6	77	66	58	52	75	65	57	52	63	56	52		61	55	51		59	54	50	49
7	73	61	53	48	71	60	53	48	58	52	47		57	51	47		55	50	47	45
8	69	57	50	44	67	56	49	44	55	48	44		53	48	44		52	47	43	42
9	65	53	46	41	64	53	46	41	52	45	41		50	45	41		49	44	40	39
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246525
5°	181893
10°	115667
15°	91931
20°	63390
25°	31869
30°	25091
35°	21870
40°	20158
45°	17866
50°	14859
55°	11775
60°	9340
65°	7390
70°	5779
75°	4618
80°	3790
85°	3049

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17866 cd/sqm

TEST NUMBER: P702679

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-CF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.6	10.4
10°-20°	508.1	20.0
20°-30°	369.0	14.5
30°-40°	338.5	13.3
40°-50°	349.2	13.7
50°-60°	274.4	10.8
60°-70°	186.6	7.3
70°-80°	119.5	4.7
80°-90°	73.9	2.9
90°-100°	42.8	1.7
100°-110°	12.9	0.5
110°-120°	0.4	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1141.7	45.0
0°-40°	1480.2	58.3
0°-60°	2103.7	82.8
0°-90°	2483.6	97.8
90°-120°	56.0	2.2
90°-150°	56.0	2.2
90°-180°	56.0	2.2
0°-180°	2539.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3779	
5°	3108	265
15°	1857	508
25°	724	369
35°	536	339
45°	457	349
55°	305	274
65°	188	187
75°	111	119
85°	67	59
90°	50	28
95°	41	30
105°	12	13
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702679

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-CF

CANDELA DISTRIBUTION (FULL):

0°	
0°	3778.7
2.5°	3646.9
5°	3107.9
7.5°	2525.0
10°	2164.7
12.5°	1974.3
15°	1857.1
17.5°	1713.6
20°	1365.0
22.5°	913.9
25°	723.5
27.5°	650.3
30°	594.6
32.5°	556.6
35°	536.1
37.5°	518.5
40°	506.8
42.5°	486.3
45°	457.0
47.5°	421.8
50°	383.7
52.5°	342.7
55°	304.6
57.5°	269.5
60°	240.2
62.5°	210.9
65°	187.5
67.5°	164.0
70°	143.5
72.5°	126.0
75°	111.3
77.5°	99.6
80°	87.9
82.5°	76.2
85°	67.4
87.5°	58.6
90°	49.8
92.5°	46.9
95°	41.0
97.5°	32.2
100°	23.4
102.5°	17.6
105°	11.7
107.5°	5.9
110°	2.9

TEST NUMBER: P702679

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-CF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)