

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P853469

Luminaire Tested: **CRTK-N-50-740-U-T5R**

Issue Date: 7/11/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P853469  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-111-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/11/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: CRTK-N-50-740-U-T5R  
Description:  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6494 lumens  
Efficiency: N/A  
Efficacy: 136.1 lumens/watt  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G1  
  
Input Watts (W): 47.7  
Input Voltage (V): 120.0  
Input Current (Ain): 0.398  
Voltage Rise (V): NR  
Power Factor: 0.9969  
Total Harmonic Distortion (THDi): 6.56%  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P853469  
 CATALOG NUMBER: CRTK-N-50-740-U-T5R

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1 fc  
 Type V - Short - N/A

REPORT NUMBER: P853469  
CATALOG NUMBER: CRTK-N-50-740-U-T5R

### Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P853469  
 CATALOG NUMBER: CRTK-N-50-740-U-T5R


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	3247.0	0.0	3247.0
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	3247.0	0.0	3247.0
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	6494.0	0.0	6494.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.6	0.9
10°-20°	192.0	3.0
20°-30°	369.8	5.7
30°-40°	601.5	9.3
40°-50°	889.2	13.7
50°-60°	1283.9	19.8
60°-70°	1832.8	28.2
70°-80°	1222.3	18.8
80°-90°	44.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6494.0	100.0
0°-180°	6494.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P853469


CATALOG NUMBER: CRTK-N-50-740-U-T5R

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	309.7	4.8			
FM (30°-60°)	1387.3	21.4			
FH (60°-80°)	1527.6	23.5			G1/1800
FVH (80°-90°)	22.4	0.3			G1/100
BL (0°-30°)	309.7	4.8	B1/500		
BM (30°-60°)	1387.3	21.4	B2/2500		
BH (60°-80°)	1527.6	23.5	B3/2500		G1/1800
BVH (80°-90°)	22.4	0.3			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G1**

Type V Short



REPORT NUMBER: P853469

CATALOG NUMBER: CRTK-N-50-740-U-T5R

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	591.3
2.5°	593.0
5°	598.3
7.5°	605.4
10°	616.0
12.5°	639.1
15°	670.9
17.5°	702.8
20°	729.3
22.5°	755.9
25°	789.5
27.5°	832.0
30°	872.7
32.5°	913.4
35°	957.7
37.5°	993.1
40°	1033.8
42.5°	1083.4
45°	1140.0
47.5°	1203.8
50°	1271.0
52.5°	1341.8
55°	1419.7
57.5°	1508.2
60°	1612.7
62.5°	1747.2
65°	1892.4
67.5°	1975.6
70°	1910.1
72.5°	1635.7
75°	1276.3
77.5°	697.5
80°	166.4
82.5°	51.3
85°	24.8
87.5°	5.3
90°	0.0

(END OF REPORT)