

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702682

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702682  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA  
Light Source: 5000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2909.0 lumens  
Efficiency: N/A  
Efficacy: 72.0 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.89  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct

Input Watts (W): 40.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702682

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

### Luminous Intensity Polar Plot



TEST NUMBER: P702682

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90	87	85	83
3	100	93	87	83	98	91	86	82	88	84	81		86	82	79		84	81	78	76
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	74	71	70
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	58	78	68	62	57	67	61	57		66	60	57		64	60	56	55
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61	56	52	51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49	48
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54	49	46	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	194163
5°	186659
10°	177562
15°	160061
20°	144597
25°	123354
30°	105263
35°	75821
40°	57879
45°	38917
50°	24085
55°	17323
60°	12618
65°	8599
70°	7268
75°	5898
80°	5485
85°	4416

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 38917 cd/sqm

TEST NUMBER: P702682

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	267.0	9.2
10°-20°	668.4	23.0
20°-30°	787.9	27.1
30°-40°	612.6	21.1
40°-50°	336.0	11.6
50°-60°	140.1	4.8
60°-70°	59.3	2.0
70°-80°	25.5	0.9
80°-90°	7.2	0.2
90°-100°	3.2	0.1
100°-110°	1.9	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1723.3	59.2
0°-40°	2335.8	80.3
0°-60°	2812.0	96.7
0°-90°	2903.9	99.8
90°-120°	5.1	0.2
90°-150°	5.1	0.2
90°-180°	5.0	0.2
0°-180°	2909.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2976	
5°	2850	267
15°	2370	668
25°	1714	788
35°	952	613
45°	422	336
55°	152	140
65°	56	59
75°	23	25
85°	6	6
90°	3	2
95°	3	2
105°	3	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702682

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2976.1
2.5°	2943.9
5°	2850.2
7.5°	2765.2
10°	2680.3
12.5°	2525.0
15°	2369.8
17.5°	2270.2
20°	2082.7
22.5°	1857.1
25°	1713.6
27.5°	1573.0
30°	1397.3
32.5°	1183.4
35°	952.0
37.5°	785.0
40°	679.6
42.5°	577.1
45°	421.8
47.5°	304.6
50°	237.3
52.5°	187.5
55°	152.3
57.5°	123.0
60°	96.7
62.5°	70.3
65°	55.7
67.5°	46.9
70°	38.1
72.5°	29.3
75°	23.4
77.5°	17.6
80°	14.6
82.5°	8.8
85°	5.9
87.5°	2.9
90°	2.9
92.5°	2.9
95°	2.9
97.5°	2.9
100°	2.9
102.5°	2.9
105°	2.9
107.5°	0.0
110°	0.0

TEST NUMBER: P702682

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)