

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702700

Luminaire Tested: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-CF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-12)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-CF
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL FROSTED GLASS KIT.
Light Source: 2400K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2404.4 lumens
Efficiency: N/A
Efficacy: 51.2 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.55
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702700

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-CF

Luminous Intensity Polar Plot



TEST NUMBER: P702700

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-CF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	98	107	103	99	96	98	95	93		94	92	90		90	88	87	84
2	101	94	88	83	99	92	87	82	88	84	80		85	81	78		82	79	76	74
3	94	85	78	72	92	83	77	72	80	75	70		77	73	69		75	71	67	65
4	88	77	70	64	85	76	69	64	73	67	63		71	66	62		69	64	61	59
5	82	71	63	58	80	70	63	57	68	61	56		66	60	56		64	59	55	53
6	77	66	58	52	75	65	57	52	63	56	52		61	55	51		59	54	50	49
7	73	61	53	48	71	60	53	48	58	52	47		57	51	47		55	50	47	45
8	69	57	50	44	67	56	49	44	55	48	44		53	48	44		52	47	43	42
9	65	53	46	41	64	53	46	41	52	45	41		50	45	41		49	44	40	39
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	233392
5°	172207
10°	109506
15°	87035
20°	60014
25°	30174
30°	23758
35°	20703
40°	19084
45°	16912
50°	14069
55°	11149
60°	8842
65°	6996
70°	5473
75°	4373
80°	3587
85°	2886

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16912 cd/sqm

TEST NUMBER: P702700

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-CF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.5	10.4
10°-20°	481.0	20.0
20°-30°	349.3	14.5
30°-40°	320.5	13.3
40°-50°	330.6	13.7
50°-60°	259.8	10.8
60°-70°	176.6	7.3
70°-80°	113.1	4.7
80°-90°	69.9	2.9
90°-100°	40.5	1.7
100°-110°	12.2	0.5
110°-120°	0.4	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1080.9	45.0
0°-40°	1401.3	58.3
0°-60°	1991.6	82.8
0°-90°	2351.3	97.8
90°-120°	53.0	2.2
90°-150°	53.0	2.2
90°-180°	53.0	2.2
0°-180°	2404.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3577	
5°	2942	251
15°	1758	481
25°	685	349
35°	508	320
45°	433	331
55°	288	260
65°	178	177
75°	105	113
85°	64	56
90°	47	27
95°	39	28
105°	11	12
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702700

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-CF

CANDELA DISTRIBUTION (FULL):

0°	
0°	3577.4
2.5°	3452.6
5°	2942.4
7.5°	2390.5
10°	2049.4
12.5°	1869.1
15°	1758.2
17.5°	1622.3
20°	1292.3
22.5°	865.2
25°	685.0
27.5°	615.7
30°	563.0
32.5°	526.9
35°	507.5
37.5°	490.9
40°	479.8
42.5°	460.4
45°	432.6
47.5°	399.3
50°	363.3
52.5°	324.5
55°	288.4
57.5°	255.1
60°	227.4
62.5°	199.7
65°	177.5
67.5°	155.3
70°	135.9
72.5°	119.2
75°	105.4
77.5°	94.3
80°	83.2
82.5°	72.1
85°	63.8
87.5°	55.5
90°	47.1
92.5°	44.4
95°	38.8
97.5°	30.5
100°	22.2
102.5°	16.6
105°	11.1
107.5°	5.5
110°	2.8

TEST NUMBER: P702700

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-CF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)