

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P690911

Luminaire Tested: **CRTK2-C01-5TLD-U-T5R-7050-U0**

Issue Date: 6/13/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P690911  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-903-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/13/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: CRTK2-C01-5TLD-U-T5R-7050-U0  
Description: CARETAKER AREA AND ROADWAY LUMINAIRE  
(1) 70 CRI, 5000K LED WITH TYPE V ROUND OPTIC AND UO SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9230 lumens  
Efficiency: N/A  
Efficacy: 153.8 lumens/watt  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G2


Input Watts (W): 60  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P690911  
 CATALOG NUMBER: CRTK2-C01-5TLD-U-T5R-7050-U0

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.4 fc  
 Type V - Short - N/A

REPORT NUMBER: P690911  
CATALOG NUMBER: CRTK2-C01-5TLD-U-T5R-7050-U0

### Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P690911  
 CATALOG NUMBER: CRTK2-C01-5TLD-U-T5R-7050-U0


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	4615.0	0.0	4615.0
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	4615.0	0.0	4615.0
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	9230.0	0.0	9230.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.4	0.9
10°-20°	217.8	2.4
20°-30°	375.3	4.1
30°-40°	637.4	6.9
40°-50°	1124.5	12.2
50°-60°	1916.5	20.8
60°-70°	2756.6	29.9
70°-80°	2004.5	21.7
80°-90°	117.0	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9230.0	100.0
0°-180°	9230.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P690911  
 CATALOG NUMBER: CRTK2-C01-5TLD-U-T5R-7050-U0

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	336.8	3.6			
FM (30°-60°)	1839.2	19.9			
FH (60°-80°)	2380.5	25.8			G2/5000
FVH (80°-90°)	58.5	0.6			G1/100
BL (0°-30°)	336.8	3.6	B1/500		
BM (30°-60°)	1839.2	19.9	B2/2500		
BH (60°-80°)	2380.5	25.8	B3/2500		G2/5000
BVH (80°-90°)	58.5	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G2**  
 Type V Short



REPORT NUMBER: P690911  
CATALOG NUMBER: CRTK2-C01-5TLD-U-T5R-7050-U0

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	897.7
2.5°	883.1
5°	865.6
7.5°	833.6
10°	798.6
12.5°	775.3
15°	763.6
17.5°	760.7
20°	763.6
22.5°	778.2
25°	801.5
27.5°	833.6
30°	871.5
32.5°	923.9
35°	996.8
37.5°	1087.1
40°	1180.4
42.5°	1294.1
45°	1428.1
47.5°	1585.5
50°	1757.5
52.5°	1941.1
55°	2133.5
57.5°	2314.2
60°	2497.8
62.5°	2666.8
65°	2865.0
67.5°	2946.6
70°	2742.6
72.5°	2427.8
75°	2022.7
77.5°	1460.2
80°	652.9
82.5°	84.5
85°	17.5
87.5°	2.9
90°	0.0

(END OF REPORT)