

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P691003

Luminaire Tested: **CRTK2-C01-D-U-T5R-7050-U0**

Issue Date: 6/13/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P691003  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-903-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/13/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: CRTK2-C01-D-U-T5R-7050-U0  
Description: CARETAKER AREA AND ROADWAY LUMINAIRE  
(1) 70 CRI, 5000K LED WITH TYPE V ROUND OPTIC AND UO SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9237 lumens  
Efficiency: N/A  
Efficacy: 151.4 lumens/watt  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G2


Input Watts (W): 61  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P691003  
 CATALOG NUMBER: CRTK2-C01-D-U-T5R-7050-U0

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.4 fc  
 Type V - Short - N/A

REPORT NUMBER: P691003  
CATALOG NUMBER: CRTK2-C01-D-U-T5R-7050-U0

### Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P691003  
 CATALOG NUMBER: CRTK2-C01-D-U-T5R-7050-U0


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	4618.5	0.0	4618.5
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	4618.5	0.0	4618.5
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	9237.0	0.0	9237.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.5	0.9
10°-20°	218.0	2.4
20°-30°	375.6	4.1
30°-40°	637.8	6.9
40°-50°	1125.4	12.2
50°-60°	1918.0	20.8
60°-70°	2758.6	29.9
70°-80°	2006.0	21.7
80°-90°	117.1	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9237.0	100.0
0°-180°	9237.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P691003  
 CATALOG NUMBER: CRTK2-C01-D-U-T5R-7050-U0

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	337.0	3.6			
FM (30°-60°)	1840.6	19.9			
FH (60°-80°)	2382.3	25.8			G2/5000
FVH (80°-90°)	58.5	0.6			G1/100
BL (0°-30°)	337.0	3.6	B1/500		
BM (30°-60°)	1840.6	19.9	B2/2500		
BH (60°-80°)	2382.3	25.8	B3/2500		G2/5000
BVH (80°-90°)	58.5	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G2**  
 Type V Short



REPORT NUMBER: P691003  
CATALOG NUMBER: CRTK2-C01-D-U-T5R-7050-U0

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	898.4
2.5°	883.8
5°	866.3
7.5°	834.2
10°	799.2
12.5°	775.9
15°	764.2
17.5°	761.3
20°	764.2
22.5°	778.8
25°	802.1
27.5°	834.2
30°	872.1
32.5°	924.6
35°	997.5
37.5°	1088.0
40°	1181.3
42.5°	1295.0
45°	1429.2
47.5°	1586.7
50°	1758.8
52.5°	1942.6
55°	2135.1
57.5°	2315.9
60°	2499.7
62.5°	2668.8
65°	2867.2
67.5°	2948.8
70°	2744.7
72.5°	2429.7
75°	2024.2
77.5°	1461.3
80°	653.4
82.5°	84.6
85°	17.5
87.5°	2.9
90°	0.0

(END OF REPORT)