

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702737

Luminaire Tested: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-10)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-FF
Description: FARALLON 6" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2711.1 lumens
Efficiency: N/A
Efficacy: 57.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.81
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702737

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

Luminous Intensity Polar Plot



TEST NUMBER: P702737

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		99	99	99	97
1	110	106	102	99	107	103	100	97	99	96	93		94	92	90		90	89	87	85
2	102	96	90	86	100	94	89	84	90	86	82		86	83	80		83	80	78	76
3	96	87	81	76	93	86	80	75	83	77	73		80	75	72		77	73	70	68
4	90	80	73	68	88	79	72	67	76	71	66		74	69	65		71	67	64	62
5	85	74	67	62	83	73	66	61	71	65	61		69	64	60		67	62	59	57
6	80	69	62	57	78	68	61	56	66	60	56		64	59	55		63	58	54	53
7	75	64	57	52	74	64	57	52	62	56	52		60	55	51		59	54	51	49
8	71	60	53	49	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	68	57	50	45	66	56	50	45	55	49	45		54	48	45		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153583
5°	136781
10°	119979
15°	106613
20°	93705
25°	78258
30°	35122
35°	18708
40°	14864
45°	11951
50°	9604
55°	7615
60°	6342
65°	5356
70°	4925
75°	4510
80°	4101
85°	3687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11951 cd/sqm

TEST NUMBER: P702737

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.9	8.1
10°-20°	605.0	22.3
20°-30°	737.9	27.2
30°-40°	312.4	11.5
40°-50°	237.1	8.7
50°-60°	179.5	6.6
60°-70°	137.2	5.1
70°-80°	114.9	4.2
80°-90°	88.9	3.3
90°-100°	59.3	2.2
100°-110°	17.6	0.7
110°-120°	1.3	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1562.9	57.6
0°-40°	1875.3	69.2
0°-60°	2291.9	84.5
0°-90°	2632.8	97.1
90°-120°	78.3	2.9
90°-150°	78.3	2.9
90°-180°	78.0	2.9
0°-180°	2711.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2354	
5°	2337	220
15°	2154	605
25°	1777	738
35°	459	312
45°	306	237
55°	197	179
65°	136	137
75°	109	115
85°	82	69
90°	68	38
95°	58	41
105°	14	18
115°	0	1
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702737

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

CANDELA DISTRIBUTION (FULL):

0°	
0°	2354.1
2.5°	2350.7
5°	2337.1
7.5°	2296.4
10°	2245.4
12.5°	2201.2
15°	2153.7
17.5°	2095.9
20°	2017.8
22.5°	1922.7
25°	1776.6
27.5°	1386.0
30°	832.3
32.5°	546.9
35°	458.6
37.5°	411.0
40°	373.7
42.5°	339.7
45°	305.7
47.5°	275.2
50°	248.0
52.5°	220.8
55°	197.0
57.5°	180.0
60°	163.1
62.5°	146.1
65°	135.9
67.5°	129.1
70°	122.3
72.5°	115.5
75°	108.7
77.5°	101.9
80°	95.1
82.5°	88.3
85°	81.5
87.5°	74.7
90°	67.9
92.5°	64.5
95°	57.7
97.5°	44.2
100°	34.0
102.5°	23.8
105°	13.6
107.5°	10.2
110°	3.4

TEST NUMBER: P702737

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	3.4
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)