

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702739

Luminaire Tested: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702739
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2987.2 lumens
Efficiency: N/A
Efficacy: 63.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702739

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P702739

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	168654
5°	151494
10°	130687
15°	82396
20°	58843
25°	45190
30°	36409
35°	30625
40°	27023
45°	23109
50°	18550
55°	14446
60°	11358
65°	8971
70°	7249
75°	5779
80°	4687
85°	3687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23109 cd/sqm

TEST NUMBER: P702739

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.4	8.1
10°-20°	480.4	16.1
20°-30°	476.0	15.9
30°-40°	474.2	15.9
40°-50°	452.6	15.2
50°-60°	337.8	11.3
60°-70°	229.0	7.7
70°-80°	149.3	5.0
80°-90°	90.7	3.0
90°-100°	47.3	1.6
100°-110°	6.4	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1199.8	40.2
0°-40°	1674.0	56.0
0°-60°	2464.4	82.5
0°-90°	2933.5	98.2
90°-120°	53.7	1.8
90°-150°	53.7	1.8
90°-180°	54.0	1.8
0°-180°	2987.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2585	
5°	2588	243
15°	1664	480
25°	1026	476
35°	751	474
45°	591	453
55°	374	338
65°	228	229
75°	139	149
85°	82	73
90°	61	34
95°	44	32
105°	3	6
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702739

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2585.1
2.5°	2588.5
5°	2588.5
7.5°	2568.1
10°	2445.8
12.5°	2068.8
15°	1664.5
17.5°	1436.9
20°	1267.1
22.5°	1131.2
25°	1025.9
27.5°	937.6
30°	862.8
32.5°	798.3
35°	750.7
37.5°	713.4
40°	679.4
42.5°	642.0
45°	591.1
47.5°	536.7
50°	479.0
52.5°	424.6
55°	373.7
57.5°	329.5
60°	292.1
62.5°	258.2
65°	227.6
67.5°	203.8
70°	180.0
72.5°	159.7
75°	139.3
77.5°	122.3
80°	108.7
82.5°	95.1
85°	81.5
87.5°	71.3
90°	61.1
92.5°	54.4
95°	44.2
97.5°	34.0
100°	20.4
102.5°	10.2
105°	3.4
107.5°	0.0
110°	0.0

TEST NUMBER: P702739

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)