

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702257

Luminaire Tested: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702257
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-14)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, FROSTED OUTSIDE KIT.
Light Source: 2400K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 369.9 lumens
Efficiency: N/A
Efficacy: 51.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.63
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702257

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

Luminous Intensity Polar Plot



TEST NUMBER: P702257

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109		104	104	104		99	99	99	96
1	107	102	97	93	104	99	95	91	94	91	88		90	87	84		85	83	81	79
2	98	89	82	77	95	87	81	75	83	78	73		79	75	71		76	72	69	66
3	90	79	71	65	87	77	70	64	74	68	62		71	65	61		68	63	59	57
4	83	71	63	56	80	70	62	56	67	60	54		64	58	53		61	56	52	50
5	77	65	56	49	75	63	55	49	61	54	48		58	52	47		56	51	47	44
6	72	59	50	44	70	58	50	44	56	49	43		54	47	43		52	46	42	40
7	67	54	46	40	65	53	45	40	51	44	39		50	43	39		48	43	38	36
8	63	50	42	37	61	49	42	36	48	41	36		46	40	36		45	39	35	33
9	60	47	39	34	58	46	39	34	45	38	33		43	37	33		42	37	33	31
10	56	44	36	31	55	43	36	31	42	35	31		41	35	31		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20851
5°	18488
10°	15410
15°	8623
20°	5763
25°	4453
30°	3600
35°	3002
40°	2677
45°	2451
50°	2238
55°	2006
60°	1789
65°	1549
70°	1325
75°	1124
80°	953
85°	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2451 cd/sqm

TEST NUMBER: P702257

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.4	7.9
10°-20°	51.1	13.8
20°-30°	46.9	12.7
30°-40°	46.6	12.6
40°-50°	48.4	13.1
50°-60°	46.6	12.6
60°-70°	38.9	10.5
70°-80°	28.7	7.8
80°-90°	19.5	5.3
90°-100°	11.2	3.0
100°-110°	2.4	0.6
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	127.4	34.4
0°-40°	174.1	47.1
0°-60°	269.1	72.7
0°-90°	356.2	96.3
90°-120°	13.7	3.7
90°-150°	13.7	3.7
90°-180°	14.0	3.8
0°-180°	369.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	320	
5°	316	29
15°	174	51
25°	101	47
35°	74	47
45°	63	48
55°	52	47
65°	39	39
75°	27	29
85°	18	15
90°	14	8
95°	11	8
105°	2	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702257

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	319.6
2.5°	319.1
5°	315.9
7.5°	308.7
10°	288.4
12.5°	232.9
15°	174.2
17.5°	143.1
20°	124.1
22.5°	111.0
25°	101.1
27.5°	93.0
30°	85.3
32.5°	78.5
35°	73.6
37.5°	70.0
40°	67.3
42.5°	65.0
45°	62.7
47.5°	60.5
50°	57.8
52.5°	55.1
55°	51.9
57.5°	49.2
60°	46.0
62.5°	42.4
65°	39.3
67.5°	36.1
70°	32.9
72.5°	29.8
75°	27.1
77.5°	24.4
80°	22.1
82.5°	19.9
85°	17.6
87.5°	15.8
90°	14.0
92.5°	12.6
95°	10.8
97.5°	8.1
100°	5.4
102.5°	3.2
105°	1.8
107.5°	0.9
110°	0.5

TEST NUMBER: P702257

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)