

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702297

Luminaire Tested: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-GCC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702297
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-16)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-GCC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA
Light Source: 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 509.4 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.89
Luminous Opening: (L: -0.46 ' x W: 0 ' x H: 0 '
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702297

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-GCC

Luminous Intensity Polar Plot




TEST NUMBER: P702297

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-GCC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	101	96	92	104	99	95	91	96	92	89		92	90	87		90	87	85	84
3	100	93	87	83	98	91	86	82	88	84	81		86	82	79		84	81	78	76
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	71	70
5	89	79	73	68	87	78	72	68	77	71	67		75	70	66		73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	58	78	68	62	57	67	61	57		66	60	57		64	60	56	55
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61	56	52	51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49	48
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54	49	46	44

AVERAGE LUMINANCE (cd/sqm):



MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: -
 Vertical Angle: -
 Luminance: -

TEST NUMBER: P702297

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-GCC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	9.2
10°-20°	117.1	23.0
20°-30°	138.0	27.1
30°-40°	107.3	21.1
40°-50°	58.9	11.6
50°-60°	24.5	4.8
60°-70°	10.4	2.0
70°-80°	4.5	0.9
80°-90°	1.2	0.2
90°-100°	0.5	0.1
100°-110°	0.3	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	301.8	59.2
0°-40°	409.1	80.3
0°-60°	492.5	96.7
0°-90°	508.6	99.8
90°-120°	0.9	0.2
90°-150°	0.9	0.2
90°-180°	1.0	0.2
0°-180°	509.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	521	
5°	499	47
15°	415	117
25°	300	138
35°	167	107
45°	74	59
55°	27	25
65°	10	10
75°	4	4
85°	1	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702297

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-GCC

CANDELA DISTRIBUTION (FULL):

0°	
0°	521.2
2.5°	515.6
5°	499.2
7.5°	484.3
10°	469.4
12.5°	442.2
15°	415.0
17.5°	397.6
20°	364.8
22.5°	325.3
25°	300.1
27.5°	275.5
30°	244.7
32.5°	207.3
35°	166.7
37.5°	137.5
40°	119.0
42.5°	101.1
45°	73.9
47.5°	53.4
50°	41.6
52.5°	32.8
55°	26.7
57.5°	21.5
60°	16.9
62.5°	12.3
65°	9.7
67.5°	8.2
70°	6.7
72.5°	5.1
75°	4.1
77.5°	3.1
80°	2.6
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.5
92.5°	0.5
95°	0.5
97.5°	0.5
100°	0.5
102.5°	0.5
105°	0.5
107.5°	0.0
110°	0.0

TEST NUMBER: P702297

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-GCC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)