

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702304

Luminaire Tested: 340-6C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702304  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA  
Light Source: 3000K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 529.5 lumens  
Efficiency: N/A  
Efficacy: 73.5 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.89  
Luminous Opening: (L: -0.46 ' x W: 0 ' x H: 0 '  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702304

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

### Luminous Intensity Polar Plot




TEST NUMBER: P702304

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	101	96	92	104	99	95	91	96	92	89		92	90	87		90	87	85	84
3	100	93	87	83	98	91	86	82	88	84	81		86	82	79		84	81	78	76
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	71	70
5	89	79	73	68	87	78	72	68	77	71	67		75	70	66		73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	58	78	68	62	57	67	61	57		66	60	57		64	60	56	55
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61	56	52	51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49	48
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54	49	46	44

**AVERAGE LUMINANCE (cd/sqm):**



**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: -  
 Vertical Angle: -  
 Luminance: -

TEST NUMBER: P702304

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.6	9.2
10°-20°	121.7	23.0
20°-30°	143.5	27.1
30°-40°	111.5	21.1
40°-50°	61.2	11.6
50°-60°	25.5	4.8
60°-70°	10.8	2.0
70°-80°	4.6	0.9
80°-90°	1.3	0.2
90°-100°	0.5	0.1
100°-110°	0.3	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	313.8	59.2
0°-40°	425.3	80.3
0°-60°	512.0	96.7
0°-90°	528.7	99.8
90°-120°	0.9	0.2
90°-150°	0.9	0.2
90°-180°	1.0	0.2
0°-180°	529.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	542	
5°	519	49
15°	432	122
25°	312	143
35°	173	112
45°	77	61
55°	28	25
65°	10	11
75°	4	5
85°	1	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702304

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	541.8
2.5°	536.0
5°	518.9
7.5°	503.4
10°	488.0
12.5°	459.7
15°	431.5
17.5°	413.3
20°	379.2
22.5°	338.1
25°	312.0
27.5°	286.4
30°	254.4
32.5°	215.5
35°	173.3
37.5°	142.9
40°	123.7
42.5°	105.1
45°	76.8
47.5°	55.5
50°	43.2
52.5°	34.1
55°	27.7
57.5°	22.4
60°	17.6
62.5°	12.8
65°	10.1
67.5°	8.5
70°	6.9
72.5°	5.3
75°	4.3
77.5°	3.2
80°	2.7
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.5
92.5°	0.5
95°	0.5
97.5°	0.5
100°	0.5
102.5°	0.5
105°	0.5
107.5°	0.0
110°	0.0

TEST NUMBER: P702304

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)