

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702357

Luminaire Tested: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-12)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL FROSTED GLASS KIT.
Light Source: 3000K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 621.2 lumens
Efficiency: N/A
Efficacy: 62.7 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.55
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702357

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

Luminous Intensity Polar Plot



TEST NUMBER: P702357

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	98	107	103	99	96	98	95	93		94	92	90		90	88	87	84
2	101	94	88	83	99	92	87	82	88	84	80		85	81	78		82	79	76	74
3	94	85	78	72	92	83	77	72	80	75	70		77	73	69		75	71	67	65
4	88	77	70	64	85	76	69	64	73	67	63		71	66	62		69	64	61	59
5	82	71	63	58	80	70	63	57	68	61	56		66	60	56		64	59	55	53
6	77	66	58	52	75	65	57	52	63	56	52		61	55	51		59	54	50	49
7	73	61	53	48	71	60	53	48	58	52	47		57	51	47		55	50	47	45
8	69	57	50	44	67	56	49	44	55	48	44		53	48	44		52	47	43	42
9	65	53	46	41	64	53	46	41	52	45	41		50	45	41		49	44	40	39
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60302
5°	44491
10°	28293
15°	22489
20°	15506
25°	7797
30°	6136
35°	5348
40°	4932
45°	4371
50°	3636
55°	2880
60°	2286
65°	1809
70°	1414
75°	1128
80°	927
85°	746

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4371 cd/sqm

TEST NUMBER: P702357

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.7	10.4
10°-20°	124.3	20.0
20°-30°	90.3	14.5
30°-40°	82.8	13.3
40°-50°	85.4	13.8
50°-60°	67.1	10.8
60°-70°	45.6	7.3
70°-80°	29.2	4.7
80°-90°	18.1	2.9
90°-100°	10.5	1.7
100°-110°	3.1	0.5
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.3	45.0
0°-40°	362.0	58.3
0°-60°	514.6	82.8
0°-90°	607.5	97.8
90°-120°	13.7	2.2
90°-150°	13.7	2.2
90°-180°	14.0	2.3
0°-180°	621.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	924	
5°	760	65
15°	454	124
25°	177	90
35°	131	83
45°	112	85
55°	74	67
65°	46	46
75°	27	29
85°	16	14
90°	12	7
95°	10	7
105°	3	3
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702357

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

CANDELA DISTRIBUTION (FULL):

0°	
0°	924.3
2.5°	892.0
5°	760.2
7.5°	617.6
10°	529.5
12.5°	482.9
15°	454.3
17.5°	419.2
20°	333.9
22.5°	223.5
25°	177.0
27.5°	159.1
30°	145.4
32.5°	136.1
35°	131.1
37.5°	126.8
40°	124.0
42.5°	118.9
45°	111.8
47.5°	103.2
50°	93.9
52.5°	83.8
55°	74.5
57.5°	65.9
60°	58.8
62.5°	51.6
65°	45.9
67.5°	40.1
70°	35.1
72.5°	30.8
75°	27.2
77.5°	24.4
80°	21.5
82.5°	18.6
85°	16.5
87.5°	14.3
90°	12.2
92.5°	11.5
95°	10.0
97.5°	7.9
100°	5.7
102.5°	4.3
105°	2.9
107.5°	1.4
110°	0.7

TEST NUMBER: P702357

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)