

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702361

Luminaire Tested: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-GFC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 3000K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 630.1 lumens
Efficiency: N/A
Efficacy: 63.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702361

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P702361

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35576
5°	31955
10°	27566
15°	17380
20°	12413
25°	9532
30°	7680
35°	6458
40°	5700
45°	4875
50°	3911
55°	3046
60°	2395
65°	1892
70°	1530
75°	1220
80°	987
85°	778

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4875 cd/sqm

TEST NUMBER: P702361

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.3	8.1
10°-20°	101.3	16.1
20°-30°	100.4	15.9
30°-40°	100.0	15.9
40°-50°	95.5	15.2
50°-60°	71.3	11.3
60°-70°	48.3	7.7
70°-80°	31.5	5.0
80°-90°	19.1	3.0
90°-100°	10.0	1.6
100°-110°	1.3	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	253.1	40.2
0°-40°	353.1	56.0
0°-60°	519.8	82.5
0°-90°	618.8	98.2
90°-120°	11.3	1.8
90°-150°	11.3	1.8
90°-180°	11.0	1.7
0°-180°	630.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	545	
5°	546	51
15°	351	101
25°	216	100
35°	158	100
45°	125	95
55°	79	71
65°	48	48
75°	29	32
85°	17	15
90°	13	7
95°	9	7
105°	1	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702361

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	545.3
2.5°	546.0
5°	546.0
7.5°	541.7
10°	515.9
12.5°	436.4
15°	351.1
17.5°	303.1
20°	267.3
22.5°	238.6
25°	216.4
27.5°	197.8
30°	182.0
32.5°	168.4
35°	158.3
37.5°	150.5
40°	143.3
42.5°	135.4
45°	124.7
47.5°	113.2
50°	101.0
52.5°	89.6
55°	78.8
57.5°	69.5
60°	61.6
62.5°	54.5
65°	48.0
67.5°	43.0
70°	38.0
72.5°	33.7
75°	29.4
77.5°	25.8
80°	22.9
82.5°	20.1
85°	17.2
87.5°	15.0
90°	12.9
92.5°	11.5
95°	9.3
97.5°	7.2
100°	4.3
102.5°	2.1
105°	0.7
107.5°	0.0
110°	0.0

TEST NUMBER: P702361

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)