

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702333

Luminaire Tested: 340-6C-08-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-08-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 638.6 lumens
Efficiency: N/A
Efficacy: 64.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702333

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P702333

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	77	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36052
5°	32388
10°	27940
15°	17613
20°	12580
25°	9660
30°	7786
35°	6548
40°	5775
45°	4941
50°	3966
55°	3089
60°	2430
65°	1919
70°	1550
75°	1236
80°	1000
85°	787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4941 cd/sqm

TEST NUMBER: P702333

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.0	8.1
10°-20°	102.7	16.1
20°-30°	101.7	15.9
30°-40°	101.4	15.9
40°-50°	96.8	15.2
50°-60°	72.2	11.3
60°-70°	49.0	7.7
70°-80°	31.9	5.0
80°-90°	19.4	3.0
90°-100°	10.1	1.6
100°-110°	1.4	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.5	40.2
0°-40°	357.9	56.0
0°-60°	526.8	82.5
0°-90°	627.1	98.2
90°-120°	11.5	1.8
90°-150°	11.5	1.8
90°-180°	11.0	1.7
0°-180°	638.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	553	
5°	553	52
15°	356	103
25°	219	102
35°	160	101
45°	126	97
55°	80	72
65°	49	49
75°	30	32
85°	17	15
90°	13	7
95°	9	7
105°	1	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702333

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	552.6
2.5°	553.4
5°	553.4
7.5°	549.0
10°	522.9
12.5°	442.2
15°	355.8
17.5°	307.2
20°	270.9
22.5°	241.8
25°	219.3
27.5°	200.4
30°	184.5
32.5°	170.7
35°	160.5
37.5°	152.5
40°	145.2
42.5°	137.2
45°	126.4
47.5°	114.7
50°	102.4
52.5°	90.8
55°	79.9
57.5°	70.4
60°	62.5
62.5°	55.2
65°	48.7
67.5°	43.6
70°	38.5
72.5°	34.1
75°	29.8
77.5°	26.1
80°	23.2
82.5°	20.3
85°	17.4
87.5°	15.2
90°	13.1
92.5°	11.6
95°	9.4
97.5°	7.3
100°	4.4
102.5°	2.2
105°	0.7
107.5°	0.0
110°	0.0

TEST NUMBER: P702333

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)