

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702342

Luminaire Tested: 340-6C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702342
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-11)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-CC
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 681.6 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.71
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702342

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

Luminous Intensity Polar Plot



TEST NUMBER: P702342

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	61		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	54	50	69	60	54	50	59	54	50		58	53	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77415
5°	63211
10°	46320
15°	39998
20°	34256
25°	31666
30°	25523
35°	16574
40°	12528
45°	6994
50°	4070
55°	2707
60°	1840
65°	1142
70°	992
75°	756
80°	564
85°	524

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6994 cd/sqm

TEST NUMBER: P702342

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.5	12.2
10°-20°	165.7	24.3
20°-30°	195.9	28.7
30°-40°	137.1	20.1
40°-50°	64.0	9.4
50°-60°	22.2	3.3
60°-70°	8.4	1.2
70°-80°	3.4	0.5
80°-90°	0.8	0.1
90°-100°	0.5	0.1
100°-110°	0.3	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.1	65.3
0°-40°	582.2	85.4
0°-60°	668.4	98.1
0°-90°	681.0	99.9
90°-120°	0.8	0.1
90°-150°	0.8	0.1
90°-180°	1.0	0.1
0°-180°	681.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1187	
5°	965	83
15°	592	166
25°	440	196
35°	208	137
45°	76	64
55°	24	22
65°	7	8
75°	3	3
85°	1	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702342

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1186.6
2.5°	1127.9
5°	965.2
7.5°	804.7
10°	699.2
12.5°	636.8
15°	592.2
17.5°	552.1
20°	493.4
22.5°	449.5
25°	439.9
27.5°	402.7
30°	338.8
32.5°	266.8
35°	208.1
37.5°	170.2
40°	147.1
42.5°	114.4
45°	75.8
47.5°	52.8
50°	40.1
52.5°	30.5
55°	23.8
57.5°	18.6
60°	14.1
62.5°	10.4
65°	7.4
67.5°	6.7
70°	5.2
72.5°	4.5
75°	3.0
77.5°	2.2
80°	1.5
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.7
100°	0.7
102.5°	0.7
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P702342

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)