

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P320514

Luminaire Tested: **GAN-SA0A-722-U-SLL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P320514  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GAN-SA0A-722-U-SLL  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(10) 70 CRI, 2200K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 29800 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Luminous Opening: Rectangular (W 2.5' x L: 1' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B3 - U0 - G5


Input Watts (W): 323  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P320514  
 CATALOG NUMBER: GAN-SA0A-722-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 18.3 fc  
 Type III - Medium - N/A

REPORT NUMBER: P320514  
CATALOG NUMBER: GAN-SA0A-722-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P320514  
 CATALOG NUMBER: GAN-SA0A-722-U-SLL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 5248.5   | 0.0    | 5248.5  |
|                    | % Fixture | 17.6     | 0.0    | 17.6    |
| <b>Street Side</b> | Lumens    | 24551.5  | 0.0    | 24551.5 |
|                    | % Fixture | 82.4     | 0.0    | 82.4    |
| <b>Total</b>       | Lumens    | 29800.0  | 0.0    | 29800.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 700.7   | 2.4       |
| 10°-20°   | 1455.6  | 4.9       |
| 20°-30°   | 2070.2  | 6.9       |
| 30°-40°   | 2983.1  | 10.0      |
| 40°-50°   | 4204.0  | 14.1      |
| 50°-60°   | 5844.3  | 19.6      |
| 60°-70°   | 7067.5  | 23.7      |
| 70°-80°   | 4344.3  | 14.6      |
| 80°-90°   | 1130.5  | 3.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 29800.0 | 100.0     |
| 0°-180°   | 29800.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P320514  
 CATALOG NUMBER: GAN-SA0A-722-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|----------------|---------|-----------|-------------------------|------|----------|
|                |         |           | B                       | U    | G        |
| FL (0°-30°)    | 2958.8  | 9.9       |                         |      |          |
| FM (30°-60°)   | 10648.9 | 35.7      |                         |      |          |
| FH (60°-80°)   | 9940.3  | 33.4      |                         |      | G4/12000 |
| FVH (80°-90°)  | 1003.4  | 3.4       |                         |      | G5       |
| BL (0°-30°)    | 1267.6  | 4.3       | B3/2500                 |      |          |
| BM (30°-60°)   | 2382.4  | 8.0       | B2/2500                 |      |          |
| BH (60°-80°)   | 1471.5  | 4.9       | B3/2500                 |      | G3/2500  |
| BVH (80°-90°)  | 127.0   | 0.4       |                         |      | G2/225   |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G5**  
 Type III Medium





REPORT NUMBER: P320514

CATALOG NUMBER: GAN-SA0A-722-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     | 50°     |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  |
| 2.5°   | 9676.8  | 9804.3  | 9892.5  | 9979.4  | 10047.3 | 10114.1 | 10211.8 | 10309.5 | 10328.5 | 10346.4 | 10308.3 |
| 5°     | 9619.6  | 9930.6  | 10195.1 | 10458.4 | 10702.6 | 10946.9 | 11093.4 | 11240.0 | 11269.8 | 11299.5 | 11207.8 |
| 7.5°   | 9003.6  | 9462.4  | 9921.1  | 10379.8 | 10800.3 | 11220.9 | 11477.1 | 11732.0 | 11790.4 | 11847.6 | 11697.5 |
| 10°    | 8303.1  | 8836.8  | 9400.4  | 9963.9  | 10518.0 | 11072.0 | 11442.5 | 11813.0 | 11886.9 | 11960.8 | 11773.7 |
| 12.5°  | 7770.5  | 8353.1  | 8954.8  | 9556.5  | 10141.5 | 10725.3 | 11108.9 | 11492.6 | 11584.3 | 11676.0 | 11540.2 |
| 15°    | 7565.6  | 8204.2  | 8770.1  | 9336.1  | 9846.0  | 10354.7 | 10669.3 | 10982.6 | 11020.7 | 11057.7 | 11036.2 |
| 17.5°  | 7770.5  | 8474.7  | 8987.0  | 9498.1  | 9775.7  | 10052.1 | 10178.4 | 10303.5 | 10345.2 | 10385.7 | 10440.5 |
| 20°    | 8369.8  | 9129.9  | 9490.9  | 9850.8  | 9838.8  | 9825.7  | 9765.0  | 9703.0  | 9692.3  | 9681.6  | 9836.5  |
| 22.5°  | 9225.3  | 10108.1 | 10252.3 | 10395.2 | 10060.4 | 9725.7  | 9521.9  | 9317.0  | 9276.5  | 9234.8  | 9399.2  |
| 25°    | 10229.6 | 11169.7 | 11143.5 | 11116.1 | 10478.6 | 9840.0  | 9451.6  | 9063.2  | 9017.9  | 8972.7  | 9113.3  |
| 27.5°  | 11322.2 | 12220.5 | 12048.9 | 11877.4 | 11011.2 | 10145.0 | 9581.5  | 9017.9  | 8972.7  | 8927.4  | 9051.3  |
| 30°    | 12176.4 | 12991.4 | 12716.2 | 12440.9 | 11460.4 | 10479.8 | 9810.2  | 9140.7  | 9066.8  | 8991.7  | 9144.2  |
| 32.5°  | 12899.6 | 13593.0 | 13223.7 | 12854.4 | 11825.0 | 10795.6 | 10071.2 | 9346.8  | 9231.2  | 9115.6  | 9319.4  |
| 35°    | 13652.6 | 14193.5 | 13674.1 | 13153.4 | 12150.2 | 11145.8 | 10379.8 | 9612.5  | 9470.7  | 9328.9  | 9608.9  |
| 37.5°  | 14499.7 | 14948.9 | 14203.1 | 13456.0 | 12516.0 | 11576.0 | 10842.0 | 10106.9 | 9961.6  | 9816.2  | 10173.6 |
| 40°    | 15394.5 | 15768.6 | 14773.8 | 13778.9 | 12916.3 | 12053.7 | 11481.8 | 10908.7 | 10770.5 | 10631.1 | 11064.8 |
| 42.5°  | 16177.3 | 16450.1 | 15305.1 | 14160.2 | 13398.8 | 12636.3 | 12233.6 | 11829.7 | 11828.5 | 11826.2 | 12265.8 |
| 45°    | 16767.0 | 17004.1 | 15748.3 | 14491.4 | 13869.5 | 13246.3 | 13036.6 | 12827.0 | 12994.9 | 13162.9 | 13560.9 |
| 47.5°  | 17256.7 | 17417.5 | 16120.1 | 14821.4 | 14408.0 | 13994.6 | 14025.5 | 14056.5 | 14398.5 | 14740.4 | 14996.6 |
| 50°    | 17816.7 | 17686.8 | 16457.2 | 15226.5 | 15099.0 | 14971.5 | 15250.3 | 15527.9 | 15921.1 | 16313.1 | 16487.0 |
| 52.5°  | 18423.1 | 18078.8 | 16914.8 | 15749.5 | 15892.5 | 16035.5 | 16602.6 | 17169.7 | 17566.5 | 17963.2 | 18028.7 |
| 55°    | 19513.3 | 18985.5 | 17755.9 | 16525.2 | 16800.4 | 17074.4 | 17907.2 | 18738.8 | 19048.6 | 19358.4 | 19382.2 |
| 57.5°  | 20741.6 | 20273.4 | 18934.2 | 17595.1 | 17890.5 | 18186.0 | 19147.5 | 20107.8 | 20442.6 | 20776.2 | 20729.7 |
| 60°    | 21214.6 | 21237.3 | 20053.0 | 18867.5 | 19165.4 | 19463.2 | 20399.7 | 21336.2 | 21721.0 | 22104.6 | 22002.2 |
| 62.5°  | 20738.1 | 21296.8 | 20664.2 | 20030.3 | 20300.8 | 20570.1 | 21487.5 | 22404.9 | 22799.2 | 23193.6 | 23014.9 |
| 65°    | 19795.6 | 20349.7 | 20633.2 | 20916.8 | 21006.1 | 21095.5 | 21952.1 | 22807.6 | 23110.2 | 23411.6 | 23321.1 |
| 67.5°  | 18597.1 | 19045.0 | 20091.1 | 21136.0 | 20956.1 | 20776.2 | 21177.7 | 21579.2 | 21890.2 | 22201.1 | 22149.9 |
| 70°    | 17209.0 | 17742.8 | 19138.0 | 20533.1 | 19649.1 | 18763.9 | 18598.2 | 18432.6 | 18768.6 | 19103.4 | 18896.1 |
| 72.5°  | 14720.1 | 15525.5 | 17013.6 | 18500.6 | 16871.9 | 15243.2 | 14677.2 | 14111.3 | 14536.7 | 14962.0 | 14632.0 |
| 75°    | 11118.4 | 12187.2 | 13831.3 | 15474.3 | 13531.1 | 11587.9 | 10832.5 | 10077.1 | 10442.9 | 10808.7 | 10582.3 |
| 77.5°  | 7732.4  | 9072.8  | 10691.9 | 12311.1 | 10335.7 | 8359.1  | 7797.9  | 7235.6  | 7345.2  | 7453.6  | 7415.5  |
| 80°    | 5272.1  | 6153.7  | 7283.2  | 8411.5  | 7096.2  | 5780.8  | 5824.9  | 5867.8  | 5816.6  | 5764.1  | 5840.4  |
| 82.5°  | 3306.2  | 3927.0  | 4799.1  | 5670.0  | 4971.8  | 4273.7  | 4674.0  | 5074.3  | 4877.7  | 4679.9  | 4753.8  |
| 85°    | 1862.2  | 2241.1  | 3094.1  | 3946.0  | 3677.9  | 3408.7  | 3643.4  | 3876.9  | 3571.9  | 3266.9  | 3401.5  |
| 87.5°  | 355.0   | 591.0   | 1712.1  | 2832.0  | 2571.1  | 2310.2  | 2007.6  | 1704.9  | 1301.0  | 897.1   | 1310.6  |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320514  
 CATALOG NUMBER: GAN-SA0A-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 5°  | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |





REPORT NUMBER: P320514

CATALOG NUMBER: GAN-SAOA-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°     | 100°    | 105°   |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|--------|
| 0°     | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7  | 9078.7 |
| 2.5°   | 10270.1 | 10249.9 | 10229.6 | 10157.0 | 10083.1 | 9973.5  | 9882.9  | 9725.7  | 9639.9  | 9510.0  | 9380.1 |
| 5°     | 11114.9 | 10986.2 | 10857.5 | 10635.9 | 10413.1 | 10165.3 | 9880.5  | 9564.8  | 9326.5  | 9016.8  | 8707.0 |
| 7.5°   | 11547.4 | 11247.1 | 10945.7 | 10520.3 | 10093.8 | 9710.2  | 9259.8  | 8840.4  | 8483.0  | 8080.3  | 7677.6 |
| 10°    | 11586.7 | 11136.3 | 10684.8 | 10131.9 | 9577.9  | 9112.1  | 8593.8  | 8127.9  | 7699.0  | 7236.8  | 6773.3 |
| 12.5°  | 11403.2 | 10924.2 | 10444.1 | 9835.3  | 9225.3  | 8696.3  | 8138.7  | 7616.8  | 7141.4  | 6632.7  | 6122.8 |
| 15°    | 11014.8 | 10632.3 | 10248.7 | 9678.0  | 9107.3  | 8573.5  | 8032.6  | 7414.3  | 6876.9  | 6356.3  | 5834.4 |
| 17.5°  | 10494.1 | 10313.0 | 10130.7 | 9718.5  | 9305.1  | 8842.8  | 8318.6  | 7593.0  | 6963.9  | 6398.0  | 5832.1 |
| 20°    | 9990.2  | 10056.9 | 10122.4 | 9958.0  | 9793.6  | 9423.0  | 8965.5  | 8150.6  | 7347.6  | 6607.7  | 5866.6 |
| 22.5°  | 9562.4  | 9882.9  | 10202.2 | 10329.7 | 10456.0 | 10233.2 | 9875.8  | 8933.4  | 7870.6  | 6904.3  | 5938.1 |
| 25°    | 9252.7  | 9784.0  | 10315.4 | 10739.6 | 11162.5 | 11063.6 | 10788.4 | 9884.1  | 8564.0  | 7332.1  | 6098.9 |
| 27.5°  | 9175.2  | 9826.9  | 10478.6 | 11136.3 | 11792.8 | 11884.5 | 11808.3 | 10886.1 | 9390.9  | 7863.4  | 6334.8 |
| 30°    | 9296.7  | 9956.8  | 10615.7 | 11416.3 | 12215.7 | 12581.5 | 12684.0 | 11721.3 | 10335.7 | 8483.0  | 6629.1 |
| 32.5°  | 9523.1  | 10170.1 | 10817.0 | 11689.1 | 12560.1 | 13112.9 | 13439.3 | 12485.0 | 10994.5 | 8950.0  | 6904.3 |
| 35°    | 9888.9  | 10494.1 | 11099.4 | 12007.2 | 12915.1 | 13630.0 | 14225.7 | 13273.7 | 11579.5 | 9276.5  | 6972.3 |
| 37.5°  | 10529.9 | 11050.5 | 11571.2 | 12410.0 | 13247.5 | 14174.5 | 15069.2 | 14142.3 | 12212.2 | 9591.0  | 6968.7 |
| 40°    | 11498.5 | 11866.7 | 12233.6 | 12942.5 | 13650.2 | 14816.6 | 16024.8 | 15110.9 | 12911.5 | 9931.8  | 6952.0 |
| 42.5°  | 12705.4 | 12894.9 | 13083.1 | 13644.3 | 14205.4 | 15487.4 | 16892.1 | 16058.1 | 13578.7 | 10248.7 | 6918.6 |
| 45°    | 13957.6 | 14007.7 | 14057.7 | 14411.6 | 14764.2 | 16018.8 | 17483.1 | 16769.4 | 14161.4 | 10523.9 | 6885.3 |
| 47.5°  | 15251.5 | 15080.0 | 14908.4 | 15049.0 | 15189.6 | 16426.3 | 17904.8 | 17309.1 | 14746.4 | 10828.9 | 6910.3 |
| 50°    | 16661.0 | 16183.2 | 15705.5 | 15631.6 | 15557.7 | 16833.7 | 18401.7 | 17995.4 | 15449.3 | 11273.3 | 7097.4 |
| 52.5°  | 18093.1 | 17305.5 | 16518.0 | 16226.1 | 15933.0 | 17319.8 | 19060.5 | 18849.6 | 16452.5 | 11962.0 | 7470.3 |
| 55°    | 19406.0 | 18404.0 | 17402.1 | 17008.9 | 16615.7 | 18063.3 | 19864.7 | 20104.2 | 17738.0 | 12842.4 | 7945.7 |
| 57.5°  | 20682.1 | 19546.6 | 18411.2 | 18046.6 | 17682.0 | 19155.8 | 20883.4 | 21230.1 | 19036.7 | 13687.2 | 8336.4 |
| 60°    | 21899.7 | 20776.2 | 19651.5 | 19359.6 | 19066.5 | 20514.1 | 21984.3 | 21731.7 | 19706.3 | 14082.7 | 8458.0 |
| 62.5°  | 22836.2 | 21942.6 | 21049.0 | 20895.3 | 20740.4 | 21887.8 | 22830.2 | 21536.3 | 19280.9 | 13693.1 | 8105.3 |
| 65°    | 23230.5 | 22721.8 | 22211.9 | 22356.0 | 22499.0 | 22926.7 | 23041.1 | 20964.4 | 17944.2 | 12601.8 | 7259.4 |
| 67.5°  | 22097.5 | 22201.1 | 22304.8 | 22910.0 | 23514.1 | 23219.8 | 22414.4 | 19837.3 | 16041.4 | 11055.3 | 6069.2 |
| 70°    | 18687.6 | 19309.5 | 19930.3 | 21362.4 | 22793.3 | 22140.4 | 20735.7 | 17814.3 | 13751.5 | 9274.1  | 4795.5 |
| 72.5°  | 14300.8 | 15000.1 | 15698.3 | 17823.8 | 19948.1 | 19346.5 | 17626.0 | 14632.0 | 11025.5 | 7405.9  | 3785.2 |
| 75°    | 10354.7 | 11144.7 | 11933.4 | 14278.1 | 16622.9 | 15787.7 | 13184.4 | 10476.3 | 8374.6  | 5653.3  | 2930.9 |
| 77.5°  | 7376.2  | 7905.1  | 8434.1  | 10750.3 | 13065.2 | 11704.6 | 8776.1  | 7049.7  | 5796.3  | 3929.3  | 2061.2 |
| 80°    | 5916.6  | 5754.6  | 5592.6  | 6882.9  | 8173.2  | 7946.8  | 5804.7  | 4527.4  | 4011.6  | 2633.1  | 1254.6 |
| 82.5°  | 4826.5  | 4430.9  | 4035.4  | 4643.0  | 5250.6  | 5217.3  | 4028.2  | 3321.7  | 2985.7  | 1830.0  | 674.4  |
| 85°    | 3535.0  | 3376.5  | 3218.1  | 3755.4  | 4292.7  | 3834.0  | 2728.4  | 2111.2  | 2328.1  | 1347.5  | 367.0  |
| 87.5°  | 1724.0  | 1969.4  | 2213.7  | 2847.5  | 3480.2  | 2612.8  | 828.0   | 409.9   | 567.1   | 372.9   | 177.5  |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |



REPORT NUMBER: P320514  
 CATALOG NUMBER: GAN-SA0A-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 115°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 120°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 125°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 130°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 135°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 140°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 145°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 150°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 155°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 160°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 165°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 170°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 175°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 180°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |



REPORT NUMBER: P320514

CATALOG NUMBER: GAN-SAOA-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   | 160°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 |
| 2.5°   | 9283.6 | 9185.9 | 9075.1 | 8964.3 | 8838.0 | 8710.6 | 8635.5 | 8559.2 | 8477.0 | 8394.8 | 8301.9 |
| 5°     | 8502.1 | 8297.1 | 8064.8 | 7832.5 | 7602.5 | 7372.6 | 7248.7 | 7124.8 | 6993.7 | 6861.5 | 6747.1 |
| 7.5°   | 7379.7 | 7080.7 | 6759.0 | 6436.1 | 6150.2 | 5863.0 | 5685.5 | 5506.8 | 5344.8 | 5181.5 | 5044.5 |
| 10°    | 6392.0 | 6010.8 | 5687.9 | 5363.8 | 5148.2 | 4932.5 | 4769.3 | 4606.1 | 4448.8 | 4290.3 | 4139.0 |
| 12.5°  | 5741.5 | 5360.3 | 5155.3 | 4950.4 | 4771.7 | 4593.0 | 4404.7 | 4215.3 | 3999.6 | 3782.8 | 3624.3 |
| 15°    | 5487.7 | 5141.0 | 4913.5 | 4684.7 | 4445.2 | 4204.6 | 3973.4 | 3742.3 | 3487.3 | 3232.4 | 3052.4 |
| 17.5°  | 5378.1 | 4924.2 | 4606.1 | 4286.8 | 3971.0 | 3655.3 | 3387.2 | 3119.2 | 2840.4 | 2561.6 | 2379.3 |
| 20°    | 5262.6 | 4658.5 | 4232.0 | 3804.2 | 3399.2 | 2994.1 | 2690.3 | 2386.4 | 2137.4 | 1888.4 | 1749.0 |
| 22.5°  | 5157.7 | 4376.1 | 3841.2 | 3305.0 | 2826.1 | 2347.1 | 2049.3 | 1750.2 | 1597.7 | 1445.2 | 1389.2 |
| 25°    | 5114.8 | 4129.5 | 3471.8 | 2814.2 | 2309.0 | 1802.6 | 1590.6 | 1378.5 | 1320.1 | 1260.5 | 1231.9 |
| 27.5°  | 5122.0 | 3909.1 | 3160.9 | 2411.5 | 1956.3 | 1501.2 | 1355.8 | 1210.5 | 1174.8 | 1137.8 | 1119.9 |
| 30°    | 5149.4 | 3669.6 | 2867.8 | 2065.9 | 1690.6 | 1315.3 | 1221.2 | 1125.9 | 1087.8 | 1049.7 | 1027.0 |
| 32.5°  | 5180.3 | 3455.2 | 2641.4 | 1826.5 | 1520.3 | 1212.9 | 1135.4 | 1056.8 | 1019.9 | 982.9  | 960.3  |
| 35°    | 5126.7 | 3280.0 | 2486.5 | 1693.0 | 1410.7 | 1127.1 | 1061.6 | 994.8  | 954.3  | 913.8  | 892.4  |
| 37.5°  | 5036.2 | 3103.7 | 2366.2 | 1627.5 | 1339.2 | 1049.7 | 1002.0 | 953.1  | 911.4  | 868.6  | 848.3  |
| 40°    | 4954.0 | 2954.8 | 2276.8 | 1597.7 | 1299.9 | 1000.8 | 960.3  | 919.8  | 876.9  | 832.8  | 809.0  |
| 42.5°  | 4887.3 | 2854.7 | 2188.7 | 1522.6 | 1264.1 | 1004.4 | 947.2  | 888.8  | 847.1  | 805.4  | 779.2  |
| 45°    | 4837.2 | 2789.1 | 2119.6 | 1450.0 | 1230.7 | 1011.5 | 938.8  | 866.2  | 824.5  | 781.6  | 750.6  |
| 47.5°  | 4832.4 | 2754.6 | 2070.7 | 1386.8 | 1167.6 | 947.2  | 917.4  | 887.6  | 826.9  | 764.9  | 729.2  |
| 50°    | 4898.0 | 2698.6 | 2013.5 | 1327.3 | 1106.8 | 886.4  | 926.9  | 966.3  | 862.6  | 757.8  | 712.5  |
| 52.5°  | 5035.0 | 2599.7 | 1923.0 | 1246.2 | 1033.0 | 818.5  | 881.7  | 943.6  | 854.3  | 763.7  | 705.3  |
| 55°    | 5200.6 | 2454.3 | 1786.0 | 1116.4 | 935.3  | 753.0  | 809.0  | 863.8  | 807.8  | 750.6  | 680.3  |
| 57.5°  | 5304.3 | 2270.9 | 1613.2 | 955.5  | 825.7  | 695.8  | 728.0  | 758.9  | 736.3  | 713.7  | 642.2  |
| 60°    | 5242.3 | 2026.6 | 1419.0 | 810.2  | 729.2  | 648.1  | 642.2  | 635.0  | 668.4  | 701.8  | 619.5  |
| 62.5°  | 4939.7 | 1774.0 | 1247.4 | 720.8  | 660.1  | 598.1  | 585.0  | 570.7  | 625.5  | 679.1  | 592.1  |
| 65°    | 4428.6 | 1597.7 | 1139.0 | 680.3  | 612.4  | 544.5  | 530.2  | 515.9  | 532.6  | 549.3  | 508.7  |
| 67.5°  | 3779.2 | 1489.3 | 1077.1 | 664.8  | 582.6  | 499.2  | 482.5  | 465.8  | 462.3  | 458.7  | 444.4  |
| 70°    | 3109.6 | 1422.6 | 1036.5 | 650.5  | 550.4  | 449.2  | 433.7  | 418.2  | 413.4  | 407.5  | 396.7  |
| 72.5°  | 2599.7 | 1414.2 | 1031.8 | 649.3  | 524.2  | 399.1  | 384.8  | 370.5  | 364.6  | 357.4  | 349.1  |
| 75°    | 2129.1 | 1327.3 | 979.4  | 631.5  | 488.5  | 344.3  | 331.2  | 318.1  | 313.3  | 307.4  | 300.2  |
| 77.5°  | 1579.8 | 1098.5 | 823.3  | 548.1  | 418.2  | 288.3  | 275.2  | 260.9  | 259.7  | 257.3  | 251.4  |
| 80°    | 1024.6 | 794.7  | 588.6  | 382.4  | 305.0  | 226.4  | 215.6  | 203.7  | 204.9  | 206.1  | 201.4  |
| 82.5°  | 569.5  | 463.5  | 359.8  | 256.2  | 208.5  | 160.8  | 156.1  | 150.1  | 153.7  | 156.1  | 150.1  |
| 85°    | 300.2  | 233.5  | 193.0  | 152.5  | 120.3  | 88.2   | 88.2   | 87.0   | 91.7   | 96.5   | 91.7   |
| 87.5°  | 129.9  | 82.2   | 70.3   | 57.2   | 32.2   | 6.0    | 7.1    | 7.1    | 9.5    | 11.9   | 10.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P320514  
 CATALOG NUMBER: GAN-SAOA-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P320514

CATALOG NUMBER: GAN-SA0A-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   | 215°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 |
| 2.5°   | 8207.8 | 8120.8 | 8032.6 | 7936.1 | 7954.0 | 7880.1 | 7806.3 | 7759.8 | 7713.3 | 7699.0 | 7684.7 |
| 5°     | 6632.7 | 6533.8 | 6433.7 | 6344.4 | 6421.8 | 6369.4 | 6317.0 | 6309.8 | 6301.5 | 6301.5 | 6300.3 |
| 7.5°   | 4907.5 | 4801.5 | 4694.2 | 4620.4 | 4696.6 | 4687.1 | 4677.6 | 4728.8 | 4780.0 | 4821.7 | 4862.2 |
| 10°    | 3987.7 | 3859.0 | 3729.2 | 3619.6 | 3600.5 | 3545.7 | 3489.7 | 3501.6 | 3512.3 | 3557.6 | 3602.9 |
| 12.5°  | 3465.9 | 3312.2 | 3158.5 | 3029.8 | 2971.4 | 2880.9 | 2789.1 | 2732.0 | 2674.8 | 2680.7 | 2685.5 |
| 15°    | 2871.4 | 2722.4 | 2572.3 | 2461.5 | 2424.6 | 2354.3 | 2284.0 | 2212.5 | 2139.8 | 2110.0 | 2079.0 |
| 17.5°  | 2195.8 | 2076.7 | 1956.3 | 1882.5 | 1882.5 | 1862.2 | 1842.0 | 1806.2 | 1769.3 | 1739.5 | 1708.5 |
| 20°    | 1609.6 | 1546.5 | 1482.1 | 1451.2 | 1460.7 | 1461.9 | 1461.9 | 1479.8 | 1497.6 | 1488.1 | 1478.6 |
| 22.5°  | 1332.0 | 1309.4 | 1286.7 | 1273.6 | 1278.4 | 1279.6 | 1280.8 | 1297.5 | 1313.0 | 1324.9 | 1335.6 |
| 25°    | 1202.2 | 1187.9 | 1173.6 | 1168.8 | 1179.5 | 1180.7 | 1180.7 | 1191.4 | 1202.2 | 1214.1 | 1226.0 |
| 27.5°  | 1100.9 | 1094.9 | 1089.0 | 1080.6 | 1091.4 | 1091.4 | 1090.2 | 1102.1 | 1112.8 | 1123.5 | 1133.1 |
| 30°    | 1004.4 | 1006.8 | 1008.0 | 1005.6 | 1012.7 | 1017.5 | 1021.1 | 1029.4 | 1036.5 | 1044.9 | 1053.2 |
| 32.5°  | 936.5  | 932.9  | 929.3  | 926.9  | 942.4  | 950.8  | 959.1  | 967.4  | 974.6  | 978.2  | 981.7  |
| 35°    | 870.9  | 862.6  | 854.3  | 848.3  | 862.6  | 873.3  | 884.0  | 899.5  | 913.8  | 916.2  | 918.6  |
| 37.5°  | 826.9  | 816.1  | 805.4  | 798.3  | 804.2  | 809.0  | 813.7  | 830.4  | 847.1  | 856.6  | 865.0  |
| 40°    | 785.2  | 774.4  | 763.7  | 757.8  | 761.3  | 762.5  | 763.7  | 772.0  | 779.2  | 797.1  | 813.7  |
| 42.5°  | 751.8  | 738.7  | 725.6  | 718.4  | 720.8  | 723.2  | 724.4  | 723.2  | 722.0  | 738.7  | 755.4  |
| 45°    | 718.4  | 704.1  | 689.8  | 681.5  | 682.7  | 682.7  | 682.7  | 680.3  | 676.7  | 685.1  | 693.4  |
| 47.5°  | 692.2  | 675.5  | 658.9  | 650.5  | 648.1  | 645.8  | 643.4  | 642.2  | 639.8  | 645.8  | 650.5  |
| 50°    | 666.0  | 648.1  | 629.1  | 619.5  | 613.6  | 611.2  | 608.8  | 607.6  | 605.2  | 611.2  | 616.0  |
| 52.5°  | 645.8  | 624.3  | 602.9  | 587.4  | 581.4  | 577.8  | 574.3  | 575.5  | 575.5  | 577.8  | 579.0  |
| 55°    | 610.0  | 591.0  | 570.7  | 560.0  | 549.3  | 546.9  | 544.5  | 548.1  | 550.4  | 550.4  | 550.4  |
| 57.5°  | 570.7  | 552.8  | 533.8  | 526.6  | 517.1  | 517.1  | 515.9  | 520.7  | 524.2  | 526.6  | 529.0  |
| 60°    | 536.1  | 515.9  | 495.6  | 489.7  | 486.1  | 484.9  | 483.7  | 489.7  | 494.4  | 499.2  | 504.0  |
| 62.5°  | 504.0  | 482.5  | 461.1  | 453.9  | 452.7  | 453.9  | 453.9  | 459.9  | 464.7  | 469.4  | 474.2  |
| 65°    | 468.2  | 446.8  | 424.1  | 417.0  | 419.4  | 423.0  | 426.5  | 431.3  | 434.9  | 439.6  | 444.4  |
| 67.5°  | 428.9  | 411.0  | 392.0  | 384.8  | 386.0  | 390.8  | 395.6  | 399.1  | 401.5  | 406.3  | 411.0  |
| 70°    | 386.0  | 370.5  | 355.0  | 350.3  | 349.1  | 355.0  | 359.8  | 362.2  | 364.6  | 370.5  | 375.3  |
| 72.5°  | 339.6  | 326.5  | 313.3  | 309.8  | 311.0  | 314.5  | 318.1  | 321.7  | 324.1  | 330.0  | 334.8  |
| 75°    | 291.9  | 280.0  | 268.1  | 265.7  | 268.1  | 271.6  | 275.2  | 277.6  | 280.0  | 287.1  | 293.1  |
| 77.5°  | 245.4  | 232.3  | 218.0  | 216.8  | 220.4  | 224.0  | 226.4  | 229.9  | 233.5  | 243.1  | 252.6  |
| 80°    | 196.6  | 182.3  | 166.8  | 165.6  | 169.2  | 172.8  | 176.3  | 179.9  | 183.5  | 195.4  | 206.1  |
| 82.5°  | 144.2  | 127.5  | 110.8  | 108.4  | 120.3  | 123.9  | 127.5  | 133.4  | 138.2  | 148.9  | 159.7  |
| 85°    | 87.0   | 70.3   | 53.6   | 52.4   | 63.1   | 69.1   | 75.1   | 82.2   | 88.2   | 97.7   | 107.2  |
| 87.5°  | 9.5    | 4.8    | 0.0    | 0.0    | 1.2    | 6.0    | 10.7   | 16.7   | 22.6   | 32.2   | 40.5   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P320514  
 CATALOG NUMBER: GAN-SAOA-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P320514  
 CATALOG NUMBER: GAN-SA0A-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   | 270°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 |
| 2.5°   | 7632.3 | 7578.7 | 7633.5 | 7687.1 | 7709.8 | 7732.4 | 7674.0 | 7614.4 | 7707.4 | 7799.1 | 7822.9 |
| 5°     | 6252.6 | 6203.8 | 6240.7 | 6276.5 | 6196.6 | 6116.8 | 6108.5 | 6098.9 | 6168.0 | 6237.1 | 6247.9 |
| 7.5°   | 4846.7 | 4831.3 | 4865.8 | 4900.4 | 4799.1 | 4696.6 | 4646.6 | 4596.5 | 4613.2 | 4629.9 | 4627.5 |
| 10°    | 3613.6 | 3623.1 | 3666.0 | 3707.7 | 3629.1 | 3550.5 | 3515.9 | 3481.4 | 3519.5 | 3556.4 | 3591.0 |
| 12.5°  | 2706.9 | 2727.2 | 2772.5 | 2816.5 | 2784.4 | 2751.0 | 2754.6 | 2758.2 | 2802.2 | 2845.1 | 2883.3 |
| 15°    | 2102.9 | 2126.7 | 2158.9 | 2189.9 | 2191.0 | 2191.0 | 2222.0 | 2251.8 | 2248.2 | 2244.7 | 2270.9 |
| 17.5°  | 1740.7 | 1771.7 | 1775.2 | 1778.8 | 1780.0 | 1781.2 | 1778.8 | 1776.4 | 1758.6 | 1740.7 | 1760.9 |
| 20°    | 1490.5 | 1501.2 | 1510.7 | 1519.1 | 1508.4 | 1496.4 | 1466.7 | 1436.9 | 1425.0 | 1413.0 | 1432.1 |
| 22.5°  | 1355.8 | 1374.9 | 1365.4 | 1354.7 | 1333.2 | 1310.6 | 1287.9 | 1264.1 | 1262.9 | 1260.5 | 1271.3 |
| 25°    | 1242.7 | 1258.2 | 1241.5 | 1224.8 | 1209.3 | 1193.8 | 1178.3 | 1162.8 | 1161.6 | 1160.5 | 1165.2 |
| 27.5°  | 1148.5 | 1162.8 | 1147.3 | 1131.9 | 1118.8 | 1105.6 | 1093.7 | 1081.8 | 1079.4 | 1077.1 | 1078.2 |
| 30°    | 1067.5 | 1080.6 | 1067.5 | 1053.2 | 1043.7 | 1033.0 | 1024.6 | 1016.3 | 1015.1 | 1013.9 | 1013.9 |
| 32.5°  | 994.8  | 1008.0 | 998.4  | 988.9  | 980.5  | 972.2  | 966.3  | 960.3  | 954.3  | 948.4  | 935.3  |
| 35°    | 931.7  | 944.8  | 938.8  | 931.7  | 922.2  | 912.6  | 901.9  | 890.0  | 874.5  | 857.8  | 850.7  |
| 37.5°  | 878.1  | 891.2  | 885.2  | 879.3  | 866.2  | 853.1  | 834.0  | 813.7  | 809.0  | 803.0  | 801.8  |
| 40°    | 835.2  | 855.4  | 843.5  | 830.4  | 810.2  | 789.9  | 780.4  | 770.9  | 768.5  | 766.1  | 763.7  |
| 42.5°  | 787.5  | 818.5  | 797.1  | 775.6  | 756.6  | 737.5  | 735.1  | 732.7  | 731.5  | 730.3  | 730.3  |
| 45°    | 728.0  | 761.3  | 739.9  | 717.2  | 706.5  | 695.8  | 695.8  | 695.8  | 697.0  | 697.0  | 699.4  |
| 47.5°  | 672.0  | 692.2  | 681.5  | 670.8  | 664.8  | 658.9  | 660.1  | 661.2  | 664.8  | 667.2  | 673.2  |
| 50°    | 624.3  | 631.5  | 633.8  | 635.0  | 631.5  | 627.9  | 630.3  | 631.5  | 635.0  | 637.4  | 642.2  |
| 52.5°  | 589.8  | 600.5  | 600.5  | 599.3  | 599.3  | 599.3  | 601.7  | 604.1  | 607.6  | 611.2  | 616.0  |
| 55°    | 567.1  | 582.6  | 577.8  | 573.1  | 574.3  | 574.3  | 576.7  | 579.0  | 582.6  | 585.0  | 592.1  |
| 57.5°  | 545.7  | 562.4  | 557.6  | 552.8  | 552.8  | 552.8  | 554.0  | 555.2  | 558.8  | 561.2  | 565.9  |
| 60°    | 520.7  | 537.3  | 532.6  | 526.6  | 527.8  | 529.0  | 530.2  | 530.2  | 532.6  | 533.8  | 533.8  |
| 62.5°  | 490.9  | 507.5  | 502.8  | 496.8  | 500.4  | 502.8  | 502.8  | 502.8  | 505.2  | 506.4  | 502.8  |
| 65°    | 459.9  | 475.4  | 470.6  | 465.8  | 470.6  | 474.2  | 476.6  | 477.8  | 476.6  | 475.4  | 471.8  |
| 67.5°  | 426.5  | 442.0  | 437.3  | 431.3  | 437.3  | 442.0  | 446.8  | 450.4  | 446.8  | 443.2  | 438.4  |
| 70°    | 390.8  | 406.3  | 400.3  | 394.4  | 400.3  | 406.3  | 411.0  | 415.8  | 411.0  | 406.3  | 405.1  |
| 72.5°  | 352.7  | 370.5  | 363.4  | 356.2  | 363.4  | 370.5  | 372.9  | 375.3  | 371.7  | 368.2  | 365.8  |
| 75°    | 311.0  | 328.8  | 322.9  | 315.7  | 321.7  | 327.6  | 328.8  | 330.0  | 330.0  | 328.8  | 321.7  |
| 77.5°  | 266.9  | 281.2  | 277.6  | 274.0  | 277.6  | 281.2  | 281.2  | 281.2  | 282.4  | 282.4  | 272.8  |
| 80°    | 214.5  | 222.8  | 224.0  | 225.2  | 226.4  | 227.6  | 226.4  | 225.2  | 222.8  | 220.4  | 214.5  |
| 82.5°  | 159.7  | 159.7  | 169.2  | 177.5  | 177.5  | 176.3  | 175.1  | 172.8  | 168.0  | 162.0  | 148.9  |
| 85°    | 101.3  | 95.3   | 110.8  | 125.1  | 125.1  | 123.9  | 121.5  | 118.0  | 108.4  | 97.7   | 87.0   |
| 87.5°  | 34.6   | 28.6   | 44.1   | 59.6   | 60.8   | 60.8   | 58.4   | 56.0   | 46.5   | 35.7   | 27.4   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P320514  
 CATALOG NUMBER: GAN-SAOA-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |





REPORT NUMBER: P320514

CATALOG NUMBER: GAN-SA0A-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   | 325°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7 |
| 2.5°   | 7858.7 | 7874.2 | 7888.5 | 8005.2 | 8120.8 | 8256.6 | 8392.4 | 8496.1 | 8598.6 | 8704.6 | 8810.6 |
| 5°     | 6284.8 | 6303.9 | 6322.9 | 6464.7 | 6605.3 | 6794.7 | 6984.2 | 7147.4 | 7310.6 | 7502.4 | 7694.3 |
| 7.5°   | 4658.5 | 4700.2 | 4740.7 | 4892.0 | 5042.1 | 5245.9 | 5448.4 | 5661.7 | 5873.8 | 6124.0 | 6374.2 |
| 10°    | 3658.9 | 3737.5 | 3815.0 | 3969.9 | 4124.7 | 4326.1 | 4526.2 | 4749.0 | 4971.8 | 5218.5 | 5463.9 |
| 12.5°  | 2961.9 | 3066.7 | 3170.4 | 3356.3 | 3542.1 | 3782.8 | 4022.3 | 4270.1 | 4516.7 | 4733.6 | 4950.4 |
| 15°    | 2340.0 | 2454.3 | 2567.5 | 2764.1 | 2960.7 | 3225.2 | 3488.5 | 3759.0 | 4028.2 | 4288.0 | 4547.7 |
| 17.5°  | 1825.3 | 1919.4 | 2012.3 | 2179.1 | 2344.7 | 2600.9 | 2857.1 | 3140.6 | 3424.2 | 3741.1 | 4056.8 |
| 20°    | 1472.6 | 1511.9 | 1551.2 | 1671.6 | 1790.7 | 1999.2 | 2206.5 | 2496.0 | 2785.6 | 3164.4 | 3543.3 |
| 22.5°  | 1290.3 | 1310.6 | 1329.6 | 1388.0 | 1445.2 | 1579.8 | 1713.3 | 1969.4 | 2224.4 | 2637.8 | 3050.1 |
| 25°    | 1180.7 | 1196.2 | 1211.7 | 1249.8 | 1287.9 | 1352.3 | 1416.6 | 1596.5 | 1776.4 | 2182.7 | 2587.8 |
| 27.5°  | 1081.8 | 1105.6 | 1128.3 | 1146.2 | 1162.8 | 1206.9 | 1249.8 | 1367.8 | 1485.7 | 1864.6 | 2242.3 |
| 30°    | 1010.3 | 1018.7 | 1027.0 | 1054.4 | 1080.6 | 1125.9 | 1171.2 | 1253.4 | 1335.6 | 1656.1 | 1975.4 |
| 32.5°  | 926.9  | 938.8  | 950.8  | 979.4  | 1008.0 | 1049.7 | 1091.4 | 1158.1 | 1223.6 | 1497.6 | 1770.5 |
| 35°    | 851.9  | 863.8  | 875.7  | 904.3  | 931.7  | 977.0  | 1021.1 | 1077.1 | 1131.9 | 1370.1 | 1608.4 |
| 37.5°  | 805.4  | 817.3  | 829.2  | 854.3  | 878.1  | 923.4  | 967.4  | 1011.5 | 1054.4 | 1274.8 | 1495.2 |
| 40°    | 766.1  | 778.0  | 789.9  | 813.7  | 836.4  | 880.5  | 923.4  | 960.3  | 997.2  | 1203.3 | 1409.5 |
| 42.5°  | 731.5  | 744.6  | 757.8  | 781.6  | 804.2  | 843.5  | 882.9  | 931.7  | 979.4  | 1141.4 | 1302.2 |
| 45°    | 702.9  | 716.1  | 728.0  | 754.2  | 780.4  | 818.5  | 856.6  | 924.6  | 992.5  | 1109.2 | 1226.0 |
| 47.5°  | 676.7  | 691.0  | 704.1  | 732.7  | 761.3  | 809.0  | 855.4  | 912.6  | 968.6  | 1084.2 | 1199.8 |
| 50°    | 651.7  | 668.4  | 685.1  | 719.6  | 753.0  | 832.8  | 911.4  | 919.8  | 926.9  | 1063.9 | 1199.8 |
| 52.5°  | 627.9  | 646.9  | 666.0  | 708.9  | 750.6  | 843.5  | 936.5  | 906.7  | 875.7  | 1025.8 | 1175.9 |
| 55°    | 604.1  | 620.7  | 636.2  | 688.6  | 741.1  | 809.0  | 876.9  | 837.6  | 797.1  | 954.3  | 1111.6 |
| 57.5°  | 571.9  | 589.8  | 606.4  | 662.4  | 718.4  | 766.1  | 812.6  | 776.8  | 739.9  | 873.3  | 1005.6 |
| 60°    | 538.5  | 558.8  | 579.0  | 650.5  | 720.8  | 712.5  | 702.9  | 695.8  | 687.5  | 782.8  | 878.1  |
| 62.5°  | 508.7  | 530.2  | 551.6  | 644.6  | 737.5  | 680.3  | 623.1  | 629.1  | 633.8  | 704.1  | 774.4  |
| 65°    | 479.0  | 500.4  | 520.7  | 567.1  | 613.6  | 591.0  | 568.3  | 577.8  | 586.2  | 655.3  | 724.4  |
| 67.5°  | 445.6  | 464.7  | 482.5  | 498.0  | 513.5  | 515.9  | 518.3  | 527.8  | 537.3  | 619.5  | 700.6  |
| 70°    | 408.7  | 424.1  | 439.6  | 450.4  | 459.9  | 464.7  | 468.2  | 480.1  | 492.1  | 581.4  | 670.8  |
| 72.5°  | 367.0  | 380.1  | 392.0  | 401.5  | 411.0  | 414.6  | 417.0  | 428.9  | 440.8  | 536.1  | 631.5  |
| 75°    | 321.7  | 332.4  | 341.9  | 350.3  | 358.6  | 363.4  | 368.2  | 376.5  | 384.8  | 488.5  | 591.0  |
| 77.5°  | 271.6  | 282.4  | 291.9  | 299.0  | 305.0  | 309.8  | 313.3  | 324.1  | 334.8  | 421.8  | 507.5  |
| 80°    | 212.1  | 225.2  | 237.1  | 243.1  | 247.8  | 249.0  | 249.0  | 258.5  | 268.1  | 330.0  | 390.8  |
| 82.5°  | 150.1  | 164.4  | 177.5  | 182.3  | 187.1  | 187.1  | 187.1  | 197.8  | 208.5  | 250.2  | 290.7  |
| 85°    | 88.2   | 103.7  | 118.0  | 122.7  | 127.5  | 129.9  | 131.1  | 135.8  | 139.4  | 169.2  | 197.8  |
| 87.5°  | 27.4   | 40.5   | 52.4   | 54.8   | 57.2   | 62.0   | 66.7   | 67.9   | 67.9   | 88.2   | 108.4  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P320514  
 CATALOG NUMBER: GAN-SAOA-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P320514

CATALOG NUMBER: GAN-SA0A-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 335°   | 340°   | 345°   | 350°    | 355°    | 360°    |
|--------|--------|--------|--------|--------|---------|---------|---------|
| 0°     | 9078.7 | 9078.7 | 9078.7 | 9078.7 | 9078.7  | 9078.7  | 9078.7  |
| 2.5°   | 8932.2 | 9053.7 | 9195.5 | 9336.1 | 9456.4  | 9576.7  | 9676.8  |
| 5°     | 7938.5 | 8182.8 | 8481.8 | 8779.7 | 9045.3  | 9311.0  | 9619.6  |
| 7.5°   | 6689.9 | 7005.6 | 7392.8 | 7780.0 | 8155.4  | 8529.5  | 9003.6  |
| 10°    | 5785.6 | 6106.1 | 6515.9 | 6924.6 | 7346.4  | 7766.9  | 8303.1  |
| 12.5°  | 5211.3 | 5471.1 | 5867.8 | 6264.5 | 6760.2  | 7254.6  | 7770.5  |
| 15°    | 4832.4 | 5116.0 | 5502.0 | 5888.1 | 6430.2  | 6972.3  | 7565.6  |
| 17.5°  | 4428.6 | 4799.1 | 5293.5 | 5788.0 | 6430.2  | 7071.1  | 7770.5  |
| 20°    | 4005.6 | 4466.7 | 5107.7 | 5748.7 | 6613.6  | 7477.4  | 8369.8  |
| 22.5°  | 3583.8 | 4117.6 | 4939.7 | 5760.6 | 6891.2  | 8020.7  | 9225.3  |
| 25°    | 3203.8 | 3819.7 | 4837.2 | 5853.5 | 7295.1  | 8735.6  | 10229.6 |
| 27.5°  | 2915.4 | 3587.4 | 4795.5 | 6002.4 | 7807.5  | 9612.5  | 11322.2 |
| 30°    | 2659.3 | 3343.2 | 4745.5 | 6147.8 | 8300.7  | 10452.4 | 12176.4 |
| 32.5°  | 2437.7 | 3104.9 | 4649.0 | 6191.9 | 8645.0  | 11098.2 | 12899.6 |
| 35°    | 2263.7 | 2919.0 | 4486.9 | 6054.9 | 8860.7  | 11666.5 | 13652.6 |
| 37.5°  | 2113.6 | 2732.0 | 4302.3 | 5872.6 | 9052.5  | 12232.4 | 14499.7 |
| 40°    | 1970.6 | 2531.8 | 4143.8 | 5754.6 | 9317.0  | 12879.4 | 15394.5 |
| 42.5°  | 1834.8 | 2367.4 | 4016.3 | 5665.3 | 9562.4  | 13458.4 | 16177.3 |
| 45°    | 1733.5 | 2241.1 | 3903.1 | 5564.0 | 9720.9  | 13877.8 | 16767.0 |
| 47.5°  | 1683.5 | 2166.0 | 3842.4 | 5517.5 | 9879.4  | 14240.0 | 17256.7 |
| 50°    | 1676.3 | 2152.9 | 3911.5 | 5670.0 | 10222.5 | 14773.8 | 17816.7 |
| 52.5°  | 1675.2 | 2174.4 | 4110.4 | 6046.5 | 10859.9 | 15672.1 | 18423.1 |
| 55°    | 1650.1 | 2187.5 | 4347.5 | 6506.4 | 11715.3 | 16923.1 | 19513.3 |
| 57.5°  | 1573.9 | 2142.2 | 4591.8 | 7040.2 | 12619.6 | 18197.9 | 20741.6 |
| 60°    | 1455.9 | 2032.6 | 4793.1 | 7552.5 | 13227.3 | 18900.9 | 21214.6 |
| 62.5°  | 1308.2 | 1840.8 | 4859.8 | 7877.7 | 13210.6 | 18543.4 | 20738.1 |
| 65°    | 1181.9 | 1639.4 | 4640.6 | 7640.7 | 12542.2 | 17442.6 | 19795.6 |
| 67.5°  | 1069.9 | 1438.1 | 4092.6 | 6745.9 | 11340.0 | 15933.0 | 18597.1 |
| 70°    | 988.9  | 1305.8 | 3386.0 | 5466.3 | 9835.3  | 14203.1 | 17209.0 |
| 72.5°  | 937.7  | 1242.7 | 2760.5 | 4277.2 | 7981.4  | 11684.4 | 14720.1 |
| 75°    | 867.4  | 1143.8 | 2166.0 | 3187.1 | 6108.5  | 9029.9  | 11118.4 |
| 77.5°  | 736.3  | 963.9  | 1632.3 | 2300.7 | 4482.2  | 6662.5  | 7732.4  |
| 80°    | 568.3  | 744.6  | 1122.3 | 1500.0 | 3084.6  | 4669.2  | 5272.1  |
| 82.5°  | 405.1  | 519.5  | 680.3  | 841.2  | 2049.3  | 3256.2  | 3306.2  |
| 85°    | 250.2  | 302.6  | 389.6  | 476.6  | 1355.8  | 2235.1  | 1862.2  |
| 87.5°  | 134.6  | 160.8  | 206.1  | 250.2  | 433.7   | 617.2   | 355.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320514  
CATALOG NUMBER: GAN-SA0A-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

(END OF REPORT)