

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: SHAPER

Report Number: P368713

Luminaire Tested: **605-25-L3/835**

Issue Date: 11/13/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P368713  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1804-721-5)  
Test Lab: INNOVATIONS CENTER  
Issue Date: 11/13/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: SHAPER  
Catalog Number: 605-25-L3/835  
Description: 25" 605 SERIES LUMINOUS WALL SCONCE  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2060.9 lumens  
Efficiency: N/A  
Efficacy: 97.7 lumens/watt  
Spacing Criteria (0/90/45): 2.15 / 1.23 / 1.91  
Luminous Opening: Rectangular w/ Sides (W: 2.08' x L: 0.25' x H: 0.71')  
CIE Type: General Diffuse

Input Watts (W): 21.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P368713  
CATALOG NUMBER: 605-25-L3/835

### Luminous Intensity Polar Plot





TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	93	87	81	76	85	80	75	70	66	62	59	54	51	48	42	40	38	33				
2	83	74	66	59	76	67	60	54	56	50	45	45	41	37	35	32	29	24				
3	75	63	54	47	68	58	50	43	48	41	36	38	34	30	30	26	23	19				
4	68	55	46	39	62	50	42	36	42	35	30	33	28	24	26	22	19	15				
5	62	49	39	32	56	44	36	30	37	30	25	29	24	20	23	19	16	12				
6	57	43	34	28	52	40	31	25	33	26	21	26	21	17	20	16	13	10				
7	52	39	30	24	48	36	28	22	29	23	18	24	19	15	18	15	11	9				
8	48	35	26	21	44	32	24	19	27	20	16	22	17	13	17	13	10	8				
9	45	32	24	18	41	29	22	17	24	18	14	20	15	11	15	12	9	7				
10	42	29	21	16	38	27	20	15	22	17	13	18	14	10	14	11	8	6				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2939	2939	2939	2939
5°	2806	2847	1955	2847
10°	2786	2760	1353	2740
15°	2779	2659	911	2639
20°	2843	2560	646	2542
25°	2916	2464	428	2445
30°	2996	2364	301	2326
35°	3087	2242	184	2203
40°	3181	2130	121	2091
45°	3282	2007	58	1965
50°	3385	1865	35	1844
55°	3500	1703	14	1703
60°	3603	1553	13	1530
65°	3722	1394	13	1369
70°	3829	1215	13	1184
75°	3958	999	13	968
80°	4060	732	13	695
85°	4196	412	13	369



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	13.6	0.7
10°-20°	40.9	2.0
20°-30°	68.5	3.3
30°-40°	95.9	4.7
40°-50°	122.3	5.9
50°-60°	146.7	7.1
60°-70°	167.7	8.1
70°-80°	183.4	8.9
80°-90°	191.5	9.3
90°-100°	191.5	9.3
100°-110°	183.4	8.9
110°-120°	167.7	8.1
120°-130°	146.7	7.1
130°-140°	122.3	5.9
140°-150°	95.9	4.7
150°-160°	68.5	3.3
160°-170°	40.9	2.0
170°-180°	13.6	0.7
0°-30°	123.0	6.0
0°-40°	218.9	10.6
0°-60°	487.8	23.7
0°-90°	1030.5	50.0
90°-120°	542.6	26.3
90°-150°	907.5	44.0
90°-180°	1030.0	50.0
0°-180°	2060.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	142	142	142	142	142	
5°	169	141	118	141	169	17
15°	228	136	75	135	228	66
25°	297	125	44	124	297	138
35°	365	110	22	108	365	230
45°	430	92	8	90	430	334
55°	490	70	2	70	490	439
65°	539	49	2	48	539	533
75°	574	28	2	28	574	605
85°	591	8	2	8	591	481
90°	594	2	2	2	594	325
95°	591	8	2	8	591	481
105°	574	28	2	28	574	605
115°	539	49	2	48	539	533
125°	490	70	2	70	490	439
135°	430	92	8	90	430	334
145°	365	110	22	108	365	230
155°	297	125	44	124	297	138
165°	228	136	75	135	228	66
175°	169	141	118	141	169	17
180°	142	142	142	142	142	



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	155.5	155.5	155.5	155.5	155.5	154.6	154.6	154.6	154.6	153.6	153.6
5°	168.8	168.8	168.8	168.8	168.8	167.8	166.9	166.9	165.9	165.9	165.0
7.5°	183.9	183.9	183.0	183.0	182.1	182.1	181.1	181.1	180.2	179.2	178.3
10°	199.1	198.2	198.2	197.2	197.2	196.3	195.3	195.3	194.4	193.4	191.5
12.5°	213.3	213.3	212.4	212.4	211.4	210.5	209.5	208.6	207.7	206.7	204.8
15°	228.5	228.5	227.6	226.6	226.6	225.7	223.8	222.8	221.9	220.0	218.1
17.5°	245.6	245.6	244.6	243.7	242.7	241.8	239.9	238.0	236.1	234.2	232.3
20°	262.6	261.7	261.7	260.8	259.8	257.9	256.0	254.1	252.2	249.4	246.5
22.5°	279.7	278.8	277.8	277.8	275.9	275.0	273.1	270.2	267.4	264.5	261.7
25°	296.8	295.8	295.8	293.9	293.0	291.1	289.2	286.4	283.5	280.7	276.9
27.5°	313.8	312.9	312.0	311.0	309.1	307.2	305.3	302.5	298.7	295.8	291.1
30°	330.9	330.0	329.0	328.1	326.2	323.3	320.5	317.6	314.8	310.1	305.3
32.5°	348.0	347.0	346.1	344.2	342.3	340.4	336.6	333.8	330.0	325.2	319.5
35°	365.1	364.1	363.2	361.3	359.4	356.5	352.7	348.9	344.2	339.5	333.8
37.5°	381.2	380.2	379.3	377.4	374.5	372.6	368.8	364.1	359.4	353.7	348.0
40°	398.2	396.3	395.4	393.5	390.7	387.8	384.0	379.3	373.6	367.9	361.3
42.5°	414.4	413.4	411.5	409.6	406.8	403.9	399.2	394.4	388.8	382.1	374.5
45°	430.5	429.5	427.6	425.7	422.9	419.1	414.4	408.7	403.0	396.3	388.8
47.5°	445.6	443.8	442.8	440.9	438.1	434.3	428.6	422.9	417.2	410.6	402.0
50°	460.8	458.9	457.0	455.1	452.3	448.5	442.8	437.1	430.5	422.9	413.4
52.5°	475.0	473.1	472.2	469.4	466.5	462.7	456.1	450.4	442.8	435.2	425.7
55°	490.2	488.3	486.4	484.5	480.7	476.0	470.3	463.7	456.1	447.5	437.1
57.5°	502.5	500.6	498.7	495.9	493.1	488.3	482.6	476.0	468.4	458.9	449.4
60°	514.9	512.0	510.1	508.2	504.4	499.7	494.0	486.4	477.9	468.4	458.0
62.5°	526.2	524.3	522.4	519.6	516.8	511.1	504.4	497.8	488.3	478.8	467.5
65°	538.6	535.7	534.8	531.9	528.1	522.4	515.8	508.2	498.7	488.3	476.9
67.5°	547.1	545.2	543.3	540.5	536.7	531.9	525.3	516.8	508.2	497.8	486.4
70°	556.6	553.7	551.8	549.0	545.2	539.5	532.9	524.3	514.9	504.4	493.1
72.5°	565.1	562.3	561.3	557.5	553.7	548.1	540.5	531.9	522.4	511.1	499.7
75°	573.7	571.8	569.9	566.1	562.3	556.6	549.0	540.5	530.0	518.7	506.3
77.5°	578.4	575.5	574.6	570.8	567.0	561.3	553.7	545.2	534.8	523.4	511.1
80°	582.2	580.3	578.4	575.5	570.8	566.1	558.5	549.0	538.6	527.2	514.9
82.5°	586.9	584.1	583.1	579.3	575.5	569.9	562.3	552.8	542.4	531.0	518.7
85°	590.7	588.8	587.9	584.1	580.3	574.6	567.0	557.5	546.2	534.8	522.4
87.5°	592.6	589.8	588.8	585.0	581.2	575.5	568.0	557.5	548.1	535.7	523.4
90°	593.6	591.7	589.8	586.9	582.2	576.5	568.9	558.5	549.0	536.7	524.3
92.5°	592.6	589.8	588.8	585.0	581.2	575.5	568.0	557.5	548.1	535.7	523.4
95°	590.7	588.8	587.9	584.1	580.3	574.6	567.0	557.5	546.2	534.8	522.4
97.5°	586.9	584.1	583.1	579.3	575.5	569.9	562.3	552.8	542.4	531.0	518.7
100°	582.2	580.3	578.4	575.5	570.8	566.1	558.5	549.0	538.6	527.2	514.9
102.5°	578.4	575.5	574.6	570.8	567.0	561.3	553.7	545.2	534.8	523.4	511.1
105°	573.7	571.8	569.9	566.1	562.3	556.6	549.0	540.5	530.0	518.7	506.3
107.5°	565.1	562.3	561.3	557.5	553.7	548.1	540.5	531.9	522.4	511.1	499.7
110°	556.6	553.7	551.8	549.0	545.2	539.5	532.9	524.3	514.9	504.4	493.1



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	547.1	545.2	543.3	540.5	536.7	531.9	525.3	516.8	508.2	497.8	486.4
115°	538.6	535.7	534.8	531.9	528.1	522.4	515.8	508.2	498.7	488.3	476.9
117.5°	526.2	524.3	522.4	519.6	516.8	511.1	504.4	497.8	488.3	478.8	467.5
120°	513.9	512.0	510.1	508.2	504.4	499.7	494.0	486.4	477.9	468.4	458.0
122.5°	502.5	500.6	498.7	495.9	493.1	488.3	482.6	476.0	468.4	458.9	449.4
125°	490.2	488.3	486.4	484.5	480.7	476.0	470.3	463.7	456.1	447.5	437.1
127.5°	475.0	473.1	472.2	469.4	466.5	462.7	456.1	450.4	442.8	435.2	425.7
130°	460.8	458.9	457.0	455.1	452.3	448.5	442.8	437.1	430.5	422.9	413.4
132.5°	445.6	443.8	442.8	440.9	438.1	434.3	428.6	422.9	417.2	410.6	402.0
135°	430.5	429.5	427.6	425.7	422.9	419.1	414.4	408.7	403.0	396.3	388.8
137.5°	414.4	413.4	411.5	409.6	406.8	403.9	399.2	394.4	388.8	382.1	374.5
140°	398.2	396.3	395.4	393.5	390.7	387.8	384.0	379.3	373.6	367.9	361.3
142.5°	381.2	380.2	379.3	377.4	374.5	372.6	368.8	364.1	359.4	353.7	348.0
145°	365.1	364.1	363.2	361.3	359.4	356.5	352.7	348.9	344.2	339.5	333.8
147.5°	348.0	347.0	346.1	344.2	342.3	340.4	336.6	333.8	330.0	325.2	319.5
150°	330.9	330.0	329.0	328.1	326.2	323.3	320.5	317.6	314.8	310.1	305.3
152.5°	313.8	312.9	312.0	311.0	309.1	307.2	305.3	302.5	298.7	295.8	291.1
155°	296.8	295.8	295.8	293.9	293.0	291.1	289.2	286.4	283.5	280.7	276.9
157.5°	279.7	278.8	277.8	277.8	275.9	275.0	273.1	270.2	267.4	264.5	261.7
160°	262.6	261.7	261.7	260.8	259.8	257.9	256.0	254.1	252.2	249.4	246.5
162.5°	245.6	245.6	244.6	243.7	242.7	241.8	239.9	238.0	236.1	234.2	232.3
165°	228.5	228.5	227.6	226.6	226.6	225.7	223.8	222.8	221.9	220.0	218.1
167.5°	213.3	213.3	212.4	212.4	211.4	210.5	209.5	208.6	207.7	206.7	204.8
170°	199.1	198.2	198.2	197.2	197.2	196.3	195.3	195.3	194.4	193.4	191.5
172.5°	183.9	183.9	183.0	183.0	182.1	182.1	181.1	181.1	180.2	179.2	178.3
175°	168.8	168.8	168.8	168.8	168.8	167.8	166.9	166.9	165.9	165.9	165.0
177.5°	155.5	155.5	155.5	155.5	155.5	154.6	154.6	154.6	154.6	153.6	153.6
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	153.6	153.6	152.7	152.7	151.7	151.7	150.8	150.8	150.8	149.8	149.8
5°	165.0	164.0	164.0	163.1	162.1	161.2	161.2	160.2	159.3	158.3	157.4
7.5°	177.3	176.4	175.4	174.5	173.5	172.6	170.7	169.7	167.8	166.9	165.0
10°	190.6	189.6	187.7	186.8	184.9	183.0	181.1	179.2	177.3	175.4	173.5
12.5°	203.9	202.0	200.1	198.2	196.3	193.4	191.5	188.7	185.8	183.9	181.1
15°	216.2	214.3	212.4	209.5	206.7	203.9	201.0	198.2	195.3	192.5	188.7
17.5°	229.5	226.6	223.8	220.9	218.1	214.3	211.4	207.7	203.9	200.1	196.3
20°	243.7	240.8	237.0	233.3	229.5	225.7	220.9	217.1	212.4	208.6	203.9
22.5°	258.9	255.1	250.3	246.5	241.8	237.0	232.3	226.6	220.9	216.2	210.5
25°	273.1	268.3	263.6	258.9	254.1	248.4	242.7	236.1	230.4	223.8	217.1
27.5°	287.3	282.6	276.9	271.2	265.5	258.9	253.2	246.5	238.9	232.3	224.7
30°	300.6	295.8	289.2	283.5	276.9	270.2	262.6	255.1	247.5	239.9	231.4
32.5°	314.8	308.2	301.5	294.9	288.2	280.7	272.1	264.5	256.0	247.5	238.0
35°	328.1	321.4	313.8	306.3	298.7	290.1	281.6	273.1	263.6	254.1	244.6
37.5°	341.3	333.8	326.2	317.6	309.1	300.6	291.1	281.6	271.2	261.7	251.3
40°	354.6	346.1	337.6	329.0	320.5	310.1	299.6	289.2	278.8	268.3	256.0
42.5°	366.9	358.4	349.9	340.4	330.9	319.5	308.2	297.7	286.4	274.0	260.8
45°	380.2	370.7	361.3	350.8	340.4	329.0	317.6	306.3	293.0	279.7	267.4
47.5°	392.5	383.1	372.6	361.3	349.9	337.6	326.2	312.9	299.6	287.3	273.1
50°	404.9	394.4	384.0	371.7	359.4	347.0	333.8	320.5	306.3	293.0	277.8
52.5°	415.3	404.9	393.5	381.2	368.8	356.5	341.3	328.1	312.9	297.7	282.6
55°	426.7	415.3	403.0	390.7	377.4	363.2	349.9	334.7	319.5	302.5	286.4
57.5°	437.1	425.7	412.5	399.2	385.9	370.7	355.6	340.4	324.3	308.2	291.1
60°	446.6	435.2	421.9	408.7	394.4	378.3	362.2	346.1	329.0	312.0	294.9
62.5°	456.1	442.8	429.5	416.3	401.1	385.9	368.8	351.8	334.7	316.7	298.7
65°	464.6	451.3	438.1	422.9	407.7	391.6	374.5	357.5	340.4	321.4	302.5
67.5°	474.1	459.9	445.6	430.5	414.4	397.3	379.3	362.2	344.2	325.2	304.4
70°	479.8	466.5	452.3	437.1	421.0	403.9	385.0	366.9	347.0	327.1	307.2
72.5°	486.4	472.2	458.0	441.9	424.8	407.7	389.7	370.7	351.8	330.9	310.1
75°	493.1	478.8	463.7	447.5	429.5	411.5	393.5	374.5	353.7	333.8	312.9
77.5°	498.7	484.5	469.4	452.3	435.2	416.3	398.2	378.3	356.5	335.7	313.8
80°	501.6	487.4	472.2	455.1	438.1	419.1	401.1	381.2	360.3	339.5	316.7
82.5°	505.4	490.2	475.0	458.0	440.0	421.9	402.0	382.1	361.3	339.5	318.6
85°	509.2	494.0	477.9	460.8	442.8	423.8	404.9	383.1	362.2	341.3	318.6
87.5°	509.2	494.0	478.8	461.8	443.8	425.7	405.8	385.0	364.1	342.3	319.5
90°	510.1	495.0	478.8	462.7	443.8	426.7	406.8	386.9	366.0	343.2	321.4
92.5°	509.2	494.0	478.8	461.8	443.8	425.7	405.8	385.0	364.1	342.3	319.5
95°	509.2	494.0	477.9	460.8	442.8	423.8	404.9	383.1	362.2	341.3	318.6
97.5°	505.4	490.2	475.0	458.0	440.0	421.9	402.0	382.1	361.3	339.5	318.6
100°	501.6	487.4	472.2	455.1	438.1	419.1	401.1	381.2	360.3	339.5	316.7
102.5°	498.7	484.5	469.4	452.3	435.2	416.3	398.2	378.3	356.5	335.7	313.8
105°	493.1	478.8	463.7	447.5	429.5	411.5	393.5	374.5	353.7	333.8	312.9
107.5°	486.4	472.2	458.0	441.9	424.8	407.7	389.7	370.7	351.8	330.9	310.1
110°	479.8	466.5	452.3	437.1	421.0	403.9	385.0	366.9	347.0	327.1	307.2





TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	474.1	459.9	445.6	430.5	414.4	397.3	379.3	362.2	344.2	325.2	304.4
115°	464.6	451.3	438.1	422.9	407.7	391.6	374.5	357.5	340.4	321.4	302.5
117.5°	456.1	442.8	429.5	416.3	401.1	385.9	368.8	351.8	334.7	316.7	298.7
120°	446.6	435.2	421.9	408.7	394.4	378.3	362.2	346.1	329.0	312.0	294.9
122.5°	437.1	425.7	412.5	399.2	385.9	370.7	355.6	340.4	324.3	308.2	291.1
125°	426.7	415.3	403.0	390.7	377.4	363.2	349.9	334.7	319.5	302.5	286.4
127.5°	415.3	404.9	393.5	381.2	368.8	356.5	341.3	328.1	312.9	297.7	282.6
130°	404.9	394.4	384.0	371.7	359.4	347.0	333.8	320.5	306.3	293.0	277.8
132.5°	392.5	383.1	372.6	361.3	349.9	337.6	326.2	312.9	299.6	287.3	273.1
135°	380.2	370.7	361.3	350.8	340.4	329.0	317.6	306.3	293.0	279.7	267.4
137.5°	366.9	358.4	349.9	340.4	330.9	319.5	308.2	297.7	286.4	274.0	260.8
140°	354.6	346.1	337.6	329.0	320.5	310.1	299.6	289.2	278.8	268.3	256.0
142.5°	341.3	333.8	326.2	317.6	309.1	300.6	291.1	281.6	271.2	261.7	251.3
145°	328.1	321.4	313.8	306.3	298.7	290.1	281.6	273.1	263.6	254.1	244.6
147.5°	314.8	308.2	301.5	294.9	288.2	280.7	272.1	264.5	256.0	247.5	238.0
150°	300.6	295.8	289.2	283.5	276.9	270.2	262.6	255.1	247.5	239.9	231.4
152.5°	287.3	282.6	276.9	271.2	265.5	258.9	253.2	246.5	238.9	232.3	224.7
155°	273.1	268.3	263.6	258.9	254.1	248.4	242.7	236.1	230.4	223.8	217.1
157.5°	258.9	255.1	250.3	246.5	241.8	237.0	232.3	226.6	220.9	216.2	210.5
160°	243.7	240.8	237.0	233.3	229.5	225.7	220.9	217.1	212.4	208.6	203.9
162.5°	229.5	226.6	223.8	220.9	218.1	214.3	211.4	207.7	203.9	200.1	196.3
165°	216.2	214.3	212.4	209.5	206.7	203.9	201.0	198.2	195.3	192.5	188.7
167.5°	203.9	202.0	200.1	198.2	196.3	193.4	191.5	188.7	185.8	183.9	181.1
170°	190.6	189.6	187.7	186.8	184.9	183.0	181.1	179.2	177.3	175.4	173.5
172.5°	177.3	176.4	175.4	174.5	173.5	172.6	170.7	169.7	167.8	166.9	165.0
175°	165.0	164.0	164.0	163.1	162.1	161.2	161.2	160.2	159.3	158.3	157.4
177.5°	153.6	153.6	152.7	152.7	151.7	151.7	150.8	150.8	150.8	149.8	149.8
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	148.9	148.9	147.9	147.0	147.0	146.0	146.0	145.1	145.1	144.1	143.2
5°	156.5	155.5	154.6	153.6	152.7	151.7	150.8	148.9	147.9	147.0	146.0
7.5°	164.0	162.1	160.2	159.3	157.4	155.5	154.6	152.7	150.8	148.9	147.0
10°	170.7	168.8	165.9	164.0	162.1	159.3	157.4	155.5	152.7	150.8	148.9
12.5°	178.3	175.4	172.6	169.7	166.9	164.0	161.2	158.3	155.5	152.7	148.9
15°	185.8	182.1	179.2	175.4	171.6	167.8	164.0	160.2	156.5	152.7	149.8
17.5°	192.5	188.7	183.9	179.2	175.4	170.7	165.9	162.1	157.4	153.6	149.8
20°	199.1	193.4	188.7	183.9	179.2	173.5	168.8	164.0	158.3	153.6	148.9
22.5°	204.8	199.1	193.4	188.7	183.0	177.3	171.6	165.0	159.3	153.6	148.9
25°	210.5	204.8	198.2	192.5	185.8	179.2	173.5	166.9	160.2	153.6	147.9
27.5°	217.1	209.5	202.9	195.3	188.7	182.1	174.5	166.9	160.2	152.7	146.0
30°	223.8	215.2	206.7	199.1	190.6	183.0	175.4	167.8	160.2	152.7	145.1
32.5°	229.5	220.9	211.4	202.0	192.5	184.9	176.4	167.8	159.3	150.8	143.2
35°	235.1	225.7	215.2	205.8	195.3	184.9	176.4	166.9	158.3	149.8	141.3
37.5°	240.8	229.5	218.1	207.7	197.2	186.8	176.4	166.9	157.4	147.9	139.4
40°	243.7	232.3	220.9	210.5	199.1	187.7	176.4	165.9	155.5	146.0	136.5
42.5°	249.4	237.0	224.7	212.4	200.1	188.7	176.4	165.0	153.6	143.2	133.7
45°	254.1	240.8	227.6	214.3	201.0	188.7	176.4	163.1	151.7	141.3	129.9
47.5°	258.9	244.6	230.4	216.2	202.0	188.7	175.4	162.1	149.8	137.5	126.1
50°	262.6	247.5	233.3	218.1	202.9	188.7	174.5	161.2	147.0	134.6	122.3
52.5°	266.4	251.3	235.1	218.1	202.9	187.7	173.5	159.3	145.1	130.8	118.5
55°	270.2	253.2	235.1	219.0	202.9	187.7	172.6	156.5	142.2	128.0	114.7
57.5°	274.0	256.0	238.0	220.0	203.9	186.8	169.7	154.6	139.4	124.2	110.9
60°	277.8	258.9	239.9	221.9	202.9	185.8	168.8	152.7	136.5	121.4	107.1
62.5°	279.7	261.7	242.7	221.9	202.9	184.9	166.9	149.8	132.7	117.6	102.4
65°	282.6	262.6	242.7	221.9	202.9	183.9	165.9	147.9	130.8	114.7	98.6
67.5°	284.5	264.5	243.7	222.8	202.9	183.0	164.0	145.1	128.0	110.9	94.8
70°	286.4	266.4	246.5	223.8	202.0	182.1	162.1	143.2	125.2	107.1	91.0
72.5°	289.2	268.3	246.5	223.8	202.9	182.1	161.2	141.3	122.3	104.3	86.3
75°	292.0	270.2	247.5	224.7	202.9	182.1	160.2	139.4	120.4	101.5	83.4
77.5°	293.0	271.2	249.4	225.7	202.9	181.1	159.3	138.4	118.5	99.6	80.6
80°	294.9	272.1	248.4	225.7	202.9	181.1	158.3	137.5	117.6	97.7	77.8
82.5°	295.8	273.1	250.3	226.6	202.9	180.2	158.3	137.5	116.6	95.8	75.9
85°	295.8	274.0	250.3	226.6	202.9	180.2	159.3	136.5	114.7	93.9	73.0
87.5°	296.8	275.0	251.3	227.6	203.9	180.2	158.3	135.6	113.8	92.9	73.0
90°	299.6	275.9	252.2	226.6	205.8	182.1	159.3	137.5	115.7	93.9	74.0
92.5°	296.8	275.0	251.3	227.6	203.9	180.2	158.3	135.6	113.8	92.9	73.0
95°	295.8	274.0	250.3	226.6	202.9	180.2	159.3	136.5	114.7	93.9	73.0
97.5°	295.8	273.1	250.3	226.6	202.9	180.2	158.3	137.5	116.6	95.8	75.9
100°	294.9	272.1	248.4	225.7	202.9	181.1	158.3	137.5	117.6	97.7	77.8
102.5°	293.0	271.2	249.4	225.7	202.9	181.1	159.3	138.4	118.5	99.6	80.6
105°	292.0	270.2	247.5	224.7	202.9	182.1	160.2	139.4	120.4	101.5	83.4
107.5°	289.2	268.3	246.5	223.8	202.9	182.1	161.2	141.3	122.3	104.3	86.3
110°	286.4	266.4	246.5	223.8	202.0	182.1	162.1	143.2	125.2	107.1	91.0



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	284.5	264.5	243.7	222.8	202.9	183.0	164.0	145.1	128.0	110.9	94.8
115°	282.6	262.6	242.7	221.9	202.9	183.9	165.9	147.9	130.8	114.7	98.6
117.5°	279.7	261.7	242.7	221.9	202.9	184.9	166.9	149.8	132.7	117.6	102.4
120°	277.8	258.9	239.9	221.9	202.9	185.8	168.8	152.7	136.5	121.4	107.1
122.5°	274.0	256.0	238.0	220.0	203.9	186.8	169.7	154.6	139.4	124.2	110.9
125°	270.2	253.2	235.1	219.0	202.9	187.7	172.6	156.5	142.2	128.0	114.7
127.5°	266.4	251.3	235.1	218.1	202.9	187.7	173.5	159.3	145.1	130.8	118.5
130°	262.6	247.5	233.3	218.1	202.9	188.7	174.5	161.2	147.0	134.6	122.3
132.5°	258.9	244.6	230.4	216.2	202.0	188.7	175.4	162.1	149.8	137.5	126.1
135°	254.1	240.8	227.6	214.3	201.0	188.7	176.4	163.1	151.7	141.3	129.9
137.5°	249.4	237.0	224.7	212.4	200.1	188.7	176.4	165.0	153.6	143.2	133.7
140°	243.7	232.3	220.9	210.5	199.1	187.7	176.4	165.9	155.5	146.0	136.5
142.5°	240.8	229.5	218.1	207.7	197.2	186.8	176.4	166.9	157.4	147.9	139.4
145°	235.1	225.7	215.2	205.8	195.3	184.9	176.4	166.9	158.3	149.8	141.3
147.5°	229.5	220.9	211.4	202.0	192.5	184.9	176.4	167.8	159.3	150.8	143.2
150°	223.8	215.2	206.7	199.1	190.6	183.0	175.4	167.8	160.2	152.7	145.1
152.5°	217.1	209.5	202.9	195.3	188.7	182.1	174.5	166.9	160.2	152.7	146.0
155°	210.5	204.8	198.2	192.5	185.8	179.2	173.5	166.9	160.2	153.6	147.9
157.5°	204.8	199.1	193.4	188.7	183.0	177.3	171.6	165.0	159.3	153.6	148.9
160°	199.1	193.4	188.7	183.9	179.2	173.5	168.8	164.0	158.3	153.6	148.9
162.5°	192.5	188.7	183.9	179.2	175.4	170.7	165.9	162.1	157.4	153.6	149.8
165°	185.8	182.1	179.2	175.4	171.6	167.8	164.0	160.2	156.5	152.7	149.8
167.5°	178.3	175.4	172.6	169.7	166.9	164.0	161.2	158.3	155.5	152.7	148.9
170°	170.7	168.8	165.9	164.0	162.1	159.3	157.4	155.5	152.7	150.8	148.9
172.5°	164.0	162.1	160.2	159.3	157.4	155.5	154.6	152.7	150.8	148.9	147.0
175°	156.5	155.5	154.6	153.6	152.7	151.7	150.8	148.9	147.9	147.0	146.0
177.5°	148.9	148.9	147.9	147.0	147.0	146.0	146.0	145.1	145.1	144.1	143.2
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	143.2	142.2	142.2	141.3	140.3	140.3	139.4	139.4	138.4	138.4	137.5
5°	145.1	143.2	142.2	141.3	140.3	139.4	138.4	136.5	135.6	134.6	133.7
7.5°	146.0	144.1	142.2	140.3	138.4	137.5	135.6	133.7	132.7	130.8	129.0
10°	146.0	144.1	141.3	139.4	137.5	134.6	132.7	130.8	129.0	127.1	124.2
12.5°	146.0	143.2	140.3	137.5	134.6	131.8	129.9	127.1	124.2	122.3	119.5
15°	146.0	142.2	139.4	135.6	132.7	129.0	126.1	123.3	120.4	117.6	114.7
17.5°	145.1	141.3	137.5	133.7	129.9	126.1	122.3	119.5	115.7	111.9	109.0
20°	144.1	139.4	135.6	130.8	127.1	122.3	118.5	114.7	110.9	107.1	104.3
22.5°	143.2	138.4	132.7	128.0	123.3	118.5	113.8	110.0	105.2	101.5	98.6
25°	142.2	136.5	130.8	125.2	120.4	114.7	110.0	105.2	101.5	96.7	92.9
27.5°	139.4	133.7	127.1	121.4	115.7	110.9	105.2	100.5	95.8	92.0	88.2
30°	137.5	130.8	125.2	118.5	112.8	106.2	100.5	95.8	91.0	86.3	82.5
32.5°	134.6	128.0	120.4	113.8	107.1	101.5	95.8	90.1	85.3	80.6	75.9
35°	132.7	125.2	117.6	110.0	103.4	96.7	91.0	85.3	79.6	74.9	70.2
37.5°	129.9	121.4	112.8	105.2	98.6	92.0	85.3	79.6	74.9	69.2	64.5
40°	127.1	117.6	109.0	101.5	93.9	86.3	80.6	74.9	69.2	63.5	57.8
42.5°	123.3	113.8	105.2	96.7	89.1	81.5	74.9	69.2	62.6	56.9	52.2
45°	119.5	110.0	100.5	92.0	83.4	75.9	69.2	63.5	56.9	51.2	46.5
47.5°	115.7	104.3	94.8	86.3	77.8	70.2	63.5	57.8	51.2	46.5	41.7
50°	110.9	100.5	91.0	81.5	72.1	64.5	57.8	52.2	45.5	40.8	37.0
52.5°	107.1	95.8	85.3	75.9	67.3	59.7	53.1	46.5	40.8	36.0	31.3
55°	102.4	91.0	79.6	70.2	61.6	54.0	47.4	40.8	35.1	31.3	26.5
57.5°	98.6	86.3	74.9	65.4	56.9	49.3	41.7	35.1	30.3	25.6	21.8
60°	93.9	81.5	69.2	59.7	50.3	43.6	36.0	30.3	25.6	21.8	18.0
62.5°	88.2	75.9	64.5	54.0	45.5	37.9	31.3	25.6	20.9	17.1	14.2
65°	83.4	71.1	58.8	49.3	40.8	33.2	25.6	20.9	16.1	13.3	10.4
67.5°	79.6	66.4	54.0	43.6	35.1	27.5	21.8	17.1	13.3	10.4	7.6
70°	74.9	60.7	49.3	38.9	30.3	22.8	18.0	13.3	10.4	7.6	5.7
72.5°	71.1	55.9	43.6	33.2	24.7	18.0	13.3	9.5	6.6	4.7	2.8
75°	67.3	51.2	38.9	28.4	19.9	14.2	9.5	5.7	3.8	1.9	1.9
77.5°	62.6	47.4	34.1	23.7	15.2	9.5	6.6	3.8	1.9	1.9	0.9
80°	59.7	42.7	29.4	18.0	10.4	5.7	3.8	1.9	0.9	0.9	0.9
82.5°	56.9	38.9	24.7	13.3	6.6	2.8	1.9	0.9	0.9	0.9	0.9
85°	54.0	36.0	19.9	8.5	2.8	1.9	0.9	0.9	0.9	0.0	0.0
87.5°	52.2	34.1	15.2	3.8	1.9	0.9	0.9	0.0	0.9	0.0	0.0
90°	53.1	34.1	14.2	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	52.2	34.1	15.2	3.8	1.9	0.9	0.9	0.0	0.9	0.0	0.0
95°	54.0	36.0	19.9	8.5	2.8	1.9	0.9	0.9	0.9	0.0	0.0
97.5°	56.9	38.9	24.7	13.3	6.6	2.8	1.9	0.9	0.9	0.9	0.9
100°	59.7	42.7	29.4	18.0	10.4	5.7	3.8	1.9	0.9	0.9	0.9
102.5°	62.6	47.4	34.1	23.7	15.2	9.5	6.6	3.8	1.9	1.9	0.9
105°	67.3	51.2	38.9	28.4	19.9	14.2	9.5	5.7	3.8	1.9	1.9
107.5°	71.1	55.9	43.6	33.2	24.7	18.0	13.3	9.5	6.6	4.7	2.8
110°	74.9	60.7	49.3	38.9	30.3	22.8	18.0	13.3	10.4	7.6	5.7



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	79.6	66.4	54.0	43.6	35.1	27.5	21.8	17.1	13.3	10.4	7.6
115°	83.4	71.1	58.8	49.3	40.8	33.2	25.6	20.9	16.1	13.3	10.4
117.5°	88.2	75.9	64.5	54.0	45.5	37.9	31.3	25.6	20.9	17.1	14.2
120°	93.9	81.5	69.2	59.7	50.3	43.6	36.0	30.3	25.6	21.8	18.0
122.5°	98.6	86.3	74.9	65.4	56.9	49.3	41.7	35.1	30.3	25.6	21.8
125°	102.4	91.0	79.6	70.2	61.6	54.0	47.4	40.8	35.1	31.3	26.5
127.5°	107.1	95.8	85.3	75.9	67.3	59.7	53.1	46.5	40.8	36.0	31.3
130°	110.9	100.5	91.0	81.5	72.1	64.5	57.8	52.2	45.5	40.8	37.0
132.5°	115.7	104.3	94.8	86.3	77.8	70.2	63.5	57.8	51.2	46.5	41.7
135°	119.5	110.0	100.5	92.0	83.4	75.9	69.2	63.5	56.9	51.2	46.5
137.5°	123.3	113.8	105.2	96.7	89.1	81.5	74.9	69.2	62.6	56.9	52.2
140°	127.1	117.6	109.0	101.5	93.9	86.3	80.6	74.9	69.2	63.5	57.8
142.5°	129.9	121.4	112.8	105.2	98.6	92.0	85.3	79.6	74.9	69.2	64.5
145°	132.7	125.2	117.6	110.0	103.4	96.7	91.0	85.3	79.6	74.9	70.2
147.5°	134.6	128.0	120.4	113.8	107.1	101.5	95.8	90.1	85.3	80.6	75.9
150°	137.5	130.8	125.2	118.5	112.8	106.2	100.5	95.8	91.0	86.3	82.5
152.5°	139.4	133.7	127.1	121.4	115.7	110.9	105.2	100.5	95.8	92.0	88.2
155°	142.2	136.5	130.8	125.2	120.4	114.7	110.0	105.2	101.5	96.7	92.9
157.5°	143.2	138.4	132.7	128.0	123.3	118.5	113.8	110.0	105.2	101.5	98.6
160°	144.1	139.4	135.6	130.8	127.1	122.3	118.5	114.7	110.9	107.1	104.3
162.5°	145.1	141.3	137.5	133.7	129.9	126.1	122.3	119.5	115.7	111.9	109.0
165°	146.0	142.2	139.4	135.6	132.7	129.0	126.1	123.3	120.4	117.6	114.7
167.5°	146.0	143.2	140.3	137.5	134.6	131.8	129.9	127.1	124.2	122.3	119.5
170°	146.0	144.1	141.3	139.4	137.5	134.6	132.7	130.8	129.0	127.1	124.2
172.5°	146.0	144.1	142.2	140.3	138.4	137.5	135.6	133.7	132.7	130.8	129.0
175°	145.1	143.2	142.2	141.3	140.3	139.4	138.4	136.5	135.6	134.6	133.7
177.5°	143.2	142.2	142.2	141.3	140.3	140.3	139.4	139.4	138.4	138.4	137.5
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	137.5	136.5	136.5	135.6	134.6	134.6	134.6	133.7	133.7	132.7	132.7
5°	132.7	131.8	130.8	129.9	129.0	128.0	127.1	126.1	125.2	124.2	124.2
7.5°	128.0	126.1	125.2	123.3	122.3	120.4	119.5	118.5	117.6	116.6	114.7
10°	122.3	120.4	118.5	116.6	115.7	113.8	111.9	110.9	109.0	108.1	107.1
12.5°	117.6	114.7	112.8	110.9	109.0	107.1	105.2	103.4	102.4	100.5	98.6
15°	111.9	109.0	107.1	105.2	102.4	100.5	98.6	96.7	94.8	92.9	91.0
17.5°	106.2	103.4	101.5	98.6	95.8	93.9	91.0	89.1	87.2	85.3	83.4
20°	100.5	97.7	94.8	92.0	89.1	87.2	84.4	81.5	79.6	76.8	74.9
22.5°	94.8	92.0	88.2	85.3	82.5	79.6	76.8	74.0	72.1	69.2	67.3
25°	89.1	85.3	81.5	78.7	74.9	72.1	69.2	67.3	65.4	63.5	61.6
27.5°	83.4	79.6	75.9	72.1	68.3	65.4	62.6	60.7	58.8	55.9	54.0
30°	77.8	74.0	69.2	65.4	62.6	59.7	56.9	55.0	52.2	50.3	47.4
32.5°	72.1	67.3	63.5	59.7	56.9	54.0	51.2	48.4	45.5	43.6	40.8
35°	64.5	60.7	56.9	54.0	51.2	48.4	45.5	42.7	39.8	37.0	36.0
37.5°	58.8	55.0	51.2	48.4	45.5	42.7	38.9	36.0	34.1	33.2	31.3
40°	54.0	50.3	46.5	42.7	39.8	37.0	34.1	32.2	30.3	28.4	26.5
42.5°	48.4	44.6	40.8	37.0	34.1	31.3	29.4	27.5	25.6	23.7	21.8
45°	42.7	38.9	35.1	31.3	29.4	27.5	24.7	22.8	20.9	19.0	18.0
47.5°	37.9	34.1	30.3	27.5	24.7	22.8	19.9	18.0	16.1	15.2	14.2
50°	32.2	28.4	25.6	23.7	20.9	19.0	16.1	14.2	13.3	12.3	11.4
52.5°	27.5	23.7	21.8	19.0	17.1	14.2	13.3	11.4	10.4	9.5	8.5
55°	22.8	19.9	17.1	15.2	12.3	11.4	10.4	8.5	7.6	5.7	5.7
57.5°	19.0	16.1	13.3	11.4	9.5	8.5	7.6	5.7	4.7	3.8	3.8
60°	15.2	12.3	10.4	8.5	7.6	5.7	4.7	3.8	3.8	2.8	2.8
62.5°	11.4	9.5	7.6	6.6	4.7	3.8	2.8	2.8	2.8	1.9	1.9
65°	8.5	6.6	4.7	3.8	2.8	2.8	1.9	1.9	0.9	0.9	0.9
67.5°	5.7	3.8	2.8	1.9	1.9	1.9	0.9	0.9	0.9	0.9	0.9
70°	3.8	2.8	1.9	1.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
72.5°	1.9	1.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
77.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0
80°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0
105°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
107.5°	1.9	1.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
110°	3.8	2.8	1.9	1.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	5.7	3.8	2.8	1.9	1.9	1.9	0.9	0.9	0.9	0.9	0.9
115°	8.5	6.6	4.7	3.8	2.8	2.8	1.9	1.9	0.9	0.9	0.9
117.5°	11.4	9.5	7.6	6.6	4.7	3.8	2.8	2.8	2.8	1.9	1.9
120°	15.2	12.3	10.4	8.5	7.6	5.7	4.7	3.8	3.8	2.8	2.8
122.5°	19.0	16.1	13.3	11.4	9.5	8.5	7.6	5.7	4.7	3.8	3.8
125°	22.8	19.9	17.1	15.2	12.3	11.4	10.4	8.5	7.6	5.7	5.7
127.5°	27.5	23.7	21.8	19.0	17.1	14.2	13.3	11.4	10.4	9.5	8.5
130°	32.2	28.4	25.6	23.7	20.9	19.0	16.1	14.2	13.3	12.3	11.4
132.5°	37.9	34.1	30.3	27.5	24.7	22.8	19.9	18.0	16.1	15.2	14.2
135°	42.7	38.9	35.1	31.3	29.4	27.5	24.7	22.8	20.9	19.0	18.0
137.5°	48.4	44.6	40.8	37.0	34.1	31.3	29.4	27.5	25.6	23.7	21.8
140°	54.0	50.3	46.5	42.7	39.8	37.0	34.1	32.2	30.3	28.4	26.5
142.5°	58.8	55.0	51.2	48.4	45.5	42.7	38.9	36.0	34.1	33.2	31.3
145°	64.5	60.7	56.9	54.0	51.2	48.4	45.5	42.7	39.8	37.0	36.0
147.5°	72.1	67.3	63.5	59.7	56.9	54.0	51.2	48.4	45.5	43.6	40.8
150°	77.8	74.0	69.2	65.4	62.6	59.7	56.9	55.0	52.2	50.3	47.4
152.5°	83.4	79.6	75.9	72.1	68.3	65.4	62.6	60.7	58.8	55.9	54.0
155°	89.1	85.3	81.5	78.7	74.9	72.1	69.2	67.3	65.4	63.5	61.6
157.5°	94.8	92.0	88.2	85.3	82.5	79.6	76.8	74.0	72.1	69.2	67.3
160°	100.5	97.7	94.8	92.0	89.1	87.2	84.4	81.5	79.6	76.8	74.9
162.5°	106.2	103.4	101.5	98.6	95.8	93.9	91.0	89.1	87.2	85.3	83.4
165°	111.9	109.0	107.1	105.2	102.4	100.5	98.6	96.7	94.8	92.9	91.0
167.5°	117.6	114.7	112.8	110.9	109.0	107.1	105.2	103.4	102.4	100.5	98.6
170°	122.3	120.4	118.5	116.6	115.7	113.8	111.9	110.9	109.0	108.1	107.1
172.5°	128.0	126.1	125.2	123.3	122.3	120.4	119.5	118.5	117.6	116.6	114.7
175°	132.7	131.8	130.8	129.9	129.0	128.0	127.1	126.1	125.2	124.2	124.2
177.5°	137.5	136.5	136.5	135.6	134.6	134.6	134.6	133.7	133.7	132.7	132.7
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	132.7	131.8	131.8	131.8	130.8	130.8	130.8	130.8	130.8	129.9	129.9
5°	123.3	122.3	121.4	121.4	120.4	119.5	119.5	118.5	118.5	118.5	117.6
7.5°	114.7	113.8	112.8	111.9	110.9	110.0	110.0	109.0	108.1	108.1	108.1
10°	106.2	105.2	104.3	103.4	102.4	101.5	100.5	99.6	98.6	98.6	97.7
12.5°	97.7	95.8	94.8	93.9	92.9	92.0	91.0	90.1	89.1	88.2	87.2
15°	89.1	88.2	86.3	84.4	83.4	82.5	80.6	79.6	79.6	78.7	77.8
17.5°	81.5	79.6	77.8	75.9	74.0	73.0	72.1	71.1	70.2	70.2	69.2
20°	73.0	71.1	70.2	68.3	67.3	66.4	65.4	63.5	63.5	62.6	61.6
22.5°	66.4	64.5	62.6	61.6	60.7	58.8	57.8	56.9	55.9	55.0	54.0
25°	59.7	57.8	55.9	54.0	53.1	52.2	50.3	49.3	48.4	47.4	46.5
27.5°	52.2	51.2	49.3	47.4	45.5	44.6	43.6	41.7	40.8	40.8	40.8
30°	45.5	43.6	41.7	40.8	39.8	38.9	37.9	37.0	36.0	35.1	35.1
32.5°	38.9	37.9	36.0	35.1	34.1	33.2	32.2	31.3	30.3	29.4	29.4
35°	34.1	33.2	31.3	30.3	29.4	28.4	27.5	26.5	25.6	24.7	23.7
37.5°	29.4	27.5	26.5	25.6	23.7	22.8	21.8	20.9	20.9	19.9	19.0
40°	24.7	23.7	21.8	19.9	19.9	19.0	18.0	18.0	17.1	16.1	16.1
42.5°	19.9	19.0	18.0	17.1	16.1	15.2	15.2	14.2	14.2	13.3	12.3
45°	16.1	15.2	14.2	13.3	12.3	12.3	11.4	11.4	10.4	9.5	9.5
47.5°	13.3	12.3	11.4	10.4	9.5	8.5	7.6	7.6	7.6	7.6	6.6
50°	10.4	9.5	8.5	7.6	6.6	5.7	5.7	5.7	5.7	5.7	5.7
52.5°	6.6	5.7	5.7	5.7	4.7	4.7	4.7	3.8	3.8	3.8	3.8
55°	4.7	4.7	3.8	3.8	3.8	2.8	2.8	2.8	1.9	1.9	1.9
57.5°	3.8	2.8	2.8	2.8	1.9	1.9	0.9	0.9	0.9	0.9	0.9
60°	1.9	1.9	1.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
62.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
65°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
67.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
70°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
75°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
77.5°	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
80°	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
82.5°	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
85°	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
92.5°	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
95°	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
97.5°	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
100°	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
102.5°	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
105°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
107.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
110°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9





TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
115°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
117.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
120°	1.9	1.9	1.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
122.5°	3.8	2.8	2.8	2.8	1.9	1.9	0.9	0.9	0.9	0.9	0.9
125°	4.7	4.7	3.8	3.8	3.8	2.8	2.8	2.8	1.9	1.9	1.9
127.5°	6.6	5.7	5.7	5.7	4.7	4.7	4.7	3.8	3.8	3.8	3.8
130°	10.4	9.5	8.5	7.6	6.6	5.7	5.7	5.7	5.7	5.7	5.7
132.5°	13.3	12.3	11.4	10.4	9.5	8.5	7.6	7.6	7.6	7.6	6.6
135°	16.1	15.2	14.2	13.3	12.3	12.3	11.4	11.4	10.4	9.5	9.5
137.5°	19.9	19.0	18.0	17.1	16.1	15.2	15.2	14.2	14.2	13.3	12.3
140°	24.7	23.7	21.8	19.9	19.9	19.0	18.0	18.0	17.1	16.1	16.1
142.5°	29.4	27.5	26.5	25.6	23.7	22.8	21.8	20.9	20.9	19.9	19.0
145°	34.1	33.2	31.3	30.3	29.4	28.4	27.5	26.5	25.6	24.7	23.7
147.5°	38.9	37.9	36.0	35.1	34.1	33.2	32.2	31.3	30.3	29.4	29.4
150°	45.5	43.6	41.7	40.8	39.8	38.9	37.9	37.0	36.0	35.1	35.1
152.5°	52.2	51.2	49.3	47.4	45.5	44.6	43.6	41.7	40.8	40.8	40.8
155°	59.7	57.8	55.9	54.0	53.1	52.2	50.3	49.3	48.4	47.4	46.5
157.5°	66.4	64.5	62.6	61.6	60.7	58.8	57.8	56.9	55.9	55.0	54.0
160°	73.0	71.1	70.2	68.3	67.3	66.4	65.4	63.5	63.5	62.6	61.6
162.5°	81.5	79.6	77.8	75.9	74.0	73.0	72.1	71.1	70.2	70.2	69.2
165°	89.1	88.2	86.3	84.4	83.4	82.5	80.6	79.6	79.6	78.7	77.8
167.5°	97.7	95.8	94.8	93.9	92.9	92.0	91.0	90.1	89.1	88.2	87.2
170°	106.2	105.2	104.3	103.4	102.4	101.5	100.5	99.6	98.6	98.6	97.7
172.5°	114.7	113.8	112.8	111.9	110.9	110.0	110.0	109.0	108.1	108.1	108.1
175°	123.3	122.3	121.4	121.4	120.4	119.5	119.5	118.5	118.5	118.5	117.6
177.5°	132.7	131.8	131.8	131.8	130.8	130.8	130.8	130.8	130.8	129.9	129.9
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9
5°	117.6	117.6	117.6	117.6	117.6	117.6	117.6	117.6	117.6	117.6	117.6
7.5°	107.1	107.1	107.1	107.1	107.1	107.1	107.1	107.1	107.1	107.1	107.1
10°	96.7	96.7	96.7	96.7	95.8	95.8	96.7	95.8	95.8	96.7	96.7
12.5°	87.2	86.3	86.3	86.3	85.3	85.3	85.3	85.3	85.3	86.3	86.3
15°	76.8	75.9	75.9	75.9	74.9	74.9	74.9	74.9	74.9	75.9	75.9
17.5°	69.2	68.3	68.3	67.3	67.3	67.3	67.3	67.3	67.3	67.3	68.3
20°	61.6	60.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7
22.5°	53.1	53.1	52.2	52.2	52.2	51.2	51.2	51.2	52.2	52.2	52.2
25°	45.5	45.5	44.6	44.6	43.6	43.6	43.6	43.6	43.6	44.6	44.6
27.5°	39.8	39.8	38.9	38.9	37.9	37.9	37.9	37.9	37.9	38.9	38.9
30°	34.1	34.1	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2
32.5°	29.4	28.4	28.4	27.5	27.5	27.5	27.5	27.5	27.5	27.5	28.4
35°	23.7	22.8	22.8	22.8	21.8	21.8	21.8	21.8	21.8	22.8	22.8
37.5°	19.0	19.0	19.0	19.0	18.0	18.0	18.0	18.0	18.0	19.0	19.0
40°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2
42.5°	12.3	12.3	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
45°	8.5	8.5	8.5	7.6	7.6	7.6	7.6	7.6	7.6	7.6	8.5
47.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
50°	5.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
52.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
55°	2.8	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
57.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
60°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
62.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
65°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
67.5°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
70°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
72.5°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
75°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
77.5°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
82.5°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
85°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
87.5°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
90°	0.9	1.9	0.9	1.9	1.9	1.9	1.9	1.9	0.9	0.9	0.9
92.5°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
95°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
97.5°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
100°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
102.5°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
105°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
107.5°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
110°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
115°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
117.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
120°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
122.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
125°	2.8	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
127.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
130°	5.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
132.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
135°	8.5	8.5	8.5	7.6	7.6	7.6	7.6	7.6	7.6	7.6	8.5
137.5°	12.3	12.3	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
140°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2
142.5°	19.0	19.0	19.0	19.0	18.0	18.0	18.0	18.0	18.0	19.0	19.0
145°	23.7	22.8	22.8	22.8	21.8	21.8	21.8	21.8	21.8	22.8	22.8
147.5°	29.4	28.4	28.4	27.5	27.5	27.5	27.5	27.5	27.5	27.5	28.4
150°	34.1	34.1	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2
152.5°	39.8	39.8	38.9	38.9	37.9	37.9	37.9	37.9	37.9	38.9	38.9
155°	45.5	45.5	44.6	44.6	43.6	43.6	43.6	43.6	43.6	44.6	44.6
157.5°	53.1	53.1	52.2	52.2	52.2	51.2	51.2	51.2	52.2	52.2	52.2
160°	61.6	60.7	59.7	59.7	59.7	59.7	58.8	59.7	59.7	59.7	59.7
162.5°	69.2	68.3	68.3	67.3	67.3	67.3	67.3	67.3	67.3	67.3	68.3
165°	76.8	75.9	75.9	75.9	74.9	74.9	74.9	74.9	74.9	75.9	75.9
167.5°	87.2	86.3	86.3	86.3	85.3	85.3	85.3	85.3	85.3	86.3	86.3
170°	96.7	96.7	96.7	96.7	95.8	95.8	95.8	95.8	95.8	96.7	96.7
172.5°	107.1	107.1	107.1	107.1	107.1	107.1	107.1	107.1	107.1	107.1	107.1
175°	117.6	117.6	117.6	117.6	117.6	117.6	117.6	117.6	117.6	117.6	117.6
177.5°	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	129.9	129.9	129.9	129.9	130.8	130.8	130.8	130.8	130.8	131.8	131.8
5°	117.6	117.6	118.5	118.5	118.5	119.5	119.5	119.5	120.4	121.4	121.4
7.5°	107.1	107.1	108.1	108.1	108.1	109.0	110.0	110.0	110.9	111.9	112.8
10°	96.7	96.7	97.7	98.6	98.6	99.6	100.5	101.5	102.4	103.4	104.3
12.5°	86.3	87.2	87.2	88.2	89.1	90.1	91.0	92.0	92.9	93.9	94.8
15°	75.9	76.8	77.8	78.7	79.6	79.6	80.6	82.5	83.4	84.4	86.3
17.5°	68.3	69.2	69.2	70.2	70.2	71.1	72.1	73.0	74.0	74.9	76.8
20°	60.7	61.6	61.6	62.6	63.5	63.5	64.5	65.4	66.4	67.3	69.2
22.5°	53.1	53.1	54.0	55.0	55.9	55.9	56.9	57.8	59.7	60.7	62.6
25°	45.5	45.5	46.5	47.4	48.4	49.3	50.3	51.2	52.2	54.0	55.9
27.5°	39.8	39.8	40.8	40.8	40.8	41.7	42.7	43.6	45.5	47.4	48.4
30°	34.1	34.1	35.1	35.1	36.0	36.0	37.0	38.9	39.8	40.8	41.7
32.5°	28.4	29.4	29.4	29.4	30.3	31.3	32.2	33.2	34.1	35.1	36.0
35°	22.8	23.7	23.7	24.7	25.6	26.5	27.5	28.4	29.4	30.3	31.3
37.5°	19.0	19.0	19.0	19.9	20.9	20.9	21.8	22.8	23.7	25.6	26.5
40°	15.2	15.2	16.1	16.1	17.1	18.0	18.0	19.0	19.9	19.9	21.8
42.5°	12.3	12.3	12.3	13.3	14.2	14.2	14.2	15.2	16.1	17.1	18.0
45°	8.5	8.5	9.5	9.5	10.4	10.4	11.4	12.3	12.3	13.3	14.2
47.5°	6.6	6.6	6.6	6.6	6.6	6.6	7.6	8.5	9.5	10.4	11.4
50°	4.7	4.7	4.7	5.7	4.7	5.7	5.7	5.7	6.6	7.6	8.5
52.5°	3.8	3.8	3.8	3.8	3.8	3.8	4.7	4.7	4.7	5.7	5.7
55°	1.9	1.9	1.9	1.9	1.9	2.8	2.8	2.8	3.8	3.8	3.8
57.5°	1.9	0.9	0.9	0.9	0.9	0.9	0.9	1.9	1.9	2.8	2.8
60°	1.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.9
62.5°	1.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
65°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
67.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
70°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
77.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0
80°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0
82.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.9	0.0	0.0
85°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.9	0.0	0.0
87.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.9	0.0	0.0
90°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0
92.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.9	0.0	0.0
95°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.9	0.0	0.0
97.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.9	0.0	0.0
100°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0
102.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0
105°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
107.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
110°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
115°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
117.5°	1.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
120°	1.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.9
122.5°	1.9	0.9	0.9	0.9	0.9	0.9	0.9	1.9	1.9	2.8	2.8
125°	1.9	1.9	1.9	1.9	1.9	2.8	2.8	2.8	3.8	3.8	3.8
127.5°	3.8	3.8	3.8	3.8	3.8	3.8	4.7	4.7	4.7	5.7	5.7
130°	4.7	4.7	4.7	5.7	4.7	5.7	5.7	5.7	6.6	7.6	8.5
132.5°	6.6	6.6	6.6	6.6	6.6	6.6	7.6	8.5	9.5	10.4	11.4
135°	8.5	8.5	9.5	9.5	10.4	10.4	11.4	12.3	12.3	13.3	14.2
137.5°	12.3	12.3	12.3	13.3	14.2	14.2	14.2	15.2	16.1	17.1	18.0
140°	15.2	15.2	16.1	16.1	17.1	18.0	18.0	19.0	19.9	19.9	21.8
142.5°	19.0	19.0	19.0	19.9	20.9	20.9	21.8	22.8	23.7	25.6	26.5
145°	22.8	23.7	23.7	24.7	25.6	26.5	27.5	28.4	29.4	30.3	31.3
147.5°	28.4	29.4	29.4	29.4	30.3	31.3	32.2	33.2	34.1	35.1	36.0
150°	34.1	34.1	35.1	35.1	36.0	36.0	37.0	38.9	39.8	40.8	41.7
152.5°	39.8	39.8	40.8	40.8	40.8	41.7	42.7	43.6	45.5	47.4	48.4
155°	45.5	45.5	46.5	47.4	48.4	49.3	50.3	51.2	52.2	54.0	55.9
157.5°	53.1	53.1	54.0	55.0	55.9	55.9	56.9	57.8	59.7	60.7	62.6
160°	60.7	61.6	61.6	62.6	63.5	63.5	64.5	65.4	66.4	67.3	69.2
162.5°	68.3	69.2	69.2	70.2	70.2	71.1	72.1	73.0	74.0	74.9	76.8
165°	75.9	76.8	77.8	78.7	79.6	79.6	80.6	82.5	83.4	84.4	86.3
167.5°	86.3	87.2	87.2	88.2	89.1	90.1	91.0	92.0	92.9	93.9	94.8
170°	96.7	96.7	97.7	98.6	98.6	99.6	100.5	101.5	102.4	103.4	104.3
172.5°	107.1	107.1	108.1	108.1	108.1	109.0	110.0	110.0	110.9	111.9	112.8
175°	117.6	117.6	118.5	118.5	118.5	119.5	119.5	119.5	120.4	121.4	121.4
177.5°	129.9	129.9	129.9	129.9	130.8	130.8	130.8	130.8	130.8	131.8	131.8
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	131.8	132.7	132.7	132.7	133.7	133.7	134.6	134.6	135.6	135.6	136.5
5°	122.3	123.3	124.2	124.2	125.2	126.1	127.1	128.0	129.0	129.9	130.8
7.5°	113.8	114.7	114.7	116.6	117.6	118.5	119.5	120.4	122.3	123.3	125.2
10°	105.2	106.2	107.1	108.1	109.0	110.9	111.9	113.8	115.7	116.6	118.5
12.5°	95.8	97.7	98.6	100.5	101.5	103.4	105.2	107.1	109.0	110.0	111.9
15°	87.2	89.1	90.1	92.0	93.9	95.8	97.7	99.6	101.5	104.3	106.2
17.5°	78.7	80.6	82.5	84.4	86.3	88.2	90.1	92.9	94.8	97.7	100.5
20°	70.2	72.1	74.0	75.9	78.7	80.6	83.4	86.3	88.2	91.0	93.9
22.5°	63.5	65.4	67.3	68.3	71.1	73.0	75.9	78.7	81.5	84.4	88.2
25°	56.9	58.8	60.7	62.6	64.5	66.4	68.3	71.1	74.9	77.8	81.5
27.5°	50.3	52.2	54.0	55.9	57.8	60.7	62.6	65.4	68.3	71.1	74.9
30°	43.6	45.5	47.4	49.3	52.2	54.0	56.9	59.7	61.6	64.5	68.3
32.5°	37.9	38.9	40.8	43.6	45.5	48.4	51.2	53.1	55.9	58.8	62.6
35°	33.2	34.1	36.0	37.0	39.8	42.7	44.6	47.4	50.3	53.1	56.9
37.5°	27.5	29.4	31.3	33.2	34.1	36.0	38.9	41.7	44.6	48.4	51.2
40°	23.7	24.7	26.5	27.5	29.4	31.3	33.2	36.0	38.9	42.7	45.5
42.5°	19.0	19.9	21.8	22.8	24.7	27.5	29.4	31.3	33.2	37.0	39.8
45°	15.2	16.1	17.1	19.0	20.9	22.8	24.7	26.5	28.4	31.3	35.1
47.5°	12.3	12.3	14.2	15.2	16.1	18.0	19.9	21.8	24.7	26.5	29.4
50°	8.5	9.5	11.4	12.3	13.3	14.2	16.1	18.0	20.9	22.8	25.6
52.5°	5.7	6.6	8.5	9.5	10.4	11.4	12.3	14.2	17.1	19.0	21.8
55°	4.7	4.7	5.7	5.7	7.6	8.5	10.4	11.4	12.3	15.2	17.1
57.5°	2.8	3.8	3.8	3.8	4.7	5.7	7.6	8.5	9.5	11.4	13.3
60°	1.9	1.9	2.8	2.8	3.8	3.8	4.7	5.7	7.6	8.5	9.5
62.5°	0.9	0.9	1.9	1.9	2.8	2.8	2.8	3.8	4.7	5.7	7.6
65°	0.9	0.9	0.9	0.9	0.9	1.9	1.9	2.8	2.8	3.8	4.7
67.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.9	1.9	1.9	2.8
70°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.9	1.9
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
75°	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
77.5°	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9
102.5°	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
105°	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
107.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
110°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.9	1.9



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.9	1.9	1.9	2.8
115°	0.9	0.9	0.9	0.9	0.9	1.9	1.9	2.8	2.8	3.8	4.7
117.5°	0.9	0.9	1.9	1.9	2.8	2.8	2.8	3.8	4.7	5.7	7.6
120°	1.9	1.9	2.8	2.8	3.8	3.8	4.7	5.7	7.6	8.5	9.5
122.5°	2.8	3.8	3.8	3.8	4.7	5.7	7.6	8.5	9.5	11.4	13.3
125°	4.7	4.7	5.7	5.7	7.6	8.5	10.4	11.4	12.3	15.2	17.1
127.5°	5.7	6.6	8.5	9.5	10.4	11.4	12.3	14.2	17.1	19.0	21.8
130°	8.5	9.5	11.4	12.3	13.3	14.2	16.1	18.0	20.9	22.8	25.6
132.5°	12.3	12.3	14.2	15.2	16.1	18.0	19.9	21.8	24.7	26.5	29.4
135°	15.2	16.1	17.1	19.0	20.9	22.8	24.7	26.5	28.4	31.3	35.1
137.5°	19.0	19.9	21.8	22.8	24.7	27.5	29.4	31.3	33.2	37.0	39.8
140°	23.7	24.7	26.5	27.5	29.4	31.3	33.2	36.0	38.9	42.7	45.5
142.5°	27.5	29.4	31.3	33.2	34.1	36.0	38.9	41.7	44.6	48.4	51.2
145°	33.2	34.1	36.0	37.0	39.8	42.7	44.6	47.4	50.3	53.1	56.9
147.5°	37.9	38.9	40.8	43.6	45.5	48.4	51.2	53.1	55.9	58.8	62.6
150°	43.6	45.5	47.4	49.3	52.2	54.0	56.9	59.7	61.6	64.5	68.3
152.5°	50.3	52.2	54.0	55.9	57.8	60.7	62.6	65.4	68.3	71.1	74.9
155°	56.9	58.8	60.7	62.6	64.5	66.4	68.3	71.1	74.9	77.8	81.5
157.5°	63.5	65.4	67.3	68.3	71.1	73.0	75.9	78.7	81.5	84.4	88.2
160°	70.2	72.1	74.0	75.9	78.7	80.6	83.4	86.3	88.2	91.0	93.9
162.5°	78.7	80.6	82.5	84.4	86.3	88.2	90.1	92.9	94.8	97.7	100.5
165°	87.2	89.1	90.1	92.0	93.9	95.8	97.7	99.6	101.5	104.3	106.2
167.5°	95.8	97.7	98.6	100.5	101.5	103.4	105.2	107.1	109.0	110.0	111.9
170°	105.2	106.2	107.1	108.1	109.0	110.9	111.9	113.8	115.7	116.6	118.5
172.5°	113.8	114.7	114.7	116.6	117.6	118.5	119.5	120.4	122.3	123.3	125.2
175°	122.3	123.3	124.2	124.2	125.2	126.1	127.1	128.0	129.0	129.9	130.8
177.5°	131.8	132.7	132.7	132.7	133.7	133.7	134.6	134.6	135.6	135.6	136.5
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	136.5	137.5	137.5	138.4	138.4	139.4	139.4	140.3	140.3	141.3	142.2
5°	131.8	132.7	133.7	134.6	135.6	136.5	138.4	139.4	140.3	141.3	142.2
7.5°	126.1	128.0	129.0	130.8	132.7	133.7	135.6	137.5	138.4	140.3	142.2
10°	120.4	122.3	124.2	126.1	128.0	129.9	131.8	134.6	136.5	138.4	140.3
12.5°	114.7	116.6	118.5	121.4	124.2	126.1	129.0	131.8	133.7	136.5	139.4
15°	108.1	110.9	113.8	116.6	119.5	122.3	125.2	128.0	131.8	134.6	138.4
17.5°	102.4	105.2	108.1	110.9	114.7	118.5	121.4	125.2	129.0	132.7	136.5
20°	96.7	99.6	103.4	106.2	110.0	113.8	117.6	121.4	126.1	129.9	134.6
22.5°	91.0	93.9	97.7	101.5	104.3	109.0	112.8	117.6	122.3	127.1	131.8
25°	85.3	88.2	92.0	95.8	100.5	104.3	109.0	113.8	119.5	124.2	129.9
27.5°	78.7	82.5	87.2	91.0	94.8	99.6	104.3	110.0	114.7	120.4	126.1
30°	73.0	76.8	80.6	85.3	89.1	93.9	98.6	105.2	110.9	116.6	123.3
32.5°	66.4	70.2	74.9	79.6	84.4	89.1	93.9	100.5	106.2	112.8	119.5
35°	59.7	64.5	69.2	74.0	78.7	83.4	89.1	94.8	101.5	108.1	115.7
37.5°	54.0	57.8	62.6	68.3	73.0	78.7	84.4	91.0	97.7	104.3	111.9
40°	49.3	53.1	56.9	62.6	68.3	74.0	79.6	85.3	92.9	99.6	107.1
42.5°	43.6	47.4	51.2	56.9	62.6	68.3	74.0	80.6	87.2	94.8	103.4
45°	38.9	42.7	46.5	51.2	56.9	62.6	68.3	74.0	82.5	90.1	98.6
47.5°	33.2	37.0	41.7	45.5	50.3	56.9	62.6	69.2	76.8	85.3	93.9
50°	28.4	32.2	36.0	39.8	44.6	51.2	57.8	64.5	72.1	80.6	90.1
52.5°	23.7	27.5	31.3	35.1	39.8	45.5	52.2	58.8	66.4	74.9	84.4
55°	19.9	22.8	26.5	30.3	35.1	39.8	46.5	53.1	60.7	70.2	78.7
57.5°	16.1	19.0	21.8	25.6	30.3	35.1	41.7	48.4	55.9	64.5	74.0
60°	12.3	15.2	18.0	20.9	25.6	30.3	36.0	42.7	50.3	58.8	69.2
62.5°	9.5	11.4	14.2	17.1	20.9	25.6	30.3	37.9	45.5	54.0	63.5
65°	6.6	8.5	10.4	13.3	16.1	20.9	25.6	32.2	39.8	48.4	58.8
67.5°	3.8	5.7	7.6	10.4	13.3	16.1	21.8	27.5	34.1	42.7	53.1
70°	2.8	3.8	5.7	7.6	9.5	12.3	17.1	22.8	29.4	37.9	48.4
72.5°	1.9	1.9	2.8	4.7	6.6	9.5	13.3	17.1	23.7	32.2	42.7
75°	0.9	0.9	1.9	1.9	3.8	5.7	9.5	13.3	19.0	27.5	37.9
77.5°	0.9	0.9	0.9	1.9	1.9	3.8	5.7	9.5	14.2	22.8	33.2
80°	0.9	0.9	0.9	0.9	0.9	1.9	3.8	5.7	10.4	17.1	27.5
82.5°	0.0	0.9	0.9	0.9	0.9	0.9	1.9	2.8	5.7	12.3	22.8
85°	0.0	0.0	0.0	0.0	0.9	0.9	0.9	1.9	2.8	7.6	18.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9	1.9	3.8	14.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.9	10.4
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9	1.9	3.8	14.2
95°	0.0	0.0	0.0	0.0	0.9	0.9	0.9	1.9	2.8	7.6	18.0
97.5°	0.0	0.9	0.9	0.9	0.9	0.9	1.9	2.8	5.7	12.3	22.8
100°	0.9	0.9	0.9	0.9	0.9	1.9	3.8	5.7	10.4	17.1	27.5
102.5°	0.9	0.9	0.9	1.9	1.9	3.8	5.7	9.5	14.2	22.8	33.2
105°	0.9	0.9	1.9	1.9	3.8	5.7	9.5	13.3	19.0	27.5	37.9
107.5°	1.9	1.9	2.8	4.7	6.6	9.5	13.3	17.1	23.7	32.2	42.7
110°	2.8	3.8	5.7	7.6	9.5	12.3	17.1	22.8	29.4	37.9	48.4





TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	3.8	5.7	7.6	10.4	13.3	16.1	21.8	27.5	34.1	42.7	53.1
115°	6.6	8.5	10.4	13.3	16.1	20.9	25.6	32.2	39.8	48.4	58.8
117.5°	9.5	11.4	14.2	17.1	20.9	25.6	30.3	37.9	45.5	54.0	63.5
120°	12.3	15.2	18.0	20.9	25.6	30.3	36.0	42.7	50.3	58.8	69.2
122.5°	16.1	19.0	21.8	25.6	30.3	35.1	41.7	48.4	55.9	64.5	74.0
125°	19.9	22.8	26.5	30.3	35.1	39.8	46.5	53.1	60.7	70.2	78.7
127.5°	23.7	27.5	31.3	35.1	39.8	45.5	52.2	58.8	66.4	74.9	84.4
130°	28.4	32.2	36.0	39.8	44.6	51.2	57.8	64.5	72.1	80.6	90.1
132.5°	33.2	37.0	41.7	45.5	50.3	56.9	62.6	69.2	76.8	85.3	93.9
135°	38.9	42.7	46.5	51.2	56.9	62.6	68.3	74.0	82.5	90.1	98.6
137.5°	43.6	47.4	51.2	56.9	62.6	68.3	74.0	80.6	87.2	94.8	103.4
140°	49.3	53.1	56.9	62.6	68.3	74.0	79.6	85.3	92.9	99.6	107.1
142.5°	54.0	57.8	62.6	68.3	73.0	78.7	84.4	91.0	97.7	104.3	111.9
145°	59.7	64.5	69.2	74.0	78.7	83.4	89.1	94.8	101.5	108.1	115.7
147.5°	66.4	70.2	74.9	79.6	84.4	89.1	93.9	100.5	106.2	112.8	119.5
150°	73.0	76.8	80.6	85.3	89.1	93.9	98.6	105.2	110.9	116.6	123.3
152.5°	78.7	82.5	87.2	91.0	94.8	99.6	104.3	110.0	114.7	120.4	126.1
155°	85.3	88.2	92.0	95.8	100.5	104.3	109.0	113.8	119.5	124.2	129.9
157.5°	91.0	93.9	97.7	101.5	104.3	109.0	112.8	117.6	122.3	127.1	131.8
160°	96.7	99.6	103.4	106.2	110.0	113.8	117.6	121.4	126.1	129.9	134.6
162.5°	102.4	105.2	108.1	110.9	114.7	118.5	121.4	125.2	129.0	132.7	136.5
165°	108.1	110.9	113.8	116.6	119.5	122.3	125.2	128.0	131.8	134.6	138.4
167.5°	114.7	116.6	118.5	121.4	124.2	126.1	129.0	131.8	133.7	136.5	139.4
170°	120.4	122.3	124.2	126.1	128.0	129.9	131.8	134.6	136.5	138.4	140.3
172.5°	126.1	128.0	129.0	130.8	132.7	133.7	135.6	137.5	138.4	140.3	142.2
175°	131.8	132.7	133.7	134.6	135.6	136.5	138.4	139.4	140.3	141.3	142.2
177.5°	136.5	137.5	137.5	138.4	138.4	139.4	139.4	140.3	140.3	141.3	142.2
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	142.2	143.2	144.1	144.1	145.1	145.1	146.0	147.0	147.0	147.9	147.9
5°	143.2	145.1	146.0	147.0	147.9	148.9	150.8	151.7	152.7	153.6	154.6
7.5°	144.1	145.1	147.0	148.9	150.8	151.7	153.6	155.5	157.4	158.3	160.2
10°	143.2	145.1	147.9	149.8	152.7	154.6	157.4	159.3	161.2	164.0	165.9
12.5°	142.2	145.1	148.9	151.7	154.6	157.4	160.2	163.1	165.9	168.8	172.6
15°	141.3	145.1	148.9	151.7	155.5	159.3	163.1	166.9	170.7	174.5	177.3
17.5°	140.3	144.1	148.9	152.7	156.5	160.2	165.0	169.7	173.5	178.3	183.0
20°	139.4	143.2	147.9	152.7	157.4	162.1	167.8	172.6	177.3	183.0	187.7
22.5°	136.5	142.2	147.0	152.7	158.3	164.0	169.7	175.4	181.1	186.8	192.5
25°	134.6	140.3	146.0	151.7	158.3	165.0	171.6	177.3	183.9	190.6	196.3
27.5°	132.7	138.4	145.1	151.7	158.3	165.9	172.6	180.2	186.8	193.4	201.0
30°	129.0	135.6	143.2	150.8	158.3	165.9	173.5	181.1	188.7	197.2	204.8
32.5°	126.1	133.7	141.3	148.9	157.4	165.9	173.5	182.1	190.6	200.1	209.5
35°	123.3	130.8	139.4	147.9	156.5	165.0	174.5	183.0	192.5	202.9	212.4
37.5°	119.5	128.0	136.5	146.0	155.5	165.0	174.5	183.9	194.4	204.8	215.2
40°	115.7	125.2	134.6	144.1	153.6	163.1	173.5	184.9	196.3	207.7	218.1
42.5°	111.9	121.4	131.8	141.3	151.7	163.1	174.5	185.8	197.2	209.5	220.9
45°	108.1	117.6	128.0	139.4	149.8	161.2	173.5	185.8	198.2	211.4	224.7
47.5°	103.4	114.7	125.2	136.5	147.9	160.2	173.5	185.8	199.1	213.3	226.6
50°	99.6	110.0	121.4	133.7	146.0	159.3	172.6	186.8	200.1	214.3	229.5
52.5°	94.8	106.2	117.6	129.9	143.2	157.4	171.6	185.8	201.0	216.2	231.4
55°	90.1	101.5	113.8	127.1	140.3	154.6	169.7	184.9	201.0	217.1	233.3
57.5°	85.3	97.7	110.0	123.3	137.5	152.7	168.8	184.9	201.0	218.1	235.1
60°	80.6	92.9	106.2	120.4	134.6	150.8	166.9	184.9	202.0	219.0	237.0
62.5°	75.9	88.2	101.5	116.6	131.8	148.9	165.9	183.0	201.0	220.0	238.9
65°	70.2	83.4	97.7	112.8	129.0	147.0	165.0	183.0	201.0	220.0	239.9
67.5°	65.4	78.7	92.9	109.0	127.1	145.1	163.1	182.1	202.0	220.9	241.8
70°	59.7	74.0	89.1	106.2	124.2	142.2	161.2	181.1	201.0	221.9	243.7
72.5°	55.0	69.2	85.3	102.4	121.4	140.3	160.2	180.2	202.0	222.8	244.6
75°	50.3	65.4	81.5	99.6	118.5	138.4	159.3	181.1	202.0	222.8	245.6
77.5°	45.5	60.7	77.8	96.7	115.7	137.5	158.3	179.2	201.0	223.8	248.4
80°	40.8	57.8	74.9	93.9	114.7	135.6	157.4	179.2	201.0	223.8	247.5
82.5°	37.9	55.0	72.1	92.0	112.8	134.6	156.5	179.2	201.0	224.7	248.4
85°	34.1	52.2	72.1	91.0	111.9	133.7	156.5	179.2	201.0	224.7	248.4
87.5°	32.2	50.3	70.2	90.1	111.9	133.7	156.5	179.2	202.0	225.7	250.3
90°	30.3	49.3	69.2	90.1	111.9	133.7	156.5	179.2	202.0	224.7	250.3
92.5°	32.2	50.3	70.2	90.1	111.9	133.7	156.5	179.2	202.0	225.7	250.3
95°	34.1	52.2	72.1	91.0	111.9	133.7	156.5	179.2	201.0	224.7	248.4
97.5°	37.9	55.0	72.1	92.0	112.8	134.6	156.5	179.2	201.0	224.7	248.4
100°	40.8	57.8	74.9	93.9	114.7	135.6	157.4	179.2	201.0	223.8	247.5
102.5°	45.5	60.7	77.8	96.7	115.7	137.5	158.3	179.2	201.0	223.8	248.4
105°	50.3	65.4	81.5	99.6	118.5	138.4	159.3	181.1	202.0	222.8	245.6
107.5°	55.0	69.2	85.3	102.4	121.4	140.3	160.2	180.2	202.0	222.8	244.6
110°	59.7	74.0	89.1	106.2	124.2	142.2	161.2	181.1	201.0	221.9	243.7



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	65.4	78.7	92.9	109.0	127.1	145.1	163.1	182.1	202.0	220.9	241.8
115°	70.2	83.4	97.7	112.8	129.0	147.0	165.0	183.0	201.0	220.0	239.9
117.5°	75.9	88.2	101.5	116.6	131.8	148.9	165.9	183.0	201.0	220.0	238.9
120°	80.6	92.9	106.2	120.4	134.6	150.8	166.9	184.9	202.0	219.0	237.0
122.5°	85.3	97.7	110.0	123.3	137.5	152.7	168.8	184.9	201.0	218.1	235.1
125°	90.1	101.5	113.8	127.1	140.3	154.6	169.7	184.9	201.0	217.1	233.3
127.5°	94.8	106.2	117.6	129.9	143.2	157.4	171.6	185.8	201.0	216.2	231.4
130°	99.6	110.0	121.4	133.7	146.0	159.3	172.6	186.8	200.1	214.3	229.5
132.5°	103.4	114.7	125.2	136.5	147.9	160.2	173.5	185.8	199.1	213.3	226.6
135°	108.1	117.6	128.0	139.4	149.8	161.2	173.5	185.8	198.2	211.4	224.7
137.5°	111.9	121.4	131.8	141.3	151.7	163.1	174.5	185.8	197.2	209.5	220.9
140°	115.7	125.2	134.6	144.1	153.6	163.1	173.5	184.9	196.3	207.7	218.1
142.5°	119.5	128.0	136.5	146.0	155.5	165.0	174.5	183.9	194.4	204.8	215.2
145°	123.3	130.8	139.4	147.9	156.5	165.0	174.5	183.0	192.5	202.9	212.4
147.5°	126.1	133.7	141.3	148.9	157.4	165.9	173.5	182.1	190.6	200.1	209.5
150°	129.0	135.6	143.2	150.8	158.3	165.9	173.5	181.1	188.7	197.2	204.8
152.5°	132.7	138.4	145.1	151.7	158.3	165.9	172.6	180.2	186.8	193.4	201.0
155°	134.6	140.3	146.0	151.7	158.3	165.0	171.6	177.3	183.9	190.6	196.3
157.5°	136.5	142.2	147.0	152.7	158.3	164.0	169.7	175.4	181.1	186.8	192.5
160°	139.4	143.2	147.9	152.7	157.4	162.1	167.8	172.6	177.3	183.0	187.7
162.5°	140.3	144.1	148.9	152.7	156.5	160.2	165.0	169.7	173.5	178.3	183.0
165°	141.3	145.1	148.9	151.7	155.5	159.3	163.1	166.9	170.7	174.5	177.3
167.5°	142.2	145.1	148.9	151.7	154.6	157.4	160.2	163.1	165.9	168.8	172.6
170°	143.2	145.1	147.9	149.8	152.7	154.6	157.4	159.3	161.2	164.0	165.9
172.5°	144.1	145.1	147.0	148.9	150.8	151.7	153.6	155.5	157.4	158.3	160.2
175°	143.2	145.1	146.0	147.0	147.9	148.9	150.8	151.7	152.7	153.6	154.6
177.5°	142.2	143.2	144.1	144.1	145.1	145.1	146.0	147.0	147.0	147.9	147.9
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	148.9	148.9	149.8	149.8	150.8	150.8	151.7	151.7	152.7	152.7	152.7
5°	155.5	156.5	157.4	158.3	159.3	160.2	161.2	162.1	163.1	164.0	164.0
7.5°	162.1	163.1	165.0	166.9	167.8	169.7	170.7	172.6	173.5	174.5	176.4
10°	167.8	170.7	172.6	174.5	176.4	179.2	181.1	183.0	184.9	185.8	187.7
12.5°	175.4	178.3	181.1	183.9	185.8	188.7	190.6	193.4	195.3	198.2	200.1
15°	181.1	184.9	188.7	191.5	195.3	198.2	201.0	203.9	206.7	209.5	211.4
17.5°	186.8	191.5	195.3	199.1	202.9	206.7	210.5	214.3	217.1	220.9	223.8
20°	192.5	197.2	202.0	206.7	211.4	215.2	220.0	224.7	228.5	233.3	237.0
22.5°	198.2	202.9	208.6	214.3	219.0	224.7	230.4	235.1	240.8	245.6	250.3
25°	202.9	208.6	215.2	221.9	228.5	234.2	240.8	246.5	252.2	257.9	262.6
27.5°	207.7	215.2	222.8	229.5	237.0	243.7	250.3	257.0	263.6	269.3	275.0
30°	213.3	221.9	229.5	237.0	245.6	253.2	260.8	267.4	275.0	281.6	287.3
32.5°	218.1	227.6	236.1	244.6	253.2	261.7	269.3	277.8	285.4	293.0	300.6
35°	222.8	232.3	242.7	252.2	261.7	270.2	278.8	287.3	295.8	304.4	312.9
37.5°	225.7	237.0	247.5	258.9	268.3	278.8	288.2	297.7	306.3	315.7	324.3
40°	229.5	240.8	253.2	264.5	275.9	286.4	297.7	308.2	317.6	327.1	335.7
42.5°	233.3	245.6	257.9	271.2	283.5	294.9	306.3	316.7	327.1	337.6	347.0
45°	237.0	250.3	263.6	276.9	290.1	303.4	313.8	325.2	337.6	348.0	358.4
47.5°	240.8	255.1	269.3	283.5	296.8	310.1	322.4	334.7	346.1	358.4	368.8
50°	243.7	258.9	274.0	288.2	302.5	316.7	330.0	343.2	355.6	367.9	380.2
52.5°	247.5	262.6	277.8	293.9	308.2	323.3	337.6	352.7	365.1	377.4	389.7
55°	249.4	266.4	282.6	298.7	314.8	330.0	345.1	359.4	373.6	386.9	399.2
57.5°	253.2	270.2	287.3	304.4	319.5	335.7	351.8	366.0	381.2	395.4	408.7
60°	256.0	275.0	291.1	308.2	325.2	342.3	358.4	374.5	389.7	404.9	418.1
62.5°	257.9	276.9	295.8	312.9	330.9	348.0	365.1	382.1	396.3	411.5	425.7
65°	259.8	279.7	298.7	317.6	335.7	353.7	370.7	386.9	403.0	419.1	433.3
67.5°	262.6	283.5	302.5	321.4	339.5	357.5	375.5	392.5	410.6	425.7	440.9
70°	264.5	285.4	304.4	324.3	343.2	362.2	381.2	399.2	417.2	432.4	447.5
72.5°	265.5	287.3	308.2	328.1	348.0	366.9	385.0	403.0	421.0	437.1	452.3
75°	268.3	290.1	311.0	330.9	350.8	369.8	388.8	406.8	424.8	441.9	458.0
77.5°	269.3	290.1	312.0	332.8	353.7	373.6	392.5	411.5	430.5	447.5	463.7
80°	270.2	292.0	313.8	335.7	356.5	376.4	395.4	414.4	432.4	449.4	465.6
82.5°	272.1	293.0	314.8	336.6	357.5	377.4	397.3	416.3	435.2	452.3	468.4
85°	272.1	293.9	315.7	337.6	359.4	379.3	399.2	419.1	437.1	455.1	471.2
87.5°	273.1	295.8	316.7	338.5	361.3	381.2	401.1	420.0	438.1	456.1	473.1
90°	273.1	294.9	317.6	339.5	360.3	382.1	401.1	420.0	438.1	457.0	475.0
92.5°	273.1	295.8	316.7	338.5	361.3	381.2	401.1	420.0	438.1	456.1	473.1
95°	272.1	293.9	315.7	337.6	359.4	379.3	399.2	419.1	437.1	455.1	471.2
97.5°	272.1	293.0	314.8	336.6	357.5	377.4	397.3	416.3	435.2	452.3	468.4
100°	270.2	292.0	313.8	335.7	356.5	376.4	395.4	414.4	432.4	449.4	465.6
102.5°	269.3	290.1	312.0	332.8	353.7	373.6	392.5	411.5	430.5	447.5	463.7
105°	268.3	290.1	311.0	330.9	350.8	369.8	388.8	406.8	424.8	441.9	458.0
107.5°	265.5	287.3	308.2	328.1	348.0	366.9	385.0	403.0	421.0	437.1	452.3
110°	264.5	285.4	304.4	324.3	343.2	362.2	381.2	399.2	417.2	432.4	447.5



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	262.6	283.5	302.5	321.4	339.5	357.5	375.5	392.5	410.6	425.7	440.9
115°	259.8	279.7	298.7	317.6	335.7	353.7	370.7	386.9	403.0	419.1	433.3
117.5°	257.9	276.9	295.8	312.9	330.9	348.0	365.1	382.1	396.3	411.5	425.7
120°	256.0	275.0	291.1	308.2	325.2	342.3	358.4	374.5	389.7	404.9	418.1
122.5°	253.2	270.2	287.3	304.4	319.5	335.7	351.8	366.0	381.2	395.4	408.7
125°	249.4	266.4	282.6	298.7	314.8	330.0	345.1	359.4	373.6	386.9	399.2
127.5°	247.5	262.6	277.8	293.9	308.2	323.3	337.6	352.7	365.1	377.4	389.7
130°	243.7	258.9	274.0	288.2	302.5	316.7	330.0	343.2	355.6	367.9	380.2
132.5°	240.8	255.1	269.3	283.5	296.8	310.1	322.4	334.7	346.1	358.4	368.8
135°	237.0	250.3	263.6	276.9	290.1	303.4	313.8	325.2	337.6	348.0	358.4
137.5°	233.3	245.6	257.9	271.2	283.5	294.9	306.3	316.7	327.1	337.6	347.0
140°	229.5	240.8	253.2	264.5	275.9	286.4	297.7	308.2	317.6	327.1	335.7
142.5°	225.7	237.0	247.5	258.9	268.3	278.8	288.2	297.7	306.3	315.7	324.3
145°	222.8	232.3	242.7	252.2	261.7	270.2	278.8	287.3	295.8	304.4	312.9
147.5°	218.1	227.6	236.1	244.6	253.2	261.7	269.3	277.8	285.4	293.0	300.6
150°	213.3	221.9	229.5	237.0	245.6	253.2	260.8	267.4	275.0	281.6	287.3
152.5°	207.7	215.2	222.8	229.5	237.0	243.7	250.3	257.0	263.6	269.3	275.0
155°	202.9	208.6	215.2	221.9	228.5	234.2	240.8	246.5	252.2	257.9	262.6
157.5°	198.2	202.9	208.6	214.3	219.0	224.7	230.4	235.1	240.8	245.6	250.3
160°	192.5	197.2	202.0	206.7	211.4	215.2	220.0	224.7	228.5	233.3	237.0
162.5°	186.8	191.5	195.3	199.1	202.9	206.7	210.5	214.3	217.1	220.9	223.8
165°	181.1	184.9	188.7	191.5	195.3	198.2	201.0	203.9	206.7	209.5	211.4
167.5°	175.4	178.3	181.1	183.9	185.8	188.7	190.6	193.4	195.3	198.2	200.1
170°	167.8	170.7	172.6	174.5	176.4	179.2	181.1	183.0	184.9	185.8	187.7
172.5°	162.1	163.1	165.0	166.9	167.8	169.7	170.7	172.6	173.5	174.5	176.4
175°	155.5	156.5	157.4	158.3	159.3	160.2	161.2	162.1	163.1	164.0	164.0
177.5°	148.9	148.9	149.8	149.8	150.8	150.8	151.7	151.7	152.7	152.7	152.7
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2
2.5°	153.6	153.6	153.6	154.6	154.6	154.6	154.6	155.5	155.5	155.5	155.5
5°	165.0	165.9	165.9	166.9	166.9	167.8	167.8	167.8	168.8	168.8	168.8
7.5°	177.3	178.3	179.2	180.2	181.1	182.1	182.1	183.0	183.0	183.0	183.9
10°	189.6	190.6	192.5	193.4	194.4	195.3	196.3	197.2	198.2	198.2	198.2
12.5°	202.0	203.9	204.8	206.7	207.7	209.5	210.5	211.4	212.4	213.3	213.3
15°	214.3	216.2	218.1	220.0	221.9	222.8	224.7	225.7	227.6	227.6	228.5
17.5°	226.6	229.5	232.3	234.2	236.1	238.0	239.9	241.8	243.7	244.6	244.6
20°	240.8	243.7	246.5	249.4	252.2	254.1	256.0	257.9	259.8	260.8	261.7
22.5°	254.1	257.9	261.7	264.5	268.3	270.2	273.1	275.0	275.9	277.8	278.8
25°	267.4	272.1	275.9	279.7	283.5	286.4	289.2	291.1	293.0	293.9	295.8
27.5°	280.7	286.4	290.1	294.9	298.7	301.5	305.3	307.2	309.1	311.0	312.0
30°	293.9	299.6	304.4	309.1	313.8	317.6	320.5	323.3	326.2	328.1	329.0
32.5°	306.3	312.9	318.6	324.3	329.0	332.8	336.6	340.4	342.3	344.2	346.1
35°	319.5	326.2	332.8	338.5	343.2	348.0	352.7	356.5	359.4	361.3	363.2
37.5°	332.8	339.5	346.1	352.7	358.4	363.2	367.9	372.6	374.5	377.4	379.3
40°	344.2	352.7	359.4	366.0	372.6	378.3	383.1	387.8	390.7	393.5	395.4
42.5°	356.5	365.1	372.6	380.2	386.9	393.5	398.2	403.0	406.8	409.6	411.5
45°	367.9	377.4	385.9	394.4	401.1	407.7	413.4	418.1	422.9	425.7	427.6
47.5°	379.3	389.7	399.2	407.7	415.3	421.9	427.6	432.4	437.1	440.0	442.8
50°	390.7	401.1	410.6	420.0	427.6	435.2	440.9	446.6	451.3	455.1	457.0
52.5°	401.1	412.5	422.9	432.4	440.9	448.5	455.1	460.8	465.6	469.4	472.2
55°	411.5	422.9	434.3	443.8	453.2	460.8	468.4	475.0	479.8	483.6	486.4
57.5°	421.9	434.3	445.6	456.1	464.6	473.1	479.8	486.4	492.1	495.9	498.7
60°	431.4	443.8	455.1	465.6	475.0	483.6	491.2	497.8	503.5	507.3	511.1
62.5°	439.0	452.3	463.7	475.0	485.5	494.0	501.6	509.2	514.9	519.6	522.4
65°	447.5	460.8	473.1	484.5	495.0	504.4	513.0	520.6	526.2	531.0	534.8
67.5°	456.1	470.3	481.7	493.1	503.5	513.0	521.5	529.1	534.8	540.5	543.3
70°	461.8	476.0	488.3	499.7	511.1	520.6	529.1	537.6	543.3	549.0	551.8
72.5°	467.5	481.7	495.0	507.3	518.7	528.1	537.6	545.2	551.8	557.5	561.3
75°	473.1	488.3	501.6	513.9	525.3	536.7	545.2	553.7	560.4	566.1	569.9
77.5°	478.8	494.0	506.3	518.7	530.0	541.4	549.9	558.5	565.1	570.8	574.6
80°	481.7	496.8	510.1	522.4	533.8	545.2	554.7	563.2	569.9	574.6	578.4
82.5°	484.5	500.6	513.0	526.2	538.6	549.0	558.5	567.0	573.7	579.3	583.1
85°	488.3	504.4	516.8	530.0	542.4	553.7	563.2	571.8	578.4	583.1	587.9
87.5°	490.2	505.4	518.7	531.9	543.3	554.7	564.2	572.7	579.3	585.0	588.8
90°	492.1	506.3	520.6	533.8	544.3	556.6	566.1	573.7	580.3	586.0	589.8
92.5°	490.2	505.4	518.7	531.9	543.3	554.7	564.2	572.7	579.3	585.0	588.8
95°	488.3	504.4	516.8	530.0	542.4	553.7	563.2	571.8	578.4	583.1	587.9
97.5°	484.5	500.6	513.0	526.2	538.6	549.0	558.5	567.0	573.7	579.3	583.1
100°	481.7	496.8	510.1	522.4	533.8	545.2	554.7	563.2	569.9	574.6	578.4
102.5°	478.8	494.0	506.3	518.7	530.0	541.4	549.9	558.5	565.1	570.8	574.6
105°	473.1	488.3	501.6	513.9	525.3	536.7	545.2	553.7	560.4	566.1	569.9
107.5°	467.5	481.7	495.0	507.3	518.7	528.1	537.6	545.2	551.8	557.5	561.3
110°	461.8	476.0	488.3	499.7	511.1	520.6	529.1	537.6	543.3	549.0	551.8



TEST NUMBER: P368713  
 CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	456.1	470.3	481.7	493.1	503.5	513.0	521.5	529.1	534.8	540.5	543.3
115°	447.5	460.8	473.1	484.5	495.0	504.4	513.0	520.6	526.2	531.0	534.8
117.5°	439.0	452.3	463.7	475.0	485.5	494.0	501.6	509.2	514.9	519.6	522.4
120°	431.4	443.8	455.1	465.6	475.0	483.6	491.2	497.8	503.5	507.3	511.1
122.5°	421.9	434.3	445.6	456.1	464.6	473.1	479.8	486.4	492.1	495.9	498.7
125°	411.5	422.9	434.3	443.8	453.2	460.8	468.4	475.0	479.8	483.6	486.4
127.5°	401.1	412.5	422.9	432.4	440.9	448.5	455.1	460.8	465.6	469.4	472.2
130°	390.7	401.1	410.6	420.0	427.6	435.2	440.9	446.6	451.3	455.1	457.0
132.5°	379.3	389.7	399.2	407.7	415.3	421.9	427.6	432.4	437.1	440.0	442.8
135°	367.9	377.4	385.9	394.4	401.1	407.7	413.4	418.1	422.9	425.7	427.6
137.5°	356.5	365.1	372.6	380.2	386.9	393.5	398.2	403.0	406.8	409.6	411.5
140°	344.2	352.7	359.4	366.0	372.6	378.3	383.1	387.8	390.7	393.5	395.4
142.5°	332.8	339.5	346.1	352.7	358.4	363.2	367.9	372.6	374.5	377.4	379.3
145°	319.5	326.2	332.8	338.5	343.2	348.0	352.7	356.5	359.4	361.3	363.2
147.5°	306.3	312.9	318.6	324.3	329.0	332.8	336.6	340.4	342.3	344.2	346.1
150°	293.9	299.6	304.4	309.1	313.8	317.6	320.5	323.3	326.2	328.1	329.0
152.5°	280.7	286.4	290.1	294.9	298.7	301.5	305.3	307.2	309.1	311.0	312.0
155°	267.4	272.1	275.9	279.7	283.5	286.4	289.2	291.1	293.0	293.9	295.8
157.5°	254.1	257.9	261.7	264.5	268.3	270.2	273.1	275.0	275.9	277.8	278.8
160°	240.8	243.7	246.5	249.4	252.2	254.1	256.0	257.9	259.8	260.8	261.7
162.5°	226.6	229.5	232.3	234.2	236.1	238.0	239.9	241.8	243.7	244.6	244.6
165°	214.3	216.2	218.1	220.0	221.9	222.8	224.7	225.7	227.6	227.6	228.5
167.5°	202.0	203.9	204.8	206.7	207.7	209.5	210.5	211.4	212.4	213.3	213.3
170°	189.6	190.6	192.5	193.4	194.4	195.3	196.3	197.2	198.2	198.2	198.2
172.5°	177.3	178.3	179.2	180.2	181.1	182.1	182.1	183.0	183.0	183.0	183.9
175°	165.0	165.9	165.9	166.9	166.9	167.8	167.8	167.8	168.8	168.8	168.8
177.5°	153.6	153.6	153.6	154.6	154.6	154.6	154.6	155.5	155.5	155.5	155.5
180°	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2	142.2



TEST NUMBER: P368713  
CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	142.2	142.2
2.5°	155.5	155.5
5°	168.8	168.8
7.5°	183.9	183.9
10°	198.2	199.1
12.5°	213.3	213.3
15°	228.5	228.5
17.5°	245.6	245.6
20°	262.6	262.6
22.5°	279.7	279.7
25°	296.8	296.8
27.5°	312.9	313.8
30°	330.0	330.9
32.5°	347.0	348.0
35°	364.1	365.1
37.5°	380.2	381.2
40°	397.3	398.2
42.5°	413.4	414.4
45°	429.5	430.5
47.5°	444.7	445.6
50°	458.9	460.8
52.5°	474.1	475.0
55°	488.3	490.2
57.5°	500.6	502.5
60°	513.0	514.9
62.5°	524.3	526.2
65°	536.7	538.6
67.5°	545.2	547.1
70°	554.7	556.6
72.5°	563.2	565.1
75°	571.8	573.7
77.5°	576.5	578.4
80°	581.2	582.2
82.5°	585.0	586.9
85°	589.8	590.7
87.5°	590.7	592.6
90°	592.6	593.6
92.5°	590.7	592.6
95°	589.8	590.7
97.5°	585.0	586.9
100°	581.2	582.2
102.5°	576.5	578.4
105°	571.8	573.7
107.5°	563.2	565.1
110°	554.7	556.6





TEST NUMBER: P368713  
CATALOG NUMBER: 605-25-L3/835

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	545.2	547.1
115°	536.7	538.6
117.5°	524.3	526.2
120°	513.0	513.9
122.5°	500.6	502.5
125°	488.3	490.2
127.5°	474.1	475.0
130°	458.9	460.8
132.5°	444.7	445.6
135°	429.5	430.5
137.5°	413.4	414.4
140°	397.3	398.2
142.5°	380.2	381.2
145°	364.1	365.1
147.5°	347.0	348.0
150°	330.0	330.9
152.5°	312.9	313.8
155°	296.8	296.8
157.5°	279.7	279.7
160°	262.6	262.6
162.5°	245.6	245.6
165°	228.5	228.5
167.5°	213.3	213.3
170°	198.2	199.1
172.5°	183.9	183.9
175°	168.8	168.8
177.5°	155.5	155.5
180°	142.2	142.2

(END OF REPORT)