

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600585

Luminaire Tested: 205-90-30K-LL2-UNV-STD-X-X-WHHR-SR-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600585
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 205-90-30K-LL2-UNV-STD-X-X-WHHR-SR-X
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1556.3 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600585
CATALOG NUMBER: 205-90-30K-LL2-UNV-STD-X-X-WHHR-SR-X

Luminous Intensity Polar Plot





TEST NUMBER: P600585

CATALOG NUMBER: 205-90-30K-LL2-UNV-STD-X-X-WHHR-SR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	88													88															
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77													77															
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68													68															
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61													61															
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54													54															
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49													49															
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	56	50	46	44													44															
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41													41															
9	64	52	44	39	62	51	44	39	50	44	39	49	43	39	48	43	39	37													37															
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34													34															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7899
5°	7014
10°	6480
15°	6321
20°	6253
25°	6239
30°	6196
35°	6143
40°	5444
45°	2216
50°	1950
55°	1887
60°	1847
65°	1769
70°	1700
75°	1632
80°	1563
85°	1530

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2216 cd/sqm



TEST NUMBER: P600585

CATALOG NUMBER: 205-90-30K-LL2-UNV-STD-X-X-WHHR-SR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.4	5.4
10°-20°	223.9	14.4
20°-30°	337.9	21.7
30°-40°	403.0	25.9
40°-50°	208.4	13.4
50°-60°	125.7	8.1
60°-70°	96.3	6.2
70°-80°	57.8	3.7
80°-90°	18.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.2	41.5
0°-40°	1049.2	67.4
0°-60°	1383.3	88.9
0°-90°	1556.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1556.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1025	
5°	906	84
15°	792	224
25°	734	338
35°	653	403
45°	203	208
55°	140	126
65°	97	96
75°	55	58
85°	17	19
90°	0	



TEST NUMBER: P600585

CATALOG NUMBER: 205-90-30K-LL2-UNV-STD-X-X-WHHR-SR-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1024.6
2.5°	992.1
5°	906.4
7.5°	854.4
10°	827.8
12.5°	808.9
15°	792.0
17.5°	776.9
20°	762.2
22.5°	748.7
25°	733.5
27.5°	716.7
30°	696.1
32.5°	671.7
35°	652.7
37.5°	632.7
40°	541.0
42.5°	360.5
45°	203.3
47.5°	181.1
50°	162.6
52.5°	149.6
55°	140.4
57.5°	130.7
60°	119.8
62.5°	108.4
65°	97.0
67.5°	86.2
70°	75.4
72.5°	64.5
75°	54.8
77.5°	44.5
80°	35.2
82.5°	26.0
85°	17.3
87.5°	8.7
90°	0.0

(END OF REPORT)