

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600613

Luminaire Tested: 205-90-35K-LL4-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600613  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 205-90-35K-LL4-UNV-STD-X-X-WHHR-BR-X  
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2870.8 lumens  
Efficiency: N/A  
Efficacy: 123.7 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17  
Luminous Opening: Circular (Dia: 1.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600613  
CATALOG NUMBER: 205-90-35K-LL4-UNV-STD-X-X-WHHR-BR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600613

CATALOG NUMBER: 205-90-35K-LL4-UNV-STD-X-X-WHHR-BR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39	49	43	39	48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	14570
5°	12939
10°	11953
15°	11660
20°	11535
25°	11509
30°	11430
35°	11331
40°	10043
45°	4088
50°	3598
55°	3481
60°	3407
65°	3265
70°	3133
75°	3008
80°	2886
85°	2830

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4088 cd/sqm



TEST NUMBER: P600613

CATALOG NUMBER: 205-90-35K-LL4-UNV-STD-X-X-WHHR-BR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.7	5.4
10°-20°	413.0	14.4
20°-30°	623.4	21.7
30°-40°	743.3	25.9
40°-50°	384.4	13.4
50°-60°	231.8	8.1
60°-70°	177.7	6.2
70°-80°	106.6	3.7
80°-90°	35.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1192.1	41.5
0°-40°	1935.4	67.4
0°-60°	2551.6	88.9
0°-90°	2870.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2870.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1890	
5°	1672	156
15°	1461	413
25°	1353	623
35°	1204	743
45°	375	384
55°	259	232
65°	179	178
75°	101	107
85°	32	35
90°	0	



TEST NUMBER: P600613

CATALOG NUMBER: 205-90-35K-LL4-UNV-STD-X-X-WHHR-BR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1890
2.5°	1830
5°	1672
7.5°	1576
10°	1527
12.5°	1492
15°	1461
17.5°	1433
20°	1406
22.5°	1381
25°	1353
27.5°	1322
30°	1284
32.5°	1239
35°	1204
37.5°	1167
40°	998
42.5°	665
45°	375
47.5°	334
50°	300
52.5°	276
55°	259
57.5°	241
60°	221
62.5°	200
65°	179
67.5°	159
70°	139
72.5°	119
75°	101
77.5°	82
80°	65
82.5°	48
85°	32
87.5°	16
90°	0

(END OF REPORT)