

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600623

Luminaire Tested: 205-90-35K-LL7-UNV-STD-X-X-WHHR-FL-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 205-90-35K-LL7-UNV-STD-X-X-WHHR-FL-X
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5853.4 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 55.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600623
CATALOG NUMBER: 205-90-35K-LL7-UNV-STD-X-X-WHHR-FL-X

Luminous Intensity Polar Plot





TEST NUMBER: P600623

CATALOG NUMBER: 205-90-35K-LL7-UNV-STD-X-X-WHHR-FL-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39	49	43	39	48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29708
5°	26382
10°	24372
15°	23775
20°	23518
25°	23466
30°	23305
35°	23103
40°	20477
45°	8336
50°	7336
55°	7098
60°	6947
65°	6658
70°	6388
75°	6133
80°	5882
85°	5767

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8336 cd/sqm



TEST NUMBER: P600623

CATALOG NUMBER: 205-90-35K-LL7-UNV-STD-X-X-WHHR-FL-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	317.4	5.4
10°-20°	842.1	14.4
20°-30°	1271.0	21.7
30°-40°	1515.6	25.9
40°-50°	783.8	13.4
50°-60°	472.7	8.1
60°-70°	362.2	6.2
70°-80°	217.3	3.7
80°-90°	71.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2430.5	41.5
0°-40°	3946.1	67.4
0°-60°	5202.6	88.9
0°-90°	5853.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5853.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3854	
5°	3409	317
15°	2979	842
25°	2759	1271
35°	2455	1516
45°	765	784
55°	528	473
65°	365	362
75°	206	217
85°	65	71
90°	0	



TEST NUMBER: P600623

CATALOG NUMBER: 205-90-35K-LL7-UNV-STD-X-X-WHHR-FL-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	3853.6
2.5°	3731.2
5°	3409.1
7.5°	3213.3
10°	3113.4
12.5°	3042.1
15°	2978.9
17.5°	2921.8
20°	2866.7
22.5°	2815.7
25°	2758.7
27.5°	2695.5
30°	2618.0
32.5°	2526.2
35°	2454.9
37.5°	2379.4
40°	2034.8
42.5°	1355.9
45°	764.6
47.5°	681.0
50°	611.7
52.5°	562.7
55°	528.1
57.5°	491.4
60°	450.6
62.5°	407.8
65°	365.0
67.5°	324.2
70°	283.4
72.5°	242.6
75°	205.9
77.5°	167.2
80°	132.5
82.5°	97.9
85°	65.2
87.5°	32.6
90°	0.0

(END OF REPORT)