

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600674

Luminaire Tested: 215-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600674  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 215-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X  
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5302.5 lumens  
Efficiency: N/A  
Efficacy: 73.4 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.85  
Luminous Opening: Circular (Dia: 1' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600674  
CATALOG NUMBER: 215-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600674

CATALOG NUMBER: 215-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100															
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90					90															
2	104	98	93	89	102	96	92	87	93	89	86	90	87	84	87	84	82	80					80															
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72					72															
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65					65															
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59					59															
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54					54															
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50					50															
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	47	46					46															
9	68	56	49	45	66	56	49	45	55	49	45	54	48	44	53	48	44	43					43															
10	64	53	46	42	63	52	46	42	51	46	42	51	45	41	50	45	41	40					40															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	70866
5°	57848
10°	53038
15°	51883
20°	51523
25°	51184
30°	40932
35°	19762
40°	17318
45°	15726
50°	13961
55°	12267
60°	10734
65°	9382
70°	8194
75°	6910
80°	4806
85°	1714

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15726 cd/sqm



TEST NUMBER: P600674

CATALOG NUMBER: 215-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	393.7	7.4
10°-20°	1033.9	19.5
20°-30°	1514.4	28.6
30°-40°	823.1	15.5
40°-50°	624.7	11.8
50°-60°	462.0	8.7
60°-70°	290.3	5.5
70°-80°	138.7	2.6
80°-90°	21.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2941.9	55.5
0°-40°	3765.0	71.0
0°-60°	4851.6	91.5
0°-90°	5302.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5302.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5171	
5°	4205	394
15°	3657	1034
25°	3385	1514
35°	1181	823
45°	811	625
55°	513	462
65°	289	290
75°	130	139
85°	11	22
90°	0	



TEST NUMBER: P600674

CATALOG NUMBER: 215-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5170.8
2.5°	4851.0
5°	4204.9
7.5°	3922.1
10°	3811.2
12.5°	3730.7
15°	3656.7
17.5°	3587.1
20°	3532.7
22.5°	3480.5
25°	3384.8
27.5°	3249.9
30°	2586.5
32.5°	1305.2
35°	1181.2
37.5°	1068.1
40°	968.0
42.5°	887.5
45°	811.4
47.5°	733.1
50°	654.8
52.5°	583.0
55°	513.4
57.5°	450.3
60°	391.6
62.5°	339.4
65°	289.3
67.5°	248.0
70°	204.5
72.5°	167.5
75°	130.5
77.5°	95.7
80°	60.9
82.5°	34.8
85°	10.9
87.5°	4.4
90°	0.0

(END OF REPORT)