

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600682

Luminaire Tested: 215-90-30K-LL3-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600682  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 215-90-30K-LL3-UNV-STD-X-X-WHHR-BR-X  
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1808.5 lumens  
Efficiency: N/A  
Efficacy: 103.9 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.85  
Luminous Opening: Circular (Dia: 1' x H: 0')  
CIE Type: Direct

Input Watts (W): 17.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600682  
CATALOG NUMBER: 215-90-30K-LL3-UNV-STD-X-X-WHHR-BR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600682

CATALOG NUMBER: 215-90-30K-LL3-UNV-STD-X-X-WHHR-BR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100														
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90						90														
2	104	98	93	89	102	96	92	87	93	89	86	90	87	84	87	84	82	80						80														
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72						72														
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65						65														
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59						59														
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54						54														
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50						50														
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	47	46						46														
9	68	56	49	45	66	56	49	45	55	49	45	54	48	44	53	48	44	43						43														
10	64	53	46	42	63	52	46	42	51	46	42	51	45	41	50	45	41	40						40														

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	24170
5°	19729
10°	18090
15°	17696
20°	17573
25°	17457
30°	13961
35°	6741
40°	5907
45°	5363
50°	4761
55°	4184
60°	3659
65°	3201
70°	2793
75°	2356
80°	1642
85°	582

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5363 cd/sqm



TEST NUMBER: P600682

CATALOG NUMBER: 215-90-30K-LL3-UNV-STD-X-X-WHHR-BR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.3	7.4
10°-20°	352.6	19.5
20°-30°	516.5	28.6
30°-40°	280.7	15.5
40°-50°	213.0	11.8
50°-60°	157.6	8.7
60°-70°	99.0	5.5
70°-80°	47.3	2.6
80°-90°	7.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1003.4	55.5
0°-40°	1284.1	71.0
0°-60°	1654.7	91.5
0°-90°	1808.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1808.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1764	
5°	1434	134
15°	1247	353
25°	1154	517
35°	403	281
45°	277	213
55°	175	158
65°	99	99
75°	44	47
85°	4	7
90°	0	



TEST NUMBER: P600682

CATALOG NUMBER: 215-90-30K-LL3-UNV-STD-X-X-WHHR-BR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1763.6
2.5°	1654.5
5°	1434.1
7.5°	1337.7
10°	1299.9
12.5°	1272.4
15°	1247.2
17.5°	1223.4
20°	1204.9
22.5°	1187.1
25°	1154.4
27.5°	1108.4
30°	882.2
32.5°	445.2
35°	402.9
37.5°	364.3
40°	330.2
42.5°	302.7
45°	276.7
47.5°	250.0
50°	223.3
52.5°	198.8
55°	175.1
57.5°	153.6
60°	133.5
62.5°	115.7
65°	98.7
67.5°	84.6
70°	69.7
72.5°	57.1
75°	44.5
77.5°	32.6
80°	20.8
82.5°	11.9
85°	3.7
87.5°	1.5
90°	0.0

(END OF REPORT)