

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600697

Luminaire Tested: 215-90-30K-LL8-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600697  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 215-90-30K-LL8-UNV-STD-X-X-WHHR-BR-X  
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 3000K CCT, 90 CRI LEDs  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5621.4 lumens  
Efficiency: N/A  
Efficacy: 77.9 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.85  
Luminous Opening: Circular (Dia: 1' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600697  
CATALOG NUMBER: 215-90-30K-LL8-UNV-STD-X-X-WHHR-BR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600697

CATALOG NUMBER: 215-90-30K-LL8-UNV-STD-X-X-WHHR-BR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95	93	92	90
2	104	98	93	89	102	96	92	87	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	68	56	49	45	66	56	49	45	55	49	45		54	48	44		53	48	44	43
10	64	53	46	42	63	52	46	42	51	46	42		51	45	41		50	45	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	75127
5°	61326
10°	56227
15°	55003
20°	54622
25°	54262
30°	43393
35°	20950
40°	18359
45°	16672
50°	14799
55°	13003
60°	11378
65°	9946
70°	8687
75°	7329
80°	5099
85°	1808

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16672 cd/sqm



TEST NUMBER: P600697

CATALOG NUMBER: 215-90-30K-LL8-UNV-STD-X-X-WHHR-BR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	417.3	7.4
10°-20°	1096.0	19.5
20°-30°	1605.5	28.6
30°-40°	872.5	15.5
40°-50°	662.2	11.8
50°-60°	489.7	8.7
60°-70°	307.8	5.5
70°-80°	147.0	2.6
80°-90°	23.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3118.8	55.5
0°-40°	3991.4	71.0
0°-60°	5143.3	91.5
0°-90°	5621.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5621.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5482	
5°	4458	417
15°	3877	1096
25°	3588	1605
35°	1252	873
45°	860	662
55°	544	490
65°	307	308
75°	138	147
85°	12	23
90°	0	



TEST NUMBER: P600697

CATALOG NUMBER: 215-90-30K-LL8-UNV-STD-X-X-WHHR-BR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5481.7
2.5°	5142.7
5°	4457.7
7.5°	4158.0
10°	4040.3
12.5°	3955.0
15°	3876.6
17.5°	3802.8
20°	3745.2
22.5°	3689.8
25°	3588.3
27.5°	3445.4
30°	2742.0
32.5°	1383.7
35°	1252.2
37.5°	1132.3
40°	1026.2
42.5°	940.9
45°	860.2
47.5°	777.2
50°	694.1
52.5°	618.0
55°	544.2
57.5°	477.4
60°	415.1
62.5°	359.8
65°	306.7
67.5°	262.9
70°	216.8
72.5°	177.6
75°	138.4
77.5°	101.5
80°	64.6
82.5°	36.9
85°	11.5
87.5°	4.6
90°	0.0

(END OF REPORT)