

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600700

Luminaire Tested: 215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600700  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X  
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 963.0 lumens  
Efficiency: N/A  
Efficacy: 101.4 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.85  
Luminous Opening: Circular (Dia: 1' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600700  
CATALOG NUMBER: 215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600700

CATALOG NUMBER: 215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	98	93	89	102	96	92	87	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	47	46
9	68	56	49	45	66	56	49	45	55	49	45	54	48	44	53	48	44	43
10	64	53	46	42	63	52	46	42	51	46	42	51	45	41	50	45	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	12870
5°	10507
10°	9633
15°	9423
20°	9357
25°	9297
30°	7435
35°	3589
40°	3145
45°	2857
50°	2535
55°	2227
60°	1949
65°	1703
70°	1487
75°	1255
80°	876
85°	314

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2857 cd/sqm



TEST NUMBER: P600700

CATALOG NUMBER: 215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.5	7.4
10°-20°	187.8	19.5
20°-30°	275.1	28.6
30°-40°	149.5	15.5
40°-50°	113.4	11.8
50°-60°	83.9	8.7
60°-70°	52.7	5.5
70°-80°	25.2	2.6
80°-90°	4.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	534.3	55.5
0°-40°	683.8	71.0
0°-60°	881.2	91.5
0°-90°	963.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	963.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	939	
5°	764	71
15°	664	188
25°	615	275
35°	214	149
45°	147	113
55°	93	84
65°	52	53
75°	24	25
85°	2	4
90°	0	



TEST NUMBER: P600700

CATALOG NUMBER: 215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	939.1
2.5°	881.0
5°	763.7
7.5°	712.3
10°	692.2
12.5°	677.6
15°	664.1
17.5°	651.5
20°	641.6
22.5°	632.1
25°	614.8
27.5°	590.3
30°	469.8
32.5°	237.1
35°	214.5
37.5°	194.0
40°	175.8
42.5°	161.2
45°	147.4
47.5°	133.1
50°	118.9
52.5°	105.9
55°	93.2
57.5°	81.8
60°	71.1
62.5°	61.6
65°	52.5
67.5°	45.0
70°	37.1
72.5°	30.4
75°	23.7
77.5°	17.4
80°	11.1
82.5°	6.3
85°	2.0
87.5°	0.8
90°	0.0

(END OF REPORT)