

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600724

Luminaire Tested: 215-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600724  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 215-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X  
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 998.8 lumens  
Efficiency: N/A  
Efficacy: 105.1 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.85  
Luminous Opening: Circular (Dia: 1' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600724  
CATALOG NUMBER: 215-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600724

CATALOG NUMBER: 215-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100														
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90						90														
2	104	98	93	89	102	96	92	87	93	89	86	90	87	84	87	84	82	80						80														
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72						72														
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65						65														
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59						59														
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54						54														
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50						50														
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	47	46						46														
9	68	56	49	45	66	56	49	45	55	49	45	54	48	44	53	48	44	43						43														
10	64	53	46	42	63	52	46	42	51	46	42	51	45	41	50	45	41	40						40														

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	13349
5°	10897
10°	9991
15°	9773
20°	9706
25°	9642
30°	7710
35°	3723
40°	3261
45°	2962
50°	2629
55°	2311
60°	2023
65°	1767
70°	1543
75°	1303
80°	908
85°	314

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2962 cd/sqm



TEST NUMBER: P600724

CATALOG NUMBER: 215-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.2	7.4
10°-20°	194.8	19.5
20°-30°	285.3	28.6
30°-40°	155.0	15.5
40°-50°	117.7	11.8
50°-60°	87.0	8.7
60°-70°	54.7	5.5
70°-80°	26.1	2.6
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.2	55.5
0°-40°	709.2	71.0
0°-60°	913.9	91.5
0°-90°	998.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	998.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	974	
5°	792	74
15°	689	195
25°	638	285
35°	222	155
45°	153	118
55°	97	87
65°	54	55
75°	25	26
85°	2	4
90°	0	



TEST NUMBER: P600724

CATALOG NUMBER: 215-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	974.0
2.5°	913.8
5°	792.1
7.5°	738.8
10°	717.9
12.5°	702.8
15°	688.8
17.5°	675.7
20°	665.5
22.5°	655.6
25°	637.6
27.5°	612.2
30°	487.2
32.5°	245.9
35°	222.5
37.5°	201.2
40°	182.3
42.5°	167.2
45°	152.8
47.5°	138.1
50°	123.3
52.5°	109.8
55°	96.7
57.5°	84.8
60°	73.8
62.5°	63.9
65°	54.5
67.5°	46.7
70°	38.5
72.5°	31.6
75°	24.6
77.5°	18.0
80°	11.5
82.5°	6.6
85°	2.0
87.5°	0.8
90°	0.0

(END OF REPORT)