

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600574

Luminaire Tested: 225-90-27K-LL7-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 225-90-27K-LL7-UNV-STD-X-X-WHHR-BR-X
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5389.1 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 55.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600574
CATALOG NUMBER: 225-90-27K-LL7-UNV-STD-X-X-WHHR-BR-X

Luminous Intensity Polar Plot





TEST NUMBER: P600574

CATALOG NUMBER: 225-90-27K-LL7-UNV-STD-X-X-WHHR-BR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100															
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	88					88															
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77															
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68					68															
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61					61															
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54					54															
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49					49															
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	56	50	46	44					44															
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41					41															
9	64	52	44	39	62	51	44	39	50	44	39	49	43	39	48	43	39	37					37															
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34					34															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27351
5°	24289
10°	22439
15°	21889
20°	21653
25°	21605
30°	21456
35°	21271
40°	18854
45°	7675
50°	6755
55°	6535
60°	6397
65°	6129
70°	5881
75°	5647
80°	5416
85°	5316

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7675 cd/sqm



TEST NUMBER: P600574

CATALOG NUMBER: 225-90-27K-LL7-UNV-STD-X-X-WHHR-BR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.3	5.4
10°-20°	775.3	14.4
20°-30°	1170.2	21.7
30°-40°	1395.4	25.9
40°-50°	721.6	13.4
50°-60°	435.2	8.1
60°-70°	333.5	6.2
70°-80°	200.0	3.7
80°-90°	65.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2237.7	41.5
0°-40°	3633.2	67.4
0°-60°	4790.0	88.9
0°-90°	5389.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5389.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3548	
5°	3139	292
15°	2743	775
25°	2540	1170
35°	2260	1395
45°	704	722
55°	486	435
65°	336	333
75°	190	200
85°	60	66
90°	0	



TEST NUMBER: P600574

CATALOG NUMBER: 225-90-27K-LL7-UNV-STD-X-X-WHHR-BR-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	3547.9
2.5°	3435.3
5°	3138.7
7.5°	2958.5
10°	2866.5
12.5°	2800.8
15°	2742.6
17.5°	2690.0
20°	2639.4
22.5°	2592.4
25°	2539.9
27.5°	2481.7
30°	2410.3
32.5°	2325.9
35°	2260.2
37.5°	2190.7
40°	1873.5
42.5°	1248.3
45°	704.0
47.5°	627.0
50°	563.2
52.5°	518.1
55°	486.2
57.5°	452.4
60°	414.9
62.5°	375.4
65°	336.0
67.5°	298.5
70°	260.9
72.5°	223.4
75°	189.6
77.5°	153.9
80°	122.0
82.5°	90.1
85°	60.1
87.5°	30.0
90°	0.0

(END OF REPORT)