

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600578

Luminaire Tested: 225-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600578
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 225-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6193.0 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600578
CATALOG NUMBER: 225-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X

Luminous Intensity Polar Plot





TEST NUMBER: P600578

CATALOG NUMBER: 225-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|-----|--|--|--|----|--|--|--|--|--|--|--|--|----|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | | |
| RC | 80 | | | | | | | | | 70 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | 100 | | | | | | | | | | | | | | |
| 1 | 111 | 107 | 103 | 100 | 108 | 105 | 101 | 99 | 100 | 98 | 95 | 97 | 95 | 93 | 93 | 91 | 90 | 88 | | | | | | 88 | | | | | | | | | | | | | | |
| 2 | 103 | 96 | 90 | 86 | 100 | 94 | 89 | 85 | 91 | 86 | 83 | 88 | 84 | 81 | 85 | 82 | 79 | 77 | | | | | | 77 | | | | | | | | | | | | | | |
| 3 | 95 | 87 | 80 | 74 | 93 | 85 | 79 | 74 | 82 | 77 | 72 | 80 | 75 | 71 | 77 | 73 | 70 | 68 | | | | | | 68 | | | | | | | | | | | | | | |
| 4 | 89 | 79 | 71 | 65 | 87 | 77 | 70 | 65 | 75 | 69 | 64 | 73 | 68 | 63 | 71 | 66 | 63 | 61 | | | | | | 61 | | | | | | | | | | | | | | |
| 5 | 83 | 72 | 64 | 58 | 81 | 71 | 63 | 58 | 69 | 62 | 57 | 67 | 61 | 57 | 65 | 60 | 56 | 54 | | | | | | 54 | | | | | | | | | | | | | | |
| 6 | 77 | 66 | 58 | 52 | 75 | 65 | 57 | 52 | 63 | 56 | 52 | 61 | 56 | 51 | 60 | 55 | 51 | 49 | | | | | | 49 | | | | | | | | | | | | | | |
| 7 | 72 | 60 | 53 | 47 | 71 | 60 | 52 | 47 | 58 | 52 | 47 | 57 | 51 | 46 | 56 | 50 | 46 | 44 | | | | | | 44 | | | | | | | | | | | | | | |
| 8 | 68 | 56 | 48 | 43 | 66 | 55 | 48 | 43 | 54 | 47 | 43 | 53 | 47 | 42 | 52 | 46 | 42 | 41 | | | | | | 41 | | | | | | | | | | | | | | |
| 9 | 64 | 52 | 44 | 39 | 62 | 51 | 44 | 39 | 50 | 44 | 39 | 49 | 43 | 39 | 48 | 43 | 39 | 37 | | | | | | 37 | | | | | | | | | | | | | | |
| 10 | 60 | 48 | 41 | 36 | 59 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 36 | 45 | 40 | 36 | 34 | | | | | | 34 | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 31432 |
| 5° | 27912 |
| 10° | 25786 |
| 15° | 25154 |
| 20° | 24883 |
| 25° | 24827 |
| 30° | 24657 |
| 35° | 24443 |
| 40° | 21666 |
| 45° | 8820 |
| 50° | 7762 |
| 55° | 7509 |
| 60° | 7350 |
| 65° | 7043 |
| 70° | 6760 |
| 75° | 6490 |
| 80° | 6224 |
| 85° | 6103 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8820 cd/sqm



TEST NUMBER: P600578

CATALOG NUMBER: 225-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 335.8 | 5.4 |
| 10°-20° | 891.0 | 14.4 |
| 20°-30° | 1344.7 | 21.7 |
| 30°-40° | 1603.6 | 25.9 |
| 40°-50° | 829.3 | 13.4 |
| 50°-60° | 500.1 | 8.1 |
| 60°-70° | 383.2 | 6.2 |
| 70°-80° | 229.9 | 3.7 |
| 80°-90° | 75.4 | 1.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2571.5 | 41.5 |
| 0°-40° | 4175.1 | 67.4 |
| 0°-60° | 5504.5 | 88.9 |
| 0°-90° | 6193.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 6193.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4077 | |
| 5° | 3607 | 336 |
| 15° | 3152 | 891 |
| 25° | 2919 | 1345 |
| 35° | 2597 | 1604 |
| 45° | 809 | 829 |
| 55° | 559 | 500 |
| 65° | 386 | 383 |
| 75° | 218 | 230 |
| 85° | 69 | 75 |
| 90° | 0 | |



TEST NUMBER: P600578

CATALOG NUMBER: 225-90-27K-LL8-UNV-STD-X-X-WHHR-FL-X

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 4077.2 |
| 2.5° | 3947.7 |
| 5° | 3606.9 |
| 7.5° | 3399.8 |
| 10° | 3294.1 |
| 12.5° | 3218.6 |
| 15° | 3151.7 |
| 17.5° | 3091.3 |
| 20° | 3033.1 |
| 22.5° | 2979.1 |
| 25° | 2918.7 |
| 27.5° | 2851.9 |
| 30° | 2769.9 |
| 32.5° | 2672.8 |
| 35° | 2597.3 |
| 37.5° | 2517.5 |
| 40° | 2152.9 |
| 42.5° | 1434.6 |
| 45° | 809.0 |
| 47.5° | 720.5 |
| 50° | 647.2 |
| 52.5° | 595.4 |
| 55° | 558.7 |
| 57.5° | 519.9 |
| 60° | 476.7 |
| 62.5° | 431.4 |
| 65° | 386.1 |
| 67.5° | 343.0 |
| 70° | 299.9 |
| 72.5° | 256.7 |
| 75° | 217.9 |
| 77.5° | 176.9 |
| 80° | 140.2 |
| 82.5° | 103.5 |
| 85° | 69.0 |
| 87.5° | 34.5 |
| 90° | 0.0 |

(END OF REPORT)