

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152550

Luminaire Tested: **AVM-E03-LED-E-U-SL4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P152550  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: AVM-E03-LED-E-U-SL4  
Description: VISION SITE MEDIUM LED LUMINAIRE  
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL  
Light Source: (63) 4000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8862.3 lumens  
Efficiency: N/A  
Efficacy: 117.9 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short - Full Cutoff  
BUG Rating: B2 - U0 - G2


Input Watts (W): 75.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P152550  
 CATALOG NUMBER: AVM-E03-LED-E-U-SL4

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 19 fc  
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152550  
CATALOG NUMBER: AVM-E03-LED-E-U-SL4

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral    - - - Horizontal Cone Through 70-Deg Vertical



REPORT NUMBER: P152550

CATALOG NUMBER: AVM-E03-LED-E-U-SL4

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1839.7	0.0	1839.7
	% Fixture	20.8	0.0	20.8
<b>Street Side</b>	Lumens	7022.6	0.0	7022.6
	% Fixture	79.2	0.0	79.2
<b>Total</b>	Lumens	8862.3	0.0	8862.3
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.7	2.0
10°-20°	483.6	5.5
20°-30°	715.9	8.1
30°-40°	904.7	10.2
40°-50°	1023.2	11.5
50°-60°	1456.1	16.4
60°-70°	2711.8	30.6
70°-80°	1242.8	14.0
80°-90°	147.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8862.3	100.0
0°-180°	8862.3	100.0

**Coefficient of Utilization**



REPORT NUMBER: P152550


CATALOG NUMBER: AVM-E03-LED-E-U-SL4

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	807.0	9.1			
FM	(30°-60°)	2596.4	29.3			
FH	(60°-80°)	3509.8	39.6			G2/5000
FVH	(80°-90°)	109.4	1.2			G2/225
BL	(0°-30°)	569.2	6.4	B2/1000		
BM	(30°-60°)	787.7	8.9	B1/1000		
BH	(60°-80°)	444.8	5.0	B1/500		G1/500
BVH	(80°-90°)	38.1	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type IV Short





REPORT NUMBER: P152550

CATALOG NUMBER: AVM-E03-LED-E-U-SL4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1891	1891	1891	1891	1891	1891	1891	1891	1891	1891	1891
2.5°	1920	1925	1919	1918	1918	1917	1911	1910	1902	1903	1905
5°	1934	1936	1932	1931	1929	1925	1920	1914	1908	1902	1897
7.5°	1948	1946	1943	1943	1940	1934	1924	1916	1903	1896	1887
10°	1968	1965	1961	1959	1954	1945	1931	1920	1904	1890	1875
12.5°	1987	1986	1980	1977	1969	1960	1943	1926	1905	1883	1863
15°	2021	2017	2011	2005	1992	1980	1954	1934	1904	1875	1844
17.5°	2080	2073	2067	2054	2038	2017	1979	1945	1904	1862	1827
20°	2188	2173	2165	2148	2120	2082	2023	1968	1907	1853	1806
22.5°	2310	2300	2289	2278	2234	2179	2099	2017	1925	1849	1789
25°	2447	2434	2428	2409	2368	2305	2196	2082	1966	1865	1789
27.5°	2569	2565	2564	2542	2503	2429	2300	2163	2022	1898	1804
30°	2680	2676	2674	2662	2617	2529	2389	2235	2083	1944	1832
32.5°	2798	2785	2779	2756	2705	2602	2442	2282	2131	1989	1863
35°	2894	2883	2871	2838	2766	2644	2465	2298	2150	2014	1879
37.5°	2964	2953	2936	2894	2805	2658	2464	2293	2143	2010	1882
40°	2995	2984	2966	2913	2812	2650	2445	2270	2122	1989	1870
42.5°	2983	2975	2952	2901	2790	2614	2407	2227	2082	1955	1843
45°	2937	2931	2909	2855	2740	2556	2351	2173	2034	1913	1807
47.5°	2868	2866	2844	2791	2677	2498	2293	2120	1986	1872	1777
50°	2792	2782	2771	2722	2618	2448	2251	2087	1959	1857	1764
52.5°	2744	2741	2731	2687	2587	2419	2232	2075	1957	1854	1757
55°	3170	3177	3085	2894	2726	2499	2289	2136	2006	1902	1831
57.5°	4689	4658	4500	4121	3693	3128	2721	2474	2313	2331	2367
60°	5463	5457	5428	5281	4996	4566	4089	3542	3368	3387	3401
62.5°	5809	5818	5840	5785	5710	5585	5347	5127	4894	4807	4574
65°	5969	5985	6035	6066	6095	6117	6211	6469	6639	6321	5581
67.5°	5638	5715	5880	6041	6185	6390	6708	7307	7724	7333	6260
70°	4110	4215	4404	4902	5434	5899	6515	7427	8056	7754	6428
72.5°	2577	2606	2690	2873	3268	3865	4942	6310	7036	6795	5433
75°	1635	1645	1642	1684	1751	1881	2307	3727	4820	4444	3028
77.5°	974	989	995	1008	1040	1086	1121	1268	2021	1962	1099
80°	816	828	818	815	795	781	798	781	725	698	643
82.5°	432	431	428	457	516	562	597	589	533	454	385
85°	237	245	245	255	246	247	255	269	249	208	170
87.5°	20	31	25	31	42	30	29	29	25	18	16
90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P152550

CATALOG NUMBER: AVM-E03-LED-E-U-SL4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1891	1891	1891	1891	1891	1891	1891	1891	1891	1891	1891
2.5°	1900	1898	1894	1891	1891	1886	1883	1881	1880	1876	1876
5°	1894	1887	1880	1875	1872	1867	1859	1855	1850	1846	1844
7.5°	1881	1868	1857	1849	1839	1831	1821	1812	1803	1799	1797
10°	1861	1844	1827	1812	1798	1784	1771	1758	1747	1739	1731
12.5°	1842	1816	1794	1772	1750	1733	1715	1696	1680	1665	1661
15°	1816	1786	1758	1731	1704	1676	1654	1633	1607	1590	1577
17.5°	1792	1756	1722	1690	1657	1628	1595	1567	1541	1515	1496
20°	1766	1727	1691	1655	1619	1582	1544	1508	1476	1445	1414
22.5°	1743	1703	1668	1629	1589	1547	1503	1458	1421	1381	1345
25°	1729	1685	1649	1611	1567	1521	1471	1418	1373	1327	1284
27.5°	1729	1672	1635	1597	1552	1503	1448	1390	1339	1288	1235
30°	1744	1674	1624	1584	1538	1485	1424	1363	1307	1247	1196
32.5°	1758	1678	1616	1565	1512	1460	1398	1333	1271	1214	1160
35°	1767	1678	1601	1536	1476	1425	1364	1299	1236	1180	1130
37.5°	1768	1670	1577	1503	1440	1387	1329	1268	1208	1156	1114
40°	1758	1654	1553	1468	1402	1348	1295	1240	1186	1143	1107
42.5°	1740	1637	1530	1440	1371	1315	1266	1219	1172	1135	1105
45°	1713	1614	1509	1423	1355	1296	1248	1209	1169	1138	1108
47.5°	1689	1606	1516	1434	1363	1302	1253	1220	1189	1168	1127
50°	1684	1602	1519	1443	1371	1309	1266	1249	1240	1227	1164
52.5°	1670	1601	1541	1499	1453	1424	1379	1395	1385	1339	1225
55°	1817	1837	1893	1973	2047	2064	2059	2040	1939	1668	1372
57.5°	2498	2611	2717	2764	2758	2705	2667	2590	2444	2114	1662
60°	3444	3462	3406	3323	3183	3066	2941	2797	2585	2262	1840
62.5°	4315	4073	3824	3590	3377	3191	3017	2816	2540	2203	1817
65°	4930	4418	4025	3689	3388	3128	2911	2650	2339	2035	1684
67.5°	5247	4462	3859	3391	2964	2604	2315	2061	1830	1697	1474
70°	4893	3787	2947	2418	1907	1529	1208	1014	947	1073	1116
72.5°	3646	2465	1753	1356	1039	828	635	499	406	426	553
75°	1724	1064	752	572	455	377	308	282	236	196	184
77.5°	671	489	404	296	210	169	144	139	142	138	136
80°	511	346	217	159	137	121	107	103	105	110	115
82.5°	285	178	132	115	103	88	80	74	75	81	92
85°	110	86	79	76	71	57	49	50	57	68	68
87.5°	12	12	16	12	12	12	11	13	14	18	21
90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: P152550

CATALOG NUMBER: AVM-E03-LED-E-U-SL4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1891	1891	1891	1891	1891	1891	1891	1891	1891	1891	1891
2.5°	1874	1874	1874	1872	1873	1869	1869	1866	1871	1868	1867
5°	1845	1844	1840	1840	1840	1840	1843	1835	1841	1841	1838
7.5°	1796	1796	1785	1791	1789	1792	1796	1792	1798	1802	1799
10°	1728	1728	1719	1726	1723	1730	1737	1733	1737	1743	1745
12.5°	1653	1649	1641	1644	1644	1648	1651	1656	1661	1669	1673
15°	1566	1560	1550	1550	1544	1546	1552	1554	1564	1575	1588
17.5°	1477	1462	1451	1438	1428	1436	1443	1448	1456	1473	1482
20°	1393	1363	1342	1325	1314	1319	1328	1334	1341	1345	1348
22.5°	1310	1276	1247	1226	1208	1213	1209	1206	1211	1198	1197
25°	1238	1198	1159	1134	1112	1105	1084	1079	1065	1054	1046
27.5°	1186	1134	1091	1062	1027	1001	974	947	932	914	905
30°	1145	1090	1039	990	944	904	868	833	809	783	766
32.5°	1107	1056	994	927	865	820	773	733	695	661	636
35°	1081	1024	945	863	793	740	690	633	587	543	516
37.5°	1067	997	900	809	731	671	609	543	487	446	405
40°	1056	970	860	761	679	607	535	457	395	352	320
42.5°	1044	940	825	723	632	548	461	378	319	289	275
45°	1031	914	792	687	586	484	384	307	272	262	262
47.5°	1028	897	768	652	534	410	313	265	255	257	261
50°	1040	892	747	611	465	332	265	249	251	257	263
52.5°	1069	896	725	554	383	274	245	244	250	259	265
55°	1118	896	683	469	306	246	238	242	250	258	263
57.5°	1223	887	609	375	256	236	236	241	248	256	260
60°	1348	875	505	290	231	228	235	241	247	254	258
62.5°	1356	844	400	240	218	223	234	242	244	249	254
65°	1246	736	318	215	212	220	231	237	238	240	245
67.5°	1091	600	257	203	206	215	221	226	229	234	235
70°	896	482	220	191	194	204	209	214	220	226	223
72.5°	635	375	193	178	182	191	197	201	206	212	208
75°	270	262	167	161	167	173	179	185	190	193	193
77.5°	138	154	144	144	148	154	159	165	168	171	175
80°	117	119	121	125	129	135	140	145	146	147	149
82.5°	97	101	103	109	112	114	117	117	119	119	116
85°	70	75	78	79	78	79	80	82	87	87	83
87.5°	20	19	24	25	27	31	35	42	44	46	46
90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P152550

CATALOG NUMBER: AVM-E03-LED-E-U-SL4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1891	1891	1891	1891
2.5°	1866	1868	1864	1865
5°	1838	1842	1837	1843
7.5°	1802	1808	1807	1806
10°	1750	1758	1758	1761
12.5°	1684	1689	1693	1695
15°	1595	1604	1609	1609
17.5°	1488	1494	1497	1493
20°	1352	1350	1351	1341
22.5°	1195	1198	1189	1191
25°	1041	1036	1040	1034
27.5°	892	893	882	887
30°	750	745	731	738
32.5°	613	600	585	576
35°	484	464	457	454
37.5°	380	358	351	343
40°	302	294	291	293
42.5°	271	271	273	274
45°	263	266	269	270
47.5°	264	267	271	272
50°	266	269	272	273
52.5°	267	267	269	270
55°	265	264	265	266
57.5°	261	259	260	263
60°	259	256	258	260
62.5°	254	253	255	256
65°	243	244	247	247
67.5°	233	234	235	236
70°	221	222	224	225
72.5°	207	211	214	218
75°	196	200	206	210
77.5°	177	180	187	192
80°	150	149	150	153
82.5°	115	115	114	113
85°	81	80	77	77
87.5°	44	43	42	40
90°	0	0	0	0

(END OF REPORT)