

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148576

Luminaire Tested: **AVM-F04-LED-E-U-5XQ-7050**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P148576  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: AVM-F04-LED-E-U-5XQ-7050  
Description: VISION SITE MEDIUM LED LUMINAIRE  
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE  
Light Source: (28) 5000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10776.1 lumens  
Efficiency: N/A  
Efficacy: 105.4 lumens/watt  
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')  
IES Classification: Type V - Short - Non-Cutoff  
BUG Rating: B4 - U0 - G3


Input Watts (W): 102.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P148576  
 CATALOG NUMBER: AVM-F04-LED-E-U-5XQ-7050

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 2.6 fc  
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148576  
CATALOG NUMBER: AVM-F04-LED-E-U-5XQ-7050

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P148576

CATALOG NUMBER: AVM-F04-LED-E-U-5XQ-7050

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	5388.0	0.0	5388.0
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	5388.0	0.0	5388.0
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	10776.1	0.0	10776.1
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	97.3	0.9
10°-20°	287.8	2.7
20°-30°	482.0	4.5
30°-40°	734.8	6.8
40°-50°	1173.3	10.9
50°-60°	1804.1	16.7
60°-70°	2626.8	24.4
70°-80°	2959.0	27.5
80°-90°	610.9	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10776.1	100.0
0°-180°	10776.1	100.0



REPORT NUMBER: P148576


CATALOG NUMBER: AVM-F04-LED-E-U-5XQ-7050

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	433.6	4.0			
FM	(30°-60°)	1856.1	17.2			
FH	(60°-80°)	2792.9	25.9			G2/5000
FVH	(80°-90°)	305.4	2.8			G3/500
BL	(0°-30°)	433.6	4.0	B1/500		
BM	(30°-60°)	1856.1	17.2	B2/2500		
BH	(60°-80°)	2792.9	25.9	B4/5000		G2/5000
BVH	(80°-90°)	305.4	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B4-U0-G3**

Type V Short





REPORT NUMBER: P148576

CATALOG NUMBER: AVM-F04-LED-E-U-5XQ-7050

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1021.0	1021.0	1021.0	1021.0	1021.0	1021.0	1021.0	1021.0	1021.0	1021.0	1021.0
2.5°	1022.7	1023.2	1023.0	1022.4	1022.7	1022.4	1021.8	1021.6	1019.6	1020.8	1022.4
5°	1022.7	1022.2	1021.9	1021.6	1021.6	1022.4	1021.6	1020.7	1020.4	1021.0	1020.2
7.5°	1022.1	1021.0	1020.5	1020.2	1020.4	1020.7	1019.9	1018.8	1019.6	1018.7	1017.6
10°	1020.4	1019.6	1019.9	1018.8	1019.0	1018.8	1017.6	1016.8	1017.3	1016.5	1015.1
12.5°	1021.0	1019.6	1019.3	1018.8	1018.5	1018.2	1016.8	1015.4	1015.6	1015.1	1013.7
15°	1021.0	1020.2	1019.9	1018.8	1018.5	1017.9	1016.2	1015.6	1015.6	1014.8	1013.1
17.5°	1021.6	1021.0	1021.0	1019.6	1019.0	1018.8	1016.8	1015.9	1016.8	1015.1	1014.0
20°	1023.3	1022.7	1023.0	1022.1	1021.0	1021.0	1019.6	1019.0	1019.4	1019.0	1015.9
22.5°	1026.6	1026.6	1027.2	1026.9	1026.6	1027.0	1025.8	1025.8	1026.1	1026.1	1023.6
25°	1036.2	1036.0	1036.6	1036.6	1036.8	1038.8	1038.0	1037.6	1039.1	1039.1	1036.5
27.5°	1054.3	1053.8	1054.3	1054.9	1056.3	1058.8	1058.3	1059.2	1061.4	1060.8	1058.5
30°	1075.2	1074.7	1076.1	1077.8	1078.9	1082.8	1081.1	1085.4	1087.4	1089.1	1087.4
32.5°	1105.8	1105.7	1108.2	1109.4	1111.9	1115.9	1116.4	1119.8	1122.4	1125.2	1123.2
35°	1146.4	1145.8	1147.8	1149.8	1152.9	1156.5	1158.0	1162.4	1166.4	1168.4	1164.8
37.5°	1208.5	1205.4	1209.1	1210.2	1212.8	1213.6	1217.5	1223.2	1227.4	1226.9	1224.3
40°	1292.6	1292.1	1290.6	1289.0	1292.9	1294.3	1294.3	1302.0	1308.7	1307.6	1307.3
42.5°	1390.9	1388.4	1386.6	1386.7	1388.9	1389.5	1398.2	1403.9	1408.7	1409.8	1408.7
45°	1496.5	1494.0	1494.5	1493.4	1494.2	1497.9	1503.0	1513.4	1522.5	1522.8	1517.9
47.5°	1610.0	1602.1	1608.3	1599.6	1604.9	1607.8	1620.4	1635.7	1651.5	1654.4	1650.1
50°	1725.2	1724.4	1723.8	1722.1	1724.6	1730.8	1746.4	1770.4	1785.6	1795.8	1789.0
52.5°	1851.1	1846.9	1844.9	1842.1	1844.6	1856.8	1878.5	1899.4	1926.8	1938.4	1929.1
55°	1973.7	1972.3	1965.0	1964.6	1970.0	1989.0	2012.7	2038.4	2068.0	2081.0	2077.6
57.5°	2099.6	2091.4	2089.2	2085.8	2096.5	2114.3	2143.4	2189.7	2220.5	2235.2	2226.7
60°	2222.7	2216.5	2211.7	2210.6	2217.9	2242.8	2284.6	2340.2	2378.3	2397.5	2384.0
62.5°	2354.8	2350.9	2345.3	2338.8	2354.3	2386.2	2438.2	2499.7	2555.9	2579.6	2559.0
65°	2519.2	2511.0	2504.8	2496.6	2509.3	2549.4	2614.6	2701.3	2776.7	2804.4	2789.7
67.5°	2692.6	2685.0	2685.5	2680.4	2703.0	2758.6	2842.8	2960.5	3061.6	3108.8	3081.1
70°	2843.9	2848.1	2849.3	2869.9	2908.9	2993.6	3133.6	3318.0	3471.3	3543.3	3513.7
71°	2799.3	2808.6	2823.0	2844.5	2911.7	3011.9	3203.1	3426.4	3609.4	3731.4	3690.4
72.5°	2672.8	2678.4	2685.8	2718.5	2794.5	2927.2	3124.0	3379.2	3614.5	3772.3	3724.9
75°	2489.9	2495.2	2497.7	2520.6	2589.8	2705.6	2885.7	3112.2	3319.7	3454.1	3440.8
77.5°	2213.7	2214.5	2234.3	2269.6	2347.2	2479.7	2669.4	2904.3	3099.4	3203.9	3137.6
80°	1589.7	1579.0	1599.3	1644.7	1740.7	1892.6	2086.9	2355.2	2571.7	2669.4	2566.6
82.5°	604.8	637.6	689.2	764.4	796.8	965.7	1146.9	1304.5	1486.9	1690.8	1639.7
85°	65.0	73.2	91.8	113.8	143.7	198.8	274.7	375.0	462.2	543.3	482.3
87.5°	24.3	24.8	27.7	31.9	32.5	33.9	36.1	42.1	39.2	33.9	27.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148576

CATALOG NUMBER: AVM-F04-LED-E-U-5XQ-7050

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1021.0	1021.0	1021.0	1021.0	1021.0	1021.0	1021.0	1021.0
2.5°	1021.0	1021.3	1021.0	1021.3	1021.3	1020.2	1020.4	1019.8
5°	1020.7	1019.9	1020.2	1020.4	1020.2	1020.8	1019.9	1020.4
7.5°	1019.3	1017.6	1018.2	1018.2	1017.6	1018.4	1017.9	1017.6
10°	1016.5	1014.2	1015.4	1014.8	1014.5	1014.8	1014.8	1014.8
12.5°	1013.9	1012.6	1012.8	1012.5	1012.2	1013.1	1012.8	1013.1
15°	1013.4	1011.1	1010.8	1010.3	1010.6	1011.2	1011.1	1012.0
17.5°	1012.8	1010.0	1009.7	1009.1	1009.4	1010.6	1010.8	1010.3
20°	1014.5	1012.2	1011.7	1011.1	1010.8	1012.2	1012.0	1012.0
22.5°	1022.4	1019.6	1019.3	1017.1	1016.2	1017.0	1016.5	1016.5
25°	1035.1	1031.8	1030.6	1027.5	1025.2	1025.2	1024.4	1023.8
27.5°	1058.0	1052.9	1051.8	1049.2	1046.1	1046.7	1045.0	1044.7
30°	1084.6	1080.0	1076.0	1072.4	1068.7	1067.3	1065.4	1065.1
32.5°	1119.2	1114.2	1109.4	1104.9	1099.8	1097.8	1094.4	1092.8
35°	1161.9	1155.2	1149.5	1146.4	1141.3	1138.7	1136.5	1139.1
37.5°	1221.5	1213.3	1210.5	1206.8	1203.4	1199.4	1200.3	1199.4
40°	1303.9	1296.6	1293.8	1287.3	1286.4	1281.9	1284.7	1281.9
42.5°	1405.9	1392.3	1390.3	1385.2	1383.6	1381.0	1382.2	1380.2
45°	1516.8	1504.7	1502.4	1494.2	1494.5	1488.6	1490.8	1490.8
47.5°	1641.6	1628.9	1618.5	1612.6	1610.3	1606.6	1608.6	1608.4
50°	1770.4	1753.2	1741.6	1730.0	1724.9	1726.4	1722.4	1729.2
52.5°	1908.8	1883.0	1866.6	1855.6	1846.1	1848.0	1848.6	1850.6
55°	2051.9	2019.2	1995.4	1981.0	1972.3	1972.8	1975.4	1977.6
57.5°	2195.9	2155.0	2122.8	2101.3	2095.7	2098.2	2098.2	2098.0
60°	2345.3	2296.1	2254.6	2230.4	2225.3	2223.8	2234.9	2231.2
62.5°	2505.7	2446.6	2403.7	2372.7	2365.3	2370.4	2380.3	2378.0
65°	2718.2	2636.6	2581.3	2550.6	2538.1	2543.2	2556.5	2555.9
67.5°	2992.4	2878.4	2805.2	2765.7	2756.7	2762.9	2770.2	2777.3
70°	3402.4	3239.5	3135.0	3049.4	3012.7	3005.7	3013.1	3013.3
71°	3546.7	3359.5	3193.2	3088.7	3028.6	3003.2	3005.2	2992.4
72.5°	3540.8	3310.1	3115.6	3006.3	2922.7	2902.3	2892.5	2877.2
75°	3302.2	3094.4	2925.5	2806.4	2725.9	2701.9	2684.4	2683.6
77.5°	2994.7	2841.4	2655.3	2529.1	2431.1	2391.3	2373.5	2373.0
80°	2407.4	2177.8	2041.7	1965.8	1847.5	1813.3	1777.2	1763.6
82.5°	1455.8	1137.6	925.0	822.0	764.9	629.9	565.3	534.8
85°	339.1	240.8	166.0	109.0	78.5	62.4	48.0	42.4
87.5°	22.9	18.1	16.1	13.0	9.9	9.6	5.9	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)